

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P387207

Luminaire Tested: **TT-D3-750-U-5WQ-PM**

Issue Date: 2/18/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P387207  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1908-473-14)  
Test Lab: INNOVATIONS CENTER  
Issue Date: 2/18/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: TT-D3-750-U-5WQ-PM  
Description: TOPTIER LED SITE LUMINAIRE  
5000K, 70 CRI LEDS AND WIDE DISTRIBUTION  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6359 lumens  
Efficiency: N/A  
Efficacy: 134.7 lumens/watt  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2  
  
Input Watts (W): 47.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P387207  
 CATALOG NUMBER: TT-D3-750-U-5WQ-PM

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.8 fc  
 Type V - Short - N/A

REPORT NUMBER: P387207  
CATALOG NUMBER: TT-D3-750-U-5WQ-PM

### Luminous Intensity Polar Plot



REPORT NUMBER: P387207

CATALOG NUMBER: TT-D3-750-U-5WQ-PM


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	3179.5	0.0	3179.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	3179.5	0.0	3179.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	6359.0	0.0	6359.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	0.7
10°-20°	146.8	2.3
20°-30°	301.4	4.7
30°-40°	535.5	8.4
40°-50°	902.6	14.2
50°-60°	1331.5	20.9
60°-70°	1562.7	24.6
70°-80°	1217.5	19.1
80°-90°	318.3	5.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6359.0	100.0
0°-180°	6359.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P387207


CATALOG NUMBER: TT-D3-750-U-5WQ-PM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	245.4	3.9			
FM (30°-60°)	1384.8	21.8			
FH (60°-80°)	1390.1	21.9			G1/1800
FVH (80°-90°)	159.2	2.5			G2/225
BL (0°-30°)	245.4	3.9	B1/500		
BM (30°-60°)	1384.8	21.8	B2/2500		
BH (60°-80°)	1390.1	21.9	B3/2500		G1/1800
BVH (80°-90°)	159.2	2.5			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P387207  
 CATALOG NUMBER: TT-D3-750-U-5WQ-PM

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	428.0	428.0	428.0	428.0	428.0	428.0	428.0	428.0	428.0	428.0	428.0
2.5°	435.0	435.0	435.0	434.0	434.0	434.0	434.0	435.0	435.0	435.0	435.0
5°	445.0	445.0	443.0	441.0	439.0	439.0	440.0	441.0	442.0	444.0	444.0
7.5°	451.0	451.0	450.0	448.0	445.0	445.0	446.0	448.0	449.0	449.0	448.0
10°	459.0	460.0	463.0	464.0	462.0	462.0	463.0	464.0	462.0	459.0	459.0
12.5°	478.0	479.0	483.0	486.0	486.0	484.0	485.0	487.0	482.0	477.0	478.0
15°	505.0	505.0	506.0	509.0	507.0	505.0	507.0	508.0	505.0	504.0	506.0
17.5°	541.0	541.0	535.0	540.0	541.0	540.0	542.0	537.0	534.0	538.0	540.0
20°	580.0	576.0	573.0	577.0	585.0	582.0	586.0	575.0	572.0	574.0	575.0
22.5°	605.0	608.0	610.0	612.0	623.0	619.0	623.0	611.0	609.0	605.0	602.0
25°	635.0	638.0	650.0	644.0	651.0	645.0	650.0	643.0	647.0	635.0	635.0
27.5°	669.0	675.0	682.0	679.0	688.0	685.0	688.0	678.0	679.0	674.0	672.0
30°	715.0	715.0	713.0	719.0	735.0	733.0	734.0	721.0	712.0	713.0	717.0
32.5°	761.0	755.0	758.0	776.0	786.0	782.0	784.0	778.0	758.0	754.0	757.0
35°	804.0	813.0	820.0	835.0	849.0	847.0	846.0	836.0	823.0	807.0	802.0
37.5°	871.0	881.0	900.0	927.0	952.0	957.0	944.0	931.0	901.0	878.0	866.0
40°	959.0	960.0	982.0	1034.0	1057.0	1061.0	1054.0	1032.0	986.0	960.0	959.0
42.5°	1036.0	1029.0	1065.0	1108.9	1129.9	1131.9	1126.9	1108.9	1065.0	1028.0	1035.0
45°	1096.0	1096.0	1138.9	1173.9	1207.9	1215.9	1206.9	1168.9	1139.9	1096.9	1094.0
47.5°	1150.9	1165.9	1201.9	1244.9	1292.9	1303.9	1292.9	1247.9	1198.9	1166.9	1149.9
50°	1216.9	1234.9	1260.9	1327.9	1381.9	1396.9	1380.9	1331.9	1260.9	1233.9	1223.9
52.5°	1293.9	1308.9	1349.9	1433.9	1473.9	1495.9	1482.9	1435.9	1351.9	1310.9	1302.9
55°	1385.9	1371.9	1435.9	1516.9	1590.9	1619.9	1593.9	1518.9	1445.9	1371.9	1385.9
57.5°	1432.9	1416.9	1506.9	1583.9	1686.9	1724.9	1692.9	1589.9	1506.9	1421.9	1431.9
60°	1436.9	1443.9	1511.9	1637.9	1708.9	1724.9	1714.9	1646.9	1514.9	1449.9	1430.9
62.5°	1424.9	1467.9	1525.9	1655.9	1719.9	1758.9	1724.9	1657.9	1531.9	1474.9	1425.9
65°	1408.9	1451.9	1537.9	1629.9	1738.9	1777.9	1745.9	1634.9	1541.9	1451.9	1414.9
67.5°	1380.9	1365.9	1471.9	1594.9	1689.9	1712.9	1692.9	1596.9	1470.9	1363.9	1383.9
70°	1291.9	1278.9	1369.9	1504.9	1595.9	1627.9	1603.9	1506.9	1371.9	1281.9	1293.9
72.5°	1159.9	1163.9	1251.9	1380.9	1478.9	1498.9	1485.9	1379.9	1256.9	1168.9	1152.9
75°	1006.0	1016.0	1099.9	1216.9	1305.9	1317.9	1304.9	1221.9	1098.9	1022.0	1001.0
77.5°	827.0	842.0	910.0	1027.0	1086.0	1112.9	1092.0	1030.0	915.0	846.0	825.0
80°	641.0	646.0	694.0	788.0	866.0	884.0	864.0	791.0	700.0	648.0	633.0
82.5°	420.0	428.0	471.0	543.0	594.0	589.0	594.0	537.0	476.0	426.0	401.0
85°	187.0	203.0	232.0	266.0	299.0	308.0	299.0	270.0	232.0	199.0	195.0
87.5°	13.0	15.0	18.0	19.0	21.0	16.0	16.0	16.0	14.0	16.0	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)