Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P821134

Luminaire Tested: **TT-D2-830-24VDC-DL**

Issue Date: 5/19/2020

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P821134
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1908-473-26)
Test Lab:	INNOVATION CENTER
Issue Date:	5/19/2020
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	TT-D2-830-24VDC-DL
Description:	TOPTIER LED PARKING GARAGE LUMINAIRE
	3000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION
Light Source:	-
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3985 lumens
Efficiency:	N/A
Efficacy:	104.9 lumens/watt
Luminous Opening:	Circular (Dia: 1.12' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B2 - U0 - G3


Input Watts (W):	38
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	25 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821134
CATALOG NUMBER: TT-D2-830-24VDC-DL

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1.4 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821134
CATALOG NUMBER: TT-D2-830-24VDC-DL

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P821134
CATALOG NUMBER: TT-D2-830-24VDC-DL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1161.2	0.0	1161.2
	% Fixture	29.1	0.0	29.1
Street Side	Lumens	2823.8	0.0	2823.8
	% Fixture	70.9	0.0	70.9
Total	Lumens	3985.0	0.0	3985.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.9	0.2
10°-20°	33.1	0.8
20°-30°	78.2	2.0
30°-40°	176.9	4.4
40°-50°	394.4	9.9
50°-60°	793.0	19.9
60°-70°	1164.6	29.2
70°-80°	1024.1	25.7
80°-90°	311.8	7.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3985.0	100.0
0°-180°	3985.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P821134
CATALOG NUMBER: TT-D2-830-24VDC-DL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	69.6	1.7			
FM	(30°-60°)	933.2	23.4			
FH	(60°-80°)	1589.9	39.9			G1/1800
FVH	(80°-90°)	231.0	5.8			G3/500
BL	(0°-30°)	50.5	1.3	B0/110		
BM	(30°-60°)	431.1	10.8	B1/1000		
BH	(60°-80°)	598.8	15.0	B2/1000		G2/1000
BVH	(80°-90°)	80.8	2.0			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821134
CATALOG NUMBER: TT-D2-830-24VDC-DL

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	42.5°	45°	55°	65°	75°	85°
0°	86.4	86.4	86.4	86.4	86.4	86.4	*86.4*	86.4	86.4	86.4	86.4
2.5°	90.2	89.4	89.4	89.4	88.7	88.7	*88.7*	88.7	87.9	87.9	87.9
5°	95.4	94.6	95.4	93.9	93.1	93.1	*92.4*	92.4	91.7	90.9	90.2
7.5°	102.8	102.1	102.1	100.6	99.9	99.1	*99.1*	97.6	96.9	95.4	93.9
10°	111.0	111.0	110.3	109.5	108.0	106.6	*106.6*	104.3	103.6	101.3	99.1
12.5°	120.7	120.7	120.7	119.2	117.7	117.0	*115.5*	114.0	111.8	108.0	105.8
15°	132.6	132.6	132.6	131.1	129.7	128.2	*127.4*	124.4	120.7	117.0	112.5
17.5°	147.5	146.1	146.1	144.6	143.1	142.3	*140.8*	137.9	132.6	128.2	122.2
20°	163.9	163.2	162.4	162.4	161.0	159.5	*158.7*	154.2	148.3	140.1	132.6
22.5°	182.6	181.8	181.8	183.3	182.6	180.3	*180.3*	173.6	165.4	155.7	144.6
25°	205.7	204.9	206.4	209.4	209.4	207.9	*205.7*	199.0	187.0	173.6	160.2
27.5°	231.0	230.3	233.2	238.5	239.9	237.7	*236.2*	228.8	215.4	197.5	178.1
30°	261.6	262.3	270.5	276.5	280.2	278.7	*277.9*	269.7	248.1	227.3	201.9
32.5°	298.8	296.6	307.0	316.7	323.4	327.1	*324.9*	315.2	296.6	263.8	231.7
35°	338.3	339.0	351.7	365.9	381.5	383.0	*387.5*	377.8	352.5	313.7	269.0
37.5°	389.7	383.8	400.1	427.0	445.6	462.0	*459.0*	453.1	423.2	371.8	310.7
40°	435.9	434.4	457.5	494.8	529.1	552.9	*555.9*	548.4	508.9	435.9	355.4
42.5°	488.8	493.3	525.3	576.8	628.9	663.2	*655.0*	651.3	605.1	511.9	416.5
45°	542.5	557.4	598.4	672.9	734.0	783.2	*797.3*	784.7	728.0	631.9	494.0
47.5°	607.3	627.4	678.1	778.7	878.5	935.9	*938.9*	976.9	891.2	747.4	574.5
50°	693.0	701.9	772.7	895.7	1032.8	1113.3	*1136.4*	1137.1	1051.4	863.6	665.4
52.5°	777.2	783.9	877.1	1035.8	1222.1	1313.7	*1318.9*	1348.0	1231.0	1051.4	795.8
55°	878.5	875.6	1003.7	1194.5	1414.3	1547.7	*1586.4*	1625.9	1476.9	1199.7	870.3
57.5°	976.9	972.4	1126.7	1377.1	1677.4	1810.0	*1842.0*	1813.7	1592.4	1261.6	906.9
60°	1067.8	1083.5	1271.2	1579.0	1880.8	2007.5	*2029.1*	1952.3	1666.9	1309.2	930.0
62.5°	1162.4	1193.7	1421.0	1747.4	2036.5	2127.4	*2128.9*	2038.8	1791.4	1401.6	1005.2
65°	1251.1	1301.0	1537.3	1891.2	2145.3	2236.2	*2246.7*	2165.4	1913.6	1482.1	1017.9
67.5°	*1329.4*	*1395.7*	*1617.7*	*1968.7*	*2219.1*	*2277.9*	*2283.2*	*2166.2*	*1884.5*	*1449.3*	*982.9*
70°	1392.7	1446.4	1667.7	1970.2	2167.7	2184.1	*2180.3*	2055.9	1804.0	1384.5	924.0
72.5°	1417.3	1461.3	1643.8	1877.8	2016.4	2012.7	*2009.7*	1894.9	1671.4	1276.5	839.0
75°	1382.3	1394.9	1513.4	1680.3	1768.3	1789.1	*1792.1*	1688.5	1466.5	1116.2	719.8
77.5°	1237.7	1231.0	1321.9	1432.2	1498.5	1513.4	*1510.4*	1424.0	1229.5	927.7	603.6
80°	981.4	995.5	1052.2	1125.2	1191.5	1207.9	*1197.5*	1131.9	956.8	723.5	463.5
82.5°	686.3	703.4	751.1	806.3	856.2	856.2	*865.9*	802.5	678.1	519.4	324.1
85°	370.3	360.7	412.8	475.4	511.2	517.9	*521.6*	500.7	419.5	313.7	192.3
87.5°	61.1	65.6	81.2	124.4	141.6	163.9	*174.4*	136.4	82.7	52.9	38.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821134
CATALOG NUMBER: TT-D2-830-24VDC-DL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.4
2.5°	87.9	87.2	86.4	85.7	85.7	84.9	84.9	84.9	85.7	85.7	85.7
5°	90.2	89.4	88.7	87.9	86.4	86.4	86.4	86.4	86.4	86.4	86.4
7.5°	93.9	92.4	91.7	90.2	88.7	88.7	87.9	87.9	87.9	88.7	87.9
10°	98.4	96.9	95.4	93.1	92.4	91.7	90.9	90.9	91.7	91.7	90.9
12.5°	103.6	102.8	99.9	97.6	96.1	95.4	94.6	95.4	94.6	95.4	95.4
15°	111.0	108.8	105.1	102.8	100.6	99.9	99.1	99.9	99.9	100.6	99.9
17.5°	119.2	116.2	112.5	108.8	105.8	105.1	105.1	105.1	105.8	106.6	105.8
20°	128.9	125.2	120.0	115.5	112.5	111.8	111.8	112.5	113.3	114.0	114.0
22.5°	138.6	135.6	128.2	122.2	120.7	120.0	119.2	120.7	122.2	123.0	123.7
25°	153.5	147.5	138.6	131.9	128.9	128.9	129.7	131.1	131.9	133.4	132.6
27.5°	169.2	162.4	151.3	142.3	140.1	139.3	140.8	142.3	145.3	145.3	144.6
30°	190.8	179.6	165.4	157.2	151.3	152.0	154.2	156.5	159.5	161.0	161.0
32.5°	215.4	203.4	184.1	171.4	168.4	169.2	169.9	173.6	176.6	179.6	177.3
35°	247.4	232.5	208.6	194.5	187.0	186.3	189.3	193.7	196.7	198.2	198.2
37.5°	282.4	263.0	233.2	221.3	212.4	211.6	212.4	216.1	219.8	221.3	224.3
40°	324.9	301.0	266.0	246.6	239.9	238.5	241.4	246.6	246.6	248.9	249.6
42.5°	377.0	346.5	307.8	282.4	274.2	274.2	273.5	277.9	277.9	277.9	276.5
45°	443.4	409.1	358.4	332.3	318.2	310.7	313.0	310.0	309.2	311.5	304.8
47.5°	507.5	464.2	404.6	376.3	362.1	357.7	349.5	347.2	343.5	343.5	333.8
50°	582.0	528.3	470.9	430.7	417.3	404.6	397.9	387.5	376.3	374.1	370.3
52.5°	706.4	639.3	549.2	506.0	471.7	459.0	443.4	430.0	416.5	406.1	412.1
55°	757.1	688.5	602.8	561.1	537.3	525.3	496.3	478.4	458.3	443.4	451.6
57.5°	782.4	707.9	628.2	596.9	590.2	579.0	557.4	526.8	503.7	485.1	486.6
60°	796.6	718.3	641.6	613.3	609.5	617.0	605.8	584.9	549.2	530.6	528.3
62.5°	851.0	769.0	679.6	639.3	631.1	636.4	639.3	626.7	596.9	572.3	565.6
65°	862.1	775.0	687.0	661.0	661.7	663.2	665.4	652.0	637.1	606.6	600.6
67.5°	*828.6*	*742.9*	*664.7*	*643.1*	*644.6*	*661.7*	*675.1*	*674.4*	*658.0*	*631.9*	*629.7*
70°	777.9	694.5	622.2	602.8	606.6	622.2	651.3	666.2	663.2	646.1	649.8
72.5°	699.0	624.4	561.1	546.2	555.1	570.0	597.6	624.4	640.1	643.8	652.0
75°	606.6	546.9	487.3	478.4	485.1	502.2	527.6	558.9	593.1	611.8	617.0
77.5°	500.7	446.3	402.4	396.4	406.1	421.8	447.1	471.7	510.4	543.2	550.7
80°	392.0	345.0	313.7	308.5	314.5	327.9	347.2	367.4	404.6	430.0	433.7
82.5°	272.0	243.7	223.5	220.6	224.3	229.5	245.2	263.8	284.7	304.8	307.0
85°	158.0	140.1	134.9	130.4	138.6	138.6	142.3	152.8	163.2	164.7	169.2
87.5°	29.1	27.6	28.3	20.9	26.1	18.6	18.6	23.8	17.9	20.9	17.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-7

Test Date: 09/27/2024

Luminaire Tested: MEM2-HTN-VA-30-830-U-WQ

Data in this report applies to families of products including MEM2-HTN-VA-30-830-U-WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-176-7
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	09/27/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**MEM2-HTN-VA-30-830-U-WQ**
Description:	EPIC MODERN VISUAL COMFORT 30W WAVESTREAM WIDE

Spectral Parameters

CCT (K):	2984	CRI (Ra):	81.8		
CIE u':	0.2500	R1:	79.4	R9:	-1.1
CIE v':	0.5264	R2:	89.9	R10:	78.4
Duv:	0.0033	R3:	96.6	R11:	80.8
CIE x:	0.4431	R4:	80.6	R12:	72.8
CIE y:	0.4147	R5:	80.1	R13:	81.7
CIE z:	0.1422	R6:	88.9	R14:	98.5
Peak Wavelength (nm):	601	R7:	82.6	R15:	70.2
Dominant Wavelength (nm):	581	R8:	56.0		
Purity:	57.4798				

Rf:	85.8
Rg:	94.1



Test Conditions


Stabilization Time:	29M
Operation Time:	1H 29M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-176-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-176-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2984K
CIE x = 0.4431
CIE y = 0.4147
Duv = 0.0033

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			

REPORT NUMBER: SP1-2407-176-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.32**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			

REPORT NUMBER: SP1-2407-176-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.51**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			


REPORT NUMBER: SP1-2407-176-7

TM-30-18


Summary


R_f = 85.8
R_g = 94.1
CIE R_a = 81.8
R_9 = -1.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-176-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 86	CES51 = 95	CES76 = 84
CES02 = 63	CES27 = 95	CES52 = 94	CES77 = 86
CES03 = 31	CES28 = 95	CES53 = 90	CES78 = 83
CES04 = 70	CES29 = 89	CES54 = 91	CES79 = 90
CES05 = 50	CES30 = 95	CES55 = 91	CES80 = 90
CES06 = 51	CES31 = 91	CES56 = 87	CES81 = 70
CES07 = 42	CES32 = 85	CES57 = 86	CES82 = 96
CES08 = 41	CES33 = 93	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 92	CES84 = 92
CES10 = 76	CES35 = 97	CES60 = 94	CES85 = 77
CES11 = 59	CES36 = 90	CES61 = 90	CES86 = 66
CES12 = 65	CES37 = 97	CES62 = 94	CES87 = 84
CES13 = 43	CES38 = 97	CES63 = 88	CES88 = 86
CES14 = 74	CES39 = 98	CES64 = 84	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 80	CES90 = 88
CES16 = 47	CES41 = 97	CES66 = 83	CES91 = 81
CES17 = 50	CES42 = 99	CES67 = 82	CES92 = 64
CES18 = 56	CES43 = 93	CES68 = 84	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 89	CES94 = 60
CES20 = 67	CES45 = 94	CES70 = 82	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 81	CES96 = 83
CES22 = 79	CES47 = 93	CES72 = 93	CES97 = 89
CES23 = 92	CES48 = 83	CES73 = 77	CES98 = 84
CES24 = 91	CES49 = 92	CES74 = 92	CES99 = 75
CES25 = 72	CES50 = 95	CES75 = 83	





REPORT NUMBER: SP1-2407-176-7

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-176-7

TM-30-18

Measure Comparisons





(END OF REPORT)