Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P821155

Luminaire Tested: **TT-D3-830-24VDC-RW**

Issue Date: 10/15/2020

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P821155
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-981-1)
Test Lab:	INNOVATION CENTER
Issue Date:	10/15/2020
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	TT-D3-830-24VDC-RW
Description:	TOPTIER LED PARKING GARAGE LUMINAIRE
	3000K, 80 CRI LEDS AND RECTANGULAR DISTRIBUTION
Light Source:	-
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4526 lumens
Efficiency:	N/A
Efficacy:	98.4 lumens/watt
Luminous Opening:	Circular (Dia: 1.12' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	46
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	25 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821155
CATALOG NUMBER: TT-D3-830-24VDC-RW

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 1.4 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821155
CATALOG NUMBER: TT-D3-830-24VDC-RW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P821155
CATALOG NUMBER: TT-D3-830-24VDC-RW

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2263.0	0.0	2263.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2263.0	0.0	2263.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	4526.0	0.0	4526.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.6	0.2
10°-20°	32.3	0.7
20°-30°	74.6	1.6
30°-40°	168.6	3.7
40°-50°	410.8	9.1
50°-60°	923.7	20.4
60°-70°	1350.0	29.8
70°-80°	1176.3	26.0
80°-90°	381.0	8.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4526.0	100.0
0°-180°	4526.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P821155
CATALOG NUMBER: TT-D3-830-24VDC-RW

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	57.8	1.3			
FM	(30°-60°)	751.6	16.6			
FH	(60°-80°)	1263.2	27.9			G1/1800
FVH	(80°-90°)	190.5	4.2			G2/225
BL	(0°-30°)	57.8	1.3	B0/110		
BM	(30°-60°)	751.6	16.6	B1/1000		
BH	(60°-80°)	1263.2	27.9	B3/2500		G3/2500
BVH	(80°-90°)	190.5	4.2			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821155
CATALOG NUMBER: TT-D3-830-24VDC-RW

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	82.7	82.7	82.7	82.7	82.7	82.7	82.7	82.7	82.7	82.7	*82.7*
2.5°	83.8	83.8	84.8	84.8	84.8	84.8	84.8	84.8	84.8	84.8	*84.8*
5°	87.0	87.0	87.0	87.0	88.1	88.1	87.0	87.0	87.0	87.0	*87.0*
7.5°	92.4	91.3	92.4	92.4	92.4	91.3	91.3	91.3	90.2	90.2	*90.2*
10°	97.7	97.7	98.8	97.7	97.7	96.7	96.7	96.7	95.6	95.6	*95.6*
12.5°	105.2	105.2	105.2	105.2	104.2	104.2	103.1	102.0	100.9	100.9	*100.9*
15°	114.9	113.8	113.8	112.8	111.7	110.6	109.5	109.5	108.5	108.5	*108.5*
17.5°	124.6	124.6	123.5	122.4	120.3	119.2	119.2	118.1	117.1	117.1	*117.1*
20°	136.4	136.4	135.3	133.2	131.0	129.9	128.9	128.9	127.8	127.8	*127.8*
22.5°	150.3	149.3	147.1	145.0	142.8	141.8	140.7	139.6	139.6	139.6	*139.6*
25°	165.4	164.3	163.2	160.0	156.8	155.7	153.6	153.6	152.5	153.6	*153.6*
27.5°	183.6	182.6	180.4	177.2	172.9	170.8	169.7	169.7	170.8	170.8	*171.8*
30°	206.2	204.0	201.9	197.6	193.3	190.1	190.1	191.2	194.4	196.5	*196.5*
32.5°	233.0	232.0	228.7	224.4	216.9	214.8	216.9	223.4	227.7	230.9	*233.0*
35°	264.2	263.1	258.8	251.3	245.9	244.9	251.3	262.0	276.0	280.3	*282.4*
37.5°	298.5	299.6	294.2	285.7	280.3	282.4	295.3	315.7	329.7	339.4	*341.5*
40°	341.5	343.6	337.2	327.5	322.2	330.8	351.2	374.8	399.5	411.3	*414.5*
42.5°	392.0	395.2	386.6	376.9	373.7	387.7	416.7	455.3	499.4	513.3	*518.7*
45°	454.3	456.4	445.7	437.1	434.9	459.6	509.0	573.5	643.3	675.5	*680.9*
47.5°	528.4	527.3	517.6	506.9	509.0	544.5	618.6	705.6	779.7	829.1	*839.8*
50°	613.2	607.8	600.3	587.4	601.4	652.9	746.4	851.6	976.2	1020.2	*1039.5*
52.5°	698.0	688.4	681.9	673.3	698.0	764.6	895.6	1079.3	1267.2	1368.2	*1388.6*
55°	774.3	766.8	763.5	764.6	803.3	898.9	1070.7	1305.9	1487.4	1571.1	*1586.2*
57.5°	849.5	845.2	841.9	848.4	909.6	1034.2	1227.5	1447.6	1596.9	1659.2	*1669.9*
60°	920.3	924.6	922.5	941.8	1015.9	1141.6	1309.1	1526.0	1669.9	1726.8	*1738.7*
62.5°	998.7	1002.0	1002.0	1023.4	1083.6	1194.2	1364.9	1618.4	1800.9	1884.7	*1897.6*
65°	*1066.4*	*1068.5*	*1072.8*	*1073.9*	*1129.7*	*1240.4*	*1463.7*	*1703.2*	*1866.4*	*1963.1*	*1971.7*
67.5°	1116.9	1119.0	1113.6	1108.3	1151.2	1251.1	1456.2	1692.5	1837.5	1910.5	*1916.9*
70°	1157.7	1148.0	1133.0	1106.1	1120.1	1195.3	1393.9	1606.6	1752.6	1818.1	*1827.8*
72.5°	1163.0	1154.4	1107.2	1047.1	1029.9	1095.4	1284.4	1475.5	1601.2	1663.5	*1664.6*
75°	1130.8	1108.3	1029.9	939.7	907.4	969.7	1131.9	1305.9	1406.8	1459.4	*1464.8*
77.5°	1022.4	1000.9	902.1	799.0	762.5	816.2	953.6	1094.3	1191.0	1242.5	*1245.7*
80°	830.1	822.6	732.4	637.9	593.9	625.0	745.3	855.9	934.3	995.5	*1000.9*
82.5°	612.1	605.7	537.0	454.3	418.8	444.6	530.5	612.1	685.2	734.6	*737.8*
85°	382.3	369.4	326.5	268.5	244.9	262.0	318.9	373.7	439.2	477.9	*480.0*
87.5°	127.8	122.4	105.2	87.0	73.0	76.2	93.4	113.8	166.5	183.6	*194.4*
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-7

Test Date: 09/27/2024

Luminaire Tested: MEM2-HTN-VA-30-830-U-WQ

Data in this report applies to families of products including MEM2-HTN-VA-30-830-U-WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-176-7
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	09/27/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**MEM2-HTN-VA-30-830-U-WQ**
Description:	EPIC MODERN VISUAL COMFORT 30W WAVESTREAM WIDE

Spectral Parameters

CCT (K):	2984	CRI (Ra):	81.8		
CIE u':	0.2500	R1:	79.4	R9:	-1.1
CIE v':	0.5264	R2:	89.9	R10:	78.4
Duv:	0.0033	R3:	96.6	R11:	80.8
CIE x:	0.4431	R4:	80.6	R12:	72.8
CIE y:	0.4147	R5:	80.1	R13:	81.7
CIE z:	0.1422	R6:	88.9	R14:	98.5
Peak Wavelength (nm):	601	R7:	82.6	R15:	70.2
Dominant Wavelength (nm):	581	R8:	56.0		
Purity:	57.4798				

Rf:	85.8
Rg:	94.1



Test Conditions


Stabilization Time:	29M
Operation Time:	1H 29M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-176-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-176-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2984K
CIE x = 0.4431
CIE y = 0.4147
Duv = 0.0033

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			

REPORT NUMBER: SP1-2407-176-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.32**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			

REPORT NUMBER: SP1-2407-176-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.51**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			


REPORT NUMBER: SP1-2407-176-7

TM-30-18


Summary


R_f = 85.8
R_g = 94.1
CIE R_a = 81.8
R_9 = -1.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-176-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 86	CES51 = 95	CES76 = 84
CES02 = 63	CES27 = 95	CES52 = 94	CES77 = 86
CES03 = 31	CES28 = 95	CES53 = 90	CES78 = 83
CES04 = 70	CES29 = 89	CES54 = 91	CES79 = 90
CES05 = 50	CES30 = 95	CES55 = 91	CES80 = 90
CES06 = 51	CES31 = 91	CES56 = 87	CES81 = 70
CES07 = 42	CES32 = 85	CES57 = 86	CES82 = 96
CES08 = 41	CES33 = 93	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 92	CES84 = 92
CES10 = 76	CES35 = 97	CES60 = 94	CES85 = 77
CES11 = 59	CES36 = 90	CES61 = 90	CES86 = 66
CES12 = 65	CES37 = 97	CES62 = 94	CES87 = 84
CES13 = 43	CES38 = 97	CES63 = 88	CES88 = 86
CES14 = 74	CES39 = 98	CES64 = 84	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 80	CES90 = 88
CES16 = 47	CES41 = 97	CES66 = 83	CES91 = 81
CES17 = 50	CES42 = 99	CES67 = 82	CES92 = 64
CES18 = 56	CES43 = 93	CES68 = 84	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 89	CES94 = 60
CES20 = 67	CES45 = 94	CES70 = 82	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 81	CES96 = 83
CES22 = 79	CES47 = 93	CES72 = 93	CES97 = 89
CES23 = 92	CES48 = 83	CES73 = 77	CES98 = 84
CES24 = 91	CES49 = 92	CES74 = 92	CES99 = 75
CES25 = 72	CES50 = 95	CES75 = 83	





REPORT NUMBER: SP1-2407-176-7

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-176-7

TM-30-18

Measure Comparisons





(END OF REPORT)