

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P1445176

Luminaire Tested: TPTN-VA3-830-U-MQ-CG-GM

Issue Date: 05/21/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1445176  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 5/21/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: MCGRAW-EDISON  
Catalog Number: TPTN-VA3-830-U-MQ-CG-GM  
Description: TOPTIER NANO SPIDER MOUNT VISUAL COMFORT LED LUMINAIRE 60W 80CRI 3000K w/  
TYPE V MEDIUM DISTRIBUTION OPTIC AND GLASS  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4997.9 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B2 - U0 - G1

Input Watts (W): 60  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.98  
Total Harmonic Distortion (THDi): 5.3%  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1445176

CATALOG NUMBER: TPTN-VA3-830-U-MQ-CG-GM

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 8.8 fc

Type V - Short - N/A

REPORT NUMBER: P1445176

CATALOG NUMBER: TPTN-VA3-830-U-MQ-CG-GM

## Luminous Intensity Polar Plot



REPORT NUMBER: P1445176

CATALOG NUMBER: TPTN-VA3-830-U-MQ-CG-GM


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2499.0   | 0.0    | 2499.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2499.0   | 0.0    | 2499.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 4997.9   | 0.0    | 4997.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 79.6   | 1.6       |
| 10°-20°   | 231.5  | 4.6       |
| 20°-30°   | 431.1  | 8.6       |
| 30°-40°   | 631.4  | 12.6      |
| 40°-50°   | 817.3  | 16.4      |
| 50°-60°   | 1020.3 | 20.4      |
| 60°-70°   | 1011.9 | 20.2      |
| 70°-80°   | 638.7  | 12.8      |
| 80°-90°   | 136.0  | 2.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4997.9 | 100.0     |
| 0°-180°   | 4997.9 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P1445176


CATALOG NUMBER: TPTN-VA3-830-U-MQ-CG-GM

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 371.1  | 7.4       |                         |      |         |
| FM   | (30°-60°)   | 1234.5 | 24.7      |                         |      |         |
| FH   | (60°-80°)   | 825.3  | 16.5      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 68.0   | 1.4       |                         |      | G1/100  |
| BL   | (0°-30°)    | 371.1  | 7.4       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1234.5 | 24.7      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 825.3  | 16.5      | B2/1000                 |      | G1/1800 |
| BVH  | (80°-90°)   | 68.0   | 1.4       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G1**

Type V Short



REPORT NUMBER: P1445176

CATALOG NUMBER: TPTN-VA3-830-U-MQ-CG-GM

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°   | 75°   | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|-------|-------|--------|--------|
| 0°    | 880.4  | 880.4  | 880.4  | 880.4  | 880.4  | 880.4  | 880.4  | 880.4 | 880.4 | 880.4  | 880.4  |
| 2.5°  | 871.5  | 871.5  | 871.5  | 871.5  | 871.5  | 871.5  | 871.5  | 872.4 | 872.4 | 872.4  | 872.4  |
| 5°    | 851.8  | 850.9  | 850.9  | 850.9  | 853.6  | 855.3  | 859.8  | 862.5 | 865.2 | 866.1  | 866.1  |
| 7.5°  | 812.4  | 813.3  | 814.1  | 815.0  | 816.8  | 821.3  | 827.6  | 833.9 | 838.3 | 841.0  | 841.9  |
| 10°   | 781.0  | 781.0  | 781.9  | 781.0  | 783.7  | 789.1  | 797.1  | 807.9 | 815.9 | 820.4  | 820.4  |
| 12.5° | 773.8  | 773.8  | 776.5  | 779.2  | 782.8  | 788.2  | 797.1  | 806.1 | 814.1 | 817.7  | 817.7  |
| 15°   | 785.5  | 788.2  | 791.8  | 798.9  | 802.5  | 803.4  | 808.8  | 815.9 | 824.0 | 828.5  | 829.4  |
| 17.5° | 812.4  | 814.1  | 824.0  | 829.4  | 828.5  | 824.0  | 824.0  | 828.5 | 837.4 | 843.7  | 843.7  |
| 20°   | 861.6  | 863.4  | 867.9  | 868.8  | 862.5  | 850.0  | 840.1  | 841.9 | 853.6 | 861.6  | 863.4  |
| 22.5° | 928.8  | 928.8  | 924.3  | 922.5  | 904.6  | 880.4  | 861.6  | 858.9 | 870.6 | 883.1  | 884.0  |
| 25°   | 1000.4 | 1000.4 | 991.5  | 975.4  | 949.4  | 914.5  | 886.7  | 875.1 | 887.6 | 901.9  | 904.6  |
| 27.5° | 1063.1 | 1062.2 | 1045.2 | 1018.4 | 991.5  | 948.5  | 911.8  | 892.1 | 901.0 | 918.9  | 921.6  |
| 30°   | 1104.3 | 1100.8 | 1073.0 | 1038.1 | 1010.3 | 965.5  | 924.3  | 901.0 | 909.1 | 928.8  | 931.5  |
| 32.5° | 1133.0 | 1127.6 | 1092.7 | 1054.2 | 1023.7 | 978.1  | 932.4  | 907.3 | 914.5 | 936.0  | 937.7  |
| 35°   | 1150.0 | 1143.7 | 1107.0 | 1068.5 | 1034.5 | 987.9  | 937.7  | 909.1 | 916.3 | 939.5  | 942.2  |
| 37.5° | 1159.9 | 1153.6 | 1121.4 | 1082.8 | 1046.1 | 1001.3 | 943.1  | 911.8 | 917.1 | 941.3  | 944.0  |
| 40°   | 1163.5 | 1161.7 | 1135.7 | 1099.0 | 1059.6 | 1013.9 | 950.3  | 912.7 | 917.1 | 943.1  | 946.7  |
| 42.5° | 1167.0 | 1168.8 | 1150.0 | 1116.0 | 1077.5 | 1029.1 | 958.3  | 914.5 | 917.1 | 945.8  | 947.6  |
| 45°   | 1177.8 | 1178.7 | 1171.5 | 1143.7 | 1106.1 | 1057.8 | 973.6  | 923.4 | 921.6 | 951.2  | 955.7  |
| 47.5° | 1198.4 | 1201.1 | 1201.1 | 1183.2 | 1153.6 | 1105.2 | 1002.2 | 938.6 | 934.2 | 970.9  | 974.5  |
| 50°   | 1211.8 | 1215.4 | 1228.8 | 1216.3 | 1197.5 | 1145.5 | 1030.0 | 949.4 | 945.8 | 984.3  | 987.9  |
| 52.5° | 1226.1 | 1230.6 | 1252.1 | 1258.4 | 1244.1 | 1186.7 | 1059.6 | 968.2 | 953.0 | 996.9  | 1000.4 |
| 55°   | 1244.1 | 1245.0 | 1275.4 | 1296.9 | 1290.6 | 1244.1 | 1090.0 | 980.7 | 961.0 | 1009.4 | 1015.7 |
| 57.5° | 1225.3 | 1227.9 | 1270.0 | 1296.0 | 1306.8 | 1262.0 | 1098.1 | 965.5 | 944.0 | 993.3  | 999.5  |
| 60°   | 1189.4 | 1195.7 | 1238.7 | 1278.1 | 1286.2 | 1241.4 | 1079.3 | 936.9 | 910.0 | 964.6  | 968.2  |
| 62.5° | 1146.4 | 1157.2 | 1196.6 | 1242.3 | 1258.4 | 1219.0 | 1054.2 | 896.5 | 868.8 | 932.4  | 934.2  |
| 65°   | 1073.9 | 1088.2 | 1146.4 | 1185.8 | 1218.1 | 1178.7 | 1020.1 | 843.7 | 819.5 | 873.3  | 873.3  |
| 67.5° | 980.7  | 989.7  | 1045.2 | 1110.6 | 1131.2 | 1103.4 | 948.5  | 777.4 | 737.1 | 790.9  | 797.1  |
| 70°   | 879.5  | 884.9  | 927.0  | 996.9  | 1020.1 | 1008.5 | 859.8  | 692.3 | 644.9 | 704.9  | 706.7  |
| 72.5° | 755.0  | 764.0  | 806.1  | 864.3  | 893.9  | 884.9  | 754.1  | 592.0 | 549.9 | 601.9  | 596.5  |
| 75°   | 605.5  | 616.2  | 657.4  | 710.3  | 744.3  | 734.4  | 634.1  | 481.0 | 447.8 | 482.8  | 481.9  |
| 77.5° | 468.4  | 468.4  | 505.1  | 554.4  | 575.9  | 568.7  | 489.0  | 370.8 | 335.9 | 365.4  | 368.1  |
| 80°   | 325.1  | 324.2  | 355.6  | 390.5  | 408.4  | 407.5  | 352.0  | 257.1 | 234.7 | 250.8  | 246.3  |
| 82.5° | 196.1  | 197.9  | 216.7  | 240.0  | 257.9  | 258.8  | 222.1  | 158.5 | 142.4 | 148.7  | 145.1  |
| 85°   | 85.1   | 89.6   | 103.0  | 118.2  | 131.7  | 131.7  | 116.4  | 78.8  | 69.9  | 64.5   | 59.1   |
| 87.5° | 20.6   | 20.6   | 26.9   | 33.1   | 39.4   | 42.1   | 38.5   | 29.6  | 26.0  | 15.2   | 7.2    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2411-284-4

Test Date: 11/22/2024

Luminaire Tested: TTN-D0-830-U-WQ

Data in this report applies to families of products including TTN-D0-830-U-WQ




### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2411-284-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 11/22/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: MCGRAW EDISON  
 Catalog Number: **TTN-D0-830-U-WQ**  
 Description: TOPTIER NANO LED PARKING GARAGE LUMINAIRE. 3000K, 80 CRI LEDS AND WIDE DISTRIBUTION

### Spectral Parameters

CCT (K): 2963  
 CIE  $u'$ : 0.2515  
 CIE  $v'$ : 0.5238  
 Duv: 0.0012  
 CIE x: 0.4414  
 CIE y: 0.4086  
 CIE z: 0.1501  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 582  
 Purity: 55.12798  
 R<sub>f</sub>: 86.1  
 R<sub>g</sub>: 94.9

CRI (Ra): 82.9  
 R1: 81.4  
 R2: 91.9  
 R3: 95.2  
 R4: 81.6  
 R5: 82.3  
 R6: 91.4  
 R7: 82.0  
 R8: 57.2  
 R9: 3.9  
 R10: 82.5  
 R11: 82.3  
 R12: 76.5  
 R13: 83.9  
 R14: 97.8  
 R15: 72.6



### Test Conditions


Stabilization Time: 37M  
 Operation Time: 1H 37M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2411-284-4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/22/2024       | 10/22/2025           |
| DC Power Source                | IN0208                | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | IN0085                | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | IN0046                | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2411-284-4

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle


REPORT NUMBER: SP1-2411-284-4

**Photopic Flux vs. Wavelength**

**Photopic Lumens: NR**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 267                                  | NR                             | 620               | 915                                  | NR                             | 750               | 23                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 315                                  | NR                             | 625               | 866                                  | NR                             | 755               | 20                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 360                                  | NR                             | 630               | 811                                  | NR                             | 760               | 17                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 396                                  | NR                             | 635               | 750                                  | NR                             | 765               | 14                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 418                                  | NR                             | 640               | 686                                  | NR                             | 770               | 12                                   | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 435                                  | NR                             | 645               | 619                                  | NR                             | 775               | 10                                   | NR                             | 905               | 0                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 448                                  | NR                             | 650               | 554                                  | NR                             | 780               | 9                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 462                                  | NR                             | 655               | 491                                  | NR                             | 785               | 7                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 476                                  | NR                             | 660               | 431                                  | NR                             | 790               | 6                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 495                                  | NR                             | 665               | 376                                  | NR                             | 795               | 5                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 5                                    | NR                             | 540               | 520                                  | NR                             | 670               | 325                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 547                                  | NR                             | 675               | 280                                  | NR                             | 805               | 4                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 21                                   | NR                             | 550               | 576                                  | NR                             | 680               | 241                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 42                                   | NR                             | 555               | 612                                  | NR                             | 685               | 207                                  | NR                             | 815               | 3                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 77                                   | NR                             | 560               | 651                                  | NR                             | 690               | 176                                  | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 135                                  | NR                             | 565               | 693                                  | NR                             | 695               | 149                                  | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 215                                  | NR                             | 570               | 741                                  | NR                             | 700               | 127                                  | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 321                                  | NR                             | 575               | 793                                  | NR                             | 705               | 107                                  | NR                             | 835               | 2                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 479                                  | NR                             | 580               | 847                                  | NR                             | 710               | 89                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 432                                  | NR                             | 585               | 897                                  | NR                             | 715               | 75                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 265                                  | NR                             | 590               | 940                                  | NR                             | 720               | 62                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 231                                  | NR                             | 595               | 971                                  | NR                             | 725               | 51                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 204                                  | NR                             | 600               | 993                                  | NR                             | 730               | 43                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 168                                  | NR                             | 605               | 996                                  | NR                             | 735               | 36                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 183                                  | NR                             | 610               | 986                                  | NR                             | 740               | 31                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 223                                  | NR                             | 615               | 957                                  | NR                             | 745               | 26                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2411-284-4

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.34

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 267                         | NR               | 620       | 915                         | NR               | 750       | 23                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 315                         | NR               | 625       | 866                         | NR               | 755       | 20                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 360                         | NR               | 630       | 811                         | NR               | 760       | 17                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 396                         | NR               | 635       | 750                         | NR               | 765       | 14                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 418                         | NR               | 640       | 686                         | NR               | 770       | 12                          | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 435                         | NR               | 645       | 619                         | NR               | 775       | 10                          | NR               | 905       | 0                           | NR               |
| 390       | 0                           | NR               | 520       | 448                         | NR               | 650       | 554                         | NR               | 780       | 9                           | NR               | 910       | 0                           | NR               |
| 395       | 0                           | NR               | 525       | 462                         | NR               | 655       | 491                         | NR               | 785       | 7                           | NR               | 915       | 0                           | NR               |
| 400       | 1                           | NR               | 530       | 476                         | NR               | 660       | 431                         | NR               | 790       | 6                           | NR               | 920       | 0                           | NR               |
| 405       | 2                           | NR               | 535       | 495                         | NR               | 665       | 376                         | NR               | 795       | 5                           | NR               | 925       | 0                           | NR               |
| 410       | 5                           | NR               | 540       | 520                         | NR               | 670       | 325                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 10                          | NR               | 545       | 547                         | NR               | 675       | 280                         | NR               | 805       | 4                           | NR               | 935       | 0                           | NR               |
| 420       | 21                          | NR               | 550       | 576                         | NR               | 680       | 241                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 42                          | NR               | 555       | 612                         | NR               | 685       | 207                         | NR               | 815       | 3                           | NR               | 945       | 0                           | NR               |
| 430       | 77                          | NR               | 560       | 651                         | NR               | 690       | 176                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 135                         | NR               | 565       | 693                         | NR               | 695       | 149                         | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 215                         | NR               | 570       | 741                         | NR               | 700       | 127                         | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 321                         | NR               | 575       | 793                         | NR               | 705       | 107                         | NR               | 835       | 2                           | NR               | 965       | 0                           | NR               |
| 450       | 479                         | NR               | 580       | 847                         | NR               | 710       | 89                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 432                         | NR               | 585       | 897                         | NR               | 715       | 75                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 265                         | NR               | 590       | 940                         | NR               | 720       | 62                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 231                         | NR               | 595       | 971                         | NR               | 725       | 51                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 204                         | NR               | 600       | 993                         | NR               | 730       | 43                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 168                         | NR               | 605       | 996                         | NR               | 735       | 36                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 183                         | NR               | 610       | 986                         | NR               | 740       | 31                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 223                         | NR               | 615       | 957                         | NR               | 745       | 26                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2411-284-4

**Melanopic Flux vs. Wavelength**

**Melanopic Lumens: NR**
**M/P: 2.58**


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 267                                  | NR                             | 620               | 915                                  | NR                             | 750               | 23                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 315                                  | NR                             | 625               | 866                                  | NR                             | 755               | 20                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 360                                  | NR                             | 630               | 811                                  | NR                             | 760               | 17                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 396                                  | NR                             | 635               | 750                                  | NR                             | 765               | 14                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 418                                  | NR                             | 640               | 686                                  | NR                             | 770               | 12                                   | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 435                                  | NR                             | 645               | 619                                  | NR                             | 775               | 10                                   | NR                             | 905               | 0                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 448                                  | NR                             | 650               | 554                                  | NR                             | 780               | 9                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 462                                  | NR                             | 655               | 491                                  | NR                             | 785               | 7                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 476                                  | NR                             | 660               | 431                                  | NR                             | 790               | 6                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 495                                  | NR                             | 665               | 376                                  | NR                             | 795               | 5                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 5                                    | NR                             | 540               | 520                                  | NR                             | 670               | 325                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 547                                  | NR                             | 675               | 280                                  | NR                             | 805               | 4                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 21                                   | NR                             | 550               | 576                                  | NR                             | 680               | 241                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 42                                   | NR                             | 555               | 612                                  | NR                             | 685               | 207                                  | NR                             | 815               | 3                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 77                                   | NR                             | 560               | 651                                  | NR                             | 690               | 176                                  | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 135                                  | NR                             | 565               | 693                                  | NR                             | 695               | 149                                  | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 215                                  | NR                             | 570               | 741                                  | NR                             | 700               | 127                                  | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 321                                  | NR                             | 575               | 793                                  | NR                             | 705               | 107                                  | NR                             | 835               | 2                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 479                                  | NR                             | 580               | 847                                  | NR                             | 710               | 89                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 432                                  | NR                             | 585               | 897                                  | NR                             | 715               | 75                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 265                                  | NR                             | 590               | 940                                  | NR                             | 720               | 62                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 231                                  | NR                             | 595               | 971                                  | NR                             | 725               | 51                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 204                                  | NR                             | 600               | 993                                  | NR                             | 730               | 43                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 168                                  | NR                             | 605               | 996                                  | NR                             | 735               | 36                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 183                                  | NR                             | 610               | 986                                  | NR                             | 740               | 31                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 223                                  | NR                             | 615               | 957                                  | NR                             | 745               | 26                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2411-284-4





TM-30-18

### Summary

$R_f = 86.1$   
 $R_g = 94.9$   
 $CIE R_a = 82.9$   
 $R_9 = 3.9$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 87 | CES51 = 95 | CES76 = 85 |
| CES02 = 63 | CES27 = 95 | CES52 = 95 | CES77 = 85 |
| CES03 = 31 | CES28 = 96 | CES53 = 91 | CES78 = 83 |
| CES04 = 70 | CES29 = 90 | CES54 = 92 | CES79 = 89 |
| CES05 = 50 | CES30 = 96 | CES55 = 91 | CES80 = 89 |
| CES06 = 51 | CES31 = 92 | CES56 = 88 | CES81 = 70 |
| CES07 = 42 | CES32 = 86 | CES57 = 87 | CES82 = 96 |
| CES08 = 41 | CES33 = 94 | CES58 = 88 | CES83 = 94 |
| CES09 = 29 | CES34 = 94 | CES59 = 92 | CES84 = 92 |
| CES10 = 76 | CES35 = 97 | CES60 = 93 | CES85 = 76 |
| CES11 = 59 | CES36 = 88 | CES61 = 90 | CES86 = 66 |
| CES12 = 65 | CES37 = 98 | CES62 = 92 | CES87 = 85 |
| CES13 = 44 | CES38 = 95 | CES63 = 90 | CES88 = 87 |
| CES14 = 74 | CES39 = 98 | CES64 = 85 | CES89 = 75 |
| CES15 = 72 | CES40 = 96 | CES65 = 81 | CES90 = 89 |
| CES16 = 48 | CES41 = 97 | CES66 = 84 | CES91 = 80 |
| CES17 = 50 | CES42 = 98 | CES67 = 83 | CES92 = 64 |
| CES18 = 57 | CES43 = 92 | CES68 = 85 | CES93 = 79 |
| CES19 = 72 | CES44 = 99 | CES69 = 89 | CES94 = 61 |
| CES20 = 67 | CES45 = 94 | CES70 = 83 | CES95 = 75 |
| CES21 = 87 | CES46 = 91 | CES71 = 81 | CES96 = 84 |
| CES22 = 79 | CES47 = 92 | CES72 = 93 | CES97 = 89 |
| CES23 = 92 | CES48 = 84 | CES73 = 78 | CES98 = 85 |
| CES24 = 91 | CES49 = 92 | CES74 = 91 | CES99 = 76 |
| CES25 = 72 | CES50 = 95 | CES75 = 84 |            |





Color Rendition by Hue-Angle Bin



**Measure Comparisons**


(END OF REPORT)