Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P821260

Luminaire Tested: **TT-D5-735-24VDC-WQ-UPL**

Issue Date: 7/23/2020

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P821260
	REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G2-2002-677-2) AND
Test Lab:	INNOVATION CENTER
Issue Date:	7/23/2020
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	TT-D5-735-24VDC-WQ-UPL
Description:	TOPTIER LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
	3500K, 70 CRI LEDS AND WIDE DISTRIBUTION
Light Source:	-
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	9840.7 lumens
Efficiency:	N/A
Efficacy:	134.8 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.12' x H: 0.1')
IES Classification:	Type V - Short
BUG Rating:	B3 - U4 - G3


Input Watts (W):	73
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	25 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821260
CATALOG NUMBER: TT-D5-735-24VDC-WQ-UPL

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 3.1 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821260
CATALOG NUMBER: TT-D5-735-24VDC-WQ-UPL

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P821260
CATALOG NUMBER: TT-D5-735-24VDC-WQ-UPL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4504.5	415.9	4920.4
	% Fixture	45.8	4.2	50.0
Street Side	Lumens	4504.5	415.9	4920.4
	% Fixture	45.8	4.2	50.0
Total	Lumens	9009.0	831.7	9840.7
	% Fixture	91.5	8.5	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.4	0.6
10°-20°	207.9	2.1
20°-30°	426.8	4.3
30°-40°	758.3	7.7
40°-50°	1278.2	13.0
50°-60°	1885.6	19.2
60°-70°	2213.0	22.5
70°-80°	1724.1	17.5
80°-90°	454.7	4.6
90°-100°	42.6	0.4
100°-110°	66.0	0.7
110°-120°	91.9	0.9
120°-130°	119.0	1.2
130°-140°	138.7	1.4
140°-150°	140.5	1.4
150°-160°	121.9	1.2
160°-170°	82.2	0.8
170°-180°	28.9	0.3
0°-90°	9009.0	91.5
0°-180°	9840.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P821260
CATALOG NUMBER: TT-D5-735-24VDC-WQ-UPL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	347.6	3.5			
FM	(30°-60°)	1961.1	19.9			
FH	(60°-80°)	1968.5	20.0			G2/5000
FVH	(80°-90°)	227.4	2.3			G3/500
BL	(0°-30°)	347.6	3.5	B1/500		
BM	(30°-60°)	1961.1	19.9	B2/2500		
BH	(60°-80°)	1968.5	20.0	B3/2500		G2/5000
BVH	(80°-90°)	227.4	2.3			G3/500
UL	(90°-100°)	42.6	0.4		U2/50	
UH	(100°-180°)	789.1	8.0		U4/1000	

BUG Rating: B3-U4-G3
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821260
CATALOG NUMBER: TT-D5-735-24VDC-WQ-UPL

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	606.1	606.1	606.1	606.1	606.1	*606.1*	606.1	606.1	606.1	606.1	606.1
2.5°	616.0	616.0	616.0	614.6	614.6	*614.6*	614.6	616.0	616.0	616.0	616.0
5°	630.1	630.1	627.3	624.5	621.6	*621.6*	623.1	624.5	625.9	628.7	628.7
7.5°	638.6	638.6	637.2	634.4	630.1	*630.1*	631.6	634.4	635.8	635.8	634.4
10°	650.0	651.4	655.6	657.0	654.2	*654.2*	655.6	657.0	654.2	650.0	650.0
12.5°	676.9	678.3	683.9	688.2	688.2	*685.4*	686.8	689.6	682.5	675.5	676.9
15°	715.1	715.1	716.5	720.8	717.9	*715.1*	717.9	719.3	715.1	713.7	716.5
17.5°	766.1	766.1	757.6	764.7	766.1	*764.7*	767.5	760.4	756.2	761.8	764.7
20°	821.3	815.6	811.4	817.1	828.4	*824.1*	829.8	814.2	810.0	812.8	814.2
22.5°	856.7	861.0	863.8	866.6	882.2	*876.5*	882.2	865.2	862.4	856.7	852.5
25°	899.2	903.4	920.4	911.9	921.8	*913.3*	920.4	910.5	916.2	899.2	899.2
27.5°	947.3	955.8	965.7	961.5	974.2	*970.0*	974.2	960.1	961.5	954.4	951.6
30°	1012.5	1012.5	1009.6	1018.1	1040.8	*1038.0*	1039.4	1021.0	1008.2	1009.6	1015.3
32.5°	1077.6	1069.1	1073.4	1098.8	1113.0	*1107.3*	1110.2	1101.7	1073.4	1067.7	1071.9
35°	1138.5	1151.2	1161.2	1182.4	1202.2	*1199.4*	1198.0	1183.8	1165.4	1142.7	1135.7
37.5°	1233.4	1247.5	1274.4	1312.7	1348.1	*1355.1*	1336.7	1318.3	1275.9	1243.3	1226.3
40°	1358.0	1359.4	1390.5	1464.2	1496.8	*1502.4*	1492.5	1461.4	1396.2	1359.4	1358.0
42.5°	1467.0	1457.1	1508.1	1570.4	1600.1	*1603.0*	1595.9	1570.4	1508.1	1455.7	1465.6
45°	1552.0	1552.0	1612.9	1662.4	1710.6	*1721.9*	1709.2	1655.3	1614.3	1553.4	1549.1
47.5°	1629.9	1651.1	1702.1	1763.0	1830.9	*1846.5*	1830.9	1767.2	1697.8	1652.5	1628.4
50°	1723.3	1748.8	1785.6	1880.5	1957.0	*1978.2*	1955.5	1886.2	1785.6	1747.4	1733.2
52.5°	1832.4	1853.6	1911.7	2030.6	2087.2	*2118.4*	2100.0	2033.4	1914.5	1856.4	1845.1
55°	1962.6	1942.8	2033.4	2148.1	2252.9	*2294.0*	2257.2	2151.0	2047.6	1942.8	1962.6
57.5°	2029.2	2006.5	2134.0	2243.0	2388.9	*2442.7*	2397.4	2251.5	2134.0	2013.6	2027.8
60°	2034.8	2044.8	2141.1	2319.5	2420.0	*2442.7*	2428.5	2332.2	2145.3	2053.3	2026.4
62.5°	2017.9	2078.7	2160.9	2345.0	2435.6	*2490.8*	2442.7	2347.8	2169.4	2088.7	2019.3
65°	*1995.2*	*2056.1*	*2177.9*	*2308.1*	*2462.5*	*2517.7*	*2472.4*	*2315.2*	*2183.5*	*2056.1*	*2003.7*
67.5°	1955.5	1934.3	2084.4	2258.6	2393.1	*2425.7*	2397.4	2261.4	2083.0	1931.5	1959.8
70°	1829.5	1811.1	1940.0	2131.1	2260.0	*2305.3*	2271.3	2134.0	1942.8	1815.4	1832.4
72.5°	1642.6	1648.3	1772.9	1955.5	2094.3	*2122.6*	2104.2	1954.1	1780.0	1655.3	1632.7
75°	1424.5	1438.7	1557.6	1723.3	1849.3	*1866.3*	1847.9	1730.4	1556.2	1447.2	1417.5
77.5°	1171.1	1192.3	1288.6	1454.3	1537.8	*1576.1*	1546.3	1458.5	1295.7	1198.0	1168.2
80°	907.7	914.8	982.7	1115.8	1226.3	*1251.8*	1223.5	1120.1	991.2	917.6	896.4
82.5°	594.7	606.1	667.0	768.9	841.1	*834.0*	841.1	760.4	674.0	603.2	567.8
85°	264.8	287.5	328.5	376.7	423.4	*436.1*	423.4	382.3	328.5	281.8	276.1
87.5°	18.4	21.2	25.5	26.9	29.7	*22.7*	22.7	22.7	19.8	22.7	18.4
90°	30.1	29.1	29.1	29.1	29.1	*29.1*	29.1	29.1	29.1	29.1	29.1
92.5°	34.8	34.2	34.2	33.8	33.8	*33.8*	33.8	33.8	33.8	33.8	33.8
95°	39.4	39.4	39.4	38.5	38.5	*38.5*	38.5	38.5	38.5	38.5	38.5
97.5°	44.6	44.6	44.6	44.2	44.2	*44.2*	44.2	44.2	44.2	44.2	44.2
100°	49.8	49.8	49.8	49.8	49.8	*49.8*	49.8	49.8	49.8	49.8	49.8
102.5°	55.9	55.9	55.9	55.9	55.9	*55.9*	55.9	56.4	55.9	55.9	55.9
105°	62.0	62.0	62.0	62.0	62.0	*62.0*	62.0	62.9	62.0	62.0	62.0
107.5°	68.6	68.6	69.0	69.0	69.0	*69.0*	69.0	69.5	69.0	69.0	69.0
110°	75.1	75.1	76.1	76.1	76.1	*76.1*	76.1	76.1	76.1	76.1	76.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821260
CATALOG NUMBER: TT-D5-735-24VDC-WQ-UPL

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	83.1	83.1	84.0	84.0	84.0	*84.0*	84.6	84.6	84.0	84.0	84.0
115°	91.1	91.1	92.0	92.0	92.0	*92.0*	93.0	93.0	92.0	92.0	92.0
117.5°	100.5	100.5	101.0	101.4	101.4	*101.4*	102.4	102.4	101.4	101.4	101.4
120°	109.9	109.9	109.9	110.8	110.8	*110.8*	111.8	111.8	110.8	110.8	110.8
122.5°	120.7	120.7	121.2	121.6	121.6	*121.6*	122.6	122.6	122.1	122.1	121.6
125°	131.5	131.5	132.4	132.4	132.4	*132.4*	133.4	133.4	133.4	133.4	132.4
127.5°	143.2	143.2	144.2	144.2	144.2	*144.2*	145.1	145.1	145.1	145.1	144.2
130°	155.0	155.0	155.9	155.9	155.9	*155.9*	156.8	156.8	156.8	156.8	155.9
132.5°	167.2	167.2	167.6	167.6	167.6	*168.1*	168.6	168.6	168.6	168.6	168.1
135°	179.4	179.4	179.4	179.4	179.4	*180.3*	180.3	180.3	180.3	180.3	180.3
137.5°	191.2	190.6	191.2	190.6	191.2	*191.6*	191.6	191.6	191.6	191.6	191.6
140°	202.9	201.9	202.9	201.9	202.9	*202.9*	202.9	202.9	202.9	202.9	202.9
142.5°	213.7	213.2	213.7	212.7	213.7	*213.7*	213.7	213.7	213.7	213.7	213.7
145°	224.5	224.5	224.5	223.5	224.5	*224.5*	224.5	224.5	224.5	224.5	224.5
147.5°	235.8	235.3	235.8	234.8	235.8	*235.8*	235.8	235.8	235.8	235.8	235.8
150°	247.0	246.1	247.0	246.1	247.0	*247.0*	247.0	247.0	247.0	247.0	247.0
152.5°	256.0	255.5	256.4	255.5	256.0	*256.0*	256.4	256.0	256.0	256.0	256.0
155°	264.9	264.9	265.8	264.9	264.9	*264.9*	265.8	264.9	264.9	264.9	264.9
157.5°	272.4	272.4	273.3	272.4	272.4	*272.4*	273.3	272.4	272.4	272.4	272.4
160°	279.9	279.9	280.8	279.9	279.9	*279.9*	280.8	279.9	279.9	279.9	279.9
162.5°	286.0	286.0	286.9	286.0	286.0	*286.0*	286.9	286.0	286.0	286.0	286.0
165°	292.1	292.1	293.0	292.1	292.1	*292.1*	293.0	292.1	292.1	292.1	292.1
167.5°	295.8	295.8	296.8	295.8	295.8	*295.8*	296.8	295.8	295.8	295.8	295.8
170°	299.6	299.6	300.5	299.6	299.6	*299.6*	300.5	299.6	299.6	299.6	299.6
172.5°	302.0	302.0	302.8	302.0	302.4	*302.0*	302.8	302.0	302.0	302.0	302.0
175°	304.3	304.3	305.2	304.3	305.2	*304.3*	305.2	304.3	304.3	304.3	304.3
177.5°	305.2	305.2	305.7	305.2	305.7	*305.2*	305.7	305.2	305.2	305.2	305.2
180°	306.2	306.2	306.2	306.2	306.2	*306.2*	306.2	306.2	306.2	306.2	306.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-4

Test Date: 09/24/2024

Luminaire Tested: MEM2-HTN-VA-30-735-U-WQ

Data in this report applies to families of products including MEM2-HTN-VA-30-735-U-WQ


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-176-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	09/27/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**MEM2-HTN-VA-30-735-U-WQ**
Description:	EPIC MODERN VISUAL COMFORT 30W WAVESTREAM WIDE

Spectral Parameters

CCT (K):	3348	CRI (Ra):	73.4		
CIE u':	0.2384	R1:	70.8	R9:	-19.2
CIE v':	0.5184	R2:	79.9	R10:	52.5
Duv:	0.0030	R3:	87.6	R11:	68.0
CIE x:	0.4177	R4:	72.6	R12:	42.6
CIE y:	0.4036	R5:	69.3	R13:	72.0
CIE z:	0.1787	R6:	71.3	R14:	92.6
Peak Wavelength (nm):	593	R7:	82.1	R15:	63.8
Dominant Wavelength (nm):	580	R8:	53.3		
Purity:	46.5223				
Rf:	75.8				
Rg:	95.8				



Test Conditions


Stabilization Time:	30M
Operation Time:	1H 30M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-176-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-176-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3348K
CIE x = 0.4177
CIE y = 0.4036
Duv = 0.0030

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	110	NR	620	844	NR	750	28	NR	880	0	NR
365	0	NR	495	150	NR	625	792	NR	755	25	NR	885	0	NR
370	0	NR	500	214	NR	630	737	NR	760	22	NR	890	0	NR
375	0	NR	505	293	NR	635	683	NR	765	19	NR	895	0	NR
380	0	NR	510	376	NR	640	625	NR	770	16	NR	900	0	NR
385	0	NR	515	458	NR	645	566	NR	775	14	NR	905	0	NR
390	0	NR	520	526	NR	650	509	NR	780	12	NR	910	0	NR
395	1	NR	525	584	NR	655	453	NR	785	10	NR	915	0	NR
400	3	NR	530	631	NR	660	401	NR	790	9	NR	920	0	NR
405	5	NR	535	671	NR	665	353	NR	795	8	NR	925	0	NR
410	10	NR	540	704	NR	670	308	NR	800	7	NR	930	0	NR
415	21	NR	545	737	NR	675	269	NR	805	6	NR	935	0	NR
420	44	NR	550	766	NR	680	235	NR	810	5	NR	940	0	NR
425	90	NR	555	797	NR	685	204	NR	815	4	NR	945	0	NR
430	171	NR	560	832	NR	690	177	NR	820	4	NR	950	0	NR
435	305	NR	565	866	NR	695	152	NR	825	3	NR	955	0	NR
440	455	NR	570	901	NR	700	131	NR	830	3	NR	960	0	NR
445	615	NR	575	933	NR	705	112	NR	835	3	NR	965	0	NR
450	771	NR	580	963	NR	710	96	NR	840	2	NR	970	0	NR
455	579	NR	585	984	NR	715	80	NR	845	2	NR	975	0	NR
460	313	NR	590	1000	NR	720	67	NR	850	2	NR	980	0	NR
465	221	NR	595	999	NR	725	55	NR	855	1	NR	985	0	NR
470	156	NR	600	990	NR	730	46	NR	860	1	NR	990	0	NR
475	103	NR	605	968	NR	735	40	NR	865	1	NR	995	0	NR
480	89	NR	610	937	NR	740	35	NR	870	1	NR	1000	0	NR
485	93	NR	615	893	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-176-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.31**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	110	NR	620	844	NR	750	28	NR	880	0	NR
365	0	NR	495	150	NR	625	792	NR	755	25	NR	885	0	NR
370	0	NR	500	214	NR	630	737	NR	760	22	NR	890	0	NR
375	0	NR	505	293	NR	635	683	NR	765	19	NR	895	0	NR
380	0	NR	510	376	NR	640	625	NR	770	16	NR	900	0	NR
385	0	NR	515	458	NR	645	566	NR	775	14	NR	905	0	NR
390	0	NR	520	526	NR	650	509	NR	780	12	NR	910	0	NR
395	1	NR	525	584	NR	655	453	NR	785	10	NR	915	0	NR
400	3	NR	530	631	NR	660	401	NR	790	9	NR	920	0	NR
405	5	NR	535	671	NR	665	353	NR	795	8	NR	925	0	NR
410	10	NR	540	704	NR	670	308	NR	800	7	NR	930	0	NR
415	21	NR	545	737	NR	675	269	NR	805	6	NR	935	0	NR
420	44	NR	550	766	NR	680	235	NR	810	5	NR	940	0	NR
425	90	NR	555	797	NR	685	204	NR	815	4	NR	945	0	NR
430	171	NR	560	832	NR	690	177	NR	820	4	NR	950	0	NR
435	305	NR	565	866	NR	695	152	NR	825	3	NR	955	0	NR
440	455	NR	570	901	NR	700	131	NR	830	3	NR	960	0	NR
445	615	NR	575	933	NR	705	112	NR	835	3	NR	965	0	NR
450	771	NR	580	963	NR	710	96	NR	840	2	NR	970	0	NR
455	579	NR	585	984	NR	715	80	NR	845	2	NR	975	0	NR
460	313	NR	590	1000	NR	720	67	NR	850	2	NR	980	0	NR
465	221	NR	595	999	NR	725	55	NR	855	1	NR	985	0	NR
470	156	NR	600	990	NR	730	46	NR	860	1	NR	990	0	NR
475	103	NR	605	968	NR	735	40	NR	865	1	NR	995	0	NR
480	89	NR	610	937	NR	740	35	NR	870	1	NR	1000	0	NR
485	93	NR	615	893	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-176-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.4**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	110	NR	620	844	NR	750	28	NR	880	0	NR
365	0	NR	495	150	NR	625	792	NR	755	25	NR	885	0	NR
370	0	NR	500	214	NR	630	737	NR	760	22	NR	890	0	NR
375	0	NR	505	293	NR	635	683	NR	765	19	NR	895	0	NR
380	0	NR	510	376	NR	640	625	NR	770	16	NR	900	0	NR
385	0	NR	515	458	NR	645	566	NR	775	14	NR	905	0	NR
390	0	NR	520	526	NR	650	509	NR	780	12	NR	910	0	NR
395	1	NR	525	584	NR	655	453	NR	785	10	NR	915	0	NR
400	3	NR	530	631	NR	660	401	NR	790	9	NR	920	0	NR
405	5	NR	535	671	NR	665	353	NR	795	8	NR	925	0	NR
410	10	NR	540	704	NR	670	308	NR	800	7	NR	930	0	NR
415	21	NR	545	737	NR	675	269	NR	805	6	NR	935	0	NR
420	44	NR	550	766	NR	680	235	NR	810	5	NR	940	0	NR
425	90	NR	555	797	NR	685	204	NR	815	4	NR	945	0	NR
430	171	NR	560	832	NR	690	177	NR	820	4	NR	950	0	NR
435	305	NR	565	866	NR	695	152	NR	825	3	NR	955	0	NR
440	455	NR	570	901	NR	700	131	NR	830	3	NR	960	0	NR
445	615	NR	575	933	NR	705	112	NR	835	3	NR	965	0	NR
450	771	NR	580	963	NR	710	96	NR	840	2	NR	970	0	NR
455	579	NR	585	984	NR	715	80	NR	845	2	NR	975	0	NR
460	313	NR	590	1000	NR	720	67	NR	850	2	NR	980	0	NR
465	221	NR	595	999	NR	725	55	NR	855	1	NR	985	0	NR
470	156	NR	600	990	NR	730	46	NR	860	1	NR	990	0	NR
475	103	NR	605	968	NR	735	40	NR	865	1	NR	995	0	NR
480	89	NR	610	937	NR	740	35	NR	870	1	NR	1000	0	NR
485	93	NR	615	893	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-176-4

TM-30-18


Summary


R_f = 75.8
R_g = 95.8
CIE R_a = 73.4
R_9 = -19.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-176-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 65	CES51 = 88	CES76 = 55
CES02 = 62	CES27 = 88	CES52 = 87	CES77 = 74
CES03 = 31	CES28 = 83	CES53 = 77	CES78 = 58
CES04 = 70	CES29 = 66	CES54 = 86	CES79 = 84
CES05 = 48	CES30 = 79	CES55 = 84	CES80 = 81
CES06 = 51	CES31 = 69	CES56 = 74	CES81 = 78
CES07 = 41	CES32 = 62	CES57 = 73	CES82 = 92
CES08 = 40	CES33 = 75	CES58 = 75	CES83 = 89
CES09 = 29	CES34 = 73	CES59 = 87	CES84 = 88
CES10 = 75	CES35 = 85	CES60 = 91	CES85 = 79
CES11 = 58	CES36 = 95	CES61 = 84	CES86 = 71
CES12 = 64	CES37 = 80	CES62 = 88	CES87 = 79
CES13 = 43	CES38 = 88	CES63 = 73	CES88 = 81
CES14 = 74	CES39 = 96	CES64 = 69	CES89 = 71
CES15 = 71	CES40 = 91	CES65 = 66	CES90 = 80
CES16 = 47	CES41 = 91	CES66 = 62	CES91 = 81
CES17 = 50	CES42 = 81	CES67 = 60	CES92 = 63
CES18 = 56	CES43 = 77	CES68 = 68	CES93 = 78
CES19 = 72	CES44 = 99	CES69 = 76	CES94 = 56
CES20 = 65	CES45 = 85	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 82	CES71 = 55	CES96 = 79
CES22 = 79	CES47 = 83	CES72 = 85	CES97 = 84
CES23 = 92	CES48 = 75	CES73 = 52	CES98 = 77
CES24 = 91	CES49 = 79	CES74 = 96	CES99 = 68
CES25 = 72	CES50 = 87	CES75 = 57	





REPORT NUMBER: SP1-2407-176-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-176-4

TM-30-18

Measure Comparisons





(END OF REPORT)