

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636737

Luminaire Tested: GWS-SA4B-735-U-T3-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-25)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4B-735-U-T3-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (64) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12184.6 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 94.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636737
 CATALOG NUMBER: GWS-SA4B-735-U-T3-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 6.3 fc
 Type II - Short - N/A

REPORT NUMBER: P636737
CATALOG NUMBER: GWS-SA4B-735-U-T3-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636737
 CATALOG NUMBER: GWS-SA4B-735-U-T3-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3856.4 | 0.0 | 3856.4 |
| | % Fixture | 31.6 | 0.0 | 31.6 |
| Street Side | Lumens | 8328.2 | 0.0 | 8328.2 |
| | % Fixture | 68.4 | 0.0 | 68.4 |
| Total | Lumens | 12184.6 | 0.0 | 12184.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 222.9 | 1.8 |
| 10°-20° | 733.0 | 6.0 |
| 20°-30° | 1319.9 | 10.8 |
| 30°-40° | 1993.6 | 16.4 |
| 40°-50° | 2684.6 | 22.0 |
| 50°-60° | 3225.9 | 26.5 |
| 60°-70° | 1571.1 | 12.9 |
| 70°-80° | 387.1 | 3.2 |
| 80°-90° | 46.5 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 12184.6 | 100.0 |
| 0°-180° | 12184.6 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636737


CATALOG NUMBER: GWS-SA4B-735-U-T3-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1223.9 | 10.0 | | | |
| FM (30°-60°) | 5792.0 | 47.5 | | | |
| FH (60°-80°) | 1294.9 | 10.6 | | | G1/1800 |
| FVH (80°-90°) | 17.5 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1052.0 | 8.6 | B3/2500 | | |
| BM (30°-60°) | 2112.1 | 17.3 | B2/2500 | | |
| BH (60°-80°) | 663.3 | 5.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 29.0 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2

Type II Short





REPORT NUMBER: P636737

CATALOG NUMBER: GWS-SA4B-735-U-T3-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 47° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 |
| 2.5° | 2255.6 | 2254.5 | 2254.5 | 2260.7 | 2260.7 | 2262.7 | 2265.8 | 2268.9 | 2269.9 | 2264.8 | 2253.5 |
| 5° | 2280.1 | 2280.1 | 2280.1 | 2285.2 | 2285.2 | 2287.3 | 2291.4 | 2292.4 | 2291.4 | 2283.2 | 2271.9 |
| 7.5° | 2319.0 | 2319.0 | 2320.0 | 2326.2 | 2331.3 | 2334.4 | 2341.5 | 2340.5 | 2337.4 | 2324.1 | 2309.8 |
| 10° | 2382.5 | 2385.5 | 2388.6 | 2395.8 | 2406.0 | 2413.2 | 2418.3 | 2418.3 | 2414.2 | 2393.7 | 2375.3 |
| 12.5° | 2472.5 | 2476.6 | 2479.7 | 2485.8 | 2494.0 | 2506.3 | 2517.5 | 2517.5 | 2512.4 | 2486.8 | 2459.2 |
| 15° | 2577.9 | 2582.0 | 2581.0 | 2583.0 | 2598.4 | 2615.8 | 2625.0 | 2631.1 | 2633.2 | 2597.4 | 2554.4 |
| 17.5° | 2698.7 | 2702.8 | 2698.7 | 2692.5 | 2694.6 | 2722.2 | 2738.6 | 2761.1 | 2774.4 | 2726.3 | 2657.8 |
| 20° | 2808.2 | 2804.1 | 2804.1 | 2808.2 | 2814.3 | 2848.1 | 2872.7 | 2909.5 | 2925.9 | 2867.5 | 2761.1 |
| 22.5° | 2923.8 | 2933.0 | 2929.0 | 2929.0 | 2953.5 | 3009.8 | 3039.5 | 3087.6 | 3105.0 | 3029.2 | 2886.0 |
| 25° | 3073.2 | 3081.4 | 3079.4 | 3081.4 | 3110.1 | 3189.9 | 3219.6 | 3308.6 | 3326.0 | 3217.5 | 3024.1 |
| 27.5° | 3237.0 | 3250.3 | 3256.4 | 3254.4 | 3300.4 | 3404.8 | 3441.7 | 3565.5 | 3597.2 | 3428.4 | 3171.5 |
| 30° | 3449.9 | 3464.2 | 3469.3 | 3467.3 | 3521.5 | 3663.7 | 3705.7 | 3846.9 | 3892.0 | 3678.1 | 3358.8 |
| 32.5° | 3696.5 | 3710.8 | 3726.2 | 3732.3 | 3801.9 | 3947.2 | 4007.6 | 4154.0 | 4218.4 | 3966.7 | 3584.9 |
| 35° | 3941.1 | 3953.4 | 3983.0 | 4031.1 | 4126.3 | 4274.7 | 4327.9 | 4472.2 | 4534.7 | 4266.5 | 3858.2 |
| 37.5° | 4211.3 | 4219.4 | 4245.0 | 4311.6 | 4448.7 | 4589.9 | 4643.1 | 4781.3 | 4788.5 | 4556.1 | 4167.3 |
| 40° | 4507.0 | 4507.0 | 4501.9 | 4567.4 | 4710.7 | 4852.9 | 4899.0 | 4978.8 | 4936.8 | 4779.2 | 4468.1 |
| 42.5° | 4757.8 | 4753.7 | 4757.8 | 4819.2 | 4925.6 | 5041.2 | 5081.1 | 5065.8 | 5012.6 | 4950.2 | 4740.4 |
| 45° | 4983.9 | 4987.0 | 5023.8 | 5070.9 | 5126.2 | 5194.7 | 5218.3 | 5131.3 | 5083.2 | 5087.3 | 4958.3 |
| 47.5° | 5137.4 | 5140.5 | 5226.5 | 5305.3 | 5339.0 | 5360.5 | 5350.3 | 5229.5 | 5205.0 | 5251.0 | 5126.2 |
| 50° | 5157.9 | 5174.3 | 5322.7 | 5484.4 | 5568.3 | 5571.4 | 5542.7 | 5395.3 | 5388.2 | 5440.4 | 5216.2 |
| 52.5° | 5162.0 | 5178.4 | 5363.6 | 5655.3 | 5873.3 | 5919.3 | 5886.6 | 5733.0 | 5658.3 | 5606.1 | 5326.8 |
| 55° | 5146.6 | 5165.1 | 5369.7 | 5769.9 | 6187.4 | 6371.6 | 6374.7 | 6157.8 | 5919.3 | 5884.5 | 5642.0 |
| 57.5° | 4543.9 | 4551.0 | 4868.3 | 5478.2 | 6175.2 | 6697.1 | 6737.0 | 6442.3 | 6170.0 | 6137.3 | 5894.7 |
| 60° | 3165.4 | 3194.0 | 3538.9 | 4344.3 | 5187.6 | 6107.6 | 6236.6 | 6150.6 | 5968.4 | 5730.0 | 5057.6 |
| 62.5° | 1585.2 | 1609.8 | 1955.7 | 2717.1 | 3577.8 | 4304.4 | 4442.5 | 4533.6 | 4576.6 | 4320.8 | 3443.7 |
| 65° | 682.6 | 701.0 | 915.9 | 1419.4 | 2025.3 | 2376.3 | 2424.4 | 2533.9 | 2802.0 | 2500.1 | 1855.4 |
| 67.5° | 456.4 | 468.7 | 578.2 | 865.8 | 1193.3 | 1215.8 | 1208.6 | 1232.2 | 1290.5 | 1065.4 | 838.2 |
| 70° | 350.0 | 360.2 | 433.9 | 634.5 | 857.6 | 733.8 | 694.9 | 630.4 | 684.6 | 698.0 | 679.5 |
| 72.5° | 253.8 | 262.0 | 317.3 | 432.9 | 537.3 | 468.7 | 462.6 | 495.3 | 569.0 | 589.5 | 578.2 |
| 75° | 163.7 | 167.8 | 201.6 | 237.4 | 277.3 | 300.9 | 313.2 | 372.5 | 447.2 | 462.6 | 449.3 |
| 77.5° | 109.5 | 112.6 | 132.0 | 152.5 | 157.6 | 158.6 | 162.7 | 189.3 | 240.5 | 269.2 | 266.1 |
| 80° | 57.3 | 57.3 | 64.5 | 64.5 | 73.7 | 88.0 | 92.1 | 109.5 | 133.0 | 147.4 | 148.4 |
| 82.5° | 22.5 | 23.5 | 27.6 | 30.7 | 36.8 | 45.0 | 48.1 | 57.3 | 69.6 | 79.8 | 89.0 |
| 85° | 9.2 | 10.2 | 11.3 | 13.3 | 16.4 | 20.5 | 21.5 | 24.6 | 32.7 | 40.9 | 46.1 |
| 87.5° | 0.0 | 0.0 | 1.0 | 1.0 | 2.0 | 3.1 | 3.1 | 4.1 | 5.1 | 9.2 | 12.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636737

CATALOG NUMBER: GWS-SA4B-735-U-T3-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 | 2259.7 |
| 2.5° | 2266.8 | 2253.5 | 2266.8 | 2270.9 | 2282.2 | 2286.3 | 2279.1 | 2278.1 | 2278.1 | 2267.8 | 2264.8 |
| 5° | 2282.2 | 2269.9 | 2283.2 | 2289.3 | 2305.7 | 2315.9 | 2318.0 | 2326.2 | 2331.3 | 2327.2 | 2326.2 |
| 7.5° | 2320.0 | 2304.7 | 2319.0 | 2328.2 | 2349.7 | 2366.1 | 2373.2 | 2391.7 | 2405.0 | 2402.9 | 2401.9 |
| 10° | 2386.6 | 2366.1 | 2382.5 | 2397.8 | 2421.3 | 2440.8 | 2441.8 | 2452.0 | 2465.4 | 2461.3 | 2459.2 |
| 12.5° | 2463.3 | 2443.9 | 2462.3 | 2477.6 | 2505.3 | 2513.5 | 2500.1 | 2496.1 | 2498.1 | 2493.0 | 2488.9 |
| 15° | 2557.5 | 2529.8 | 2546.2 | 2563.6 | 2579.0 | 2569.7 | 2541.1 | 2529.8 | 2528.8 | 2521.6 | 2517.5 |
| 17.5° | 2651.6 | 2616.8 | 2629.1 | 2638.3 | 2631.1 | 2602.5 | 2566.7 | 2547.2 | 2538.0 | 2523.7 | 2519.6 |
| 20° | 2744.7 | 2700.7 | 2698.7 | 2691.5 | 2658.8 | 2606.6 | 2558.5 | 2519.6 | 2496.1 | 2476.6 | 2469.4 |
| 22.5° | 2851.2 | 2789.8 | 2759.1 | 2726.3 | 2654.7 | 2569.7 | 2497.1 | 2441.8 | 2404.0 | 2379.4 | 2371.2 |
| 25° | 2965.8 | 2878.8 | 2815.4 | 2749.9 | 2613.7 | 2490.9 | 2389.6 | 2313.9 | 2268.9 | 2242.3 | 2233.0 |
| 27.5° | 3079.4 | 2959.7 | 2864.5 | 2752.9 | 2531.9 | 2377.3 | 2241.2 | 2138.9 | 2093.9 | 2072.4 | 2065.2 |
| 30° | 3232.9 | 3067.1 | 2922.8 | 2713.0 | 2424.4 | 2219.7 | 2049.9 | 1946.5 | 1916.8 | 1901.5 | 1895.3 |
| 32.5° | 3409.9 | 3203.2 | 3000.6 | 2629.1 | 2287.3 | 2035.5 | 1856.4 | 1784.8 | 1764.3 | 1734.7 | 1733.6 |
| 35° | 3643.3 | 3397.7 | 3074.3 | 2505.3 | 2114.3 | 1838.0 | 1708.0 | 1656.9 | 1620.0 | 1573.0 | 1568.9 |
| 37.5° | 3915.5 | 3640.2 | 3114.2 | 2347.7 | 1912.7 | 1675.3 | 1597.5 | 1540.2 | 1480.8 | 1418.4 | 1410.2 |
| 40° | 4196.9 | 3923.7 | 3117.3 | 2161.4 | 1715.2 | 1567.8 | 1502.3 | 1427.6 | 1353.9 | 1284.4 | 1275.1 |
| 42.5° | 4492.7 | 4187.7 | 3063.0 | 1946.5 | 1553.5 | 1474.7 | 1408.2 | 1314.0 | 1231.1 | 1184.1 | 1178.9 |
| 45° | 4756.7 | 4400.6 | 2940.2 | 1720.3 | 1433.8 | 1396.9 | 1312.0 | 1210.7 | 1166.7 | 1132.9 | 1125.7 |
| 47.5° | 4964.5 | 4541.8 | 2774.4 | 1517.7 | 1336.6 | 1317.1 | 1206.6 | 1154.4 | 1120.6 | 1089.9 | 1082.7 |
| 50° | 5066.8 | 4573.5 | 2558.5 | 1352.9 | 1246.5 | 1223.0 | 1147.2 | 1107.3 | 1084.8 | 1060.2 | 1054.1 |
| 52.5° | 5193.7 | 4609.4 | 2372.2 | 1214.8 | 1158.5 | 1126.8 | 1098.1 | 1066.4 | 1050.0 | 1034.7 | 1029.5 |
| 55° | 5485.4 | 4744.4 | 2274.0 | 1104.2 | 1074.6 | 1060.2 | 1056.1 | 1029.5 | 1024.4 | 1014.2 | 1005.0 |
| 57.5° | 5604.1 | 4657.5 | 2041.7 | 1014.2 | 1008.0 | 1010.1 | 1020.3 | 995.8 | 990.6 | 978.4 | 972.2 |
| 60° | 4507.0 | 3520.5 | 1382.6 | 936.4 | 952.8 | 966.1 | 976.3 | 951.8 | 944.6 | 942.5 | 934.4 |
| 62.5° | 2888.0 | 2165.5 | 965.1 | 863.7 | 888.3 | 904.7 | 910.8 | 887.3 | 882.2 | 898.5 | 899.6 |
| 65° | 1503.4 | 1180.0 | 782.9 | 786.0 | 806.4 | 831.0 | 843.3 | 835.1 | 833.0 | 850.4 | 851.5 |
| 67.5° | 767.5 | 721.5 | 682.6 | 693.9 | 710.2 | 742.0 | 770.6 | 806.4 | 818.7 | 820.8 | 821.8 |
| 70° | 653.9 | 633.5 | 614.0 | 621.2 | 638.6 | 656.0 | 683.6 | 701.0 | 680.6 | 675.4 | 673.4 |
| 72.5° | 556.7 | 541.4 | 532.2 | 540.4 | 549.6 | 546.5 | 538.3 | 546.5 | 549.6 | 550.6 | 551.6 |
| 75° | 432.9 | 421.6 | 414.5 | 415.5 | 415.5 | 404.2 | 388.9 | 379.7 | 369.4 | 361.3 | 361.3 |
| 77.5° | 265.1 | 267.1 | 274.3 | 273.2 | 272.2 | 268.1 | 252.8 | 244.6 | 220.0 | 212.9 | 212.9 |
| 80° | 151.5 | 154.5 | 161.7 | 163.7 | 163.7 | 158.6 | 143.3 | 134.1 | 122.8 | 117.7 | 116.7 |
| 82.5° | 92.1 | 96.2 | 100.3 | 102.3 | 103.4 | 97.2 | 83.9 | 76.8 | 70.6 | 65.5 | 65.5 |
| 85° | 48.1 | 50.1 | 54.2 | 55.3 | 52.2 | 46.1 | 38.9 | 35.8 | 29.7 | 28.7 | 28.7 |
| 87.5° | 13.3 | 14.3 | 16.4 | 13.3 | 12.3 | 9.2 | 5.1 | 4.1 | 2.0 | 1.0 | 1.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 3388 | CRI (Ra): | 73.1 | R9: | -34.6 |
| CIE u': | 0.2371 | R1: | 68.9 | R10: | 57.8 |
| CIE v': | 0.5177 | R2: | 81.1 | R11: | 68.6 |
| Duv: | 0.0032 | R3: | 93.1 | R12: | 53.9 |
| CIE x: | 0.4153 | R4: | 71.6 | R13: | 70.9 |
| CIE y: | 0.4030 | R5: | 69.4 | R14: | 96.2 |
| CIE z: | 0.1817 | R6: | 75.0 | | |
| Peak Wavelength (nm): | 590 | R7: | 79.5 | | |
| Dominant Wavelength (nm): | 580 | R8: | 46.4 | | |
| Purity: | 45.7 | | | | |
| Rf: | 76.9 | | | | |
| Rg: | 94.4 | | | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 CIE $R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)