Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P821427

Luminaire Tested: **TT-D1-830-12VDC-CQ-UPL**

Issue Date: 7/23/2020

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

**Test Information**

| | |
|---|---|
| Test Method: | LM-79-08 |
| Report Number: | P821427 |
| | REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G2-2002-677-2) AND |
| Test Lab: | INNOVATION CENTER |
| Issue Date: | 7/23/2020 |
| Manufacturer: | COOPER LIGHTING SOLUTIONS (FORMERLY EATON) |
| Product Line: | McGRAW-EDISON |
| Catalog Number: | TT-D1-830-12VDC-CQ-UPL |
| Description: | TOPTIER LED PARKING GARAGE LUMINAIRE WITH UPLIGHT |
| | 3000K, 80 CRI LEDS AND CONCENTRATED DISTRIBUTION |
| Light Source: | - |
| Ballast/Driver: | ELECTRONIC DRIVER |

**Summary**

| | |
|---|---|
| Lumens per Lamp: | N/A |
| Luminaire Lumens: | 4244.7 lumens |
| Efficiency: | N/A |
| Efficacy: | 151.6 lumens/watt |
| Luminous Opening: | Vertical Cylinder (Dia: 1.12' x H: 0.1') |
| IES Classification: | Type V - Short |
| BUG Rating: | B1 - U4 - G1 |


| | |
|---|---|
| Input Watts (W): | 28 |
| Input Voltage (V): | NR |
| Input Current (Ain): | NR |
| Voltage Rise (V): | NR |
| Power Factor: | NR |
| Total Harmonic Distortion (THDi): | NR |
| Frequency (hertz): | 60 |
| Stabilization Time: | NR |
| Operation Time: | NR |
| Ambient Temperature (°C): | NR |
| Test Distance: | 25 FT |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821427
CATALOG NUMBER: TT-D1-830-12VDC-CQ-UPL

## Iso-Footcandle Lines of Horizontal Illumination





Based on 15 foot mounting height. Maximum calculated value = 3.8 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821427
CATALOG NUMBER: TT-D1-830-12VDC-CQ-UPL

## Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P821427
CATALOG NUMBER: TT-D1-830-12VDC-CQ-UPL

**FLUX DISTRIBUTION:**

| | | Downward | Upward | Total |
|---|---|---|---|---|
| **House Side** | Lumens | 1706.5 | 415.9 | 2122.4 |
| | % Fixture | 40.2 | 9.8 | 50.0 |
| **Street Side** | Lumens | 1706.5 | 415.9 | 2122.4 |
| | % Fixture | 40.2 | 9.8 | 50.0 |
| **Total** | Lumens | 3413.0 | 831.7 | 4244.7 |
| | % Fixture | 80.4 | 19.6 | 100.0 |

**ZONAL LUMENS:**

| Zone | Lumens | % Fixture |
|---|---|---|
| 0°-10° | 81.1 | 1.9 |
| 10°-20° | 237.5 | 5.6 |
| 20°-30° | 377.8 | 8.9 |
| 30°-40° | 497.0 | 11.7 |
| 40°-50° | 608.2 | 14.3 |
| 50°-60° | 658.8 | 15.5 |
| 60°-70° | 566.8 | 13.4 |
| 70°-80° | 318.6 | 7.5 |
| 80°-90° | 67.2 | 1.6 |
| 90°-100° | 42.6 | 1.0 |
| 100°-110° | 66.0 | 1.6 |
| 110°-120° | 91.9 | 2.2 |
| 120°-130° | 119.0 | 2.8 |
| 130°-140° | 138.7 | 3.3 |
| 140°-150° | 140.5 | 3.3 |
| 150°-160° | 121.9 | 2.9 |
| 160°-170° | 82.2 | 1.9 |
| 170°-180° | 28.9 | 0.7 |
| 0°-90° | 3413.0 | 80.4 |
| 0°-180° | 4244.7 | 100.0 |



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P821427
CATALOG NUMBER: TT-D1-830-12VDC-CQ-UPL

## LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | | Lumens | % Fixture | Zone Rating/Lumen Limit B | U | G |
|---|---|---|---|---|---|---|
| FL | (0°-30°) | 348.2 | 8.2 | | | |
| FM | (30°-60°) | 882.0 | 20.8 | | | |
| FH | (60°-80°) | 442.7 | 10.4 | | | G0/660 |
| FVH | (80°-90°) | 33.6 | 0.8 | | | G1/100 |
| BL | (0°-30°) | 348.2 | 8.2 | B1/500 | | |
| BM | (30°-60°) | 882.0 | 20.8 | B1/1000 | | |
| BH | (60°-80°) | 442.7 | 10.4 | B1/500 | | G0/660 |
| BVH | (80°-90°) | 33.6 | 0.8 | | | G1/100 |
| UL | (90°-100°) | 42.6 | 1.0 | | U2/50 | |
| UH | (100°-180°) | 789.1 | 18.6 | | U4/1000 | |

**BUG Rating: B1-U4-G1**
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821427
CATALOG NUMBER: TT-D1-830-12VDC-CQ-UPL

**CANDELA DISTRIBUTION (FULL):**

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|---|---|---|---|---|---|---|---|---|---|---|---|
| 0° | 852.8 | 852.8 | 852.8 | 852.8 | 852.8 | 852.8 | 852.8 | 852.8 | 852.8 | 852.8 | 852.8 |
| 2.5° | 850.7 | 853.4 | 852.3 | 852.3 | 852.3 | 852.3 | 851.2 | 852.3 | 852.3 | 852.8 | 852.3 |
| 5° | 851.2 | 850.7 | 850.7 | 851.2 | 851.2 | 851.7 | 850.7 | 851.2 | 851.7 | 851.7 | 852.3 |
| 7.5° | 849.6 | 850.1 | 849.0 | 850.1 | 849.0 | 849.6 | 849.6 | 850.1 | 849.6 | 850.1 | 851.2 |
| 10° | 846.3 | 846.9 | 846.3 | 846.3 | 846.3 | 847.4 | 845.2 | 846.9 | 846.3 | 846.9 | 846.3 |
| 12.5° | 840.4 | 843.1 | 842.0 | 843.1 | 843.1 | 843.1 | 841.4 | 842.5 | 843.1 | 843.1 | 843.1 |
| 15° | 837.6 | 838.2 | 836.6 | 838.7 | 839.3 | 839.8 | 837.6 | 838.7 | 838.7 | 839.3 | 839.8 |
| 17.5° | 831.7 | 834.4 | 833.8 | 835.5 | 834.9 | 836.6 | 836.0 | 835.5 | 834.9 | 836.0 | 834.9 |
| 20° | 827.3 | 830.0 | 829.5 | 831.1 | 831.7 | 833.3 | 831.7 | 831.7 | 830.0 | 830.6 | 832.2 |
| 22.5° | 823.0 | 824.1 | 824.1 | 825.7 | 825.7 | 827.3 | 825.7 | 825.2 | 825.2 | 824.6 | 826.2 |
| 25° | 815.9 | 816.5 | 815.9 | 817.6 | 818.7 | 819.7 | 819.2 | 818.1 | 817.6 | 817.6 | 817.0 |
| 27.5° | 804.5 | 806.7 | 807.8 | 810.0 | 810.5 | 812.1 | 810.0 | 810.0 | 808.9 | 807.8 | 808.3 |
| 30° | 795.9 | 797.0 | 797.0 | 801.8 | 801.8 | 804.5 | 801.8 | 801.3 | 800.8 | 800.2 | 799.1 |
| 32.5° | 787.7 | 789.4 | 791.0 | 794.8 | 797.5 | 798.6 | 797.0 | 795.9 | 793.2 | 791.5 | 791.0 |
| 35° | 781.2 | 781.8 | 785.0 | 790.4 | 793.7 | 796.4 | 794.2 | 791.5 | 787.7 | 785.0 | 787.2 |
| 37.5° | 776.3 | 776.9 | 781.8 | 788.8 | 794.8 | 797.0 | 793.7 | 789.4 | 783.4 | 780.1 | 779.1 |
| 40° | 772.0 | 775.3 | 780.7 | 790.4 | 797.0 | 800.2 | 797.5 | 791.5 | 782.8 | 776.3 | 775.8 |
| 42.5° | 769.8 | 771.5 | 779.6 | 791.0 | 800.2 | 804.5 | 800.8 | 792.6 | 781.8 | 774.2 | 773.6 |
| 45° | 764.4 | 769.3 | 776.9 | 791.5 | 801.8 | 807.3 | 801.8 | 791.5 | 778.5 | 769.8 | 768.2 |
| 47.5° | 760.1 | 761.7 | 773.6 | 790.4 | 802.9 | 807.3 | 801.8 | 788.8 | 772.5 | 761.1 | 760.1 |
| 50° | 749.8 | 753.6 | 765.5 | 783.4 | 798.0 | 802.4 | 795.9 | 778.5 | 760.1 | 747.6 | 745.4 |
| 52.5° | 734.0 | 737.3 | 751.4 | 773.6 | 787.7 | 792.6 | 782.8 | 764.4 | 742.7 | 727.5 | 727.5 |
| 55° | 709.6 | 714.5 | 729.1 | 751.9 | 769.8 | 774.2 | 762.8 | 743.2 | 718.8 | 703.6 | 703.1 |
| 57.5° | 680.3 | 683.6 | 699.3 | 724.3 | 741.6 | 748.1 | 736.7 | 715.0 | 690.6 | 672.7 | 671.1 |
| 60° | 642.3 | 646.7 | 663.5 | 687.4 | 705.3 | 710.7 | 700.9 | 679.2 | 654.3 | 635.3 | 635.3 |
| 62.5° | 596.8 | 601.6 | 618.5 | 642.9 | 661.3 | 669.5 | 655.9 | 635.3 | 609.2 | 590.8 | 589.2 |
| 65° | 543.6 | 547.9 | 563.1 | 588.6 | 607.6 | 613.6 | 603.3 | 581.6 | 556.6 | 539.3 | 537.6 |
| 67.5° | 483.9 | 489.9 | 505.1 | 526.8 | 543.1 | 550.7 | 544.1 | 524.6 | 498.6 | 480.7 | 479.0 |
| 70° | 419.4 | 423.7 | 435.6 | 455.7 | 474.2 | 479.6 | 469.8 | 456.8 | 432.4 | 416.1 | 413.9 |
| 72.5° | 350.5 | 354.3 | 364.0 | 383.0 | 396.0 | 403.1 | 397.7 | 380.8 | 361.3 | 347.8 | 349.9 |
| 75° | 281.0 | 280.5 | 291.3 | 304.9 | 316.8 | 321.7 | 317.9 | 307.1 | 289.2 | 277.8 | 277.2 |
| 77.5° | 211.6 | 217.0 | 220.8 | 232.2 | 242.0 | 245.8 | 240.3 | 231.7 | 218.1 | 208.9 | 210.5 |
| 80° | 148.6 | 145.4 | 152.4 | 159.5 | 166.0 | 169.8 | 166.6 | 161.7 | 152.4 | 145.4 | 144.3 |
| 82.5° | 91.1 | 88.4 | 91.7 | 98.2 | 102.5 | 103.6 | 104.2 | 98.2 | 94.4 | 89.0 | 90.1 |
| 85° | 40.1 | 40.7 | 43.4 | 47.7 | 48.3 | 48.8 | 48.8 | 47.7 | 43.4 | 42.9 | 41.8 |
| 87.5° | 9.8 | 9.8 | 10.3 | 11.9 | 11.9 | 12.5 | 12.5 | 10.9 | 10.3 | 9.2 | 9.8 |
| 90° | 30.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 | 29.1 |
| 92.5° | 34.8 | 34.2 | 34.2 | 33.8 | 33.8 | 33.8 | 33.8 | 33.8 | 33.8 | 33.8 | 33.8 |
| 95° | 39.4 | 39.4 | 39.4 | 38.5 | 38.5 | 38.5 | 38.5 | 38.5 | 38.5 | 38.5 | 38.5 |
| 97.5° | 44.6 | 44.6 | 44.6 | 44.2 | 44.2 | 44.2 | 44.2 | 44.2 | 44.2 | 44.2 | 44.2 |
| 100° | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 | 49.8 |
| 102.5° | 55.9 | 55.9 | 55.9 | 55.9 | 55.9 | 55.9 | 55.9 | 56.4 | 55.9 | 55.9 | 55.9 |
| 105° | 62.0 | 62.0 | 62.0 | 62.0 | 62.0 | 62.0 | 62.0 | 62.9 | 62.0 | 62.0 | 62.0 |
| 107.5° | 68.6 | 68.6 | 69.0 | 69.0 | 69.0 | 69.0 | 69.0 | 69.5 | 69.0 | 69.0 | 69.0 |
| 110° | 75.1 | 75.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 | 76.1 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821427
CATALOG NUMBER: TT-D1-830-12VDC-CQ-UPL

**CANDELA DISTRIBUTION (continued):**

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|---|---|---|---|---|---|---|---|---|---|---|---|
| 112.5° | 83.1 | *83.1* | 84.0 | 84.0 | 84.0 | 84.0 | 84.6 | 84.6 | 84.0 | 84.0 | 84.0 |
| 115° | 91.1 | *91.1* | 92.0 | 92.0 | 92.0 | 92.0 | 93.0 | 93.0 | 92.0 | 92.0 | 92.0 |
| 117.5° | 100.5 | *100.5* | 101.0 | 101.4 | 101.4 | 101.4 | 102.4 | 102.4 | 101.4 | 101.4 | 101.4 |
| 120° | 109.9 | *109.9* | 109.9 | 110.8 | 110.8 | 110.8 | 111.8 | 111.8 | 110.8 | 110.8 | 110.8 |
| 122.5° | 120.7 | *120.7* | 121.2 | 121.6 | 121.6 | 121.6 | 122.6 | 122.6 | 122.1 | 122.1 | 121.6 |
| 125° | 131.5 | *131.5* | 132.4 | 132.4 | 132.4 | 132.4 | 133.4 | 133.4 | 133.4 | 133.4 | 132.4 |
| 127.5° | 143.2 | *143.2* | 144.2 | 144.2 | 144.2 | 144.2 | 145.1 | 145.1 | 145.1 | 145.1 | 144.2 |
| 130° | 155.0 | *155.0* | 155.9 | 155.9 | 155.9 | 155.9 | 156.8 | 156.8 | 156.8 | 156.8 | 155.9 |
| 132.5° | 167.2 | *167.2* | 167.6 | 167.6 | 167.6 | 168.1 | 168.6 | 168.6 | 168.6 | 168.6 | 168.1 |
| 135° | 179.4 | *179.4* | 179.4 | 179.4 | 179.4 | 180.3 | 180.3 | 180.3 | 180.3 | 180.3 | 180.3 |
| 137.5° | 191.2 | *190.6* | 191.2 | 190.6 | 191.2 | 191.6 | 191.6 | 191.6 | 191.6 | 191.6 | 191.6 |
| 140° | 202.9 | *201.9* | 202.9 | 201.9 | 202.9 | 202.9 | 202.9 | 202.9 | 202.9 | 202.9 | 202.9 |
| 142.5° | 213.7 | *213.2* | 213.7 | 212.7 | 213.7 | 213.7 | 213.7 | 213.7 | 213.7 | 213.7 | 213.7 |
| 145° | 224.5 | *224.5* | 224.5 | 223.5 | 224.5 | 224.5 | 224.5 | 224.5 | 224.5 | 224.5 | 224.5 |
| 147.5° | 235.8 | *235.3* | 235.8 | 234.8 | 235.8 | 235.8 | 235.8 | 235.8 | 235.8 | 235.8 | 235.8 |
| 150° | 247.0 | *246.1* | 247.0 | 246.1 | 247.0 | 247.0 | 247.0 | 247.0 | 247.0 | 247.0 | 247.0 |
| 152.5° | 256.0 | *255.5* | 256.4 | 255.5 | 256.0 | 256.0 | 256.4 | 256.0 | 256.0 | 256.0 | 256.0 |
| 155° | 264.9 | *264.9* | 265.8 | 264.9 | 264.9 | 264.9 | 265.8 | 264.9 | 264.9 | 264.9 | 264.9 |
| 157.5° | 272.4 | *272.4* | 273.3 | 272.4 | 272.4 | 272.4 | 273.3 | 272.4 | 272.4 | 272.4 | 272.4 |
| 160° | 279.9 | *279.9* | 280.8 | 279.9 | 279.9 | 279.9 | 280.8 | 279.9 | 279.9 | 279.9 | 279.9 |
| 162.5° | 286.0 | *286.0* | 286.9 | 286.0 | 286.0 | 286.0 | 286.9 | 286.0 | 286.0 | 286.0 | 286.0 |
| 165° | 292.1 | *292.1* | 293.0 | 292.1 | 292.1 | 292.1 | 293.0 | 292.1 | 292.1 | 292.1 | 292.1 |
| 167.5° | 295.8 | *295.8* | 296.8 | 295.8 | 295.8 | 295.8 | 296.8 | 295.8 | 295.8 | 295.8 | 295.8 |
| 170° | 299.6 | *299.6* | 300.5 | 299.6 | 299.6 | 299.6 | 300.5 | 299.6 | 299.6 | 299.6 | 299.6 |
| 172.5° | 302.0 | *302.0* | 302.8 | 302.0 | 302.4 | 302.0 | 302.8 | 302.0 | 302.0 | 302.0 | 302.0 |
| 175° | 304.3 | *304.3* | 305.2 | 304.3 | 305.2 | 304.3 | 305.2 | 304.3 | 304.3 | 304.3 | 304.3 |
| 177.5° | 305.2 | *305.2* | 305.7 | 305.2 | 305.7 | 305.2 | 305.7 | 305.2 | 305.2 | 305.2 | 305.2 |
| 180° | 306.2 | *306.2* | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 | 306.2 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

# LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-7

Test Date: 09/27/2024

Luminaire Tested: MEM2-HTN-VA-30-830-U-WQ

Data in this report applies to families of products including MEM2-HTN-VA-30-830-U-WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


## Test Information

| | |
|---|---|
| Test Method: | LM-79-2019 |
| Report Number: | SP1-2407-176-7 |
| Test Lab: | COOPER LIGHTING SOLUTIONS |
| Photometer: | SP1 - 76IN SPHERE |
| Measurement Geometry: | 4π |
| Issue Date: | 09/27/2024 |
| Manufacturer: | COOPER LIGHTING SOLUTIONS |
| Product Line: | Streetworks |
| Catalog Number: | **MEM2-HTN-VA-30-830-U-WQ** |
| Description: | EPIC MODERN VISUAL COMFORT 30W WAVESTREAM WIDE |

## Spectral Parameters

| | | | | | |
|---|---|---|---|---|---|
| CCT (K): | 2984 | CRI (Ra): | 81.8 | | |
| CIE u': | 0.2500 | R1: | 79.4 | R9: | -1.1 |
| CIE v': | 0.5264 | R2: | 89.9 | R10: | 78.4 |
| Duv: | 0.0033 | R3: | 96.6 | R11: | 80.8 |
| CIE x: | 0.4431 | R4: | 80.6 | R12: | 72.8 |
| CIE y: | 0.4147 | R5: | 80.1 | R13: | 81.7 |
| CIE z: | 0.1422 | R6: | 88.9 | R14: | 98.5 |
| Peak Wavelength (nm): | 601 | R7: | 82.6 | R15: | 70.2 |
| Dominant Wavelength (nm): | 581 | R8: | 56.0 | | |
| Purity: | 57.4798 | | | | |

| | |
|---|---|
| Rf: | 85.8 |
| Rg: | 94.1 |




## Test Conditions


| | |
|---|---|
| Stabilization Time: | 29M |
| Operation Time: | 1H 29M |
| Sphere Temperature (°C): | 25.2 |

REPORT NUMBER: SP1-2407-176-7


| Measurement and Test Equipment | | | |
|---|---|---|---|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-176-7

## CIE 1931 Chromaticity Diagram




## CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles





CCT = 2984K
CIE x = 0.4431
CIE y = 0.4147
Duv = 0.0033

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-7

## Photopic Flux vs. Wavelength





## Photopic Lumens: NR

| λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 0 | NR | 490 | 260 | NR | 620 | 905 | NR | 750 | 22 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 312 | NR | 625 | 856 | NR | 755 | 19 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 362 | NR | 630 | 801 | NR | 760 | 17 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 399 | NR | 635 | 742 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 425 | NR | 640 | 677 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 446 | NR | 645 | 613 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 459 | NR | 650 | 549 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 473 | NR | 655 | 485 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 490 | NR | 660 | 425 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 2 | NR | 535 | 511 | NR | 665 | 371 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 535 | NR | 670 | 321 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 11 | NR | 545 | 565 | NR | 675 | 276 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 24 | NR | 550 | 595 | NR | 680 | 238 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 631 | NR | 685 | 203 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 86 | NR | 560 | 672 | NR | 690 | 174 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 144 | NR | 565 | 715 | NR | 695 | 148 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 224 | NR | 570 | 763 | NR | 700 | 124 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 342 | NR | 575 | 814 | NR | 705 | 105 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 446 | NR | 580 | 866 | NR | 710 | 88 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 357 | NR | 585 | 912 | NR | 715 | 73 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 237 | NR | 590 | 954 | NR | 720 | 59 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 202 | NR | 595 | 981 | NR | 725 | 48 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 172 | NR | 600 | 996 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 152 | NR | 605 | 996 | NR | 735 | 34 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 171 | NR | 610 | 980 | NR | 740 | 29 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 210 | NR | 615 | 947 | NR | 745 | 25 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-7

## Scotopic Flux vs. Wavelength





**Scotopic Lumens: NR** **S/P: 1.32**

| λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 0 | NR | 490 | 260 | NR | 620 | 905 | NR | 750 | 22 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 312 | NR | 625 | 856 | NR | 755 | 19 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 362 | NR | 630 | 801 | NR | 760 | 17 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 399 | NR | 635 | 742 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 425 | NR | 640 | 677 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 446 | NR | 645 | 613 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 459 | NR | 650 | 549 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 473 | NR | 655 | 485 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 490 | NR | 660 | 425 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 2 | NR | 535 | 511 | NR | 665 | 371 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 535 | NR | 670 | 321 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 11 | NR | 545 | 565 | NR | 675 | 276 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 24 | NR | 550 | 595 | NR | 680 | 238 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 631 | NR | 685 | 203 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 86 | NR | 560 | 672 | NR | 690 | 174 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 144 | NR | 565 | 715 | NR | 695 | 148 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 224 | NR | 570 | 763 | NR | 700 | 124 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 342 | NR | 575 | 814 | NR | 705 | 105 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 446 | NR | 580 | 866 | NR | 710 | 88 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 357 | NR | 585 | 912 | NR | 715 | 73 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 237 | NR | 590 | 954 | NR | 720 | 59 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 202 | NR | 595 | 981 | NR | 725 | 48 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 172 | NR | 600 | 996 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 152 | NR | 605 | 996 | NR | 735 | 34 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 171 | NR | 610 | 980 | NR | 740 | 29 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 210 | NR | 615 | 947 | NR | 745 | 25 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-7

## Melanopic Flux vs. Wavelength




**Melanopic Lumens: NR** **M/P: 2.51**

| λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) | λ (nm) | Power W^/nm | Lumens (ϕ/nm) |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 360 | 0 | NR | 490 | 260 | NR | 620 | 905 | NR | 750 | 22 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 312 | NR | 625 | 856 | NR | 755 | 19 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 362 | NR | 630 | 801 | NR | 760 | 17 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 399 | NR | 635 | 742 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 425 | NR | 640 | 677 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 446 | NR | 645 | 613 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 459 | NR | 650 | 549 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 473 | NR | 655 | 485 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 1 | NR | 530 | 490 | NR | 660 | 425 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 2 | NR | 535 | 511 | NR | 665 | 371 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 535 | NR | 670 | 321 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 11 | NR | 545 | 565 | NR | 675 | 276 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 24 | NR | 550 | 595 | NR | 680 | 238 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 631 | NR | 685 | 203 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 86 | NR | 560 | 672 | NR | 690 | 174 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 144 | NR | 565 | 715 | NR | 695 | 148 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 224 | NR | 570 | 763 | NR | 700 | 124 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 342 | NR | 575 | 814 | NR | 705 | 105 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 446 | NR | 580 | 866 | NR | 710 | 88 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 357 | NR | 585 | 912 | NR | 715 | 73 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 237 | NR | 590 | 954 | NR | 720 | 59 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 202 | NR | 595 | 981 | NR | 725 | 48 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 172 | NR | 600 | 996 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 152 | NR | 605 | 996 | NR | 735 | 34 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 171 | NR | 610 | 980 | NR | 740 | 29 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 210 | NR | 615 | 947 | NR | 745 | 25 | NR | 875 | 0 | NR | | | |


REPORT NUMBER: SP1-2407-176-7

# TM-30-18


## Summary


$R_f$ = 85.8
$R_g$ = 94.1
CIE $R_a$ = 81.8
$R_9$ = -1.1


## Spectral Power Distribution Comparison





## Color Vector Graphics







REPORT NUMBER: SP1-2407-176-7

# TM-30-18

**Individual Sample Fidelity Index ($R_{f,i}$)**


| | | | |
|---|---|---|---|
| CES01 = 86 | CES26 = 86 | CES51 = 95 | CES76 = 84 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 86 |
| CES03 = 31 | CES28 = 95 | CES53 = 90 | CES78 = 83 |
| CES04 = 70 | CES29 = 89 | CES54 = 91 | CES79 = 90 |
| CES05 = 50 | CES30 = 95 | CES55 = 91 | CES80 = 90 |
| CES06 = 51 | CES31 = 91 | CES56 = 87 | CES81 = 70 |
| CES07 = 42 | CES32 = 85 | CES57 = 86 | CES82 = 96 |
| CES08 = 41 | CES33 = 93 | CES58 = 87 | CES83 = 94 |
| CES09 = 29 | CES34 = 94 | CES59 = 92 | CES84 = 92 |
| CES10 = 76 | CES35 = 97 | CES60 = 94 | CES85 = 77 |
| CES11 = 59 | CES36 = 90 | CES61 = 90 | CES86 = 66 |
| CES12 = 65 | CES37 = 97 | CES62 = 94 | CES87 = 84 |
| CES13 = 43 | CES38 = 97 | CES63 = 88 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 84 | CES89 = 75 |
| CES15 = 72 | CES40 = 95 | CES65 = 80 | CES90 = 88 |
| CES16 = 47 | CES41 = 97 | CES66 = 83 | CES91 = 81 |
| CES17 = 50 | CES42 = 99 | CES67 = 82 | CES92 = 64 |
| CES18 = 56 | CES43 = 93 | CES68 = 84 | CES93 = 79 |
| CES19 = 72 | CES44 = 99 | CES69 = 89 | CES94 = 60 |
| CES20 = 67 | CES45 = 94 | CES70 = 82 | CES95 = 74 |
| CES21 = 87 | CES46 = 90 | CES71 = 81 | CES96 = 83 |
| CES22 = 79 | CES47 = 93 | CES72 = 93 | CES97 = 89 |
| CES23 = 92 | CES48 = 83 | CES73 = 77 | CES98 = 84 |
| CES24 = 91 | CES49 = 92 | CES74 = 92 | CES99 = 75 |
| CES25 = 72 | CES50 = 95 | CES75 = 83 | |





REPORT NUMBER: SP1-2407-176-7

**TM-30-18**

## Color Rendition by Hue-Angle Bin











REPORT NUMBER: SP1-2407-176-7

# TM-30-18

## Measure Comparisons




(END OF REPORT)