

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629828

Luminaire Tested: GWS-SA1C-740-U-5WQ-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P629828  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1C-740-U-5WQ-W  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND  
TYPE V WIDE OPTICS  
Light Source: (16) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4872.9 lumens  
Efficiency: N/A  
Efficacy: 142.9 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G1

Input Watts (W): 34.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P629828

CATALOG NUMBER: GWS-SA1C-740-U-5WQ-W

## Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.8 fc  
 Type V - Short - N/A

REPORT NUMBER: P629828

CATALOG NUMBER: GWS-SA1C-740-U-5WQ-W

## Luminous Intensity Polar Plot



REPORT NUMBER: P629828

CATALOG NUMBER: GWS-SA1C-740-U-5WQ-W


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2436.5   | 0.0    | 2436.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2436.5   | 0.0    | 2436.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 4872.9   | 0.0    | 4872.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 35.9   | 0.7       |
| 10°-20°   | 106.5  | 2.2       |
| 20°-30°   | 191.0  | 3.9       |
| 30°-40°   | 322.7  | 6.6       |
| 40°-50°   | 566.9  | 11.6      |
| 50°-60°   | 1093.6 | 22.4      |
| 60°-70°   | 1586.6 | 32.6      |
| 70°-80°   | 907.8  | 18.6      |
| 80°-90°   | 62.0   | 1.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4872.9 | 100.0     |
| 0°-180°   | 4872.9 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P629828


CATALOG NUMBER: GWS-SA1C-740-U-5WQ-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 166.7  | 3.4       |                         |      |         |
| FM   | (30°-60°)   | 991.6  | 20.3      |                         |      |         |
| FH   | (60°-80°)   | 1247.2 | 25.6      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 31.0   | 0.6       |                         |      | G1/100  |
| BL   | (0°-30°)    | 166.7  | 3.4       | B1/500                  |      |         |
| BM   | (30°-60°)   | 991.6  | 20.3      | B1/1000                 |      |         |
| BH   | (60°-80°)   | 1247.2 | 25.6      | B3/2500                 |      | G1/1800 |
| BVH  | (80°-90°)   | 31.0   | 0.6       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G1**

Type V Short



REPORT NUMBER: P629828

CATALOG NUMBER: GWS-SA1C-740-U-5WQ-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 382.1  | 382.1  | 382.1  | 382.1  | 382.1  | 382.1  | 382.1  | 382.1  | 382.1  | 382.1  | 382.1  |
| 2.5°  | 379.0  | 379.4  | 380.1  | 380.1  | 380.8  | 381.8  | 382.1  | 381.4  | 381.8  | 380.1  | 381.8  |
| 5°    | 378.0  | 378.3  | 378.7  | 378.0  | 378.0  | 378.3  | 378.3  | 377.7  | 378.0  | 376.3  | 378.0  |
| 7.5°  | 375.6  | 375.9  | 375.9  | 374.9  | 373.9  | 374.6  | 374.6  | 373.9  | 374.2  | 372.5  | 374.6  |
| 10°   | 373.5  | 373.5  | 373.2  | 371.1  | 370.1  | 371.1  | 371.5  | 371.8  | 373.2  | 371.8  | 374.2  |
| 12.5° | 374.9  | 374.9  | 373.9  | 371.1  | 369.4  | 370.1  | 370.8  | 371.5  | 373.9  | 373.5  | 376.3  |
| 15°   | 378.7  | 379.0  | 376.3  | 373.2  | 372.1  | 373.2  | 372.5  | 372.1  | 375.2  | 376.3  | 379.4  |
| 17.5° | 381.8  | 381.8  | 378.3  | 375.2  | 375.6  | 377.3  | 375.9  | 374.2  | 377.3  | 379.4  | 382.8  |
| 20°   | 384.5  | 384.2  | 380.4  | 378.3  | 379.7  | 382.1  | 381.1  | 378.7  | 380.8  | 383.2  | 386.3  |
| 22.5° | 391.4  | 391.1  | 387.0  | 385.9  | 387.3  | 389.7  | 388.7  | 386.6  | 389.0  | 392.5  | 396.3  |
| 25°   | 411.1  | 410.4  | 404.2  | 400.7  | 400.1  | 401.8  | 401.4  | 400.7  | 404.5  | 408.7  | 413.1  |
| 27.5° | 437.3  | 436.9  | 432.4  | 429.0  | 424.5  | 423.1  | 424.2  | 427.3  | 432.8  | 435.9  | 439.7  |
| 30°   | 450.4  | 450.4  | 449.7  | 455.2  | 464.8  | 474.1  | 466.9  | 455.2  | 450.4  | 449.0  | 452.8  |
| 32.5° | 467.6  | 469.3  | 466.9  | 473.1  | 489.3  | 503.1  | 489.3  | 470.3  | 466.9  | 466.9  | 471.0  |
| 35°   | 507.2  | 507.9  | 504.1  | 503.1  | 508.2  | 510.0  | 503.4  | 496.5  | 500.3  | 501.0  | 506.2  |
| 37.5° | 538.9  | 538.9  | 537.2  | 540.0  | 550.6  | 557.2  | 546.5  | 534.1  | 535.1  | 535.8  | 542.4  |
| 40°   | 587.8  | 589.2  | 585.1  | 584.7  | 588.9  | 594.7  | 583.4  | 575.4  | 581.0  | 582.7  | 592.7  |
| 42.5° | 648.8  | 648.8  | 642.6  | 640.9  | 643.7  | 649.9  | 639.2  | 634.0  | 641.3  | 642.6  | 648.5  |
| 45°   | 721.5  | 723.3  | 715.0  | 711.9  | 713.3  | 715.3  | 707.8  | 705.3  | 712.2  | 715.3  | 725.7  |
| 47.5° | 810.1  | 811.8  | 804.6  | 804.2  | 802.9  | 804.2  | 797.0  | 795.6  | 801.1  | 798.7  | 809.8  |
| 50°   | 919.3  | 922.4  | 916.2  | 924.8  | 923.8  | 927.9  | 918.0  | 910.7  | 910.7  | 904.2  | 910.4  |
| 52.5° | 1041.7 | 1047.9 | 1051.0 | 1065.4 | 1076.5 | 1086.8 | 1070.3 | 1058.9 | 1042.3 | 1028.9 | 1045.8 |
| 55°   | 1175.0 | 1173.3 | 1192.9 | 1224.6 | 1257.0 | 1281.5 | 1249.1 | 1213.3 | 1186.4 | 1158.5 | 1165.0 |
| 57.5° | 1291.8 | 1297.7 | 1323.5 | 1381.4 | 1445.5 | 1497.2 | 1438.9 | 1370.0 | 1309.0 | 1269.1 | 1274.6 |
| 60°   | 1389.0 | 1393.8 | 1428.3 | 1511.7 | 1623.6 | 1695.0 | 1602.6 | 1488.9 | 1400.4 | 1345.2 | 1351.1 |
| 62.5° | 1478.6 | 1483.1 | 1517.9 | 1609.9 | 1751.1 | 1844.2 | 1724.9 | 1569.5 | 1471.0 | 1415.5 | 1419.0 |
| 65°   | 1530.3 | 1533.0 | 1580.6 | 1677.4 | 1826.3 | 1922.4 | 1788.0 | 1627.8 | 1531.0 | 1474.4 | 1476.5 |
| 67.5° | 1436.2 | 1440.7 | 1540.9 | 1674.6 | 1840.7 | 1923.8 | 1790.8 | 1629.5 | 1520.6 | 1446.9 | 1448.6 |
| 70°   | 1133.0 | 1129.2 | 1248.7 | 1478.6 | 1757.7 | 1865.9 | 1711.2 | 1507.2 | 1339.0 | 1236.0 | 1234.3 |
| 72.5° | 863.9  | 864.9  | 931.4  | 1088.9 | 1433.1 | 1721.8 | 1509.9 | 1213.6 | 1032.3 | 954.1  | 951.0  |
| 75°   | 626.4  | 636.1  | 690.2  | 805.6  | 1002.4 | 1287.0 | 1136.8 | 899.3  | 778.1  | 731.2  | 724.3  |
| 77.5° | 282.2  | 294.6  | 370.1  | 505.8  | 670.2  | 711.2  | 714.0  | 610.6  | 460.7  | 382.8  | 370.8  |
| 80°   | 82.4   | 88.2   | 113.4  | 194.0  | 312.2  | 403.5  | 320.5  | 269.5  | 167.8  | 131.6  | 125.4  |
| 82.5° | 34.8   | 39.6   | 48.6   | 53.8   | 90.6   | 187.1  | 116.5  | 74.1   | 68.9   | 55.8   | 51.0   |
| 85°   | 14.8   | 15.9   | 20.3   | 21.7   | 29.3   | 40.0   | 36.9   | 33.4   | 32.0   | 24.8   | 22.7   |
| 87.5° | 6.2    | 6.2    | 6.2    | 5.5    | 5.2    | 5.5    | 7.6    | 9.6    | 12.7   | 10.0   | 9.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021




### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 |      |       |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R9:  | -29.7 |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R10: | 46.2  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R11: | 68.8  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R12: | 45.6  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R13: | 69.5  |
| CIE z:                    | 0.2385  | R6:       | 68.3 | R14: | 90.7  |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



### Test Conditions

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1


REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |



REPORT NUMBER: SP1-2101-121-2

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 2.7              | 620       | 97577            | 25.4             | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 4.8              | 625       | 90158            | 19.9             | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 8.0              | 630       | 82240            | 14.9             | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 13.3             | 635       | 74361            | 11.2             | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 20.2             | 640       | 66994            | 8.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 28.5             | 645       | 60405            | 5.8              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 37.4             | 650       | 53806            | 3.9              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 44.9             | 655       | 47610            | 2.7              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 52.6             | 660       | 42018            | 1.8              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 58.4             | 665       | 36742            | 1.2              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.0              | 540       | 96845            | 63.1             | 670       | 32105            | 0.7              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.0              | 545       | 100829           | 67.1             | 675       | 27946            | 0.5              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 0.1              | 550       | 105648           | 71.8             | 680       | 24146            | 0.3              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 0.2              | 555       | 110017           | 75.1             | 685       | 21191            | 0.2              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 0.5              | 560       | 114586           | 77.9             | 690       | 18544            | 0.1              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 1.2              | 565       | 118987           | 79.1             | 695       | 16058            | 0.1              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 2.1              | 570       | 122326           | 79.5             | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 2.9              | 575       | 125968           | 78.4             | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 2.7              | 580       | 127613           | 75.8             | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 2.0              | 585       | 129466           | 71.9             | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 1.5              | 590       | 128813           | 66.6             | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 1.3              | 595       | 126387           | 59.9             | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 1.0              | 600       | 123477           | 53.2             | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 1.1              | 605       | 118718           | 46.0             | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 1.2              | 610       | 112091           | 38.5             | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 1.7              | 615       | 105039           | 31.7             | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 10425.8

S/P: 1.47

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 29.3             | 620       | 97577            | 1.2              | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 43.0             | 625       | 90158            | 0.8              | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 60.8             | 630       | 82240            | 0.5              | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 81.1             | 635       | 74361            | 0.3              | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 99.6             | 640       | 66994            | 0.2              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 113.9            | 645       | 60405            | 0.1              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 122.6            | 650       | 53806            | 0.1              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 125.0            | 655       | 47610            | 0.0              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 123.1            | 660       | 42018            | 0.0              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.1              | 535       | 94097            | 117.3            | 665       | 36742            | 0.0              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.2              | 540       | 96845            | 107.0            | 670       | 32105            | 0.0              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.9              | 545       | 100829           | 96.7             | 675       | 27946            | 0.0              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 3.0              | 550       | 105648           | 86.4             | 680       | 24146            | 0.0              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 9.3              | 555       | 110017           | 75.2             | 685       | 21191            | 0.0              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 23.0             | 560       | 114586           | 64.0             | 690       | 18544            | 0.0              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 45.7             | 565       | 118987           | 53.4             | 695       | 16058            | 0.0              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 75.5             | 570       | 122326           | 43.2             | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 93.8             | 575       | 125968           | 34.3             | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 79.3             | 580       | 127613           | 26.3             | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 51.3             | 585       | 129466           | 19.8             | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 35.6             | 590       | 128813           | 14.3             | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 26.0             | 595       | 126387           | 10.1             | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 19.3             | 600       | 123477           | 7.0              | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 16.8             | 605       | 118718           | 4.7              | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 17.7             | 610       | 112091           | 3.0              | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 21.4             | 615       | 105039           | 1.9              | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2

### Melanopic Flux vs. Wavelength




**Melanopic Lumens: 3927.2**

**M/P: 0.55**





| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 15.8             | 620       | 97577            | 0.1              | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 22.0             | 625       | 90158            | 0.0              | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 29.2             | 630       | 82240            | 0.0              | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 36.6             | 635       | 74361            | 0.0              | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 42.2             | 640       | 66994            | 0.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 44.9             | 645       | 60405            | 0.0              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 44.9             | 650       | 53806            | 0.0              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 42.4             | 655       | 47610            | 0.0              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 38.6             | 660       | 42018            | 0.0              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 33.9             | 665       | 36742            | 0.0              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.2              | 540       | 96845            | 28.3             | 670       | 32105            | 0.0              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.6              | 545       | 100829           | 23.4             | 675       | 27946            | 0.0              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 2.1              | 550       | 105648           | 19.0             | 680       | 24146            | 0.0              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 5.9              | 555       | 110017           | 14.8             | 685       | 21191            | 0.0              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 14.3             | 560       | 114586           | 11.3             | 690       | 18544            | 0.0              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 27.3             | 565       | 118987           | 8.4              | 695       | 16058            | 0.0              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 45.1             | 570       | 122326           | 6.0              | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 55.3             | 575       | 125968           | 4.2              | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 47.2             | 580       | 127613           | 2.9              | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 30.8             | 585       | 129466           | 1.9              | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 21.7             | 590       | 128813           | 1.3              | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 16.1             | 595       | 126387           | 0.8              | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 12.0             | 600       | 123477           | 0.5              | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 10.3             | 605       | 118718           | 0.3              | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 10.5             | 610       | 112091           | 0.2              | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 12.1             | 615       | 105039           | 0.1              | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

### Summary

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |







Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)