

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P972420

Luminaire Tested: **GKO-PB2B-730-U-T1**

Issue Date: 02/27/2025



Test Information

Test Method: LM-79-08
Report Number: P972420
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/27/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2B-730-U-T1
Description: GEKKO WALL PACK 6000LM PACKAGE 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6281.6 lumens
Efficiency: N/A
Efficacy: 150.3 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 41.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 8%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P972420

CATALOG NUMBER: GKO-PB2B-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 15.6 fc
 Type I - Short - N/A

REPORT NUMBER: P972420

CATALOG NUMBER: GKO-PB2B-730-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P972420

CATALOG NUMBER: GKO-PB2B-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3140.8	0.0	3140.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3140.8	0.0	3140.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	6281.6	0.0	6281.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	2.4
10°-20°	450.5	7.2
20°-30°	749.1	11.9
30°-40°	995.1	15.8
40°-50°	1121.9	17.9
50°-60°	1153.6	18.4
60°-70°	1090.2	17.4
70°-80°	533.7	8.5
80°-90°	38.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6281.6	100.0
0°-180°	6281.6	100.0

Coefficient of Utilization



REPORT NUMBER: P972420


CATALOG NUMBER: GKO-PB2B-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	674.5	10.7			
FM	(30°-60°)	1635.3	26.0			
FH	(60°-80°)	811.9	12.9			G1/1800
FVH	(80°-90°)	19.1	0.3			G1/100
BL	(0°-30°)	674.5	10.7	B2/1000		
BM	(30°-60°)	1635.3	26.0	B2/2500		
BH	(60°-80°)	811.9	12.9	B2/1000		G2/1000
BVH	(80°-90°)	19.1	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type I Short



REPORT NUMBER: P972420

CATALOG NUMBER: GKO-PB2B-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1558.7	1558.7	1558.7	1558.7	1558.7	1558.7	1558.7	1558.7	1558.7	1558.7	1558.7
2.5°	1559.9	1562.2	1557.6	1557.6	1559.9	1561.0	1561.0	1562.2	1559.9	1559.9	1558.7
5°	1559.9	1561.0	1558.7	1558.7	1561.0	1564.5	1563.4	1565.7	1565.7	1564.5	1564.5
7.5°	1558.7	1561.0	1558.7	1559.9	1563.4	1570.3	1570.3	1570.3	1572.6	1574.9	1574.9
10°	1557.6	1559.9	1561.0	1562.2	1566.8	1577.3	1579.6	1580.7	1584.2	1587.7	1587.7
12.5°	1551.8	1554.1	1557.6	1562.2	1570.3	1584.2	1588.8	1592.3	1598.1	1601.6	1603.9
15°	1543.7	1544.8	1552.9	1562.2	1574.9	1592.3	1601.6	1607.4	1615.5	1620.1	1623.6
17.5°	1532.1	1533.2	1546.0	1559.9	1578.4	1602.7	1617.8	1627.1	1635.2	1642.1	1646.7
20°	1517.0	1520.5	1535.6	1557.6	1584.2	1613.2	1635.2	1651.4	1659.5	1666.4	1673.4
22.5°	1498.5	1502.0	1520.5	1551.8	1590.0	1627.1	1656.0	1676.8	1687.3	1696.5	1704.6
25°	1470.7	1475.3	1497.4	1537.9	1592.3	1642.1	1679.2	1705.8	1715.1	1726.6	1733.6
27.5°	1427.9	1431.3	1458.0	1510.1	1585.4	1658.3	1705.8	1737.1	1747.5	1760.2	1767.2
30°	1360.7	1367.6	1400.1	1464.9	1568.0	1671.1	1737.1	1768.3	1781.1	1793.8	1803.1
32.5°	1273.8	1284.3	1320.2	1403.5	1534.4	1675.7	1770.6	1806.5	1822.8	1836.7	1848.2
35°	1166.1	1176.6	1219.4	1324.8	1481.1	1666.4	1804.2	1850.6	1870.2	1888.8	1902.7
37.5°	1043.4	1052.7	1104.8	1225.2	1404.7	1637.5	1830.9	1899.2	1925.8	1950.1	1968.7
40°	919.5	929.9	986.7	1115.2	1312.1	1581.9	1842.4	1952.5	1986.0	2017.3	2040.5
42.5°	785.2	797.9	861.6	998.2	1204.4	1505.5	1833.2	2004.6	2046.3	2089.1	2123.9
45°	665.9	668.2	737.7	869.7	1086.2	1407.0	1800.8	2054.4	2111.1	2171.3	2221.1
47.5°	551.2	555.9	616.1	746.9	963.5	1295.9	1741.7	2093.7	2184.1	2261.7	2334.6
50°	449.3	455.1	509.5	626.5	840.7	1174.3	1661.8	2116.9	2246.6	2352.0	2453.9
52.5°	365.9	372.9	418.1	521.1	716.8	1046.9	1563.4	2120.4	2303.3	2442.3	2577.8
55°	304.6	309.2	343.9	426.2	597.6	914.9	1451.0	2103.0	2340.4	2523.4	2704.0
57.5°	257.1	261.7	286.0	350.9	489.9	779.4	1314.4	2062.5	2360.1	2594.0	2831.4
60°	223.5	227.0	244.3	290.7	403.0	652.0	1167.3	1990.7	2354.3	2638.0	2936.8
62.5°	199.2	200.3	215.4	247.8	332.4	531.5	1001.7	1883.0	2306.8	2643.8	3008.6
65°	177.2	178.3	187.6	210.8	273.3	427.3	829.2	1734.7	2216.5	2603.3	3019.0
67.5°	143.6	145.9	159.8	177.2	224.7	338.1	653.1	1540.2	2075.2	2497.9	2960.0
70°	114.6	115.8	129.7	149.4	183.0	266.4	501.4	1278.5	1854.0	2326.5	2807.1
72.5°	85.7	88.0	100.7	120.4	149.4	206.1	362.5	967.0	1482.3	1961.7	2444.6
75°	68.3	69.5	74.1	92.6	115.8	156.3	244.3	586.0	892.9	1213.6	1498.5
77.5°	57.9	59.1	59.1	71.8	85.7	105.4	129.7	232.8	377.5	537.3	712.2
80°	47.5	49.8	45.2	53.3	61.4	61.4	60.2	111.2	178.3	252.5	331.2
82.5°	34.7	37.1	34.7	37.1	37.1	33.6	31.3	41.7	56.7	77.6	84.5
85°	24.3	25.5	27.8	25.5	24.3	19.7	15.1	11.6	6.9	8.1	11.6
87.5°	16.2	19.7	23.2	22.0	18.5	15.1	10.4	6.9	3.5	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P972420

CATALOG NUMBER: GKO-PB2B-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1558.7	1558.7	1558.7
2.5°	1559.9	1558.7	1557.6
5°	1565.7	1564.5	1563.4
7.5°	1573.8	1573.8	1573.8
10°	1586.5	1588.8	1588.8
12.5°	1602.7	1605.0	1605.0
15°	1622.4	1623.6	1625.9
17.5°	1646.7	1647.9	1647.9
20°	1675.7	1674.5	1676.8
22.5°	1704.6	1704.6	1704.6
25°	1734.7	1734.7	1734.7
27.5°	1769.5	1769.5	1767.2
30°	1807.7	1807.7	1807.7
32.5°	1854.0	1855.2	1856.3
35°	1913.1	1915.4	1918.9
37.5°	1980.3	1986.0	1989.5
40°	2060.2	2062.5	2068.3
42.5°	2149.3	2156.3	2157.4
45°	2260.5	2272.1	2276.7
47.5°	2391.4	2407.6	2415.7
50°	2537.3	2555.8	2567.4
52.5°	2695.9	2726.0	2739.9
55°	2865.0	2917.1	2932.2
57.5°	3056.1	3126.7	3147.6
60°	3243.7	3343.3	3376.9
62.5°	3403.5	3543.6	3585.3
65°	3515.8	3684.9	3746.3
67.5°	3539.0	3739.3	3812.3
70°	3400.0	3605.0	3689.5
72.5°	2956.5	3141.8	3247.2
75°	1746.3	1879.5	1847.1
77.5°	876.6	914.9	920.6
80°	384.5	407.6	416.9
82.5°	95.0	97.3	110.0
85°	12.7	15.1	13.9
87.5°	4.6	4.6	5.8
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-4

Test Date: 04/10/2025

Luminaire Tested: GKO-PB1E-730-U-T4W

Data in this report applies to families of products including GKO-PB1E-730-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-730-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3072
 CIE u' : 0.2482
 CIE v' : 0.5193
 Duv: -0.0004
 CIE x: 0.4313
 CIE y: 0.4010
 CIE z: 0.1677
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 49.8225
 R_f: 74.7
 R_g: 94.2

CRI (Ra): 71.7
 R1: 68.1
 R2: 82.1
 R3: 93.4
 R4: 67.3
 R5: 67.2
 R6: 74.9
 R7: 77.5
 R8: 43.4
 R9: -33.9
 R10: 58.6
 R11: 62.0
 R12: 48.5
 R13: 70.7
 R14: 96.4
 R15: 60.2



Test Conditions


Stabilization Time: 30M
 Operation Time: 1H 30M
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP2-2501-321-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.24

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.3

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4





TM-30-18

Summary

$R_f = 74.7$
 $R_g = 94.2$
 $CIE R_a = 71.7$
 $R_g = -33.9$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 65	CES51 = 86	CES76 = 58
CES02 = 62	CES27 = 89	CES52 = 85	CES77 = 76
CES03 = 31	CES28 = 84	CES53 = 77	CES78 = 62
CES04 = 71	CES29 = 68	CES54 = 85	CES79 = 85
CES05 = 49	CES30 = 83	CES55 = 84	CES80 = 84
CES06 = 51	CES31 = 71	CES56 = 74	CES81 = 73
CES07 = 41	CES32 = 64	CES57 = 74	CES82 = 93
CES08 = 40	CES33 = 78	CES58 = 75	CES83 = 91
CES09 = 29	CES34 = 75	CES59 = 85	CES84 = 88
CES10 = 76	CES35 = 87	CES60 = 90	CES85 = 76
CES11 = 59	CES36 = 94	CES61 = 81	CES86 = 64
CES12 = 65	CES37 = 84	CES62 = 89	CES87 = 77
CES13 = 43	CES38 = 92	CES63 = 75	CES88 = 80
CES14 = 74	CES39 = 96	CES64 = 65	CES89 = 67
CES15 = 71	CES40 = 92	CES65 = 65	CES90 = 79
CES16 = 47	CES41 = 93	CES66 = 60	CES91 = 80
CES17 = 50	CES42 = 86	CES67 = 58	CES92 = 57
CES18 = 56	CES43 = 78	CES68 = 66	CES93 = 74
CES19 = 73	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 66	CES45 = 85	CES70 = 60	CES95 = 67
CES21 = 87	CES46 = 81	CES71 = 57	CES96 = 77
CES22 = 79	CES47 = 86	CES72 = 85	CES97 = 83
CES23 = 92	CES48 = 75	CES73 = 52	CES98 = 76
CES24 = 91	CES49 = 79	CES74 = 95	CES99 = 64
CES25 = 73	CES50 = 86	CES75 = 60	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)