

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1211826

Luminaire Tested: **GKO-PB1A-735-U-T3**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1211826
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1A-735-U-T3
Description: GEKKO WALL PACK 750LM PACKAGE 70CRI 3500K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source: (10) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 735.2 lumens
Efficiency: N/A
Efficacy: 153.2 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B0 - U0 - G0

Input Watts (W): 4.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 16%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1211826
 CATALOG NUMBER: GKO-PB1A-735-U-T3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 0.6 fc
 Type III - Medium - N/A

REPORT NUMBER: P1211826
CATALOG NUMBER: GKO-PB1A-735-U-T3

Luminous Intensity Polar Plot



REPORT NUMBER: P1211826

CATALOG NUMBER: GKO-PB1A-735-U-T3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	188.2	0.0	188.2
	% Fixture	25.6	0.0	25.6
Street Side	Lumens	546.9	0.0	546.9
	% Fixture	74.4	0.0	74.4
Total	Lumens	735.2	0.0	735.2
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.8	1.6
10°-20°	35.6	4.8
20°-30°	61.3	8.3
30°-40°	95.0	12.9
40°-50°	130.2	17.7
50°-60°	155.3	21.1
60°-70°	155.6	21.2
70°-80°	82.4	11.2
80°-90°	8.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	735.2	100.0
0°-180°	735.2	100.0



REPORT NUMBER: P1211826


CATALOG NUMBER: GKO-PB1A-735-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	64.9	8.8			
FM	(30°-60°)	287.8	39.2			
FH	(60°-80°)	191.0	26.0			G0/660
FVH	(80°-90°)	3.1	0.4			G0/10
BL	(0°-30°)	43.7	5.9	B0/110		
BM	(30°-60°)	92.7	12.6	B0/220		
BH	(60°-80°)	47.0	6.4	B0/110		G0/110
BVH	(80°-90°)	4.8	0.7			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G0

Type III Medium



REPORT NUMBER: P1211826

CATALOG NUMBER: GKO-PB1A-735-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	123.3	123.3	123.3	123.3	123.3	123.3	123.3	123.3	123.3	123.3	123.3
2.5°	128.4	128.4	128.1	128.0	127.9	127.0	126.4	125.7	125.7	124.6	123.6
5°	132.9	133.0	132.4	132.4	131.9	130.7	129.6	128.1	128.1	126.4	124.4
7.5°	136.7	137.1	136.6	136.6	136.0	134.7	132.9	130.9	130.9	128.4	125.6
10°	140.4	140.7	140.4	140.7	139.9	138.7	136.6	133.9	133.7	130.7	126.7
12.5°	143.4	143.7	143.8	144.3	143.6	142.7	140.7	137.3	136.9	133.3	128.1
15°	146.3	146.6	147.0	147.6	147.4	146.7	144.8	141.0	140.7	136.1	130.0
17.5°	148.6	148.7	149.6	150.7	151.0	151.1	149.1	145.1	144.8	139.4	132.0
20°	151.8	152.1	153.0	154.1	155.0	155.5	154.0	149.6	149.3	143.3	134.6
22.5°	159.3	158.8	159.3	159.3	159.7	160.5	159.4	155.0	154.4	147.8	137.7
25°	173.2	172.8	171.7	169.1	166.3	166.1	164.8	160.5	159.8	152.6	140.7
27.5°	192.8	191.8	189.7	184.2	177.4	173.0	171.0	166.5	165.7	157.3	143.6
30°	213.5	214.6	211.1	203.6	191.1	181.7	177.8	172.8	172.1	162.5	147.0
32.5°	237.6	237.7	234.2	223.9	207.6	192.7	186.1	180.0	179.4	168.7	151.6
35°	251.6	252.2	250.6	241.0	222.5	204.8	196.1	188.7	188.2	176.4	157.3
37.5°	266.1	267.4	265.0	254.4	233.8	216.1	207.2	199.1	198.6	185.2	164.4
40°	287.7	287.1	284.6	269.0	244.3	225.5	218.2	211.8	210.8	196.1	171.7
42.5°	303.2	304.7	299.1	281.6	255.9	234.9	229.2	221.9	220.6	202.6	176.0
45°	308.5	307.2	301.1	288.3	271.0	243.5	239.6	234.0	232.8	214.2	184.4
47.5°	309.7	307.4	302.0	292.3	283.8	254.6	252.3	251.0	249.2	228.8	194.5
50°	302.7	301.1	298.5	293.7	292.1	265.0	266.1	270.9	269.3	244.5	205.8
52.5°	286.8	286.1	288.4	291.5	287.4	274.0	282.6	292.1	291.5	261.7	217.9
55°	257.0	257.0	269.9	280.8	283.3	279.8	300.3	316.7	315.9	281.1	229.5
57.5°	229.8	230.2	240.9	265.6	275.8	286.1	319.9	342.4	341.2	303.0	241.6
60°	195.4	195.4	211.6	242.6	265.1	291.0	337.4	367.2	367.9	324.1	253.6
62.5°	154.7	155.1	177.7	214.1	249.7	291.8	351.2	390.6	390.4	343.2	262.9
65°	114.0	114.2	144.8	182.4	226.6	285.8	358.8	408.6	409.4	358.3	268.3
67.5°	74.1	75.5	106.6	148.0	193.9	268.9	354.8	418.1	419.1	365.3	266.6
68°	69.4	69.6	100.9	138.6	185.1	264.6	352.9	418.6	419.4	365.2	264.9
70°	45.0	45.0	72.2	108.2	147.7	237.9	336.8	411.8	412.8	358.9	252.4
72.5°	24.3	24.7	41.2	65.5	100.9	184.1	304.0	376.9	378.6	324.5	220.8
75°	17.0	17.3	24.0	36.7	54.9	119.9	237.6	288.0	287.7	224.2	138.3
77.5°	12.3	12.3	13.7	22.8	28.8	54.8	117.6	138.7	137.1	109.5	69.8
80°	8.0	8.0	8.6	12.0	13.8	16.7	36.0	60.1	61.2	53.4	34.8
82.5°	3.3	3.4	3.7	4.9	5.0	7.0	10.3	17.3	16.7	13.6	9.8
85°	0.4	0.4	0.6	0.7	0.9	1.6	1.4	1.4	1.4	1.7	1.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.3	0.4	0.4	0.6	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1211826

CATALOG NUMBER: GKO-PB1A-735-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	123.3	123.3	123.3	123.3	123.3	123.3	123.3	123.3	123.3	123.3	123.3
2.5°	123.3	123.3	122.4	121.6	120.7	120.0	119.0	118.3	118.4	118.9	118.7
5°	124.0	123.3	121.6	119.7	118.3	117.0	115.2	114.2	114.0	114.3	114.2
7.5°	124.4	123.3	120.7	117.9	115.6	113.9	111.3	110.3	109.9	110.0	110.0
10°	125.3	123.4	119.9	115.9	113.0	110.6	107.9	106.5	106.0	106.0	105.9
12.5°	126.3	123.7	119.0	114.2	110.5	107.6	104.5	102.9	102.5	102.5	102.3
15°	127.3	124.2	118.2	112.3	108.0	104.6	101.6	99.8	99.2	99.2	99.5
17.5°	128.6	124.6	117.3	110.6	105.5	101.6	98.5	96.6	95.9	96.3	96.6
20°	129.9	125.4	116.4	108.7	102.9	98.9	95.8	93.9	93.2	93.9	94.0
22.5°	131.7	126.2	115.4	106.6	100.3	95.9	93.0	91.3	90.9	91.6	92.2
25°	133.6	127.0	114.2	104.3	97.0	92.8	90.5	89.2	89.3	90.3	90.9
27.5°	135.6	127.7	112.9	101.5	93.5	89.5	87.8	87.5	88.0	89.2	89.9
30°	138.0	128.7	111.2	98.2	89.5	85.9	85.2	86.1	87.1	88.2	88.9
32.5°	141.1	130.0	109.5	94.5	85.3	82.1	83.2	85.1	86.2	87.3	88.0
35°	145.6	132.6	108.5	90.8	80.9	78.8	81.3	84.3	85.2	85.9	86.8
37.5°	150.7	136.0	108.0	87.3	76.9	75.9	79.5	83.1	83.3	83.6	84.5
40°	155.7	138.6	106.9	83.6	72.8	72.8	77.2	80.6	80.5	80.1	80.6
42.5°	157.7	138.3	103.6	80.1	69.5	69.6	73.6	76.9	76.1	76.1	76.9
45°	163.4	140.6	101.2	77.2	66.5	65.9	69.1	71.6	73.1	74.9	75.8
47.5°	170.7	143.7	99.3	73.9	63.6	61.8	63.5	67.8	70.2	72.2	72.9
50°	178.2	147.3	97.6	70.5	60.8	57.1	57.9	62.6	64.8	65.8	66.2
52.5°	185.9	150.6	96.3	67.6	57.5	51.5	53.4	57.8	59.4	59.9	60.2
55°	192.8	153.3	95.2	65.2	53.8	47.1	48.5	53.1	54.2	54.8	55.2
57.5°	200.1	156.3	94.5	62.9	49.7	43.2	44.2	48.4	49.9	50.5	50.9
60°	206.5	159.1	93.9	60.5	45.8	39.8	40.4	44.4	46.1	46.4	46.8
62.5°	210.8	161.0	93.0	57.5	42.2	36.5	36.7	40.5	42.4	42.7	43.0
65°	211.9	160.5	90.5	53.5	38.7	33.3	33.3	37.0	39.0	40.0	40.4
67.5°	208.5	157.0	85.1	48.4	35.2	30.3	30.3	33.5	35.7	36.8	37.2
68°	207.4	155.4	83.3	47.1	34.4	29.5	29.5	33.0	35.0	36.0	36.2
70°	197.6	147.7	75.5	42.2	31.7	27.4	27.4	30.4	32.5	32.5	32.4
72.5°	171.7	128.0	62.1	35.4	27.7	24.3	24.7	27.5	28.3	29.0	28.8
75°	106.3	76.6	41.7	28.0	23.3	21.3	22.1	24.7	25.1	26.7	26.3
77.5°	53.2	37.5	22.1	16.3	18.0	18.3	19.8	21.7	23.0	24.7	23.5
80°	26.3	18.3	13.0	10.1	10.6	13.4	17.3	18.7	21.0	22.1	21.1
82.5°	7.3	5.6	5.3	5.6	7.8	10.4	13.6	16.6	19.6	20.5	19.1
85°	1.3	1.0	0.9	2.7	5.4	7.7	11.0	14.7	17.6	16.8	15.8
87.5°	0.4	0.3	0.3	1.7	4.0	6.3	9.4	13.1	15.0	13.6	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-2

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-735-U-T4W

Data in this report applies to families of products including GKO-PB1C


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-735-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3481
 CIE u' : 0.2357
 CIE v' : 0.5131
 Duv: 0.0011
 CIE x: 0.4076
 CIE y: 0.3944
 CIE z: 0.1981
 Peak Wavelength (nm): 589
 Dominant Wavelength (nm): 580
 Purity: 40.6853
 R_f: 73.8
 R_g: 93.8

CRI (Ra): 71.1
 R1: 67.5
 R2: 79.5
 R3: 90.0
 R4: 69.0
 R5: 67.0
 R6: 71.2
 R7: 78.9
 R8: 45.9
 R9: -37.9
 R10: 52.4
 R11: 64.5
 R12: 43.0
 R13: 69.5
 R14: 94.3
 R15: 59.3



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.36

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.56


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2





TM-30-18

Summary

$R_f = 73.8$
 $R_g = 93.8$
 $CIE R_a = 71.1$
 $R_g = -37.9$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 63	CES51 = 88	CES76 = 53
CES02 = 61	CES27 = 88	CES52 = 87	CES77 = 73
CES03 = 31	CES28 = 83	CES53 = 77	CES78 = 56
CES04 = 70	CES29 = 65	CES54 = 84	CES79 = 83
CES05 = 48	CES30 = 79	CES55 = 83	CES80 = 81
CES06 = 51	CES31 = 69	CES56 = 73	CES81 = 76
CES07 = 40	CES32 = 61	CES57 = 72	CES82 = 92
CES08 = 39	CES33 = 75	CES58 = 74	CES83 = 90
CES09 = 29	CES34 = 72	CES59 = 85	CES84 = 87
CES10 = 75	CES35 = 85	CES60 = 90	CES85 = 77
CES11 = 58	CES36 = 93	CES61 = 82	CES86 = 68
CES12 = 64	CES37 = 81	CES62 = 88	CES87 = 77
CES13 = 42	CES38 = 89	CES63 = 73	CES88 = 79
CES14 = 74	CES39 = 96	CES64 = 66	CES89 = 68
CES15 = 71	CES40 = 91	CES65 = 63	CES90 = 79
CES16 = 47	CES41 = 92	CES66 = 60	CES91 = 78
CES17 = 50	CES42 = 83	CES67 = 57	CES92 = 57
CES18 = 56	CES43 = 77	CES68 = 65	CES93 = 74
CES19 = 72	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 65	CES45 = 85	CES70 = 58	CES95 = 66
CES21 = 87	CES46 = 81	CES71 = 53	CES96 = 76
CES22 = 79	CES47 = 84	CES72 = 84	CES97 = 83
CES23 = 92	CES48 = 74	CES73 = 49	CES98 = 75
CES24 = 91	CES49 = 79	CES74 = 96	CES99 = 63
CES25 = 72	CES50 = 87	CES75 = 55	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)