

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1211765

Luminaire Tested: **GKO-PB1B-735-U-T4W**

Issue Date: 11/5/2025

Test Information

Test Method: LM-79-08
Report Number: P1211765
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1B-735-U-T4W
Description: GEKKO WALL PACK 1500LM PACKAGE 70CRI 3500K FIXTURE w/ TYPE IV WIDE DISTRIBUTION OPTIC
Light Source: (10) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1387.8 lumens
Efficiency: N/A
Efficacy: 149.2 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G1


Input Watts (W): 9.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 14%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1211765
 CATALOG NUMBER: GKO-PB1B-735-U-T4W

Iso-Footcandle Lines of Horizontal Illumination

× Max cd


--- 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 1.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P1211765
CATALOG NUMBER: GKO-PB1B-735-U-T4W

Luminous Intensity Polar Plot



REPORT NUMBER: P1211765

CATALOG NUMBER: GKO-PB1B-735-U-T4W

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	373.3	0.0	373.3
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	1014.5	0.0	1014.5
	% Fixture	73.1	0.0	73.1
Total	Lumens	1387.8	0.0	1387.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.8	1.6
10°-20°	66.9	4.8
20°-30°	115.9	8.3
30°-40°	171.9	12.4
40°-50°	233.6	16.8
50°-60°	286.7	20.7
60°-70°	302.2	21.8
70°-80°	166.8	12.0
80°-90°	22.0	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	1387.8	100.0
0°-180°	1387.8	100.0



REPORT NUMBER: P1211765


CATALOG NUMBER: GKO-PB1B-735-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	122.1	8.8			
FM	(30°-60°)	506.9	36.5			
FH	(60°-80°)	377.5	27.2			G0/660
FVH	(80°-90°)	8.0	0.6			G0/10
BL	(0°-30°)	82.5	5.9	B0/110		
BM	(30°-60°)	185.4	13.4	B0/220		
BH	(60°-80°)	91.5	6.6	B0/110		G0/110
BVH	(80°-90°)	13.9	1.0			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type IV Short





REPORT NUMBER: P1211765

CATALOG NUMBER: GKO-PB1B-735-U-T4W

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	227.8	227.8	227.8	227.8	227.8	227.8	227.8	227.8	227.8	227.8	227.8
2.5°	238.3	238.9	238.3	237.8	236.7	236.1	235.6	234.2	232.5	230.0	228.1
5°	248.9	248.9	248.1	247.5	245.8	244.2	243.3	240.0	236.4	232.2	228.3
7.5°	258.6	259.7	258.3	257.0	254.5	251.7	251.1	246.1	241.1	235.6	229.7
10°	270.8	271.7	269.7	268.6	263.9	260.3	259.2	253.1	246.4	239.5	232.0
12.5°	283.3	283.9	282.5	280.0	275.0	270.6	268.9	260.8	252.2	243.9	234.5
15°	294.2	294.7	294.2	291.4	286.7	281.1	278.9	270.0	259.5	248.6	237.5
17.5°	302.2	303.3	303.3	302.0	297.8	292.5	291.1	280.0	267.8	254.2	241.1
20°	309.2	309.7	310.9	310.0	307.8	303.3	301.4	290.8	276.1	260.6	244.7
22.5°	314.7	315.3	317.2	317.0	315.6	313.4	311.4	301.7	285.8	267.0	248.1
25°	324.5	324.2	325.3	324.5	322.8	322.0	320.9	312.2	295.6	274.5	252.5
27.5°	341.4	340.9	339.7	335.6	331.4	330.3	329.5	323.4	307.0	283.1	257.5
30°	366.4	367.0	361.7	352.2	343.9	340.6	339.5	335.3	319.7	293.1	263.1
32.5°	396.1	395.9	387.2	373.9	360.9	354.2	352.0	347.5	332.5	303.1	269.5
35°	417.5	417.0	412.5	400.6	387.0	371.1	367.0	360.0	346.1	314.5	275.8
37.5°	446.4	445.6	437.0	424.5	412.2	389.5	384.7	375.3	359.2	325.6	283.1
40°	479.5	474.2	460.0	447.2	430.6	406.4	402.5	390.3	374.2	339.2	291.4
42.5°	509.5	501.7	483.4	467.2	446.4	426.4	421.4	407.0	388.6	351.7	300.0
45°	554.5	535.6	509.2	499.7	463.6	445.3	441.1	423.4	404.5	365.3	308.6
47.5°	548.9	535.6	527.0	525.9	481.7	465.9	459.7	441.4	421.4	379.7	317.5
50°	559.8	549.2	549.8	536.1	498.1	483.4	478.9	460.3	438.6	393.9	327.0
52.5°	557.5	560.6	558.9	537.8	513.9	501.7	498.4	479.7	455.0	407.5	335.3
55°	575.3	573.6	570.0	549.2	531.4	518.9	516.1	500.0	471.7	419.2	342.5
57.5°	588.4	579.8	579.5	562.0	550.9	540.6	536.1	520.9	487.2	429.5	348.1
60°	580.3	570.0	577.5	563.9	562.8	558.9	556.4	539.2	501.1	437.2	350.3
62.5°	537.3	539.8	562.0	561.1	575.9	579.5	576.7	552.0	510.3	440.0	348.6
65°	480.3	487.8	522.0	551.1	591.1	603.6	600.9	561.1	509.5	433.6	337.5
67°	412.5	420.6	473.9	527.0	589.8	616.4	614.5	567.8	499.5	417.2	317.5
67.5°	397.5	406.7	460.0	515.9	584.8	615.3	613.9	568.4	496.1	409.5	309.7
70°	292.5	303.3	378.6	453.4	544.8	583.1	582.8	547.5	461.7	367.2	268.6
72.5°	182.2	192.0	270.0	353.6	472.0	519.2	517.3	477.0	397.5	299.7	212.0
75°	111.7	117.8	170.0	230.6	342.2	420.3	423.1	372.8	271.1	178.1	119.7
77.5°	68.3	75.0	107.2	142.2	209.2	261.4	262.0	206.7	139.2	96.9	65.6
80°	38.1	39.7	55.8	74.4	107.2	107.8	103.3	91.1	72.2	46.7	33.6
82.5°	15.0	16.1	24.2	30.0	30.6	31.9	29.7	26.9	22.8	15.0	10.6
85°	0.0	0.0	0.0	0.6	1.9	3.9	3.9	2.8	1.1	0.8	0.8
87.5°	0.0	0.0	0.0	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1211765

CATALOG NUMBER: GKO-PB1B-735-U-T4W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	227.8	227.8	227.8	227.8	227.8	227.8	227.8	227.8	227.8	227.8	227.8
2.5°	227.5	227.2	225.3	223.1	221.4	220.0	218.6	217.0	217.0	217.5	217.2
5°	227.0	225.6	222.0	218.1	215.0	212.2	209.7	207.5	207.2	207.5	207.8
7.5°	227.2	224.7	219.2	213.3	208.3	204.7	201.1	199.5	199.2	199.2	199.2
10°	228.3	224.7	217.2	209.2	203.1	197.8	193.9	192.2	192.5	192.8	193.1
12.5°	230.3	225.3	215.8	205.6	197.8	192.5	188.6	187.2	188.3	189.7	190.0
15°	232.2	226.4	214.5	202.5	193.6	187.8	185.0	184.7	186.7	189.2	189.7
17.5°	234.5	227.2	212.8	198.6	189.2	184.5	183.1	183.9	187.0	190.8	191.7
20°	236.7	228.3	210.8	195.0	185.0	181.7	182.5	185.0	188.9	193.6	194.5
22.5°	238.9	229.2	208.3	190.6	180.6	179.5	182.5	186.7	190.6	195.8	197.0
25°	241.4	230.3	205.3	185.0	176.1	177.0	182.2	187.2	191.4	197.0	198.3
27.5°	245.3	232.0	202.2	180.0	171.1	173.9	180.8	187.0	191.4	196.7	198.3
30°	249.2	233.6	199.7	174.7	166.1	169.7	178.1	185.6	190.0	194.7	197.0
32.5°	253.6	235.8	197.5	169.5	160.6	165.0	174.2	182.5	187.8	192.0	194.2
35°	258.3	239.2	195.8	164.7	155.0	158.9	168.3	178.6	183.9	187.8	189.7
37.5°	264.5	242.8	194.7	160.0	149.2	152.5	162.2	173.1	179.2	182.2	184.7
40°	271.1	248.1	194.7	156.1	143.6	145.8	155.8	167.5	173.6	176.1	178.6
42.5°	277.8	253.3	194.5	152.2	137.8	139.5	149.5	161.4	167.2	169.2	171.1
45°	285.6	259.5	194.2	147.8	131.4	133.1	143.3	155.3	160.8	162.5	164.2
47.5°	293.9	265.6	193.1	142.2	125.6	127.0	137.2	148.3	153.9	155.8	157.5
50°	301.4	271.4	190.3	135.8	120.3	121.7	130.8	140.0	145.0	147.2	148.9
52.5°	308.1	275.6	185.8	128.6	114.5	116.1	123.1	131.1	135.0	136.7	137.8
55°	313.4	277.8	178.6	121.7	108.9	109.7	115.3	122.5	125.6	125.8	126.7
57.5°	317.0	277.5	168.9	113.6	103.3	103.6	107.5	113.9	116.1	115.8	116.4
60°	317.8	273.9	157.2	106.1	97.8	96.9	100.8	105.3	106.7	107.8	109.2
62.5°	314.5	265.3	143.9	98.6	92.2	90.8	93.6	97.5	99.7	100.3	100.8
65°	302.2	249.5	127.8	90.8	86.7	84.2	87.2	92.8	96.4	97.5	97.2
67°	280.8	227.2	113.9	85.0	81.1	78.9	83.3	89.2	91.7	93.3	93.3
67.5°	273.9	219.2	109.2	83.1	79.7	77.8	81.9	87.5	90.8	92.8	92.8
70°	232.5	179.7	92.2	73.3	71.7	71.9	76.9	83.1	87.2	89.2	89.2
72.5°	177.2	139.2	75.0	63.9	63.3	65.3	71.7	77.2	82.5	85.8	85.6
75°	100.6	80.3	54.7	52.2	54.4	58.3	66.4	72.5	77.2	80.6	80.3
77.5°	58.6	48.3	37.8	35.8	42.2	51.1	59.4	67.2	70.6	71.7	70.8
80°	29.7	25.3	23.6	24.4	28.3	38.1	51.9	61.1	63.6	64.4	63.6
82.5°	9.4	8.6	9.4	12.5	18.9	30.0	41.9	55.3	58.3	58.3	58.1
85°	0.6	0.6	0.6	5.6	13.1	22.2	32.8	48.3	54.7	54.2	53.3
87.5°	0.3	0.3	0.3	3.6	10.3	18.6	28.9	43.9	52.2	48.3	45.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-2

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-735-U-T4W


Data in this report applies to families of products including GKO-PB1C

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-735-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	3481	CRI (Ra):	71.1		
CIE u':	0.2357	R1:	67.5	R9:	-37.9
CIE v':	0.5131	R2:	79.5	R10:	52.4
Duv:	0.0011	R3:	90.0	R11:	64.5
CIE x:	0.4076	R4:	69.0	R12:	43.0
CIE y:	0.3944	R5:	67.0	R13:	69.5
CIE z:	0.1981	R6:	71.2	R14:	94.3
Peak Wavelength (nm):	589	R7:	78.9	R15:	59.3
Dominant Wavelength (nm):	580	R8:	45.9		
Purity:	40.6853				
Rf:	73.8				
Rg:	93.8				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-595-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.36

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.56


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2





TM-30-18

Summary

$R_f = 73.8$
 $R_g = 93.8$
 $CIE R_a = 71.1$
 $R_g = -37.9$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 63	CES51 = 88	CES76 = 53
CES02 = 61	CES27 = 88	CES52 = 87	CES77 = 73
CES03 = 31	CES28 = 83	CES53 = 77	CES78 = 56
CES04 = 70	CES29 = 65	CES54 = 84	CES79 = 83
CES05 = 48	CES30 = 79	CES55 = 83	CES80 = 81
CES06 = 51	CES31 = 69	CES56 = 73	CES81 = 76
CES07 = 40	CES32 = 61	CES57 = 72	CES82 = 92
CES08 = 39	CES33 = 75	CES58 = 74	CES83 = 90
CES09 = 29	CES34 = 72	CES59 = 85	CES84 = 87
CES10 = 75	CES35 = 85	CES60 = 90	CES85 = 77
CES11 = 58	CES36 = 93	CES61 = 82	CES86 = 68
CES12 = 64	CES37 = 81	CES62 = 88	CES87 = 77
CES13 = 42	CES38 = 89	CES63 = 73	CES88 = 79
CES14 = 74	CES39 = 96	CES64 = 66	CES89 = 68
CES15 = 71	CES40 = 91	CES65 = 63	CES90 = 79
CES16 = 47	CES41 = 92	CES66 = 60	CES91 = 78
CES17 = 50	CES42 = 83	CES67 = 57	CES92 = 57
CES18 = 56	CES43 = 77	CES68 = 65	CES93 = 74
CES19 = 72	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 65	CES45 = 85	CES70 = 58	CES95 = 66
CES21 = 87	CES46 = 81	CES71 = 53	CES96 = 76
CES22 = 79	CES47 = 84	CES72 = 84	CES97 = 83
CES23 = 92	CES48 = 74	CES73 = 49	CES98 = 75
CES24 = 91	CES49 = 79	CES74 = 96	CES99 = 63
CES25 = 72	CES50 = 87	CES75 = 55	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)