

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1211756

Luminaire Tested: **GKO-PB1F-735-U-T1**

Issue Date: 11/5/2025

Test Information

Test Method: LM-79-08
Report Number: P1211756
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1F-735-U-T1
Description: GEKKO WALL PACK 6500LM PACKAGE 70CRI 3500K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (10) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6704.9 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B2 - U0 - G2

Input Watts (W): 54.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 5.7%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1211756
 CATALOG NUMBER: GKO-PB1F-735-U-T1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 7.4 fc
 Type I - Short - N/A

REPORT NUMBER: P1211756
CATALOG NUMBER: GKO-PB1F-735-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1211756

CATALOG NUMBER: GKO-PB1F-735-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3352.5	0.0	3352.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3352.5	0.0	3352.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	6704.9	0.0	6704.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.6	2.4
10°-20°	480.8	7.2
20°-30°	799.5	11.9
30°-40°	1062.2	15.8
40°-50°	1197.5	17.9
50°-60°	1231.3	18.4
60°-70°	1163.6	17.4
70°-80°	569.6	8.5
80°-90°	40.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6704.9	100.0
0°-180°	6704.9	100.0



REPORT NUMBER: P1211756


CATALOG NUMBER: GKO-PB1F-735-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	720.0	10.7			
FM	(30°-60°)	1745.5	26.0			
FH	(60°-80°)	866.6	12.9			G1/1800
FVH	(80°-90°)	20.4	0.3			G1/100
BL	(0°-30°)	720.0	10.7	B2/1000		
BM	(30°-60°)	1745.5	26.0	B2/2500		
BH	(60°-80°)	866.6	12.9	B2/1000		G2/1000
BVH	(80°-90°)	20.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type I Short



REPORT NUMBER: P1211756

CATALOG NUMBER: GKO-PB1F-735-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1663.8	1663.8	1663.8	1663.8	1663.8	1663.8	1663.8	1663.8	1663.8	1663.8	1663.8
2.5°	1665.0	1667.5	1662.5	1662.5	1665.0	1666.2	1666.2	1667.5	1665.0	1665.0	1663.8
5°	1665.0	1666.2	1663.8	1663.8	1666.2	1669.9	1668.7	1671.2	1671.2	1669.9	1669.9
7.5°	1663.8	1666.2	1663.8	1665.0	1668.7	1676.1	1676.1	1676.1	1678.6	1681.1	1681.1
10°	1662.5	1665.0	1666.2	1667.5	1672.4	1683.5	1686.0	1687.2	1691.0	1694.7	1694.7
12.5°	1656.3	1658.8	1662.5	1667.5	1676.1	1691.0	1695.9	1699.6	1705.8	1709.5	1712.0
15°	1647.7	1648.9	1657.6	1667.5	1681.1	1699.6	1709.5	1715.7	1724.3	1729.3	1733.0
17.5°	1635.3	1636.6	1650.2	1665.0	1684.8	1710.7	1726.8	1736.7	1745.3	1752.8	1757.7
20°	1619.3	1623.0	1639.0	1662.5	1691.0	1721.9	1745.3	1762.6	1771.3	1778.7	1786.1
22.5°	1599.5	1603.2	1623.0	1656.3	1697.1	1736.7	1767.6	1789.8	1801.0	1810.9	1819.5
25°	1569.8	1574.8	1598.2	1641.5	1699.6	1752.8	1792.3	1820.7	1830.6	1843.0	1850.4
27.5°	1524.1	1527.8	1556.2	1611.8	1692.2	1770.1	1820.7	1854.1	1865.2	1878.8	1886.3
30°	1452.4	1459.8	1494.4	1563.6	1673.6	1783.7	1854.1	1887.5	1901.1	1914.7	1924.6
32.5°	1359.7	1370.8	1409.1	1498.1	1637.8	1788.6	1890.0	1928.3	1945.6	1960.4	1972.8
35°	1244.7	1255.9	1301.6	1414.1	1580.9	1778.7	1925.8	1975.3	1996.3	2016.0	2030.9
37.5°	1113.7	1123.6	1179.2	1307.8	1499.4	1747.8	1954.2	2027.2	2055.6	2081.6	2101.3
40°	981.4	992.6	1053.1	1190.3	1400.5	1688.5	1966.6	2084.0	2119.9	2153.2	2178.0
42.5°	838.1	851.7	919.6	1065.5	1285.5	1606.9	1956.7	2139.6	2184.1	2229.9	2267.0
45°	710.7	713.2	787.4	928.3	1159.4	1501.8	1922.1	2192.8	2253.4	2317.6	2370.8
47.5°	588.4	593.3	657.6	797.3	1028.4	1383.2	1859.1	2234.8	2331.2	2414.1	2491.9
50°	479.6	485.8	543.9	668.7	897.4	1253.4	1773.8	2259.5	2398.0	2510.5	2619.2
52.5°	390.6	398.0	446.2	556.2	765.1	1117.4	1668.7	2263.3	2458.6	2606.9	2751.5
55°	325.1	330.0	367.1	454.9	637.8	976.5	1548.8	2244.7	2498.1	2693.4	2886.2
57.5°	274.4	279.4	305.3	374.5	522.9	831.9	1402.9	2201.5	2519.1	2768.8	3022.2
60°	238.6	242.3	260.8	310.3	430.2	695.9	1246.0	2124.8	2512.9	2815.8	3134.7
62.5°	212.6	213.8	229.9	264.5	354.8	567.4	1069.2	2009.9	2462.3	2822.0	3211.3
65°	189.1	190.4	200.2	225.0	291.7	456.1	885.0	1851.6	2365.9	2778.7	3222.5
67.5°	153.3	155.7	170.6	189.1	239.8	360.9	697.1	1644.0	2215.0	2666.2	3159.4
70°	122.4	123.6	138.4	159.5	195.3	284.3	535.2	1364.6	1979.0	2483.3	2996.2
72.5°	91.5	93.9	107.5	128.6	159.5	220.0	386.9	1032.1	1582.2	2093.9	2609.4
75°	72.9	74.2	79.1	98.9	123.6	166.9	260.8	625.5	953.0	1295.4	1599.5
77.5°	61.8	63.0	63.0	76.6	91.5	112.5	138.4	248.5	403.0	573.5	760.2
80°	50.7	53.2	48.2	56.9	65.5	65.5	64.3	118.7	190.4	269.5	353.5
82.5°	37.1	39.6	37.1	39.6	39.6	35.8	33.4	44.5	60.6	82.8	90.2
85°	26.0	27.2	29.7	27.2	26.0	21.0	16.1	12.4	7.4	8.7	12.4
87.5°	17.3	21.0	24.7	23.5	19.8	16.1	11.1	7.4	3.7	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1211756
 CATALOG NUMBER: GKO-PB1F-735-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1663.8	1663.8	1663.8
2.5°	1665.0	1663.8	1662.5
5°	1671.2	1669.9	1668.7
7.5°	1679.8	1679.8	1679.8
10°	1693.4	1695.9	1695.9
12.5°	1710.7	1713.2	1713.2
15°	1731.7	1733.0	1735.5
17.5°	1757.7	1758.9	1758.9
20°	1788.6	1787.4	1789.8
22.5°	1819.5	1819.5	1819.5
25°	1851.6	1851.6	1851.6
27.5°	1888.7	1888.7	1886.3
30°	1929.5	1929.5	1929.5
32.5°	1979.0	1980.2	1981.4
35°	2042.0	2044.5	2048.2
37.5°	2113.7	2119.9	2123.6
40°	2199.0	2201.5	2207.6
42.5°	2294.2	2301.6	2302.8
45°	2412.8	2425.2	2430.1
47.5°	2552.5	2569.8	2578.5
50°	2708.2	2728.0	2740.4
52.5°	2877.6	2909.7	2924.6
55°	3058.1	3113.7	3129.7
57.5°	3262.0	3337.4	3359.7
60°	3462.3	3568.6	3604.4
62.5°	3632.8	3782.4	3826.9
65°	3752.7	3933.2	3998.7
67.5°	3777.4	3991.3	4069.2
70°	3629.1	3847.9	3938.1
72.5°	3155.7	3353.5	3466.0
75°	1864.0	2006.2	1971.5
77.5°	935.7	976.5	982.7
80°	410.4	435.1	445.0
82.5°	101.4	103.8	117.4
85°	13.6	16.1	14.8
87.5°	4.9	4.9	6.2
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-2

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-735-U-T4W


Data in this report applies to families of products including GKO-PB1C

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-735-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	3481	CRI (Ra):	71.1		
CIE u':	0.2357	R1:	67.5	R9:	-37.9
CIE v':	0.5131	R2:	79.5	R10:	52.4
Duv:	0.0011	R3:	90.0	R11:	64.5
CIE x:	0.4076	R4:	69.0	R12:	43.0
CIE y:	0.3944	R5:	67.0	R13:	69.5
CIE z:	0.1981	R6:	71.2	R14:	94.3
Peak Wavelength (nm):	589	R7:	78.9	R15:	59.3
Dominant Wavelength (nm):	580	R8:	45.9		
Purity:	40.6853				
Rf:	73.8				
Rg:	93.8				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-595-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.36

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.56


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2



TM-30-18

Summary

$R_f = 73.8$
 $R_g = 93.8$
 $CIE R_a = 71.1$
 $R_g = -37.9$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 63	CES51 = 88	CES76 = 53
CES02 = 61	CES27 = 88	CES52 = 87	CES77 = 73
CES03 = 31	CES28 = 83	CES53 = 77	CES78 = 56
CES04 = 70	CES29 = 65	CES54 = 84	CES79 = 83
CES05 = 48	CES30 = 79	CES55 = 83	CES80 = 81
CES06 = 51	CES31 = 69	CES56 = 73	CES81 = 76
CES07 = 40	CES32 = 61	CES57 = 72	CES82 = 92
CES08 = 39	CES33 = 75	CES58 = 74	CES83 = 90
CES09 = 29	CES34 = 72	CES59 = 85	CES84 = 87
CES10 = 75	CES35 = 85	CES60 = 90	CES85 = 77
CES11 = 58	CES36 = 93	CES61 = 82	CES86 = 68
CES12 = 64	CES37 = 81	CES62 = 88	CES87 = 77
CES13 = 42	CES38 = 89	CES63 = 73	CES88 = 79
CES14 = 74	CES39 = 96	CES64 = 66	CES89 = 68
CES15 = 71	CES40 = 91	CES65 = 63	CES90 = 79
CES16 = 47	CES41 = 92	CES66 = 60	CES91 = 78
CES17 = 50	CES42 = 83	CES67 = 57	CES92 = 57
CES18 = 56	CES43 = 77	CES68 = 65	CES93 = 74
CES19 = 72	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 65	CES45 = 85	CES70 = 58	CES95 = 66
CES21 = 87	CES46 = 81	CES71 = 53	CES96 = 76
CES22 = 79	CES47 = 84	CES72 = 84	CES97 = 83
CES23 = 92	CES48 = 74	CES73 = 49	CES98 = 75
CES24 = 91	CES49 = 79	CES74 = 96	CES99 = 63
CES25 = 72	CES50 = 87	CES75 = 55	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)