Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P821130

Luminaire Tested: **TT-D2-830-24VDC-CQ-UPL**

Issue Date: 7/23/2020

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P821130
	REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G2-2002-677-2) AND
Test Lab:	INNOVATION CENTER
Issue Date:	7/23/2020
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	TT-D2-830-24VDC-CQ-UPL
Description:	TOPTIER LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
	3000K, 80 CRI LEDS AND CONCENTRATED DISTRIBUTION
Light Source:	-
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5475.7 lumens
Efficiency:	N/A
Efficacy:	144.1 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.12' x H: 0.1')
IES Classification:	Type V - Short
BUG Rating:	B2 - U4 - G1


Input Watts (W):	38
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	25 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821130
CATALOG NUMBER: TT-D2-830-24VDC-CQ-UPL

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 5.2 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821130
CATALOG NUMBER: TT-D2-830-24VDC-CQ-UPL

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P821130
CATALOG NUMBER: TT-D2-830-24VDC-CQ-UPL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2322.0	415.9	2737.9
	% Fixture	42.4	7.6	50.0
Street Side	Lumens	2322.0	415.9	2737.9
	% Fixture	42.4	7.6	50.0
Total	Lumens	4644.0	831.7	5475.7
	% Fixture	84.8	15.2	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	2.0
10°-20°	323.3	5.9
20°-30°	514.2	9.4
30°-40°	676.4	12.4
40°-50°	827.9	15.1
50°-60°	896.7	16.4
60°-70°	771.4	14.1
70°-80°	433.7	7.9
80°-90°	90.0	1.6
90°-100°	42.6	0.8
100°-110°	66.0	1.2
110°-120°	91.9	1.7
120°-130°	119.0	2.2
130°-140°	138.7	2.5
140°-150°	140.5	2.6
150°-160°	121.9	2.2
160°-170°	82.2	1.5
170°-180°	28.9	0.5
0°-90°	4644.0	84.8
0°-180°	5475.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P821130
CATALOG NUMBER: TT-D2-830-24VDC-CQ-UPL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	474.0	8.7			
FM	(30°-60°)	1200.5	21.9			
FH	(60°-80°)	602.6	11.0			G0/660
FVH	(80°-90°)	45.0	0.8			G1/100
BL	(0°-30°)	474.0	8.7	B1/500		
BM	(30°-60°)	1200.5	21.9	B2/2500		
BH	(60°-80°)	602.6	11.0	B2/1000		G0/660
BVH	(80°-90°)	45.0	0.8			G1/100
UL	(90°-100°)	42.6	0.8		U2/50	
UH	(100°-180°)	789.1	14.4		U4/1000	

BUG Rating: B2-U4-G1
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821130
CATALOG NUMBER: TT-D2-830-24VDC-CQ-UPL

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1160.8	*1160.8*	1160.8	1160.8	1160.8	1160.8	1160.8	1160.8	1160.8	1160.8	1160.8
2.5°	*1157.8*	*1161.5*	*1160.1*	*1160.1*	*1160.1*	*1160.1*	*1158.6*	*1160.1*	*1160.1*	*1160.8*	*1160.1*
5°	1158.6	*1157.8*	1157.8	1158.6	1158.6	1159.3	1157.8	1158.6	1159.3	1159.3	1160.1
7.5°	1156.4	*1157.1*	1155.6	1157.1	1155.6	1156.4	1156.4	1157.1	1156.4	1157.1	1158.6
10°	1151.9	*1152.7*	1151.9	1151.9	1151.9	1153.4	1150.5	1152.7	1151.9	1152.7	1151.9
12.5°	1143.8	*1147.5*	1146.0	1147.5	1147.5	1147.5	1145.3	1146.8	1147.5	1147.5	1147.5
15°	1140.1	*1140.9*	1138.6	1141.6	1142.3	1143.1	1140.1	1141.6	1141.6	1142.3	1143.1
17.5°	1132.0	*1135.7*	1134.9	1137.2	1136.4	1138.6	1137.9	1137.2	1136.4	1137.9	1136.4
20°	1126.1	*1129.8*	1129.0	1131.3	1132.0	1134.2	1132.0	1132.0	1129.8	1130.5	1132.7
22.5°	1120.2	*1121.7*	1121.7	1123.9	1123.9	1126.1	1123.9	1123.1	1123.1	1122.4	1124.6
25°	1110.6	*1111.3*	1110.6	1112.8	1114.3	1115.7	1115.0	1113.5	1112.8	1112.8	1112.1
27.5°	1095.1	*1098.0*	1099.5	1102.5	1103.2	1105.4	1102.5	1102.5	1101.0	1099.5	1100.2
30°	1083.3	*1084.7*	1084.7	1091.4	1091.4	1095.1	1091.4	1090.6	1089.9	1089.2	1087.7
32.5°	1072.2	*1074.4*	1076.6	1081.8	1085.5	1087.0	1084.7	1083.3	1079.6	1077.4	1076.6
35°	1063.3	*1064.1*	1068.5	1075.9	1080.3	1084.0	1081.0	1077.4	1072.2	1068.5	1071.4
37.5°	1056.7	*1057.4*	1064.1	1073.7	1081.8	1084.7	1080.3	1074.4	1066.3	1061.8	1060.4
40°	1050.8	*1055.2*	1062.6	1075.9	1084.7	1089.2	1085.5	1077.4	1065.5	1056.7	1055.9
42.5°	1047.8	*1050.0*	1061.1	1076.6	1089.2	1095.1	1089.9	1078.8	1064.1	1053.7	1053.0
45°	1040.4	*1047.1*	1057.4	1077.4	1091.4	1098.8	1091.4	1077.4	1059.6	1047.8	1045.6
47.5°	1034.5	*1036.7*	1053.0	1075.9	1092.9	1098.8	1091.4	1073.7	1051.5	1036.0	1034.5
50°	1020.5	*1025.7*	1041.9	1066.3	1086.2	1092.1	1083.3	1059.6	1034.5	1017.5	1014.6
52.5°	999.1	*1003.5*	1022.7	1053.0	1072.2	1078.8	1065.5	1040.4	1010.9	990.2	990.2
55°	965.8	*972.5*	992.4	1023.4	1047.8	1053.7	1038.2	1011.6	978.4	957.7	957.0
57.5°	926.0	*930.4*	951.8	985.8	1009.4	1018.3	1002.8	973.2	940.0	915.6	913.4
60°	874.3	*880.2*	903.1	935.6	959.9	967.3	954.0	924.5	890.5	864.7	864.7
62.5°	812.3	*818.9*	841.8	875.0	900.1	911.2	892.7	864.7	829.2	804.1	801.9
65°	739.9	*745.8*	766.5	801.2	827.0	835.2	821.1	791.6	757.6	734.0	731.8
67.5°	658.7	*666.8*	687.5	717.0	739.2	749.5	740.6	714.0	678.6	654.2	652.0
70°	570.8	*576.7*	592.9	620.3	645.4	652.8	639.5	621.7	588.5	566.4	563.4
72.5°	477.0	*482.2*	495.5	521.3	539.0	548.6	541.3	518.4	491.8	473.3	476.3
75°	382.5	*381.8*	396.5	415.0	431.2	437.9	432.7	417.9	393.6	378.1	377.3
77.5°	288.0	*295.4*	300.5	316.0	329.3	334.5	327.1	315.3	296.8	284.3	286.5
80°	202.3	*197.9*	207.5	217.1	226.0	231.1	226.7	220.0	207.5	197.9	196.4
82.5°	124.1	*120.4*	124.8	133.7	139.6	141.0	141.8	133.7	128.5	121.1	122.6
85°	54.6	*55.4*	59.1	65.0	65.7	66.5	66.5	65.0	59.1	58.3	56.9
87.5°	13.3	*13.3*	14.0	16.2	16.2	17.0	17.0	14.8	14.0	12.6	13.3
90°	30.1	*29.1*	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
92.5°	34.8	*34.2*	34.2	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.8
95°	39.4	*39.4*	39.4	38.5	38.5	38.5	38.5	38.5	38.5	38.5	38.5
97.5°	44.6	*44.6*	44.6	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2
100°	49.8	*49.8*	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8
102.5°	55.9	*55.9*	55.9	55.9	55.9	55.9	55.9	56.4	55.9	55.9	55.9
105°	62.0	*62.0*	62.0	62.0	62.0	62.0	62.0	62.9	62.0	62.0	62.0
107.5°	68.6	*68.6*	69.0	69.0	69.0	69.0	69.0	69.5	69.0	69.0	69.0
110°	75.1	*75.1*	76.1	76.1	76.1	76.1	76.1	76.1	76.1	76.1	76.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821130
CATALOG NUMBER: TT-D2-830-24VDC-CQ-UPL

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	83.1	*83.1*	84.0	84.0	84.0	84.0	84.6	84.6	84.0	84.0	84.0
115°	91.1	*91.1*	92.0	92.0	92.0	92.0	93.0	93.0	92.0	92.0	92.0
117.5°	100.5	*100.5*	101.0	101.4	101.4	101.4	102.4	102.4	101.4	101.4	101.4
120°	109.9	*109.9*	109.9	110.8	110.8	110.8	111.8	111.8	110.8	110.8	110.8
122.5°	120.7	*120.7*	121.2	121.6	121.6	121.6	122.6	122.6	122.1	122.1	121.6
125°	131.5	*131.5*	132.4	132.4	132.4	132.4	133.4	133.4	133.4	133.4	132.4
127.5°	143.2	*143.2*	144.2	144.2	144.2	144.2	145.1	145.1	145.1	145.1	144.2
130°	155.0	*155.0*	155.9	155.9	155.9	155.9	156.8	156.8	156.8	156.8	155.9
132.5°	167.2	*167.2*	167.6	167.6	167.6	168.1	168.6	168.6	168.6	168.6	168.1
135°	179.4	*179.4*	179.4	179.4	179.4	180.3	180.3	180.3	180.3	180.3	180.3
137.5°	191.2	*190.6*	191.2	190.6	191.2	191.6	191.6	191.6	191.6	191.6	191.6
140°	202.9	*201.9*	202.9	201.9	202.9	202.9	202.9	202.9	202.9	202.9	202.9
142.5°	213.7	*213.2*	213.7	212.7	213.7	213.7	213.7	213.7	213.7	213.7	213.7
145°	224.5	*224.5*	224.5	223.5	224.5	224.5	224.5	224.5	224.5	224.5	224.5
147.5°	235.8	*235.3*	235.8	234.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8
150°	247.0	*246.1*	247.0	246.1	247.0	247.0	247.0	247.0	247.0	247.0	247.0
152.5°	256.0	*255.5*	256.4	255.5	256.0	256.0	256.4	256.0	256.0	256.0	256.0
155°	264.9	*264.9*	265.8	264.9	264.9	264.9	265.8	264.9	264.9	264.9	264.9
157.5°	272.4	*272.4*	273.3	272.4	272.4	272.4	273.3	272.4	272.4	272.4	272.4
160°	279.9	*279.9*	280.8	279.9	279.9	279.9	280.8	279.9	279.9	279.9	279.9
162.5°	286.0	*286.0*	286.9	286.0	286.0	286.0	286.9	286.0	286.0	286.0	286.0
165°	292.1	*292.1*	293.0	292.1	292.1	292.1	293.0	292.1	292.1	292.1	292.1
167.5°	295.8	*295.8*	296.8	295.8	295.8	295.8	296.8	295.8	295.8	295.8	295.8
170°	299.6	*299.6*	300.5	299.6	299.6	299.6	300.5	299.6	299.6	299.6	299.6
172.5°	302.0	*302.0*	302.8	302.0	302.4	302.0	302.8	302.0	302.0	302.0	302.0
175°	304.3	*304.3*	305.2	304.3	305.2	304.3	305.2	304.3	304.3	304.3	304.3
177.5°	305.2	*305.2*	305.7	305.2	305.7	305.2	305.7	305.2	305.2	305.2	305.2
180°	306.2	*306.2*	306.2	306.2	306.2	306.2	306.2	306.2	306.2	306.2	306.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-7

Test Date: 09/27/2024

Luminaire Tested: MEM2-HTN-VA-30-830-U-WQ

Data in this report applies to families of products including MEM2-HTN-VA-30-830-U-WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-176-7
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	09/27/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**MEM2-HTN-VA-30-830-U-WQ**
Description:	EPIC MODERN VISUAL COMFORT 30W WAVESTREAM WIDE

Spectral Parameters

CCT (K):	2984	CRI (Ra):	81.8		
CIE u':	0.2500	R1:	79.4	R9:	-1.1
CIE v':	0.5264	R2:	89.9	R10:	78.4
Duv:	0.0033	R3:	96.6	R11:	80.8
CIE x:	0.4431	R4:	80.6	R12:	72.8
CIE y:	0.4147	R5:	80.1	R13:	81.7
CIE z:	0.1422	R6:	88.9	R14:	98.5
Peak Wavelength (nm):	601	R7:	82.6	R15:	70.2
Dominant Wavelength (nm):	581	R8:	56.0		
Purity:	57.4798				

Rf:	85.8
Rg:	94.1



Test Conditions


Stabilization Time:	29M
Operation Time:	1H 29M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-176-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-176-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2984K
CIE x = 0.4431
CIE y = 0.4147
Duv = 0.0033

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			

REPORT NUMBER: SP1-2407-176-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.32**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			

REPORT NUMBER: SP1-2407-176-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.51**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	260	NR	620	905	NR	750	22	NR	880	0	NR
365	0	NR	495	312	NR	625	856	NR	755	19	NR	885	0	NR
370	0	NR	500	362	NR	630	801	NR	760	17	NR	890	0	NR
375	0	NR	505	399	NR	635	742	NR	765	14	NR	895	0	NR
380	0	NR	510	425	NR	640	677	NR	770	12	NR	900	0	NR
385	0	NR	515	446	NR	645	613	NR	775	10	NR	905	0	NR
390	0	NR	520	459	NR	650	549	NR	780	9	NR	910	0	NR
395	0	NR	525	473	NR	655	485	NR	785	7	NR	915	0	NR
400	1	NR	530	490	NR	660	425	NR	790	6	NR	920	0	NR
405	2	NR	535	511	NR	665	371	NR	795	5	NR	925	0	NR
410	5	NR	540	535	NR	670	321	NR	800	4	NR	930	0	NR
415	11	NR	545	565	NR	675	276	NR	805	4	NR	935	0	NR
420	24	NR	550	595	NR	680	238	NR	810	3	NR	940	0	NR
425	47	NR	555	631	NR	685	203	NR	815	3	NR	945	0	NR
430	86	NR	560	672	NR	690	174	NR	820	2	NR	950	0	NR
435	144	NR	565	715	NR	695	148	NR	825	2	NR	955	0	NR
440	224	NR	570	763	NR	700	124	NR	830	2	NR	960	0	NR
445	342	NR	575	814	NR	705	105	NR	835	2	NR	965	0	NR
450	446	NR	580	866	NR	710	88	NR	840	1	NR	970	0	NR
455	357	NR	585	912	NR	715	73	NR	845	1	NR	975	0	NR
460	237	NR	590	954	NR	720	59	NR	850	1	NR	980	0	NR
465	202	NR	595	981	NR	725	48	NR	855	1	NR	985	0	NR
470	172	NR	600	996	NR	730	40	NR	860	1	NR	990	0	NR
475	152	NR	605	996	NR	735	34	NR	865	1	NR	995	0	NR
480	171	NR	610	980	NR	740	29	NR	870	0	NR	1000	0	NR
485	210	NR	615	947	NR	745	25	NR	875	0	NR			


REPORT NUMBER: SP1-2407-176-7

TM-30-18


Summary


R_f = 85.8
R_g = 94.1
CIE R_a = 81.8
R_9 = -1.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-176-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 86	CES51 = 95	CES76 = 84
CES02 = 63	CES27 = 95	CES52 = 94	CES77 = 86
CES03 = 31	CES28 = 95	CES53 = 90	CES78 = 83
CES04 = 70	CES29 = 89	CES54 = 91	CES79 = 90
CES05 = 50	CES30 = 95	CES55 = 91	CES80 = 90
CES06 = 51	CES31 = 91	CES56 = 87	CES81 = 70
CES07 = 42	CES32 = 85	CES57 = 86	CES82 = 96
CES08 = 41	CES33 = 93	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 92	CES84 = 92
CES10 = 76	CES35 = 97	CES60 = 94	CES85 = 77
CES11 = 59	CES36 = 90	CES61 = 90	CES86 = 66
CES12 = 65	CES37 = 97	CES62 = 94	CES87 = 84
CES13 = 43	CES38 = 97	CES63 = 88	CES88 = 86
CES14 = 74	CES39 = 98	CES64 = 84	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 80	CES90 = 88
CES16 = 47	CES41 = 97	CES66 = 83	CES91 = 81
CES17 = 50	CES42 = 99	CES67 = 82	CES92 = 64
CES18 = 56	CES43 = 93	CES68 = 84	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 89	CES94 = 60
CES20 = 67	CES45 = 94	CES70 = 82	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 81	CES96 = 83
CES22 = 79	CES47 = 93	CES72 = 93	CES97 = 89
CES23 = 92	CES48 = 83	CES73 = 77	CES98 = 84
CES24 = 91	CES49 = 92	CES74 = 92	CES99 = 75
CES25 = 72	CES50 = 95	CES75 = 83	





REPORT NUMBER: SP1-2407-176-7

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-176-7

TM-30-18

Measure Comparisons





(END OF REPORT)