

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1212007

Luminaire Tested: **GKO-PB2E-735-U-T1**

Issue Date: 11/5/2025

Test Information

Test Method: LM-79-08
Report Number: P1212007
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2E-735-U-T1
Description: GEKKO WALL PACK 12000LM PACKAGE 70CRI 3500K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12891.1 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B3 - U0 - G3

Input Watts (W): 104.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 6%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT


REPORT NUMBER: P1212007

CATALOG NUMBER: GKO-PB2E-735-U-T1

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 14.2 fc

Type I - Short - N/A

REPORT NUMBER: P1212007
CATALOG NUMBER: GKO-PB2E-735-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1212007

CATALOG NUMBER: GKO-PB2E-735-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6445.5	0.0	6445.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6445.5	0.0	6445.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	12891.1	0.0	12891.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.8	2.4
10°-20°	924.5	7.2
20°-30°	1537.2	11.9
30°-40°	2042.1	15.8
40°-50°	2302.3	17.9
50°-60°	2367.4	18.4
60°-70°	2237.2	17.4
70°-80°	1095.2	8.5
80°-90°	78.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12891.1	100.0
0°-180°	12891.1	100.0



REPORT NUMBER: P1212007


CATALOG NUMBER: GKO-PB2E-735-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1384.2	10.7			
FM	(30°-60°)	3355.9	26.0			
FH	(60°-80°)	1666.2	12.9			G1/1800
FVH	(80°-90°)	39.2	0.3			G1/100
BL	(0°-30°)	1384.2	10.7	B3/2500		
BM	(30°-60°)	3355.9	26.0	B3/5000		
BH	(60°-80°)	1666.2	12.9	B3/2500		G3/2500
BVH	(80°-90°)	39.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type I Short



REPORT NUMBER: P1212007

CATALOG NUMBER: GKO-PB2E-735-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3198.8	3198.8	3198.8	3198.8	3198.8	3198.8	3198.8	3198.8	3198.8	3198.8	3198.8
2.5°	3201.2	3205.9	3196.4	3196.4	3201.2	3203.6	3203.6	3205.9	3201.2	3201.2	3198.8
5°	3201.2	3203.6	3198.8	3198.8	3203.6	3210.7	3208.3	3213.1	3213.1	3210.7	3210.7
7.5°	3198.8	3203.6	3198.8	3201.2	3208.3	3222.6	3222.6	3222.6	3227.3	3232.1	3232.1
10°	3196.4	3201.2	3203.6	3205.9	3215.4	3236.8	3241.6	3244.0	3251.1	3258.2	3258.2
12.5°	3184.5	3189.3	3196.4	3205.9	3222.6	3251.1	3260.6	3267.7	3279.6	3286.7	3291.5
15°	3167.9	3170.3	3186.9	3205.9	3232.1	3267.7	3286.7	3298.6	3315.3	3324.8	3331.9
17.5°	3144.1	3146.5	3172.7	3201.2	3239.2	3289.1	3320.0	3339.0	3355.7	3369.9	3379.4
20°	3113.2	3120.4	3151.3	3196.4	3251.1	3310.5	3355.7	3388.9	3405.6	3419.8	3434.1
22.5°	3075.2	3082.4	3120.4	3184.5	3263.0	3339.0	3398.4	3441.2	3462.6	3481.6	3498.2
25°	3018.2	3027.7	3072.8	3156.0	3267.7	3369.9	3446.0	3500.6	3519.6	3543.4	3557.7
27.5°	2930.3	2937.4	2992.0	3099.0	3253.5	3403.2	3500.6	3564.8	3586.2	3612.3	3626.6
30°	2792.4	2806.7	2873.2	3006.3	3217.8	3429.3	3564.8	3629.0	3655.1	3681.2	3700.2
32.5°	2614.2	2635.6	2709.2	2880.3	3148.9	3438.8	3633.7	3707.4	3740.6	3769.2	3792.9
35°	2393.2	2414.5	2502.5	2718.7	3039.6	3419.8	3702.6	3797.7	3838.1	3876.1	3904.6
37.5°	2141.2	2160.3	2267.2	2514.4	2882.7	3360.4	3757.3	3897.5	3952.2	4002.1	4040.1
40°	1887.0	1908.3	2024.8	2288.6	2692.6	3246.3	3781.1	4006.8	4075.7	4139.9	4187.4
42.5°	1611.3	1637.4	1768.1	2048.6	2471.6	3089.5	3762.0	4113.8	4199.3	4287.3	4358.5
45°	1366.5	1371.3	1513.8	1784.8	2229.2	2887.5	3695.5	4216.0	4332.4	4456.0	4558.2
47.5°	1131.2	1140.7	1264.3	1532.9	1977.3	2659.3	3574.3	4296.8	4482.1	4641.4	4791.1
50°	922.1	934.0	1045.7	1285.7	1725.4	2409.8	3410.3	4344.3	4610.5	4826.7	5035.9
52.5°	751.0	765.2	857.9	1069.4	1471.1	2148.4	3208.3	4351.4	4726.9	5012.1	5290.1
55°	625.0	634.5	705.8	874.6	1226.3	1877.5	2977.8	4315.8	4803.0	5178.4	5549.2
57.5°	527.6	537.1	587.0	720.1	1005.3	1599.4	2697.4	4232.6	4843.4	5323.4	5810.6
60°	458.7	465.8	501.4	596.5	827.0	1338.0	2395.5	4085.2	4831.5	5413.7	6026.9
62.5°	408.8	411.1	442.0	508.6	682.1	1090.8	2055.7	3864.2	4734.0	5425.6	6174.2
65°	363.6	366.0	385.0	432.5	560.9	876.9	1701.6	3560.0	4548.7	5342.4	6195.6
67.5°	294.7	299.4	328.0	363.6	461.0	693.9	1340.4	3160.8	4258.7	5126.2	6074.4
70°	235.3	237.7	266.2	306.6	375.5	546.6	1029.0	2623.7	3804.8	4774.4	5760.7
72.5°	175.9	180.6	206.8	247.2	306.6	423.0	743.9	1984.4	3042.0	4025.8	5016.8
75°	140.2	142.6	152.1	190.1	237.7	320.8	501.4	1202.5	1832.3	2490.6	3075.2
77.5°	118.8	121.2	121.2	147.3	175.9	216.3	266.2	477.7	774.7	1102.7	1461.6
80°	97.4	102.2	92.7	109.3	126.0	126.0	123.6	228.1	366.0	518.1	679.7
82.5°	71.3	76.0	71.3	76.0	76.0	68.9	64.2	85.6	116.4	159.2	173.5
85°	49.9	52.3	57.0	52.3	49.9	40.4	30.9	23.8	14.3	16.6	23.8
87.5°	33.3	40.4	47.5	45.2	38.0	30.9	21.4	14.3	7.1	9.5	9.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1212007
 CATALOG NUMBER: GKO-PB2E-735-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3198.8	3198.8	3198.8
2.5°	3201.2	3198.8	3196.4
5°	3213.1	3210.7	3208.3
7.5°	3229.7	3229.7	3229.7
10°	3255.8	3260.6	3260.6
12.5°	3289.1	3293.9	3293.9
15°	3329.5	3331.9	3336.6
17.5°	3379.4	3381.8	3381.8
20°	3438.8	3436.5	3441.2
22.5°	3498.2	3498.2	3498.2
25°	3560.0	3560.0	3560.0
27.5°	3631.3	3631.3	3626.6
30°	3709.8	3709.8	3709.8
32.5°	3804.8	3807.2	3809.6
35°	3926.0	3930.8	3937.9
37.5°	4063.9	4075.7	4082.9
40°	4227.8	4232.6	4244.5
42.5°	4410.8	4425.1	4427.5
45°	4639.0	4662.7	4672.2
47.5°	4907.5	4940.8	4957.4
50°	5207.0	5245.0	5268.8
52.5°	5532.5	5594.3	5622.9
55°	5879.5	5986.5	6017.4
57.5°	6271.6	6416.6	6459.4
60°	6656.6	6861.0	6929.9
62.5°	6984.6	7272.2	7357.7
65°	7215.1	7562.1	7688.1
67.5°	7262.7	7673.8	7823.5
70°	6977.5	7398.1	7571.6
72.5°	6067.3	6447.5	6663.8
75°	3583.8	3857.1	3790.6
77.5°	1799.0	1877.5	1889.3
80°	789.0	836.5	855.5
82.5°	194.9	199.6	225.8
85°	26.1	30.9	28.5
87.5°	9.5	9.5	11.9
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-2

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-735-U-T4W


Data in this report applies to families of products including GKO-PB1C

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-735-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	3481	CRI (Ra):	71.1		
CIE u':	0.2357	R1:	67.5	R9:	-37.9
CIE v':	0.5131	R2:	79.5	R10:	52.4
Duv:	0.0011	R3:	90.0	R11:	64.5
CIE x:	0.4076	R4:	69.0	R12:	43.0
CIE y:	0.3944	R5:	67.0	R13:	69.5
CIE z:	0.1981	R6:	71.2	R14:	94.3
Peak Wavelength (nm):	589	R7:	78.9	R15:	59.3
Dominant Wavelength (nm):	580	R8:	45.9		
Purity:	40.6853				
Rf:	73.8				
Rg:	93.8				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-595-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.36

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.56


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2




TM-30-18

Summary

$R_f = 73.8$
 $R_g = 93.8$
 $CIE R_a = 71.1$
 $R_g = -37.9$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 63	CES51 = 88	CES76 = 53
CES02 = 61	CES27 = 88	CES52 = 87	CES77 = 73
CES03 = 31	CES28 = 83	CES53 = 77	CES78 = 56
CES04 = 70	CES29 = 65	CES54 = 84	CES79 = 83
CES05 = 48	CES30 = 79	CES55 = 83	CES80 = 81
CES06 = 51	CES31 = 69	CES56 = 73	CES81 = 76
CES07 = 40	CES32 = 61	CES57 = 72	CES82 = 92
CES08 = 39	CES33 = 75	CES58 = 74	CES83 = 90
CES09 = 29	CES34 = 72	CES59 = 85	CES84 = 87
CES10 = 75	CES35 = 85	CES60 = 90	CES85 = 77
CES11 = 58	CES36 = 93	CES61 = 82	CES86 = 68
CES12 = 64	CES37 = 81	CES62 = 88	CES87 = 77
CES13 = 42	CES38 = 89	CES63 = 73	CES88 = 79
CES14 = 74	CES39 = 96	CES64 = 66	CES89 = 68
CES15 = 71	CES40 = 91	CES65 = 63	CES90 = 79
CES16 = 47	CES41 = 92	CES66 = 60	CES91 = 78
CES17 = 50	CES42 = 83	CES67 = 57	CES92 = 57
CES18 = 56	CES43 = 77	CES68 = 65	CES93 = 74
CES19 = 72	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 65	CES45 = 85	CES70 = 58	CES95 = 66
CES21 = 87	CES46 = 81	CES71 = 53	CES96 = 76
CES22 = 79	CES47 = 84	CES72 = 84	CES97 = 83
CES23 = 92	CES48 = 74	CES73 = 49	CES98 = 75
CES24 = 91	CES49 = 79	CES74 = 96	CES99 = 63
CES25 = 72	CES50 = 87	CES75 = 55	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)