Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P821195

Luminaire Tested: **TT-D1-735-24VDC-MQ-UPL**

Issue Date: 7/23/2020

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P821195
	REPORT IS FROM IESNA LM-79-08 TEST DATA - UPLIGHT (G2-2002-677-2) AND
Test Lab:	INNOVATION CENTER
Issue Date:	7/23/2020
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	TT-D1-735-24VDC-MQ-UPL
Description:	TOPTIER LED PARKING GARAGE LUMINAIRE WITH UPLIGHT
	3500K, 70 CRI LEDS AND MEDIUM DISTRIBUTION
Light Source:	-
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4706.7 lumens
Efficiency:	N/A
Efficacy:	168.1 lumens/watt
Luminous Opening:	Vertical Cylinder (Dia: 1.12' x H: 0.1')
IES Classification:	Type V - Short
BUG Rating:	B2 - U4 - G1


Input Watts (W):	28
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	25 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821195
CATALOG NUMBER: TT-D1-735-24VDC-MQ-UPL

Iso-Footcandle Lines of Horizontal Illumination




Based on 15 foot mounting height. Maximum calculated value = 3.4 fc
Type V - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821195
CATALOG NUMBER: TT-D1-735-24VDC-MQ-UPL

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P821195
CATALOG NUMBER: TT-D1-735-24VDC-MQ-UPL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1937.5	415.9	2353.4
	% Fixture	41.2	8.8	50.0
Street Side	Lumens	1937.5	415.9	2353.4
	% Fixture	41.2	8.8	50.0
Total	Lumens	3875.0	831.7	4706.7
	% Fixture	82.3	17.7	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.5	1.6
10°-20°	216.1	4.6
20°-30°	347.2	7.4
30°-40°	458.4	9.7
40°-50°	573.5	12.2
50°-60°	682.1	14.5
60°-70°	739.9	15.7
70°-80°	588.9	12.5
80°-90°	195.4	4.2
90°-100°	42.6	0.9
100°-110°	66.0	1.4
110°-120°	91.9	2.0
120°-130°	119.0	2.5
130°-140°	138.7	2.9
140°-150°	140.5	3.0
150°-160°	121.9	2.6
160°-170°	82.2	1.7
170°-180°	28.9	0.6
0°-90°	3875.0	82.3
0°-180°	4706.7	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P821195
CATALOG NUMBER: TT-D1-735-24VDC-MQ-UPL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	318.4	6.8			
FM	(30°-60°)	857.0	18.2			
FH	(60°-80°)	664.4	14.1			G1/1800
FVH	(80°-90°)	97.7	2.1			G1/100
BL	(0°-30°)	318.4	6.8	B1/500		
BM	(30°-60°)	857.0	18.2	B1/1000		
BH	(60°-80°)	664.4	14.1	B2/1000		G1/1800
BVH	(80°-90°)	97.7	2.1			G1/100
UL	(90°-100°)	42.6	0.9		U2/50	
UH	(100°-180°)	789.1	16.8		U4/1000	

BUG Rating: B2-U4-G1
Type V Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821195
CATALOG NUMBER: TT-D1-735-24VDC-MQ-UPL

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	771.0	771.0	771.0	771.0	771.0	771.0	771.0	771.0	771.0	771.0	771.0
2.5°	772.1	771.6	772.1	771.6	771.6	771.0	771.6	771.6	771.6	771.6	771.6
5°	771.6	771.0	771.0	771.6	771.0	771.0	771.0	771.0	771.0	771.0	771.0
7.5°	769.3	769.3	769.8	769.3	769.3	769.3	769.3	769.3	769.3	769.8	769.8
10°	767.5	767.0	767.5	767.5	767.0	767.5	767.0	767.5	767.5	767.5	767.5
12.5°	765.2	764.6	765.2	765.2	764.6	764.1	764.6	764.6	765.2	765.2	765.2
15°	761.2	761.2	762.3	761.8	761.8	761.2	762.3	761.8	761.2	761.8	761.8
17.5°	758.3	758.3	759.5	760.6	760.6	760.6	760.6	760.0	758.9	759.5	758.3
20°	758.9	759.5	760.0	761.8	762.9	763.5	763.5	761.8	760.0	760.6	760.0
22.5°	757.2	756.6	757.2	758.3	760.0	760.0	760.0	757.7	757.2	756.6	756.6
25°	750.3	750.3	751.4	752.6	753.7	753.1	753.7	752.6	751.4	750.3	750.3
27.5°	742.2	742.2	743.9	745.1	746.2	746.2	745.6	744.5	743.9	742.8	742.2
30°	734.1	734.1	735.9	737.0	738.7	738.2	738.2	736.4	734.7	733.6	733.6
32.5°	725.5	724.9	726.6	729.5	731.8	731.8	731.8	728.4	726.1	724.9	724.3
35°	718.0	718.0	720.3	725.5	728.4	728.4	727.2	724.9	719.7	718.0	718.0
37.5°	715.7	717.4	723.8	731.3	737.0	738.2	736.4	730.1	723.2	718.0	716.3
40°	723.2	724.9	733.0	745.1	753.7	755.4	753.7	744.5	732.4	724.3	723.8
42.5°	724.3	725.5	735.3	749.1	757.2	760.0	757.2	748.0	734.7	724.9	724.3
45°	720.3	720.9	732.4	746.8	756.6	760.0	756.6	745.6	731.8	720.9	720.3
47.5°	715.1	716.3	729.0	743.9	756.0	758.3	755.4	743.3	727.8	716.9	715.1
50°	711.1	714.6	726.1	742.8	757.2	764.1	757.2	741.0	725.5	713.4	711.1
52.5°	713.4	714.6	729.5	753.1	772.7	775.6	772.1	753.1	728.4	714.6	712.8
55°	720.3	725.5	741.6	775.6	793.4	798.6	791.1	774.4	742.2	725.5	720.3
57.5°	729.5	731.3	754.3	784.2	810.7	826.3	811.3	783.7	756.0	730.1	729.0
60°	722.0	716.9	745.6	780.8	816.5	822.8	814.2	781.3	744.5	716.3	721.5
62.5°	701.9	705.3	729.0	777.3	802.1	809.0	799.8	777.3	727.8	708.2	700.2
65°	685.8	706.5	732.4	767.0	806.7	826.3	807.3	765.8	733.6	703.0	684.0
67.5°	663.3	667.3	705.9	748.5	784.2	794.0	783.7	749.1	702.5	664.5	667.3
70°	625.3	619.6	658.7	708.2	742.2	757.7	743.3	705.9	657.0	618.4	623.6
72.5°	562.5	566.0	602.3	654.7	689.8	704.8	690.4	650.6	601.1	569.5	566.0
75°	496.9	500.9	536.1	583.9	619.6	625.9	621.9	581.0	537.2	500.4	496.9
77.5°	422.1	426.1	454.9	507.3	528.6	538.4	529.7	510.2	453.7	425.5	420.9
80°	339.1	338.0	363.3	408.2	434.7	445.7	434.7	409.4	362.2	340.3	332.8
82.5°	242.4	243.6	267.2	298.3	323.6	327.0	321.9	301.1	264.9	246.4	236.1
85°	134.7	139.9	157.2	180.2	196.9	202.7	194.0	174.5	156.6	142.2	137.6
87.5°	32.2	35.1	40.9	51.8	58.2	63.9	58.2	54.1	38.6	35.1	32.2
90°	30.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
92.5°	34.8	34.2	34.2	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.8
95°	39.4	39.4	39.4	38.5	38.5	38.5	38.5	38.5	38.5	38.5	38.5
97.5°	44.6	44.6	44.6	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2
100°	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8
102.5°	55.9	55.9	55.9	55.9	55.9	55.9	55.9	56.4	55.9	55.9	55.9
105°	62.0	62.0	62.0	62.0	62.0	62.0	62.0	62.9	62.0	62.0	62.0
107.5°	68.6	68.6	69.0	69.0	69.0	69.0	69.0	69.5	69.0	69.0	69.0
110°	75.1	75.1	76.1	76.1	76.1	76.1	76.1	76.1	76.1	76.1	76.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P821195
CATALOG NUMBER: TT-D1-735-24VDC-MQ-UPL

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	83.1	83.1	84.0	84.0	84.0	*84.0*	84.6	84.6	84.0	84.0	84.0
115°	91.1	91.1	92.0	92.0	92.0	*92.0*	93.0	93.0	92.0	92.0	92.0
117.5°	100.5	100.5	101.0	101.4	101.4	*101.4*	102.4	102.4	101.4	101.4	101.4
120°	109.9	109.9	109.9	110.8	110.8	*110.8*	111.8	111.8	110.8	110.8	110.8
122.5°	120.7	120.7	121.2	121.6	121.6	*121.6*	122.6	122.6	122.1	122.1	121.6
125°	131.5	131.5	132.4	132.4	132.4	*132.4*	133.4	133.4	133.4	133.4	132.4
127.5°	143.2	143.2	144.2	144.2	144.2	*144.2*	145.1	145.1	145.1	145.1	144.2
130°	155.0	155.0	155.9	155.9	155.9	*155.9*	156.8	156.8	156.8	156.8	155.9
132.5°	167.2	167.2	167.6	167.6	167.6	*168.1*	168.6	168.6	168.6	168.6	168.1
135°	179.4	179.4	179.4	179.4	179.4	*180.3*	180.3	180.3	180.3	180.3	180.3
137.5°	191.2	190.6	191.2	190.6	191.2	*191.6*	191.6	191.6	191.6	191.6	191.6
140°	202.9	201.9	202.9	201.9	202.9	*202.9*	202.9	202.9	202.9	202.9	202.9
142.5°	213.7	213.2	213.7	212.7	213.7	*213.7*	213.7	213.7	213.7	213.7	213.7
145°	224.5	224.5	224.5	223.5	224.5	*224.5*	224.5	224.5	224.5	224.5	224.5
147.5°	235.8	235.3	235.8	234.8	235.8	*235.8*	235.8	235.8	235.8	235.8	235.8
150°	247.0	246.1	247.0	246.1	247.0	*247.0*	247.0	247.0	247.0	247.0	247.0
152.5°	256.0	255.5	256.4	255.5	256.0	*256.0*	256.4	256.0	256.0	256.0	256.0
155°	264.9	264.9	265.8	264.9	264.9	*264.9*	265.8	264.9	264.9	264.9	264.9
157.5°	272.4	272.4	273.3	272.4	272.4	*272.4*	273.3	272.4	272.4	272.4	272.4
160°	279.9	279.9	280.8	279.9	279.9	*279.9*	280.8	279.9	279.9	279.9	279.9
162.5°	286.0	286.0	286.9	286.0	286.0	*286.0*	286.9	286.0	286.0	286.0	286.0
165°	292.1	292.1	293.0	292.1	292.1	*292.1*	293.0	292.1	292.1	292.1	292.1
167.5°	295.8	295.8	296.8	295.8	295.8	*295.8*	296.8	295.8	295.8	295.8	295.8
170°	299.6	299.6	300.5	299.6	299.6	*299.6*	300.5	299.6	299.6	299.6	299.6
172.5°	302.0	302.0	302.8	302.0	302.4	*302.0*	302.8	302.0	302.0	302.0	302.0
175°	304.3	304.3	305.2	304.3	305.2	*304.3*	305.2	304.3	304.3	304.3	304.3
177.5°	305.2	305.2	305.7	305.2	305.7	*305.2*	305.7	305.2	305.2	305.2	305.2
180°	306.2	306.2	306.2	306.2	306.2	*306.2*	306.2	306.2	306.2	306.2	306.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-4

Test Date: 09/24/2024

Luminaire Tested: MEM2-HTN-VA-30-735-U-WQ

Data in this report applies to families of products including MEM2-HTN-VA-30-735-U-WQ


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-176-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	09/27/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Streetworks
Catalog Number:	**MEM2-HTN-VA-30-735-U-WQ**
Description:	EPIC MODERN VISUAL COMFORT 30W WAVESTREAM WIDE

Spectral Parameters

CCT (K):	3348	CRI (Ra):	73.4		
CIE u':	0.2384	R1:	70.8	R9:	-19.2
CIE v':	0.5184	R2:	79.9	R10:	52.5
Duv:	0.0030	R3:	87.6	R11:	68.0
CIE x:	0.4177	R4:	72.6	R12:	42.6
CIE y:	0.4036	R5:	69.3	R13:	72.0
CIE z:	0.1787	R6:	71.3	R14:	92.6
Peak Wavelength (nm):	593	R7:	82.1	R15:	63.8
Dominant Wavelength (nm):	580	R8:	53.3		
Purity:	46.5223				
Rf:	75.8				
Rg:	95.8				



Test Conditions


Stabilization Time:	30M
Operation Time:	1H 30M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-176-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-176-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3348K
CIE x = 0.4177
CIE y = 0.4036
Duv = 0.0030

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	110	NR	620	844	NR	750	28	NR	880	0	NR
365	0	NR	495	150	NR	625	792	NR	755	25	NR	885	0	NR
370	0	NR	500	214	NR	630	737	NR	760	22	NR	890	0	NR
375	0	NR	505	293	NR	635	683	NR	765	19	NR	895	0	NR
380	0	NR	510	376	NR	640	625	NR	770	16	NR	900	0	NR
385	0	NR	515	458	NR	645	566	NR	775	14	NR	905	0	NR
390	0	NR	520	526	NR	650	509	NR	780	12	NR	910	0	NR
395	1	NR	525	584	NR	655	453	NR	785	10	NR	915	0	NR
400	3	NR	530	631	NR	660	401	NR	790	9	NR	920	0	NR
405	5	NR	535	671	NR	665	353	NR	795	8	NR	925	0	NR
410	10	NR	540	704	NR	670	308	NR	800	7	NR	930	0	NR
415	21	NR	545	737	NR	675	269	NR	805	6	NR	935	0	NR
420	44	NR	550	766	NR	680	235	NR	810	5	NR	940	0	NR
425	90	NR	555	797	NR	685	204	NR	815	4	NR	945	0	NR
430	171	NR	560	832	NR	690	177	NR	820	4	NR	950	0	NR
435	305	NR	565	866	NR	695	152	NR	825	3	NR	955	0	NR
440	455	NR	570	901	NR	700	131	NR	830	3	NR	960	0	NR
445	615	NR	575	933	NR	705	112	NR	835	3	NR	965	0	NR
450	771	NR	580	963	NR	710	96	NR	840	2	NR	970	0	NR
455	579	NR	585	984	NR	715	80	NR	845	2	NR	975	0	NR
460	313	NR	590	1000	NR	720	67	NR	850	2	NR	980	0	NR
465	221	NR	595	999	NR	725	55	NR	855	1	NR	985	0	NR
470	156	NR	600	990	NR	730	46	NR	860	1	NR	990	0	NR
475	103	NR	605	968	NR	735	40	NR	865	1	NR	995	0	NR
480	89	NR	610	937	NR	740	35	NR	870	1	NR	1000	0	NR
485	93	NR	615	893	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-176-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.31**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	110	NR	620	844	NR	750	28	NR	880	0	NR
365	0	NR	495	150	NR	625	792	NR	755	25	NR	885	0	NR
370	0	NR	500	214	NR	630	737	NR	760	22	NR	890	0	NR
375	0	NR	505	293	NR	635	683	NR	765	19	NR	895	0	NR
380	0	NR	510	376	NR	640	625	NR	770	16	NR	900	0	NR
385	0	NR	515	458	NR	645	566	NR	775	14	NR	905	0	NR
390	0	NR	520	526	NR	650	509	NR	780	12	NR	910	0	NR
395	1	NR	525	584	NR	655	453	NR	785	10	NR	915	0	NR
400	3	NR	530	631	NR	660	401	NR	790	9	NR	920	0	NR
405	5	NR	535	671	NR	665	353	NR	795	8	NR	925	0	NR
410	10	NR	540	704	NR	670	308	NR	800	7	NR	930	0	NR
415	21	NR	545	737	NR	675	269	NR	805	6	NR	935	0	NR
420	44	NR	550	766	NR	680	235	NR	810	5	NR	940	0	NR
425	90	NR	555	797	NR	685	204	NR	815	4	NR	945	0	NR
430	171	NR	560	832	NR	690	177	NR	820	4	NR	950	0	NR
435	305	NR	565	866	NR	695	152	NR	825	3	NR	955	0	NR
440	455	NR	570	901	NR	700	131	NR	830	3	NR	960	0	NR
445	615	NR	575	933	NR	705	112	NR	835	3	NR	965	0	NR
450	771	NR	580	963	NR	710	96	NR	840	2	NR	970	0	NR
455	579	NR	585	984	NR	715	80	NR	845	2	NR	975	0	NR
460	313	NR	590	1000	NR	720	67	NR	850	2	NR	980	0	NR
465	221	NR	595	999	NR	725	55	NR	855	1	NR	985	0	NR
470	156	NR	600	990	NR	730	46	NR	860	1	NR	990	0	NR
475	103	NR	605	968	NR	735	40	NR	865	1	NR	995	0	NR
480	89	NR	610	937	NR	740	35	NR	870	1	NR	1000	0	NR
485	93	NR	615	893	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-176-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.4**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	110	NR	620	844	NR	750	28	NR	880	0	NR
365	0	NR	495	150	NR	625	792	NR	755	25	NR	885	0	NR
370	0	NR	500	214	NR	630	737	NR	760	22	NR	890	0	NR
375	0	NR	505	293	NR	635	683	NR	765	19	NR	895	0	NR
380	0	NR	510	376	NR	640	625	NR	770	16	NR	900	0	NR
385	0	NR	515	458	NR	645	566	NR	775	14	NR	905	0	NR
390	0	NR	520	526	NR	650	509	NR	780	12	NR	910	0	NR
395	1	NR	525	584	NR	655	453	NR	785	10	NR	915	0	NR
400	3	NR	530	631	NR	660	401	NR	790	9	NR	920	0	NR
405	5	NR	535	671	NR	665	353	NR	795	8	NR	925	0	NR
410	10	NR	540	704	NR	670	308	NR	800	7	NR	930	0	NR
415	21	NR	545	737	NR	675	269	NR	805	6	NR	935	0	NR
420	44	NR	550	766	NR	680	235	NR	810	5	NR	940	0	NR
425	90	NR	555	797	NR	685	204	NR	815	4	NR	945	0	NR
430	171	NR	560	832	NR	690	177	NR	820	4	NR	950	0	NR
435	305	NR	565	866	NR	695	152	NR	825	3	NR	955	0	NR
440	455	NR	570	901	NR	700	131	NR	830	3	NR	960	0	NR
445	615	NR	575	933	NR	705	112	NR	835	3	NR	965	0	NR
450	771	NR	580	963	NR	710	96	NR	840	2	NR	970	0	NR
455	579	NR	585	984	NR	715	80	NR	845	2	NR	975	0	NR
460	313	NR	590	1000	NR	720	67	NR	850	2	NR	980	0	NR
465	221	NR	595	999	NR	725	55	NR	855	1	NR	985	0	NR
470	156	NR	600	990	NR	730	46	NR	860	1	NR	990	0	NR
475	103	NR	605	968	NR	735	40	NR	865	1	NR	995	0	NR
480	89	NR	610	937	NR	740	35	NR	870	1	NR	1000	0	NR
485	93	NR	615	893	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-176-4

TM-30-18


Summary


R_f = 75.8
R_g = 95.8
CIE R_a = 73.4
R_9 = -19.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-176-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 65	CES51 = 88	CES76 = 55
CES02 = 62	CES27 = 88	CES52 = 87	CES77 = 74
CES03 = 31	CES28 = 83	CES53 = 77	CES78 = 58
CES04 = 70	CES29 = 66	CES54 = 86	CES79 = 84
CES05 = 48	CES30 = 79	CES55 = 84	CES80 = 81
CES06 = 51	CES31 = 69	CES56 = 74	CES81 = 78
CES07 = 41	CES32 = 62	CES57 = 73	CES82 = 92
CES08 = 40	CES33 = 75	CES58 = 75	CES83 = 89
CES09 = 29	CES34 = 73	CES59 = 87	CES84 = 88
CES10 = 75	CES35 = 85	CES60 = 91	CES85 = 79
CES11 = 58	CES36 = 95	CES61 = 84	CES86 = 71
CES12 = 64	CES37 = 80	CES62 = 88	CES87 = 79
CES13 = 43	CES38 = 88	CES63 = 73	CES88 = 81
CES14 = 74	CES39 = 96	CES64 = 69	CES89 = 71
CES15 = 71	CES40 = 91	CES65 = 66	CES90 = 80
CES16 = 47	CES41 = 91	CES66 = 62	CES91 = 81
CES17 = 50	CES42 = 81	CES67 = 60	CES92 = 63
CES18 = 56	CES43 = 77	CES68 = 68	CES93 = 78
CES19 = 72	CES44 = 99	CES69 = 76	CES94 = 56
CES20 = 65	CES45 = 85	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 82	CES71 = 55	CES96 = 79
CES22 = 79	CES47 = 83	CES72 = 85	CES97 = 84
CES23 = 92	CES48 = 75	CES73 = 52	CES98 = 77
CES24 = 91	CES49 = 79	CES74 = 96	CES99 = 68
CES25 = 72	CES50 = 87	CES75 = 57	





REPORT NUMBER: SP1-2407-176-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-176-4

TM-30-18

Measure Comparisons





(END OF REPORT)