

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P977145

Luminaire Tested: **GKO-PB1F-750-U-T1**

Issue Date: 03/19/2025



Test Information

Test Method: LM-79-08
Report Number: P977145
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/19/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1F-750-U-T1
Description: GEKKO WALL PACK 6500LM PACKAGE 70CRI 5000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (10) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7005.1 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 54.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 5.7%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P977145

CATALOG NUMBER: GKO-PB1F-750-U-T1

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
- - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 17.4 fc
Type I - Short - N/A

REPORT NUMBER: P977145
CATALOG NUMBER: GKO-PB1F-750-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P977145

CATALOG NUMBER: GKO-PB1F-750-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3502.6	0.0	3502.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3502.6	0.0	3502.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	7005.1	0.0	7005.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.7	2.4
10°-20°	502.4	7.2
20°-30°	835.3	11.9
30°-40°	1109.7	15.8
40°-50°	1251.1	17.9
50°-60°	1286.5	18.4
60°-70°	1215.7	17.4
70°-80°	595.1	8.5
80°-90°	42.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7005.1	100.0
0°-180°	7005.1	100.0

Coefficient of Utilization



REPORT NUMBER: P977145


CATALOG NUMBER: GKO-PB1F-750-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	752.2	10.7			
FM	(30°-60°)	1823.6	26.0			
FH	(60°-80°)	905.4	12.9			G1/1800
FVH	(80°-90°)	21.3	0.3			G1/100
BL	(0°-30°)	752.2	10.7	B2/1000		
BM	(30°-60°)	1823.6	26.0	B2/2500		
BH	(60°-80°)	905.4	12.9	B2/1000		G2/1000
BVH	(80°-90°)	21.3	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type I Short



REPORT NUMBER: P977145

CATALOG NUMBER: GKO-PB1F-750-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1738.3	1738.3	1738.3	1738.3	1738.3	1738.3	1738.3	1738.3	1738.3	1738.3	1738.3
2.5°	1739.6	1742.1	1737.0	1737.0	1739.6	1740.8	1740.8	1742.1	1739.6	1739.6	1738.3
5°	1739.6	1740.8	1738.3	1738.3	1740.8	1744.7	1743.4	1746.0	1746.0	1744.7	1744.7
7.5°	1738.3	1740.8	1738.3	1739.6	1743.4	1751.2	1751.2	1751.2	1753.8	1756.3	1756.3
10°	1737.0	1739.6	1740.8	1742.1	1747.3	1758.9	1761.5	1762.8	1766.7	1770.5	1770.5
12.5°	1730.5	1733.1	1737.0	1742.1	1751.2	1766.7	1771.8	1775.7	1782.2	1786.0	1788.6
15°	1721.5	1722.8	1731.8	1742.1	1756.3	1775.7	1786.0	1792.5	1801.5	1806.7	1810.6
17.5°	1708.6	1709.8	1724.1	1739.6	1760.2	1787.3	1804.1	1814.5	1823.5	1831.2	1836.4
20°	1691.8	1695.6	1712.4	1737.0	1766.7	1799.0	1823.5	1841.6	1850.6	1858.4	1866.1
22.5°	1671.1	1675.0	1695.6	1730.5	1773.1	1814.5	1846.7	1870.0	1881.6	1891.9	1901.0
25°	1640.1	1645.3	1669.8	1715.0	1775.7	1831.2	1872.6	1902.3	1912.6	1925.5	1933.3
27.5°	1592.3	1596.2	1625.9	1684.0	1768.0	1849.3	1902.3	1937.1	1948.8	1963.0	1970.7
30°	1517.4	1525.2	1561.3	1633.7	1748.6	1863.5	1937.1	1972.0	1986.2	2000.4	2010.8
32.5°	1420.6	1432.2	1472.2	1565.2	1711.1	1868.7	1974.6	2014.6	2032.7	2048.2	2061.1
35°	1300.5	1312.1	1359.9	1477.4	1651.7	1858.4	2012.0	2063.7	2085.7	2106.3	2121.8
37.5°	1163.6	1173.9	1232.0	1366.3	1566.5	1826.1	2041.7	2117.9	2147.6	2174.8	2195.4
40°	1025.4	1037.0	1100.3	1243.6	1463.2	1764.1	2054.7	2177.3	2214.8	2249.7	2275.5
42.5°	875.6	889.8	960.8	1113.2	1343.1	1678.9	2044.3	2235.5	2282.0	2329.7	2368.5
45°	742.6	745.2	822.6	969.9	1211.4	1569.1	2008.2	2291.0	2354.3	2421.4	2477.0
47.5°	614.7	619.9	687.0	833.0	1074.5	1445.1	1942.3	2334.9	2435.6	2522.2	2603.5
50°	501.1	507.5	568.2	698.7	937.6	1309.5	1853.2	2360.7	2505.4	2622.9	2736.5
52.5°	408.1	415.8	466.2	581.1	799.4	1167.5	1743.4	2364.6	2568.6	2723.6	2874.7
55°	339.6	344.8	383.6	475.2	666.4	1020.2	1618.2	2345.2	2610.0	2814.0	3015.5
57.5°	286.7	291.9	319.0	391.3	546.3	869.1	1465.8	2300.0	2631.9	2892.8	3157.5
60°	249.2	253.1	272.5	324.1	449.4	727.1	1301.8	2220.0	2625.5	2941.9	3275.1
62.5°	222.1	223.4	240.2	276.4	370.6	592.8	1117.1	2099.9	2572.5	2948.3	3355.1
65°	197.6	198.9	209.2	235.0	304.8	476.5	924.7	1934.6	2471.8	2903.1	3366.8
67.5°	160.1	162.7	178.2	197.6	250.5	377.1	728.4	1717.6	2314.2	2785.6	3300.9
70°	127.9	129.1	144.6	166.6	204.0	297.0	559.2	1425.7	2067.6	2594.5	3130.4
72.5°	95.6	98.1	112.4	134.3	166.6	229.9	404.2	1078.3	1653.0	2187.7	2726.2
75°	76.2	77.5	82.7	103.3	129.1	174.3	272.5	653.5	995.7	1353.4	1671.1
77.5°	64.6	65.9	65.9	80.1	95.6	117.5	144.6	259.6	421.0	599.2	794.2
80°	52.9	55.5	50.4	59.4	68.4	68.4	67.2	124.0	198.9	281.5	369.3
82.5°	38.7	41.3	38.7	41.3	41.3	37.5	34.9	46.5	63.3	86.5	94.3
85°	27.1	28.4	31.0	28.4	27.1	22.0	16.8	12.9	7.7	9.0	12.9
87.5°	18.1	22.0	25.8	24.5	20.7	16.8	11.6	7.7	3.9	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P977145

CATALOG NUMBER: GKO-PB1F-750-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1738.3	1738.3	1738.3
2.5°	1739.6	1738.3	1737.0
5°	1746.0	1744.7	1743.4
7.5°	1755.0	1755.0	1755.0
10°	1769.3	1771.8	1771.8
12.5°	1787.3	1789.9	1789.9
15°	1809.3	1810.6	1813.2
17.5°	1836.4	1837.7	1837.7
20°	1868.7	1867.4	1870.0
22.5°	1901.0	1901.0	1901.0
25°	1934.6	1934.6	1934.6
27.5°	1973.3	1973.3	1970.7
30°	2015.9	2015.9	2015.9
32.5°	2067.6	2068.9	2070.2
35°	2133.4	2136.0	2139.9
37.5°	2208.3	2214.8	2218.7
40°	2297.4	2300.0	2306.5
42.5°	2396.9	2404.6	2405.9
45°	2520.9	2533.8	2538.9
47.5°	2666.8	2684.9	2693.9
50°	2829.5	2850.2	2863.1
52.5°	3006.4	3040.0	3055.5
55°	3195.0	3253.1	3269.9
57.5°	3408.1	3486.9	3510.1
60°	3617.3	3728.3	3765.8
62.5°	3795.5	3951.8	3998.3
65°	3920.8	4109.3	4177.8
67.5°	3946.6	4170.0	4251.4
70°	3791.6	4020.2	4114.5
72.5°	3297.0	3503.6	3621.2
75°	1947.5	2096.0	2059.8
77.5°	977.6	1020.2	1026.7
80°	428.8	454.6	464.9
82.5°	105.9	108.5	122.7
85°	14.2	16.8	15.5
87.5°	5.2	5.2	6.5
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-5

Test Date: 04/10/2025

Luminaire Tested: GKO-PB1E-750-U-T4W


Data in this report applies to families of products including GKO-PB1E-750-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-750-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	5105	CRI (Ra):	72.2		
CIE u':	0.2079	R1:	68.8	R9:	-38.2
CIE v':	0.4868	R2:	78.3	R10:	48.2
Duv:	0.0035	R3:	84.9	R11:	68.1
CIE x:	0.3428	R4:	71.7	R12:	42.9
CIE y:	0.3567	R5:	69.8	R13:	70.6
CIE z:	0.3005	R6:	69.8	R14:	91.6
Peak Wavelength (nm):	451	R7:	81.2	R15:	61.7
Dominant Wavelength (nm):	567	R8:	53.5		
Purity:	9.884628				
Rf:	74.2				
Rg:	92.7				



Test Conditions

Stabilization Time: 30M
 Operation Time: 1H 30M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP2-2501-321-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	134	NR	620	390	NR	750	10	NR	880	0	NR
365	0	NR	495	165	NR	625	354	NR	755	9	NR	885	0	NR
370	0	NR	500	218	NR	630	319	NR	760	8	NR	890	0	NR
375	0	NR	505	281	NR	635	285	NR	765	7	NR	895	0	NR
380	0	NR	510	343	NR	640	254	NR	770	6	NR	900	0	NR
385	1	NR	515	400	NR	645	224	NR	775	5	NR	905	0	NR
390	2	NR	520	444	NR	650	197	NR	780	4	NR	910	0	NR
395	4	NR	525	477	NR	655	173	NR	785	4	NR	915	0	NR
400	6	NR	530	501	NR	660	150	NR	790	3	NR	920	0	NR
405	9	NR	535	520	NR	665	131	NR	795	3	NR	925	0	NR
410	14	NR	540	534	NR	670	113	NR	800	2	NR	930	0	NR
415	26	NR	545	547	NR	675	98	NR	805	2	NR	935	0	NR
420	50	NR	550	561	NR	680	85	NR	810	2	NR	940	0	NR
425	95	NR	555	574	NR	685	73	NR	815	2	NR	945	0	NR
430	168	NR	560	586	NR	690	63	NR	820	1	NR	950	0	NR
435	284	NR	565	596	NR	695	54	NR	825	1	NR	955	0	NR
440	452	NR	570	604	NR	700	46	NR	830	1	NR	960	0	NR
445	705	NR	575	606	NR	705	40	NR	835	1	NR	965	0	NR
450	980	NR	580	603	NR	710	34	NR	840	1	NR	970	0	NR
455	869	NR	585	592	NR	715	29	NR	845	1	NR	975	0	NR
460	531	NR	590	577	NR	720	25	NR	850	1	NR	980	0	NR
465	372	NR	595	554	NR	725	22	NR	855	1	NR	985	0	NR
470	268	NR	600	527	NR	730	19	NR	860	1	NR	990	0	NR
475	174	NR	605	497	NR	735	16	NR	865	0	NR	995	0	NR
480	135	NR	610	462	NR	740	14	NR	870	0	NR	1000	0	NR
485	126	NR	615	428	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP2-2501-321-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.82

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	134	NR	620	390	NR	750	10	NR	880	0	NR
365	0	NR	495	165	NR	625	354	NR	755	9	NR	885	0	NR
370	0	NR	500	218	NR	630	319	NR	760	8	NR	890	0	NR
375	0	NR	505	281	NR	635	285	NR	765	7	NR	895	0	NR
380	0	NR	510	343	NR	640	254	NR	770	6	NR	900	0	NR
385	1	NR	515	400	NR	645	224	NR	775	5	NR	905	0	NR
390	2	NR	520	444	NR	650	197	NR	780	4	NR	910	0	NR
395	4	NR	525	477	NR	655	173	NR	785	4	NR	915	0	NR
400	6	NR	530	501	NR	660	150	NR	790	3	NR	920	0	NR
405	9	NR	535	520	NR	665	131	NR	795	3	NR	925	0	NR
410	14	NR	540	534	NR	670	113	NR	800	2	NR	930	0	NR
415	26	NR	545	547	NR	675	98	NR	805	2	NR	935	0	NR
420	50	NR	550	561	NR	680	85	NR	810	2	NR	940	0	NR
425	95	NR	555	574	NR	685	73	NR	815	2	NR	945	0	NR
430	168	NR	560	586	NR	690	63	NR	820	1	NR	950	0	NR
435	284	NR	565	596	NR	695	54	NR	825	1	NR	955	0	NR
440	452	NR	570	604	NR	700	46	NR	830	1	NR	960	0	NR
445	705	NR	575	606	NR	705	40	NR	835	1	NR	965	0	NR
450	980	NR	580	603	NR	710	34	NR	840	1	NR	970	0	NR
455	869	NR	585	592	NR	715	29	NR	845	1	NR	975	0	NR
460	531	NR	590	577	NR	720	25	NR	850	1	NR	980	0	NR
465	372	NR	595	554	NR	725	22	NR	855	1	NR	985	0	NR
470	268	NR	600	527	NR	730	19	NR	860	1	NR	990	0	NR
475	174	NR	605	497	NR	735	16	NR	865	0	NR	995	0	NR
480	135	NR	610	462	NR	740	14	NR	870	0	NR	1000	0	NR
485	126	NR	615	428	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP2-2501-321-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.75


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	134	NR	620	390	NR	750	10	NR	880	0	NR
365	0	NR	495	165	NR	625	354	NR	755	9	NR	885	0	NR
370	0	NR	500	218	NR	630	319	NR	760	8	NR	890	0	NR
375	0	NR	505	281	NR	635	285	NR	765	7	NR	895	0	NR
380	0	NR	510	343	NR	640	254	NR	770	6	NR	900	0	NR
385	1	NR	515	400	NR	645	224	NR	775	5	NR	905	0	NR
390	2	NR	520	444	NR	650	197	NR	780	4	NR	910	0	NR
395	4	NR	525	477	NR	655	173	NR	785	4	NR	915	0	NR
400	6	NR	530	501	NR	660	150	NR	790	3	NR	920	0	NR
405	9	NR	535	520	NR	665	131	NR	795	3	NR	925	0	NR
410	14	NR	540	534	NR	670	113	NR	800	2	NR	930	0	NR
415	26	NR	545	547	NR	675	98	NR	805	2	NR	935	0	NR
420	50	NR	550	561	NR	680	85	NR	810	2	NR	940	0	NR
425	95	NR	555	574	NR	685	73	NR	815	2	NR	945	0	NR
430	168	NR	560	586	NR	690	63	NR	820	1	NR	950	0	NR
435	284	NR	565	596	NR	695	54	NR	825	1	NR	955	0	NR
440	452	NR	570	604	NR	700	46	NR	830	1	NR	960	0	NR
445	705	NR	575	606	NR	705	40	NR	835	1	NR	965	0	NR
450	980	NR	580	603	NR	710	34	NR	840	1	NR	970	0	NR
455	869	NR	585	592	NR	715	29	NR	845	1	NR	975	0	NR
460	531	NR	590	577	NR	720	25	NR	850	1	NR	980	0	NR
465	372	NR	595	554	NR	725	22	NR	855	1	NR	985	0	NR
470	268	NR	600	527	NR	730	19	NR	860	1	NR	990	0	NR
475	174	NR	605	497	NR	735	16	NR	865	0	NR	995	0	NR
480	135	NR	610	462	NR	740	14	NR	870	0	NR	1000	0	NR
485	126	NR	615	428	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP2-2501-321-5




TM-30-18

Summary

$R_f = 74.2$
 $R_g = 92.7$
 $\text{CIE } R_a = 72.2$
 $R_g = -38.2$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 63	CES51 = 89	CES76 = 51
CES02 = 59	CES27 = 89	CES52 = 89	CES77 = 68
CES03 = 30	CES28 = 81	CES53 = 79	CES78 = 54
CES04 = 69	CES29 = 69	CES54 = 84	CES79 = 80
CES05 = 46	CES30 = 88	CES55 = 83	CES80 = 77
CES06 = 50	CES31 = 72	CES56 = 74	CES81 = 79
CES07 = 38	CES32 = 63	CES57 = 73	CES82 = 91
CES08 = 38	CES33 = 82	CES58 = 74	CES83 = 90
CES09 = 29	CES34 = 70	CES59 = 86	CES84 = 85
CES10 = 72	CES35 = 83	CES60 = 88	CES85 = 78
CES11 = 56	CES36 = 88	CES61 = 82	CES86 = 75
CES12 = 61	CES37 = 78	CES62 = 81	CES87 = 77
CES13 = 41	CES38 = 98	CES63 = 73	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 64	CES89 = 73
CES15 = 70	CES40 = 91	CES65 = 61	CES90 = 80
CES16 = 46	CES41 = 96	CES66 = 56	CES91 = 72
CES17 = 49	CES42 = 80	CES67 = 54	CES92 = 58
CES18 = 55	CES43 = 79	CES68 = 64	CES93 = 75
CES19 = 71	CES44 = 99	CES69 = 73	CES94 = 53
CES20 = 63	CES45 = 87	CES70 = 56	CES95 = 64
CES21 = 85	CES46 = 85	CES71 = 47	CES96 = 76
CES22 = 77	CES47 = 90	CES72 = 82	CES97 = 86
CES23 = 91	CES48 = 80	CES73 = 47	CES98 = 76
CES24 = 90	CES49 = 83	CES74 = 90	CES99 = 62
CES25 = 71	CES50 = 89	CES75 = 50	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)