

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1212019

Luminaire Tested: **GKO-PB2C-827-U-T1**

Issue Date: 11/5/2025

Test Information

Test Method: LM-79-08
Report Number: P1212019
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2C-827-U-T1
Description: GEKKO WALL PACK 8000LM PACKAGE 80CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7398.3 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B2 - U0 - G2

Input Watts (W): 58.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 5%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1212019
 CATALOG NUMBER: GKO-PB2C-827-U-T1

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 8.2 fc
 Type I - Short - N/A

REPORT NUMBER: P1212019
CATALOG NUMBER: GKO-PB2C-827-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1212019

CATALOG NUMBER: GKO-PB2C-827-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3699.1	0.0	3699.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3699.1	0.0	3699.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	7398.3	0.0	7398.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.1	2.4
10°-20°	530.6	7.2
20°-30°	882.2	11.9
30°-40°	1172.0	15.8
40°-50°	1321.3	17.9
50°-60°	1358.7	18.4
60°-70°	1284.0	17.4
70°-80°	628.5	8.5
80°-90°	44.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7398.3	100.0
0°-180°	7398.3	100.0

Coefficient of Utilization



REPORT NUMBER: P1212019


CATALOG NUMBER: GKO-PB2C-827-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	794.4	10.7			
FM	(30°-60°)	1926.0	26.0			
FH	(60°-80°)	956.3	12.9			G1/1800
FVH	(80°-90°)	22.5	0.3			G1/100
BL	(0°-30°)	794.4	10.7	B2/1000		
BM	(30°-60°)	1926.0	26.0	B2/2500		
BH	(60°-80°)	956.3	12.9	B2/1000		G2/1000
BVH	(80°-90°)	22.5	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type I Short





REPORT NUMBER: P1212019

CATALOG NUMBER: GKO-PB2C-827-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1835.8	1835.8	1835.8	1835.8	1835.8	1835.8	1835.8	1835.8	1835.8	1835.8	1835.8
2.5°	1837.2	1839.9	1834.5	1834.5	1837.2	1838.5	1838.5	1839.9	1837.2	1837.2	1835.8
5°	1837.2	1838.5	1835.8	1835.8	1838.5	1842.6	1841.3	1844.0	1844.0	1842.6	1842.6
7.5°	1835.8	1838.5	1835.8	1837.2	1841.3	1849.5	1849.5	1849.5	1852.2	1854.9	1854.9
10°	1834.5	1837.2	1838.5	1839.9	1845.4	1857.6	1860.4	1861.7	1865.8	1869.9	1869.9
12.5°	1827.6	1830.4	1834.5	1839.9	1849.5	1865.8	1871.3	1875.4	1882.2	1886.3	1889.0
15°	1818.1	1819.4	1829.0	1839.9	1854.9	1875.4	1886.3	1893.1	1902.6	1908.1	1912.2
17.5°	1804.4	1805.8	1820.8	1837.2	1859.0	1887.6	1905.4	1916.3	1925.8	1934.0	1939.5
20°	1786.7	1790.8	1808.5	1834.5	1865.8	1899.9	1925.8	1944.9	1954.5	1962.7	1970.8
22.5°	1764.9	1769.0	1790.8	1827.6	1872.6	1916.3	1950.4	1974.9	1987.2	1998.1	2007.7
25°	1732.2	1737.6	1763.5	1811.3	1875.4	1934.0	1977.7	2009.0	2019.9	2033.6	2041.8
27.5°	1681.7	1685.8	1717.2	1778.5	1867.2	1953.1	2009.0	2045.9	2058.1	2073.1	2081.3
30°	1602.6	1610.8	1649.0	1725.3	1846.7	1968.1	2045.9	2082.7	2097.7	2112.7	2123.6
32.5°	1500.3	1512.6	1554.9	1653.1	1807.2	1973.6	2085.4	2127.7	2146.8	2163.2	2176.8
35°	1373.5	1385.7	1436.2	1560.3	1744.4	1962.7	2125.0	2179.5	2202.7	2224.5	2240.9
37.5°	1228.9	1239.8	1301.2	1443.0	1654.4	1928.6	2156.3	2236.8	2268.2	2296.8	2318.6
40°	1082.9	1095.2	1162.0	1313.4	1545.3	1863.1	2170.0	2299.5	2339.1	2375.9	2403.2
42.5°	924.7	939.7	1014.7	1175.7	1418.5	1773.1	2159.1	2360.9	2410.0	2460.5	2501.4
45°	784.2	787.0	868.8	1024.3	1279.3	1657.1	2120.9	2419.6	2486.4	2557.3	2616.0
47.5°	649.2	654.7	725.6	879.7	1134.8	1526.2	2051.3	2465.9	2572.3	2663.7	2749.6
50°	529.2	536.0	600.1	737.9	990.2	1383.0	1957.2	2493.2	2646.0	2770.1	2890.1
52.5°	431.0	439.2	492.4	613.8	844.3	1233.0	1841.3	2497.3	2712.8	2876.5	3036.1
55°	358.7	364.2	405.1	501.9	703.8	1077.5	1709.0	2476.8	2756.4	2971.9	3184.7
57.5°	302.8	308.2	336.9	413.3	576.9	917.9	1548.0	2429.1	2779.6	3055.1	3334.7
60°	263.2	267.3	287.8	342.3	474.6	767.9	1374.8	2344.6	2772.8	3107.0	3458.9
62.5°	234.6	236.0	253.7	291.9	391.4	626.0	1179.8	2217.7	2716.9	3113.8	3543.4
65°	208.7	210.0	221.0	248.2	321.9	503.3	976.6	2043.1	2610.5	3066.1	3555.7
67.5°	169.1	171.9	188.2	208.7	264.6	398.3	769.2	1814.0	2444.1	2941.9	3486.1
70°	135.0	136.4	152.8	175.9	215.5	313.7	590.6	1505.7	2183.6	2740.1	3306.1
72.5°	100.9	103.7	118.7	141.8	175.9	242.8	426.9	1138.9	1745.8	2310.5	2879.2
75°	80.5	81.8	87.3	109.1	136.4	184.1	287.8	690.1	1051.6	1429.4	1764.9
77.5°	68.2	69.6	69.6	84.6	100.9	124.1	152.8	274.1	444.6	632.9	838.8
80°	55.9	58.6	53.2	62.7	72.3	72.3	70.9	130.9	210.0	297.3	390.1
82.5°	40.9	43.6	40.9	43.6	43.6	39.6	36.8	49.1	66.8	91.4	99.6
85°	28.6	30.0	32.7	30.0	28.6	23.2	17.7	13.6	8.2	9.5	13.6
87.5°	19.1	23.2	27.3	25.9	21.8	17.7	12.3	8.2	4.1	5.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1212019

CATALOG NUMBER: GKO-PB2C-827-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1835.8	1835.8	1835.8
2.5°	1837.2	1835.8	1834.5
5°	1844.0	1842.6	1841.3
7.5°	1853.5	1853.5	1853.5
10°	1868.5	1871.3	1871.3
12.5°	1887.6	1890.4	1890.4
15°	1910.8	1912.2	1914.9
17.5°	1939.5	1940.8	1940.8
20°	1973.6	1972.2	1974.9
22.5°	2007.7	2007.7	2007.7
25°	2043.1	2043.1	2043.1
27.5°	2084.0	2084.0	2081.3
30°	2129.1	2129.1	2129.1
32.5°	2183.6	2185.0	2186.3
35°	2253.2	2255.9	2260.0
37.5°	2332.3	2339.1	2343.2
40°	2426.4	2429.1	2435.9
42.5°	2531.4	2539.6	2541.0
45°	2662.3	2676.0	2681.4
47.5°	2816.5	2835.6	2845.1
50°	2988.3	3010.1	3023.8
52.5°	3175.2	3210.6	3227.0
55°	3374.3	3435.7	3453.4
57.5°	3599.3	3682.5	3707.1
60°	3820.3	3937.6	3977.1
62.5°	4008.5	4173.5	4222.6
65°	4140.8	4339.9	4412.2
67.5°	4168.1	4404.0	4490.0
70°	4004.4	4245.8	4345.4
72.5°	3482.0	3700.3	3824.4
75°	2056.8	2213.6	2175.4
77.5°	1032.5	1077.5	1084.3
80°	452.8	480.1	491.0
82.5°	111.8	114.6	129.6
85°	15.0	17.7	16.4
87.5°	5.5	5.5	6.8
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP3-2511-595-2

Test Date: 11/12/2025

Luminaire Tested: GKO-PB1C-827-U-T4W

Data in this report applies to families of products including GKO-PB1C-827*

Test Information

Test Method: LM-79-2019
 Report Number: SP3-2511-595-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP3 - 3M SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/27/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-827-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 2740
 CIE u' : 0.2602
 CIE v' : 0.5290
 Duv: 0.0017
 CIE x: 0.4595
 CIE y: 0.4151
 CIE z: 0.1255
 Peak Wavelength (nm): 605
 Dominant Wavelength (nm): 583
 Purity: 62.5206
 R_f: 84.8
 R_g: 94.5

CRI (Ra): 81.1
 R1: 79.2
 R2: 90.4
 R3: 95.8
 R4: 79.2
 R5: 79.6
 R6: 89.5
 R7: 81.1
 R8: 54.5
 R9: -0.3
 R10: 79.1
 R11: 79.0
 R12: 72.7
 R13: 81.7
 R14: 98.3
 R15: 70.3



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2511-595-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	7/1/2025	1/1/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2511-595-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP3-2511-595-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	193	NR	620	932	NR	750	29	NR	880	1	NR
365	0	NR	495	235	NR	625	886	NR	755	25	NR	885	1	NR
370	0	NR	500	278	NR	630	832	NR	760	21	NR	890	0	NR
375	0	NR	505	318	NR	635	771	NR	765	18	NR	895	0	NR
380	0	NR	510	351	NR	640	708	NR	770	15	NR	900	0	NR
385	0	NR	515	380	NR	645	642	NR	775	13	NR	905	0	NR
390	0	NR	520	402	NR	650	578	NR	780	11	NR	910	0	NR
395	0	NR	525	423	NR	655	517	NR	785	9	NR	915	0	NR
400	1	NR	530	440	NR	660	457	NR	790	8	NR	920	0	NR
405	2	NR	535	460	NR	665	404	NR	795	7	NR	925	0	NR
410	5	NR	540	480	NR	670	352	NR	800	6	NR	930	0	NR
415	10	NR	545	507	NR	675	308	NR	805	5	NR	935	0	NR
420	19	NR	550	539	NR	680	267	NR	810	4	NR	940	0	NR
425	32	NR	555	574	NR	685	231	NR	815	4	NR	945	0	NR
430	55	NR	560	617	NR	690	198	NR	820	3	NR	950	0	NR
435	90	NR	565	668	NR	695	171	NR	825	3	NR	955	0	NR
440	151	NR	570	718	NR	700	146	NR	830	2	NR	960	0	NR
445	275	NR	575	777	NR	705	124	NR	835	2	NR	965	0	NR
450	381	NR	580	832	NR	710	106	NR	840	2	NR	970	0	NR
455	304	NR	585	886	NR	715	90	NR	845	2	NR	975	0	NR
460	227	NR	590	933	NR	720	77	NR	850	1	NR	980	0	NR
465	208	NR	595	970	NR	725	66	NR	855	1	NR	985	0	NR
470	167	NR	600	992	NR	730	56	NR	860	1	NR	990	0	NR
475	138	NR	605	1000	NR	735	47	NR	865	1	NR	995	0	NR
480	146	NR	610	991	NR	740	40	NR	870	1	NR	1000	0	NR
485	164	NR	615	969	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.22

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	193	NR	620	932	NR	750	29	NR	880	1	NR
365	0	NR	495	235	NR	625	886	NR	755	25	NR	885	1	NR
370	0	NR	500	278	NR	630	832	NR	760	21	NR	890	0	NR
375	0	NR	505	318	NR	635	771	NR	765	18	NR	895	0	NR
380	0	NR	510	351	NR	640	708	NR	770	15	NR	900	0	NR
385	0	NR	515	380	NR	645	642	NR	775	13	NR	905	0	NR
390	0	NR	520	402	NR	650	578	NR	780	11	NR	910	0	NR
395	0	NR	525	423	NR	655	517	NR	785	9	NR	915	0	NR
400	1	NR	530	440	NR	660	457	NR	790	8	NR	920	0	NR
405	2	NR	535	460	NR	665	404	NR	795	7	NR	925	0	NR
410	5	NR	540	480	NR	670	352	NR	800	6	NR	930	0	NR
415	10	NR	545	507	NR	675	308	NR	805	5	NR	935	0	NR
420	19	NR	550	539	NR	680	267	NR	810	4	NR	940	0	NR
425	32	NR	555	574	NR	685	231	NR	815	4	NR	945	0	NR
430	55	NR	560	617	NR	690	198	NR	820	3	NR	950	0	NR
435	90	NR	565	668	NR	695	171	NR	825	3	NR	955	0	NR
440	151	NR	570	718	NR	700	146	NR	830	2	NR	960	0	NR
445	275	NR	575	777	NR	705	124	NR	835	2	NR	965	0	NR
450	381	NR	580	832	NR	710	106	NR	840	2	NR	970	0	NR
455	304	NR	585	886	NR	715	90	NR	845	2	NR	975	0	NR
460	227	NR	590	933	NR	720	77	NR	850	1	NR	980	0	NR
465	208	NR	595	970	NR	725	66	NR	855	1	NR	985	0	NR
470	167	NR	600	992	NR	730	56	NR	860	1	NR	990	0	NR
475	138	NR	605	1000	NR	735	47	NR	865	1	NR	995	0	NR
480	146	NR	610	991	NR	740	40	NR	870	1	NR	1000	0	NR
485	164	NR	615	969	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-2

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.26


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	193	NR	620	932	NR	750	29	NR	880	1	NR
365	0	NR	495	235	NR	625	886	NR	755	25	NR	885	1	NR
370	0	NR	500	278	NR	630	832	NR	760	21	NR	890	0	NR
375	0	NR	505	318	NR	635	771	NR	765	18	NR	895	0	NR
380	0	NR	510	351	NR	640	708	NR	770	15	NR	900	0	NR
385	0	NR	515	380	NR	645	642	NR	775	13	NR	905	0	NR
390	0	NR	520	402	NR	650	578	NR	780	11	NR	910	0	NR
395	0	NR	525	423	NR	655	517	NR	785	9	NR	915	0	NR
400	1	NR	530	440	NR	660	457	NR	790	8	NR	920	0	NR
405	2	NR	535	460	NR	665	404	NR	795	7	NR	925	0	NR
410	5	NR	540	480	NR	670	352	NR	800	6	NR	930	0	NR
415	10	NR	545	507	NR	675	308	NR	805	5	NR	935	0	NR
420	19	NR	550	539	NR	680	267	NR	810	4	NR	940	0	NR
425	32	NR	555	574	NR	685	231	NR	815	4	NR	945	0	NR
430	55	NR	560	617	NR	690	198	NR	820	3	NR	950	0	NR
435	90	NR	565	668	NR	695	171	NR	825	3	NR	955	0	NR
440	151	NR	570	718	NR	700	146	NR	830	2	NR	960	0	NR
445	275	NR	575	777	NR	705	124	NR	835	2	NR	965	0	NR
450	381	NR	580	832	NR	710	106	NR	840	2	NR	970	0	NR
455	304	NR	585	886	NR	715	90	NR	845	2	NR	975	0	NR
460	227	NR	590	933	NR	720	77	NR	850	1	NR	980	0	NR
465	208	NR	595	970	NR	725	66	NR	855	1	NR	985	0	NR
470	167	NR	600	992	NR	730	56	NR	860	1	NR	990	0	NR
475	138	NR	605	1000	NR	735	47	NR	865	1	NR	995	0	NR
480	146	NR	610	991	NR	740	40	NR	870	1	NR	1000	0	NR
485	164	NR	615	969	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-2





TM-30-18

Summary

$R_f = 84.8$
 $R_g = 94.5$
 $CIE\ R_a = 81.1$
 $R_g = -0.3$




Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 85	CES51 = 94	CES76 = 82
CES02 = 63	CES27 = 95	CES52 = 93	CES77 = 84
CES03 = 31	CES28 = 95	CES53 = 89	CES78 = 82
CES04 = 71	CES29 = 88	CES54 = 91	CES79 = 89
CES05 = 50	CES30 = 95	CES55 = 90	CES80 = 89
CES06 = 52	CES31 = 89	CES56 = 86	CES81 = 68
CES07 = 43	CES32 = 83	CES57 = 85	CES82 = 96
CES08 = 41	CES33 = 92	CES58 = 86	CES83 = 93
CES09 = 29	CES34 = 92	CES59 = 91	CES84 = 92
CES10 = 77	CES35 = 96	CES60 = 93	CES85 = 75
CES11 = 60	CES36 = 89	CES61 = 89	CES86 = 65
CES12 = 66	CES37 = 96	CES62 = 93	CES87 = 84
CES13 = 44	CES38 = 97	CES63 = 87	CES88 = 86
CES14 = 74	CES39 = 98	CES64 = 82	CES89 = 73
CES15 = 72	CES40 = 95	CES65 = 79	CES90 = 88
CES16 = 48	CES41 = 96	CES66 = 81	CES91 = 81
CES17 = 50	CES42 = 98	CES67 = 80	CES92 = 64
CES18 = 57	CES43 = 91	CES68 = 83	CES93 = 78
CES19 = 73	CES44 = 99	CES69 = 88	CES94 = 59
CES20 = 67	CES45 = 93	CES70 = 80	CES95 = 74
CES21 = 87	CES46 = 89	CES71 = 79	CES96 = 83
CES22 = 79	CES47 = 92	CES72 = 92	CES97 = 88
CES23 = 92	CES48 = 83	CES73 = 76	CES98 = 84
CES24 = 91	CES49 = 90	CES74 = 91	CES99 = 75
CES25 = 72	CES50 = 94	CES75 = 81	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)