

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1211856

Luminaire Tested: **GKO-PB1A-835-U-T3**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1211856
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1A-835-U-T3
Description: GEKKO WALL PACK 750LM PACKAGE 80CRI 3500K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source: (10) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 687.4 lumens
Efficiency: N/A
Efficacy: 143.2 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B0 - U0 - G0

Input Watts (W): 4.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 16%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1211856
 CATALOG NUMBER: GKO-PB1A-835-U-T3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 0.6 fc
 Type III - Medium - N/A

REPORT NUMBER: P1211856
CATALOG NUMBER: GKO-PB1A-835-U-T3

Luminous Intensity Polar Plot



REPORT NUMBER: P1211856

CATALOG NUMBER: GKO-PB1A-835-U-T3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	176.0	0.0	176.0
	% Fixture	25.6	0.0	25.6
Street Side	Lumens	511.4	0.0	511.4
	% Fixture	74.4	0.0	74.4
Total	Lumens	687.4	0.0	687.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.1	1.6
10°-20°	33.2	4.8
20°-30°	57.3	8.3
30°-40°	88.9	12.9
40°-50°	121.7	17.7
50°-60°	145.2	21.1
60°-70°	145.5	21.2
70°-80°	77.0	11.2
80°-90°	7.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	687.4	100.0
0°-180°	687.4	100.0



REPORT NUMBER: P1211856


CATALOG NUMBER: GKO-PB1A-835-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	60.7	8.8			
FM	(30°-60°)	269.1	39.2			
FH	(60°-80°)	178.6	26.0			G0/660
FVH	(80°-90°)	2.9	0.4			G0/10
BL	(0°-30°)	40.9	5.9	B0/110		
BM	(30°-60°)	86.7	12.6	B0/220		
BH	(60°-80°)	43.9	6.4	B0/110		G0/110
BVH	(80°-90°)	4.5	0.7			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G0

Type III Medium





REPORT NUMBER: P1211856

CATALOG NUMBER: GKO-PB1A-835-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3
2.5°	120.1	120.1	119.8	119.7	119.6	118.8	118.2	117.6	117.6	116.5	115.6
5°	124.2	124.4	123.8	123.8	123.3	122.2	121.2	119.8	119.8	118.2	116.4
7.5°	127.8	128.2	127.7	127.7	127.2	126.0	124.2	122.4	122.4	120.1	117.4
10°	131.3	131.6	131.3	131.6	130.8	129.7	127.7	125.2	125.0	122.2	118.5
12.5°	134.1	134.4	134.5	134.9	134.2	133.4	131.6	128.4	128.0	124.6	119.8
15°	136.8	137.0	137.4	138.0	137.8	137.2	135.4	131.8	131.6	127.3	121.6
17.5°	138.9	139.0	139.8	140.9	141.2	141.3	139.4	135.7	135.4	130.4	123.4
20°	142.0	142.2	143.0	144.1	144.9	145.5	144.0	139.8	139.6	134.0	125.8
22.5°	148.9	148.5	148.9	148.9	149.3	150.1	149.1	144.9	144.4	138.2	128.8
25°	162.0	161.6	160.5	158.1	155.5	155.3	154.1	150.1	149.5	142.6	131.6
27.5°	180.3	179.3	177.3	172.3	165.9	161.7	159.9	155.7	154.9	147.1	134.2
30°	199.6	200.7	197.4	190.4	178.7	169.9	166.3	161.6	160.9	152.0	137.4
32.5°	222.2	222.3	219.0	209.4	194.2	180.1	174.0	168.3	167.7	157.7	141.7
35°	235.3	235.8	234.3	225.4	208.0	191.5	183.3	176.4	176.0	164.9	147.1
37.5°	248.9	250.1	247.8	237.9	218.6	202.0	193.8	186.1	185.7	173.2	153.7
40°	269.0	268.5	266.1	251.5	228.5	210.8	204.0	198.0	197.1	183.3	160.5
42.5°	283.6	284.9	279.7	263.3	239.3	219.6	214.3	207.5	206.3	189.5	164.5
45°	288.5	287.3	281.6	269.6	253.4	227.6	224.0	218.8	217.6	200.3	172.4
47.5°	289.6	287.4	282.4	273.3	265.4	238.1	235.9	234.7	233.0	213.9	181.9
50°	283.0	281.6	279.2	274.6	273.2	247.8	248.9	253.3	251.8	228.6	192.4
52.5°	268.2	267.5	269.7	272.6	268.7	256.2	264.2	273.2	272.6	244.7	203.8
55°	240.3	240.3	252.3	262.6	264.9	261.7	280.8	296.1	295.4	262.9	214.6
57.5°	214.8	215.2	225.2	248.3	257.9	267.5	299.2	320.1	319.1	283.3	225.9
60°	182.7	182.7	197.9	226.8	247.9	272.1	315.5	343.3	344.0	303.0	237.1
62.5°	144.6	145.0	166.1	200.2	233.5	272.9	328.4	365.2	365.1	320.9	245.8
65°	106.6	106.8	135.4	170.5	211.9	267.3	335.5	382.0	382.8	335.1	250.9
67.5°	69.3	70.6	99.7	138.4	181.3	251.4	331.7	391.0	391.9	341.6	249.3
68°	64.9	65.1	94.3	129.6	173.1	247.4	330.0	391.4	392.2	341.5	247.7
70°	42.0	42.0	67.5	101.1	138.1	222.4	314.9	385.1	386.0	335.6	236.1
72.5°	22.7	23.1	38.6	61.2	94.3	172.1	284.2	352.4	354.0	303.4	206.4
75°	15.9	16.1	22.4	34.3	51.4	112.1	222.2	269.3	269.0	209.6	129.3
77.5°	11.5	11.5	12.8	21.4	27.0	51.2	110.0	129.7	128.2	102.3	65.3
80°	7.5	7.5	8.0	11.2	12.9	15.6	33.6	56.2	57.2	49.9	32.6
82.5°	3.1	3.2	3.5	4.5	4.7	6.5	9.6	16.1	15.6	12.7	9.2
85°	0.4	0.4	0.5	0.7	0.8	1.5	1.3	1.3	1.3	1.6	1.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.3	0.4	0.4	0.5	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1211856

CATALOG NUMBER: GKO-PB1A-835-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3	115.3
2.5°	115.3	115.3	114.5	113.7	112.9	112.2	111.3	110.6	110.8	111.2	111.0
5°	116.0	115.3	113.7	112.0	110.6	109.4	107.7	106.8	106.6	106.9	106.8
7.5°	116.4	115.3	112.9	110.2	108.1	106.5	104.1	103.1	102.7	102.9	102.9
10°	117.2	115.4	112.1	108.4	105.7	103.4	100.9	99.5	99.1	99.1	99.0
12.5°	118.1	115.7	111.3	106.8	103.3	100.6	97.7	96.2	95.8	95.8	95.7
15°	119.0	116.1	110.5	105.0	101.0	97.8	95.0	93.3	92.7	92.7	93.0
17.5°	120.2	116.5	109.7	103.4	98.6	95.0	92.1	90.3	89.7	90.1	90.3
20°	121.4	117.3	108.9	101.7	96.2	92.5	89.5	87.8	87.1	87.8	87.9
22.5°	123.2	118.0	108.0	99.7	93.8	89.7	87.0	85.4	85.0	85.7	86.2
25°	124.9	118.8	106.8	97.5	90.7	86.7	84.6	83.4	83.5	84.5	85.0
27.5°	126.8	119.4	105.6	94.9	87.4	83.7	82.1	81.8	82.3	83.4	84.1
30°	129.0	120.4	104.0	91.8	83.7	80.3	79.7	80.5	81.4	82.5	83.1
32.5°	132.0	121.6	102.3	88.3	79.8	76.7	77.8	79.5	80.6	81.7	82.3
35°	136.1	124.0	101.4	84.9	75.7	73.7	76.1	78.9	79.7	80.3	81.1
37.5°	140.9	127.2	101.0	81.7	71.9	71.0	74.3	77.7	77.9	78.2	79.0
40°	145.6	129.6	99.9	78.2	68.1	68.1	72.2	75.4	75.3	74.9	75.4
42.5°	147.5	129.3	96.9	74.9	65.0	65.1	68.9	71.9	71.1	71.1	71.9
45°	152.8	131.4	94.6	72.2	62.2	61.6	64.6	67.0	68.3	70.1	70.9
47.5°	159.6	134.4	92.9	69.1	59.5	57.8	59.4	63.4	65.7	67.5	68.2
50°	166.7	137.7	91.3	65.9	56.8	53.4	54.2	58.6	60.6	61.5	61.9
52.5°	173.9	140.8	90.1	63.3	53.8	48.2	49.9	54.0	55.5	56.0	56.3
55°	180.3	143.3	89.0	61.0	50.3	44.0	45.4	49.6	50.7	51.2	51.6
57.5°	187.1	146.1	88.3	58.8	46.4	40.4	41.4	45.2	46.7	47.2	47.6
60°	193.1	148.8	87.8	56.6	42.8	37.2	37.8	41.5	43.1	43.4	43.8
62.5°	197.1	150.5	87.0	53.8	39.5	34.2	34.3	37.9	39.6	39.9	40.2
65°	198.2	150.1	84.6	50.0	36.2	31.1	31.1	34.6	36.4	37.4	37.8
67.5°	195.0	146.8	79.5	45.2	33.0	28.3	28.3	31.4	33.4	34.4	34.8
68°	193.9	145.3	77.9	44.0	32.2	27.6	27.6	30.8	32.7	33.6	33.9
70°	184.8	138.1	70.6	39.5	29.6	25.6	25.6	28.4	30.4	30.4	30.3
72.5°	160.5	119.7	58.0	33.1	25.9	22.7	23.1	25.8	26.4	27.1	27.0
75°	99.4	71.7	39.0	26.2	21.8	19.9	20.7	23.1	23.5	25.0	24.6
77.5°	49.8	35.1	20.7	15.2	16.8	17.1	18.5	20.3	21.5	23.1	22.0
80°	24.6	17.1	12.1	9.5	9.9	12.5	16.1	17.5	19.6	20.7	19.7
82.5°	6.8	5.2	4.9	5.2	7.3	9.7	12.7	15.5	18.3	19.2	17.9
85°	1.2	0.9	0.8	2.5	5.1	7.2	10.3	13.7	16.4	15.7	14.8
87.5°	0.4	0.3	0.3	1.6	3.7	5.9	8.8	12.3	14.0	12.7	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-3

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-835-U-T4W

Data in this report applies to families of products including GKO-PB1C

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-835-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3422
 CIE u' : 0.2372
 CIE v' : 0.5144
 Duv: 0.0012
 CIE x: 0.4111
 CIE y: 0.3962
 CIE z: 0.1928
 Peak Wavelength (nm): 598
 Dominant Wavelength (nm): 580
 Purity: 42.28884
 R_f: 83.9
 R_g: 95.8

CRI (Ra): 81.5
 R1: 79.2
 R2: 88.7
 R3: 96.3
 R4: 80.3
 R5: 79.7
 R6: 85.6
 R7: 83.5
 R8: 58.4
 R9: -1.4
 R10: 74.4
 R11: 79.7
 R12: 66.0
 R13: 81.3
 R14: 98.3
 R15: 71.2



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-595-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	278	NR	620	878	NR	750	23	NR	880	1	NR
365	0	NR	495	338	NR	625	823	NR	755	20	NR	885	0	NR
370	0	NR	500	398	NR	630	763	NR	760	17	NR	890	0	NR
375	0	NR	505	448	NR	635	697	NR	765	14	NR	895	0	NR
380	0	NR	510	490	NR	640	633	NR	770	12	NR	900	0	NR
385	1	NR	515	527	NR	645	568	NR	775	10	NR	905	0	NR
390	2	NR	520	550	NR	650	508	NR	780	9	NR	910	0	NR
395	3	NR	525	571	NR	655	450	NR	785	7	NR	915	0	NR
400	5	NR	530	589	NR	660	395	NR	790	6	NR	920	0	NR
405	8	NR	535	610	NR	665	345	NR	795	5	NR	925	0	NR
410	13	NR	540	631	NR	670	299	NR	800	5	NR	930	0	NR
415	21	NR	545	656	NR	675	259	NR	805	4	NR	935	0	NR
420	37	NR	550	685	NR	680	223	NR	810	4	NR	940	0	NR
425	65	NR	555	717	NR	685	191	NR	815	3	NR	945	0	NR
430	114	NR	560	758	NR	690	164	NR	820	3	NR	950	0	NR
435	198	NR	565	799	NR	695	139	NR	825	2	NR	955	0	NR
440	359	NR	570	841	NR	700	118	NR	830	2	NR	960	0	NR
445	663	NR	575	883	NR	705	101	NR	835	2	NR	965	0	NR
450	782	NR	580	924	NR	710	86	NR	840	1	NR	970	0	NR
455	533	NR	585	954	NR	715	73	NR	845	1	NR	975	0	NR
460	398	NR	590	982	NR	720	62	NR	850	1	NR	980	0	NR
465	341	NR	595	999	NR	725	52	NR	855	1	NR	985	0	NR
470	244	NR	600	996	NR	730	44	NR	860	1	NR	990	0	NR
475	204	NR	605	984	NR	735	37	NR	865	1	NR	995	0	NR
480	214	NR	610	960	NR	740	32	NR	870	1	NR	1000	0	NR
485	236	NR	615	923	NR	745	27	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-3

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.48

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	278	NR	620	878	NR	750	23	NR	880	1	NR
365	0	NR	495	338	NR	625	823	NR	755	20	NR	885	0	NR
370	0	NR	500	398	NR	630	763	NR	760	17	NR	890	0	NR
375	0	NR	505	448	NR	635	697	NR	765	14	NR	895	0	NR
380	0	NR	510	490	NR	640	633	NR	770	12	NR	900	0	NR
385	1	NR	515	527	NR	645	568	NR	775	10	NR	905	0	NR
390	2	NR	520	550	NR	650	508	NR	780	9	NR	910	0	NR
395	3	NR	525	571	NR	655	450	NR	785	7	NR	915	0	NR
400	5	NR	530	589	NR	660	395	NR	790	6	NR	920	0	NR
405	8	NR	535	610	NR	665	345	NR	795	5	NR	925	0	NR
410	13	NR	540	631	NR	670	299	NR	800	5	NR	930	0	NR
415	21	NR	545	656	NR	675	259	NR	805	4	NR	935	0	NR
420	37	NR	550	685	NR	680	223	NR	810	4	NR	940	0	NR
425	65	NR	555	717	NR	685	191	NR	815	3	NR	945	0	NR
430	114	NR	560	758	NR	690	164	NR	820	3	NR	950	0	NR
435	198	NR	565	799	NR	695	139	NR	825	2	NR	955	0	NR
440	359	NR	570	841	NR	700	118	NR	830	2	NR	960	0	NR
445	663	NR	575	883	NR	705	101	NR	835	2	NR	965	0	NR
450	782	NR	580	924	NR	710	86	NR	840	1	NR	970	0	NR
455	533	NR	585	954	NR	715	73	NR	845	1	NR	975	0	NR
460	398	NR	590	982	NR	720	62	NR	850	1	NR	980	0	NR
465	341	NR	595	999	NR	725	52	NR	855	1	NR	985	0	NR
470	244	NR	600	996	NR	730	44	NR	860	1	NR	990	0	NR
475	204	NR	605	984	NR	735	37	NR	865	1	NR	995	0	NR
480	214	NR	610	960	NR	740	32	NR	870	1	NR	1000	0	NR
485	236	NR	615	923	NR	745	27	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-3

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.92

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	278	NR	620	878	NR	750	23	NR	880	1	NR
365	0	NR	495	338	NR	625	823	NR	755	20	NR	885	0	NR
370	0	NR	500	398	NR	630	763	NR	760	17	NR	890	0	NR
375	0	NR	505	448	NR	635	697	NR	765	14	NR	895	0	NR
380	0	NR	510	490	NR	640	633	NR	770	12	NR	900	0	NR
385	1	NR	515	527	NR	645	568	NR	775	10	NR	905	0	NR
390	2	NR	520	550	NR	650	508	NR	780	9	NR	910	0	NR
395	3	NR	525	571	NR	655	450	NR	785	7	NR	915	0	NR
400	5	NR	530	589	NR	660	395	NR	790	6	NR	920	0	NR
405	8	NR	535	610	NR	665	345	NR	795	5	NR	925	0	NR
410	13	NR	540	631	NR	670	299	NR	800	5	NR	930	0	NR
415	21	NR	545	656	NR	675	259	NR	805	4	NR	935	0	NR
420	37	NR	550	685	NR	680	223	NR	810	4	NR	940	0	NR
425	65	NR	555	717	NR	685	191	NR	815	3	NR	945	0	NR
430	114	NR	560	758	NR	690	164	NR	820	3	NR	950	0	NR
435	198	NR	565	799	NR	695	139	NR	825	2	NR	955	0	NR
440	359	NR	570	841	NR	700	118	NR	830	2	NR	960	0	NR
445	663	NR	575	883	NR	705	101	NR	835	2	NR	965	0	NR
450	782	NR	580	924	NR	710	86	NR	840	1	NR	970	0	NR
455	533	NR	585	954	NR	715	73	NR	845	1	NR	975	0	NR
460	398	NR	590	982	NR	720	62	NR	850	1	NR	980	0	NR
465	341	NR	595	999	NR	725	52	NR	855	1	NR	985	0	NR
470	244	NR	600	996	NR	730	44	NR	860	1	NR	990	0	NR
475	204	NR	605	984	NR	735	37	NR	865	1	NR	995	0	NR
480	214	NR	610	960	NR	740	32	NR	870	1	NR	1000	0	NR
485	236	NR	615	923	NR	745	27	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-3




TM-30-18

Summary

$R_f = 83.9$
 $R_g = 95.8$
 $CIE R_a = 81.5$
 $R_g = -1.4$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 81	CES51 = 95	CES76 = 76
CES02 = 62	CES27 = 94	CES52 = 94	CES77 = 84
CES03 = 31	CES28 = 92	CES53 = 89	CES78 = 75
CES04 = 70	CES29 = 84	CES54 = 91	CES79 = 91
CES05 = 49	CES30 = 94	CES55 = 90	CES80 = 89
CES06 = 51	CES31 = 86	CES56 = 85	CES81 = 76
CES07 = 41	CES32 = 80	CES57 = 85	CES82 = 95
CES08 = 40	CES33 = 90	CES58 = 86	CES83 = 95
CES09 = 29	CES34 = 87	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 93	CES60 = 92	CES85 = 78
CES11 = 58	CES36 = 87	CES61 = 88	CES86 = 70
CES12 = 64	CES37 = 93	CES62 = 91	CES87 = 83
CES13 = 43	CES38 = 98	CES63 = 86	CES88 = 87
CES14 = 74	CES39 = 98	CES64 = 81	CES89 = 75
CES15 = 71	CES40 = 94	CES65 = 77	CES90 = 88
CES16 = 47	CES41 = 97	CES66 = 78	CES91 = 77
CES17 = 50	CES42 = 94	CES67 = 77	CES92 = 63
CES18 = 56	CES43 = 89	CES68 = 80	CES93 = 78
CES19 = 72	CES44 = 99	CES69 = 85	CES94 = 60
CES20 = 66	CES45 = 93	CES70 = 76	CES95 = 73
CES21 = 86	CES46 = 89	CES71 = 73	CES96 = 83
CES22 = 78	CES47 = 93	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 84	CES73 = 70	CES98 = 84
CES24 = 91	CES49 = 89	CES74 = 94	CES99 = 74
CES25 = 72	CES50 = 94	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)