

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1212044

Luminaire Tested: **GKO-PB1C-840-U-T1**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1212044
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1C-840-U-T1
Description: GEKKO WALL PACK 2500LM PACKAGE 80CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (10) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2497.8 lumens
Efficiency: N/A
Efficacy: 146.9 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 17
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 13%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1212044
 CATALOG NUMBER: GKO-PB1C-840-U-T1

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd


--- 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 2.8 fc
 Type I - Short - N/A

REPORT NUMBER: P1212044
CATALOG NUMBER: GKO-PB1C-840-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1212044

CATALOG NUMBER: GKO-PB1C-840-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1248.9	0.0	1248.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	1248.9	0.0	1248.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	2497.8	0.0	2497.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.4	2.4
10°-20°	179.1	7.2
20°-30°	297.9	11.9
30°-40°	395.7	15.8
40°-50°	446.1	17.9
50°-60°	458.7	18.4
60°-70°	433.5	17.4
70°-80°	212.2	8.5
80°-90°	15.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2497.8	100.0
0°-180°	2497.8	100.0

Coefficient of Utilization



REPORT NUMBER: P1212044


CATALOG NUMBER: GKO-PB1C-840-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	268.2	10.7			
FM	(30°-60°)	650.2	26.0			
FH	(60°-80°)	322.9	12.9			G0/660
FVH	(80°-90°)	7.6	0.3			G0/10
BL	(0°-30°)	268.2	10.7	B1/500		
BM	(30°-60°)	650.2	26.0	B1/1000		
BH	(60°-80°)	322.9	12.9	B1/500		G1/500
BVH	(80°-90°)	7.6	0.3			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type I Short





REPORT NUMBER: P1212044

CATALOG NUMBER: GKO-PB1C-840-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	619.8	619.8	619.8	619.8	619.8	619.8	619.8	619.8	619.8	619.8	619.8
2.5°	620.3	621.2	619.3	619.3	620.3	620.7	620.7	621.2	620.3	620.3	619.8
5°	620.3	620.7	619.8	619.8	620.7	622.1	621.6	622.6	622.6	622.1	622.1
7.5°	619.8	620.7	619.8	620.3	621.6	624.4	624.4	624.4	625.3	626.2	626.2
10°	619.3	620.3	620.7	621.2	623.0	627.2	628.1	628.5	629.9	631.3	631.3
12.5°	617.0	618.0	619.3	621.2	624.4	629.9	631.8	633.2	635.5	636.8	637.8
15°	613.8	614.3	617.5	621.2	626.2	633.2	636.8	639.1	642.4	644.2	645.6
17.5°	609.2	609.7	614.7	620.3	627.6	637.3	643.3	647.0	650.2	653.0	654.8
20°	603.2	604.6	610.6	619.3	629.9	641.4	650.2	656.6	659.9	662.6	665.4
22.5°	595.9	597.2	604.6	617.0	632.2	647.0	658.5	666.8	670.9	674.6	677.8
25°	584.8	586.6	595.4	611.5	633.2	653.0	667.7	678.3	682.0	686.6	689.3
27.5°	567.8	569.1	579.7	600.5	630.4	659.4	678.3	690.7	694.9	699.9	702.7
30°	541.1	543.8	556.7	582.5	623.5	664.5	690.7	703.1	708.2	713.3	717.0
32.5°	506.5	510.7	524.9	558.1	610.1	666.3	704.1	718.3	724.8	730.3	734.9
35°	463.7	467.8	484.9	526.8	588.9	662.6	717.4	735.8	743.7	751.0	756.6
37.5°	414.9	418.6	439.3	487.2	558.6	651.1	728.0	755.2	765.8	775.4	782.8
40°	365.6	369.8	392.3	443.4	521.7	629.0	732.6	776.4	789.7	802.1	811.4
42.5°	312.2	317.3	342.6	396.9	478.9	598.6	728.9	797.1	813.7	830.7	844.5
45°	264.8	265.7	293.3	345.8	431.9	559.5	716.0	816.9	839.4	863.4	883.2
47.5°	219.2	221.0	245.0	297.0	383.1	515.3	692.6	832.5	868.5	899.3	928.3
50°	178.7	181.0	202.6	249.1	334.3	466.9	660.8	841.8	893.3	935.2	975.7
52.5°	145.5	148.3	166.2	207.2	285.0	416.3	621.6	843.1	915.9	971.1	1025.0
55°	121.1	122.9	136.8	169.5	237.6	363.8	577.0	836.2	930.6	1003.4	1075.2
57.5°	102.2	104.1	113.7	139.5	194.8	309.9	522.6	820.1	938.5	1031.5	1125.9
60°	88.9	90.3	97.2	115.6	160.2	259.2	464.2	791.6	936.1	1049.0	1167.8
62.5°	79.2	79.7	85.6	98.5	132.2	211.4	398.3	748.7	917.3	1051.3	1196.3
65°	70.5	70.9	74.6	83.8	108.7	169.9	329.7	689.8	881.4	1035.2	1200.5
67.5°	57.1	58.0	63.5	70.5	89.3	134.5	259.7	612.4	825.2	993.2	1177.0
70°	45.6	46.0	51.6	59.4	72.8	105.9	199.4	508.4	737.2	925.1	1116.2
72.5°	34.1	35.0	40.1	47.9	59.4	82.0	144.1	384.5	589.4	780.0	972.1
75°	27.2	27.6	29.5	36.8	46.0	62.2	97.2	233.0	355.0	482.6	595.9
77.5°	23.0	23.5	23.5	28.5	34.1	41.9	51.6	92.6	150.1	213.7	283.2
80°	18.9	19.8	18.0	21.2	24.4	24.4	23.9	44.2	70.9	100.4	131.7
82.5°	13.8	14.7	13.8	14.7	14.7	13.4	12.4	16.6	22.6	30.9	33.6
85°	9.7	10.1	11.1	10.1	9.7	7.8	6.0	4.6	2.8	3.2	4.6
87.5°	6.4	7.8	9.2	8.7	7.4	6.0	4.1	2.8	1.4	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1212044
 CATALOG NUMBER: GKO-PB1C-840-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	619.8	619.8	619.8
2.5°	620.3	619.8	619.3
5°	622.6	622.1	621.6
7.5°	625.8	625.8	625.8
10°	630.9	631.8	631.8
12.5°	637.3	638.2	638.2
15°	645.1	645.6	646.5
17.5°	654.8	655.3	655.3
20°	666.3	665.8	666.8
22.5°	677.8	677.8	677.8
25°	689.8	689.8	689.8
27.5°	703.6	703.6	702.7
30°	718.8	718.8	718.8
32.5°	737.2	737.7	738.1
35°	760.7	761.6	763.0
37.5°	787.4	789.7	791.1
40°	819.2	820.1	822.4
42.5°	854.6	857.4	857.9
45°	898.8	903.5	905.3
47.5°	950.9	957.3	960.6
50°	1008.9	1016.3	1020.9
52.5°	1072.0	1084.0	1089.5
55°	1139.2	1159.9	1165.9
57.5°	1215.2	1243.3	1251.6
60°	1289.8	1329.4	1342.7
62.5°	1353.3	1409.1	1425.6
65°	1398.0	1465.2	1489.6
67.5°	1407.2	1486.9	1515.9
70°	1352.0	1433.5	1467.1
72.5°	1175.6	1249.3	1291.2
75°	694.4	747.4	734.5
77.5°	348.6	363.8	366.1
80°	152.9	162.1	165.8
82.5°	37.8	38.7	43.7
85°	5.1	6.0	5.5
87.5°	1.8	1.8	2.3
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP3-2511-595-3

Test Date: 11/12/2025

Luminaire Tested: GKO-PB1C-840-U-T4W

Data in this report applies to families of products including GKO-PB1C-840*


Test Information

Test Method: LM-79-2019
 Report Number: SP3-2511-595-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP3 - 3M SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/27/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-840-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3958
 CIE u' : 0.2251
 CIE v' : 0.5041
 Duv: 0.0014
 CIE x: 0.3833
 CIE y: 0.3816
 CIE z: 0.2351
 Peak Wavelength (nm): 450
 Dominant Wavelength (nm): 578
 Purity: 29.56261
 R_f: 82.9
 R_g: 94.7

CRI (Ra): 80.8
 R1: 78.3
 R2: 87.6
 R3: 95.0
 R4: 79.6
 R5: 78.8
 R6: 83.3
 R7: 84.3
 R8: 59.4
 R9: -5.1
 R10: 71.4
 R11: 78.5
 R12: 60.5
 R13: 80.5
 R14: 97.5
 R15: 70.7



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2511-595-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	7/1/2025	1/1/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2511-595-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3


Scotopic Flux vs. Wavelength


Scotopic Lumens: NR
S/P: 1.65

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.36


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3





TM-30-18

Summary

$R_f = 82.9$
 $R_g = 94.7$
 $CIE R_a = 80.8$
 $R_g = -5.1$




Color Vector Graphics







Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 80	CES51 = 94	CES76 = 73
CES02 = 61	CES27 = 93	CES52 = 94	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 88	CES78 = 72
CES04 = 70	CES29 = 85	CES54 = 89	CES79 = 91
CES05 = 48	CES30 = 96	CES55 = 88	CES80 = 89
CES06 = 50	CES31 = 87	CES56 = 84	CES81 = 79
CES07 = 40	CES32 = 80	CES57 = 83	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 84	CES83 = 95
CES09 = 29	CES34 = 86	CES59 = 90	CES84 = 90
CES10 = 74	CES35 = 92	CES60 = 90	CES85 = 78
CES11 = 57	CES36 = 83	CES61 = 86	CES86 = 72
CES12 = 63	CES37 = 91	CES62 = 86	CES87 = 83
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 87
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 76
CES15 = 71	CES40 = 95	CES65 = 75	CES90 = 87
CES16 = 47	CES41 = 99	CES66 = 74	CES91 = 71
CES17 = 49	CES42 = 93	CES67 = 73	CES92 = 62
CES18 = 56	CES43 = 89	CES68 = 77	CES93 = 77
CES19 = 71	CES44 = 99	CES69 = 82	CES94 = 60
CES20 = 65	CES45 = 93	CES70 = 73	CES95 = 70
CES21 = 86	CES46 = 90	CES71 = 67	CES96 = 82
CES22 = 78	CES47 = 96	CES72 = 89	CES97 = 90
CES23 = 91	CES48 = 84	CES73 = 66	CES98 = 84
CES24 = 90	CES49 = 89	CES74 = 93	CES99 = 73
CES25 = 71	CES50 = 94	CES75 = 70	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)