

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1212047

Luminaire Tested: **GKO-PB2E-840-U-T1**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1212047
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2E-840-U-T1
Description: GEKKO WALL PACK 12000LM PACKAGE 80CRI 4000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12444.7 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B3 - U0 - G3

Input Watts (W): 104.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 6%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT


REPORT NUMBER: P1212047

CATALOG NUMBER: GKO-PB2E-840-U-T1

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 13.7 fc

Type I - Short - N/A

REPORT NUMBER: P1212047
CATALOG NUMBER: GKO-PB2E-840-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1212047

CATALOG NUMBER: GKO-PB2E-840-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6222.4	0.0	6222.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6222.4	0.0	6222.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	12444.7	0.0	12444.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.2	2.4
10°-20°	892.5	7.2
20°-30°	1484.0	11.9
30°-40°	1971.4	15.8
40°-50°	2222.6	17.9
50°-60°	2285.4	18.4
60°-70°	2159.8	17.4
70°-80°	1057.3	8.5
80°-90°	75.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12444.7	100.0
0°-180°	12444.7	100.0

Coefficient of Utilization



REPORT NUMBER: P1212047


CATALOG NUMBER: GKO-PB2E-840-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1336.3	10.7			
FM	(30°-60°)	3239.7	26.0			
FH	(60°-80°)	1608.5	12.9			G1/1800
FVH	(80°-90°)	37.8	0.3			G1/100
BL	(0°-30°)	1336.3	10.7	B3/2500		
BM	(30°-60°)	3239.7	26.0	B3/5000		
BH	(60°-80°)	1608.5	12.9	B3/2500		G3/2500
BVH	(80°-90°)	37.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type I Short



REPORT NUMBER: P1212047

CATALOG NUMBER: GKO-PB2E-840-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3088.0	3088.0	3088.0	3088.0	3088.0	3088.0	3088.0	3088.0	3088.0	3088.0	3088.0
2.5°	3090.3	3094.9	3085.8	3085.8	3090.3	3092.6	3092.6	3094.9	3090.3	3090.3	3088.0
5°	3090.3	3092.6	3088.0	3088.0	3092.6	3099.5	3097.2	3101.8	3101.8	3099.5	3099.5
7.5°	3088.0	3092.6	3088.0	3090.3	3097.2	3111.0	3111.0	3111.0	3115.6	3120.2	3120.2
10°	3085.8	3090.3	3092.6	3094.9	3104.1	3124.8	3129.3	3131.6	3138.5	3145.4	3145.4
12.5°	3074.3	3078.9	3085.8	3094.9	3111.0	3138.5	3147.7	3154.6	3166.1	3172.9	3177.5
15°	3058.2	3060.5	3076.6	3094.9	3120.2	3154.6	3172.9	3184.4	3200.5	3209.6	3216.5
17.5°	3035.3	3037.6	3062.8	3090.3	3127.0	3175.2	3205.1	3223.4	3239.5	3253.2	3262.4
20°	3005.5	3012.3	3042.2	3085.8	3138.5	3195.9	3239.5	3271.6	3287.6	3301.4	3315.2
22.5°	2968.7	2975.6	3012.3	3074.3	3150.0	3223.4	3280.8	3322.1	3342.7	3361.1	3377.1
25°	2913.7	2922.9	2966.5	3046.8	3154.6	3253.2	3326.6	3379.4	3397.8	3420.7	3434.5
27.5°	2828.8	2835.7	2888.4	2991.7	3140.8	3285.4	3379.4	3441.4	3462.0	3487.2	3501.0
30°	2695.7	2709.5	2773.7	2902.2	3106.4	3310.6	3441.4	3503.3	3528.5	3553.8	3572.1
32.5°	2523.7	2544.3	2615.4	2780.6	3039.9	3319.8	3507.9	3579.0	3611.1	3638.7	3661.6
35°	2310.3	2330.9	2415.8	2624.6	2934.3	3301.4	3574.4	3666.2	3705.2	3741.9	3769.4
37.5°	2067.1	2085.5	2188.7	2427.3	2782.9	3244.1	3627.2	3762.6	3815.3	3863.5	3900.2
40°	1821.6	1842.3	1954.7	2209.4	2599.4	3133.9	3650.1	3868.1	3934.6	3996.6	4042.5
42.5°	1555.5	1580.7	1706.9	1977.6	2386.0	2982.5	3631.8	3971.3	4053.9	4138.8	4207.6
45°	1319.2	1323.8	1461.4	1723.0	2152.0	2787.5	3567.5	4070.0	4182.4	4301.7	4400.4
47.5°	1092.1	1101.2	1220.5	1479.8	1908.8	2567.3	3450.5	4148.0	4326.9	4480.7	4625.2
50°	890.2	901.6	1009.5	1241.2	1665.6	2326.4	3292.2	4193.9	4450.8	4659.6	4861.5
52.5°	725.0	738.7	828.2	1032.4	1420.1	2074.0	3097.2	4200.8	4563.2	4838.6	5107.0
55°	603.4	612.6	681.4	844.3	1183.8	1812.4	2874.7	4166.3	4636.7	4999.1	5357.1
57.5°	509.3	518.5	566.7	695.2	970.5	1544.0	2604.0	4086.0	4675.7	5139.1	5609.4
60°	442.8	449.7	484.1	575.9	798.4	1291.7	2312.6	3943.8	4664.2	5226.3	5818.2
62.5°	394.6	396.9	426.7	491.0	658.4	1053.1	1984.5	3730.4	4570.1	5237.7	5960.4
65°	351.0	353.3	371.7	417.6	541.4	846.6	1642.7	3436.8	4391.2	5157.5	5981.1
67.5°	284.5	289.1	316.6	351.0	445.1	669.9	1294.0	3051.3	4111.3	4948.7	5864.1
70°	227.1	229.4	257.0	296.0	362.5	527.7	993.4	2532.8	3673.1	4609.1	5561.2
72.5°	169.8	174.4	199.6	238.6	296.0	408.4	718.1	1915.7	2936.6	3886.4	4843.1
75°	135.4	137.7	146.8	183.5	229.4	309.7	484.1	1160.9	1768.9	2404.4	2968.7
77.5°	114.7	117.0	117.0	142.2	169.8	208.8	257.0	461.1	747.9	1064.5	1411.0
80°	94.1	98.7	89.5	105.5	121.6	121.6	119.3	220.2	353.3	500.1	656.2
82.5°	68.8	73.4	68.8	73.4	73.4	66.5	61.9	82.6	112.4	153.7	167.5
85°	48.2	50.5	55.1	50.5	48.2	39.0	29.8	22.9	13.8	16.1	22.9
87.5°	32.1	39.0	45.9	43.6	36.7	29.8	20.6	13.8	6.9	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1212047
 CATALOG NUMBER: GKO-PB2E-840-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3088.0	3088.0	3088.0
2.5°	3090.3	3088.0	3085.8
5°	3101.8	3099.5	3097.2
7.5°	3117.9	3117.9	3117.9
10°	3143.1	3147.7	3147.7
12.5°	3175.2	3179.8	3179.8
15°	3214.2	3216.5	3221.1
17.5°	3262.4	3264.7	3264.7
20°	3319.8	3317.5	3322.1
22.5°	3377.1	3377.1	3377.1
25°	3436.8	3436.8	3436.8
27.5°	3505.6	3505.6	3501.0
30°	3581.3	3581.3	3581.3
32.5°	3673.1	3675.4	3677.7
35°	3790.1	3794.7	3801.6
37.5°	3923.2	3934.6	3941.5
40°	4081.5	4086.0	4097.5
42.5°	4258.1	4271.9	4274.2
45°	4478.4	4501.3	4510.5
47.5°	4737.6	4769.7	4785.8
50°	5026.7	5063.4	5086.3
52.5°	5341.0	5400.6	5428.2
55°	5675.9	5779.2	5809.0
57.5°	6054.5	6194.4	6235.7
60°	6426.2	6623.5	6690.0
62.5°	6742.8	7020.4	7103.0
65°	6965.3	7300.3	7421.9
67.5°	7011.2	7408.1	7552.6
70°	6735.9	7142.0	7309.4
72.5°	5857.2	6224.3	6433.0
75°	3459.7	3723.6	3659.3
77.5°	1736.7	1812.4	1823.9
80°	761.7	807.6	825.9
82.5°	188.1	192.7	218.0
85°	25.2	29.8	27.5
87.5°	9.2	9.2	11.5
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP3-2511-595-3

Test Date: 11/12/2025

Luminaire Tested: GKO-PB1C-840-U-T4W

Data in this report applies to families of products including GKO-PB1C-840*

Test Information

Test Method: LM-79-2019
 Report Number: SP3-2511-595-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP3 - 3M SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/27/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-840-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3958
 CIE u' : 0.2251
 CIE v' : 0.5041
 Duv: 0.0014
 CIE x: 0.3833
 CIE y: 0.3816
 CIE z: 0.2351
 Peak Wavelength (nm): 450
 Dominant Wavelength (nm): 578
 Purity: 29.56261
 R_f: 82.9
 R_g: 94.7

CRI (Ra): 80.8
 R1: 78.3
 R2: 87.6
 R3: 95.0
 R4: 79.6
 R5: 78.8
 R6: 83.3
 R7: 84.3
 R8: 59.4
 R9: -5.1
 R10: 71.4
 R11: 78.5
 R12: 60.5
 R13: 80.5
 R14: 97.5
 R15: 70.7



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2511-595-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	7/1/2025	1/1/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2511-595-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP3-2511-595-3

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.65

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.36


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3




TM-30-18

Summary

$R_f = 82.9$
 $R_g = 94.7$
 $CIE R_a = 80.8$
 $R_g = -5.1$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 80	CES51 = 94	CES76 = 73
CES02 = 61	CES27 = 93	CES52 = 94	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 88	CES78 = 72
CES04 = 70	CES29 = 85	CES54 = 89	CES79 = 91
CES05 = 48	CES30 = 96	CES55 = 88	CES80 = 89
CES06 = 50	CES31 = 87	CES56 = 84	CES81 = 79
CES07 = 40	CES32 = 80	CES57 = 83	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 84	CES83 = 95
CES09 = 29	CES34 = 86	CES59 = 90	CES84 = 90
CES10 = 74	CES35 = 92	CES60 = 90	CES85 = 78
CES11 = 57	CES36 = 83	CES61 = 86	CES86 = 72
CES12 = 63	CES37 = 91	CES62 = 86	CES87 = 83
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 87
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 76
CES15 = 71	CES40 = 95	CES65 = 75	CES90 = 87
CES16 = 47	CES41 = 99	CES66 = 74	CES91 = 71
CES17 = 49	CES42 = 93	CES67 = 73	CES92 = 62
CES18 = 56	CES43 = 89	CES68 = 77	CES93 = 77
CES19 = 71	CES44 = 99	CES69 = 82	CES94 = 60
CES20 = 65	CES45 = 93	CES70 = 73	CES95 = 70
CES21 = 86	CES46 = 90	CES71 = 67	CES96 = 82
CES22 = 78	CES47 = 96	CES72 = 89	CES97 = 90
CES23 = 91	CES48 = 84	CES73 = 66	CES98 = 84
CES24 = 90	CES49 = 89	CES74 = 93	CES99 = 73
CES25 = 71	CES50 = 94	CES75 = 70	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)