

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P972246

Luminaire Tested: **GKO-PB1A-722-U-T3**

Issue Date: 02/27/2025



Test Information

Test Method: LM-79-08
Report Number: P972246
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/27/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1A-722-U-T3
Description: GEKKO WALL PACK 750LM PACKAGE 70CRI 2200K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source: (10) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 637.5 lumens
Efficiency: N/A
Efficacy: 132.8 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B0 - U0 - G0


Input Watts (W): 4.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 16%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P972246

CATALOG NUMBER: GKO-PB1A-722-U-T3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 12 foot mounting height. Maximum calculated value = 0.9 fc
 Type III - Medium - N/A

REPORT NUMBER: P972246
CATALOG NUMBER: GKO-PB1A-722-U-T3

Luminous Intensity Polar Plot



REPORT NUMBER: P972246

CATALOG NUMBER: GKO-PB1A-722-U-T3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	163.2	0.0	163.2
	% Fixture	25.6	0.0	25.6
Street Side	Lumens	474.3	0.0	474.3
	% Fixture	74.4	0.0	74.4
Total	Lumens	637.5	0.0	637.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.3	1.6
10°-20°	30.8	4.8
20°-30°	53.1	8.3
30°-40°	82.4	12.9
40°-50°	112.9	17.7
50°-60°	134.7	21.1
60°-70°	135.0	21.2
70°-80°	71.4	11.2
80°-90°	6.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	637.5	100.0
0°-180°	637.5	100.0



REPORT NUMBER: P972246


CATALOG NUMBER: GKO-PB1A-722-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	56.3	8.8			
FM	(30°-60°)	249.6	39.2			
FH	(60°-80°)	165.6	26.0			G0/660
FVH	(80°-90°)	2.7	0.4			G0/10
BL	(0°-30°)	37.9	5.9	B0/110		
BM	(30°-60°)	80.4	12.6	B0/220		
BH	(60°-80°)	40.7	6.4	B0/110		G0/110
BVH	(80°-90°)	4.2	0.7			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G0

Type III Medium



REPORT NUMBER: P972246

CATALOG NUMBER: GKO-PB1A-722-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9
2.5°	111.4	111.4	111.1	111.0	110.9	110.1	109.6	109.0	109.0	108.0	107.2
5°	115.2	115.3	114.8	114.8	114.3	113.4	112.4	111.1	111.1	109.6	107.9
7.5°	118.6	118.9	118.4	118.4	117.9	116.8	115.2	113.5	113.5	111.4	108.9
10°	121.8	122.0	121.8	122.0	121.3	120.3	118.4	116.1	116.0	113.4	109.9
12.5°	124.4	124.6	124.7	125.1	124.5	123.7	122.0	119.0	118.7	115.6	111.1
15°	126.8	127.1	127.5	128.0	127.8	127.2	125.6	122.3	122.0	118.1	112.7
17.5°	128.8	128.9	129.7	130.7	130.9	131.1	129.3	125.9	125.6	120.9	114.5
20°	131.7	131.9	132.7	133.6	134.4	134.9	133.5	129.7	129.4	124.2	116.7
22.5°	138.1	137.7	138.1	138.1	138.5	139.2	138.2	134.4	133.9	128.2	119.4
25°	150.2	149.9	148.9	146.6	144.2	144.0	142.9	139.2	138.6	132.3	122.0
27.5°	167.2	166.3	164.5	159.8	153.8	150.0	148.3	144.4	143.7	136.4	124.5
30°	185.1	186.1	183.0	176.6	165.7	157.5	154.2	149.9	149.2	141.0	127.5
32.5°	206.0	206.2	203.1	194.2	180.1	167.1	161.4	156.0	155.6	146.3	131.4
35°	218.2	218.7	217.3	209.0	192.9	177.6	170.0	163.6	163.2	153.0	136.4
37.5°	230.8	231.9	229.8	220.6	202.7	187.4	179.7	172.6	172.3	160.6	142.6
40°	249.5	249.0	246.8	233.3	211.9	195.5	189.2	183.6	182.8	170.0	148.9
42.5°	263.0	264.2	259.4	244.2	221.9	203.7	198.7	192.4	191.3	175.7	152.6
45°	267.5	266.4	261.1	250.0	235.0	211.1	207.8	202.9	201.8	185.7	159.9
47.5°	268.5	266.6	261.9	253.4	246.1	220.8	218.8	217.7	216.1	198.4	168.7
50°	262.5	261.1	258.9	254.7	253.3	229.8	230.8	234.9	233.5	212.0	178.4
52.5°	248.7	248.1	250.1	252.8	249.2	237.6	245.0	253.3	252.8	227.0	189.0
55°	222.9	222.9	234.0	243.5	245.6	242.7	260.4	274.6	274.0	243.8	199.0
57.5°	199.2	199.6	208.9	230.3	239.2	248.1	277.4	296.9	295.9	262.7	209.5
60°	169.4	169.4	183.5	210.4	229.9	252.3	292.5	318.4	319.0	281.0	219.9
62.5°	134.1	134.5	154.1	185.6	216.6	253.1	304.5	338.7	338.6	297.6	227.9
65°	98.9	99.0	125.6	158.2	196.5	247.9	311.1	354.3	355.0	310.7	232.6
67.5°	64.2	65.5	92.4	128.3	168.2	233.1	307.6	362.6	363.5	316.8	231.2
68°	60.1	60.4	87.5	120.2	160.5	229.4	306.0	363.0	363.7	316.7	229.7
70°	39.0	39.0	62.6	93.8	128.1	206.3	292.0	357.1	358.0	311.2	218.9
72.5°	21.0	21.4	35.8	56.8	87.5	159.6	263.6	326.8	328.3	281.4	191.4
75°	14.7	15.0	20.8	31.8	47.6	103.9	206.0	249.7	249.5	194.4	119.9
77.5°	10.6	10.6	11.9	19.8	25.0	47.5	102.0	120.3	118.9	94.9	60.5
80°	6.9	6.9	7.4	10.4	12.0	14.5	31.2	52.1	53.1	46.3	30.2
82.5°	2.8	3.0	3.2	4.2	4.3	6.1	8.9	15.0	14.5	11.8	8.5
85°	0.4	0.4	0.5	0.6	0.7	1.4	1.2	1.2	1.2	1.5	1.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.2	0.4	0.4	0.5	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P972246

CATALOG NUMBER: GKO-PB1A-722-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9	106.9
2.5°	106.9	106.9	106.2	105.4	104.7	104.1	103.2	102.6	102.7	103.1	103.0
5°	107.5	106.9	105.4	103.8	102.6	101.5	99.9	99.0	98.9	99.1	99.0
7.5°	107.9	106.9	104.7	102.2	100.2	98.8	96.5	95.7	95.3	95.4	95.4
10°	108.7	107.0	103.9	100.5	98.0	95.9	93.6	92.3	91.9	91.9	91.8
12.5°	109.5	107.3	103.2	99.0	95.8	93.3	90.6	89.2	88.9	88.9	88.7
15°	110.4	107.7	102.5	97.4	93.7	90.7	88.1	86.5	86.0	86.0	86.3
17.5°	111.5	108.0	101.7	95.9	91.5	88.1	85.4	83.8	83.2	83.5	83.8
20°	112.6	108.8	101.0	94.3	89.2	85.8	83.0	81.4	80.8	81.4	81.6
22.5°	114.2	109.4	100.1	92.4	87.0	83.2	80.7	79.2	78.8	79.4	79.9
25°	115.8	110.1	99.0	90.5	84.1	80.4	78.5	77.3	77.5	78.3	78.8
27.5°	117.6	110.8	97.9	88.0	81.1	77.6	76.1	75.9	76.4	77.3	78.0
30°	119.7	111.6	96.4	85.1	77.6	74.5	73.9	74.6	75.5	76.5	77.1
32.5°	122.4	112.7	94.9	81.9	74.0	71.2	72.1	73.8	74.7	75.7	76.4
35°	126.2	115.0	94.0	78.7	70.2	68.3	70.5	73.1	73.9	74.5	75.2
37.5°	130.7	117.9	93.7	75.7	66.7	65.8	68.9	72.0	72.3	72.5	73.3
40°	135.0	120.2	92.7	72.5	63.1	63.1	66.9	69.9	69.8	69.4	69.9
42.5°	136.7	119.9	89.8	69.4	60.3	60.4	63.9	66.7	66.0	66.0	66.7
45°	141.7	121.9	87.7	66.9	57.7	57.2	59.9	62.1	63.4	65.0	65.7
47.5°	148.0	124.6	86.1	64.1	55.2	53.6	55.1	58.8	60.9	62.6	63.2
50°	154.6	127.7	84.6	61.1	52.7	49.5	50.2	54.3	56.2	57.0	57.4
52.5°	161.2	130.6	83.5	58.7	49.9	44.7	46.3	50.1	51.5	52.0	52.2
55°	167.2	132.9	82.5	56.6	46.7	40.8	42.1	46.0	47.0	47.5	47.9
57.5°	173.5	135.5	81.9	54.6	43.1	37.5	38.4	42.0	43.3	43.8	44.2
60°	179.1	138.0	81.4	52.5	39.7	34.5	35.0	38.5	40.0	40.2	40.6
62.5°	182.8	139.6	80.7	49.9	36.6	31.7	31.8	35.1	36.8	37.0	37.2
65°	183.8	139.2	78.5	46.4	33.5	28.8	28.8	32.1	33.8	34.6	35.0
67.5°	180.8	136.1	73.8	42.0	30.6	26.2	26.2	29.1	30.9	31.9	32.3
68°	179.8	134.8	72.3	40.8	29.8	25.6	25.6	28.6	30.3	31.2	31.4
70°	171.4	128.1	65.5	36.6	27.5	23.8	23.8	26.4	28.2	28.2	28.1
72.5°	148.9	111.0	53.8	30.7	24.0	21.0	21.4	23.9	24.5	25.1	25.0
75°	92.2	66.5	36.1	24.3	20.2	18.4	19.2	21.4	21.8	23.1	22.8
77.5°	46.2	32.5	19.2	14.1	15.6	15.8	17.2	18.8	19.9	21.4	20.4
80°	22.8	15.8	11.3	8.8	9.2	11.6	15.0	16.2	18.2	19.2	18.3
82.5°	6.3	4.8	4.6	4.8	6.8	9.0	11.8	14.4	17.0	17.8	16.6
85°	1.1	0.9	0.7	2.4	4.7	6.7	9.5	12.7	15.2	14.6	13.7
87.5°	0.4	0.2	0.2	1.5	3.5	5.4	8.2	11.4	13.0	11.8	10.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-2

Test Date: 04/09/2025

Luminaire Tested: GKO-PB1E-722-U-T4W

Data in this report applies to families of products including GKO-PB1E-722-U-T4W


Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-722-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 2281
 CIE u' : 0.2851
 CIE v' : 0.5324
 Duv: -0.0016
 CIE x: 0.4942
 CIE y: 0.4102
 CIE z: 0.0956
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 587
 Purity: 71.48321
 R_f: 76.9
 R_g: 92.6

CRI (Ra): 70.6
 R1: 68.4
 R2: 88.7
 R3: 85.7
 R4: 63.2
 R5: 69.0
 R6: 88.6
 R7: 68.8
 R8: 32.6
 R9: -35.1
 R10: 78.0
 R11: 60.2
 R12: 73.8
 R13: 72.8
 R14: 92.4
 R15: 58.4



Test Conditions


Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP2-2501-321-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.98

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.75

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2



TM-30-18

Summary

$R_f = 76.9$
 $R_g = 92.6$
 $CIE R_a = 70.6$
 $R_g = -35.1$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 87	CES26 = 76	CES51 = 88	CES76 = 78
CES02 = 65	CES27 = 94	CES52 = 84	CES77 = 76
CES03 = 32	CES28 = 93	CES53 = 79	CES78 = 79
CES04 = 72	CES29 = 81	CES54 = 86	CES79 = 82
CES05 = 51	CES30 = 92	CES55 = 83	CES80 = 81
CES06 = 52	CES31 = 83	CES56 = 76	CES81 = 52
CES07 = 44	CES32 = 75	CES57 = 74	CES82 = 92
CES08 = 42	CES33 = 89	CES58 = 76	CES83 = 88
CES09 = 29	CES34 = 88	CES59 = 84	CES84 = 90
CES10 = 79	CES35 = 94	CES60 = 91	CES85 = 65
CES11 = 62	CES36 = 90	CES61 = 81	CES86 = 49
CES12 = 68	CES37 = 96	CES62 = 91	CES87 = 76
CES13 = 44	CES38 = 98	CES63 = 86	CES88 = 78
CES14 = 75	CES39 = 98	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 95	CES65 = 71	CES90 = 80
CES16 = 48	CES41 = 95	CES66 = 70	CES91 = 80
CES17 = 51	CES42 = 89	CES67 = 69	CES92 = 52
CES18 = 57	CES43 = 80	CES68 = 73	CES93 = 69
CES19 = 74	CES44 = 99	CES69 = 84	CES94 = 45
CES20 = 68	CES45 = 83	CES70 = 71	CES95 = 66
CES21 = 88	CES46 = 81	CES71 = 74	CES96 = 75
CES22 = 81	CES47 = 89	CES72 = 89	CES97 = 75
CES23 = 92	CES48 = 73	CES73 = 67	CES98 = 72
CES24 = 92	CES49 = 82	CES74 = 85	CES99 = 64
CES25 = 73	CES50 = 87	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)