

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1211873

Luminaire Tested: **GKO-PB1D-850-U-T3**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1211873
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1D-850-U-T3
Description: GEKKO WALL PACK 3500LM PACKAGE 80CRI 5000K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source: (10) 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3365 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G1

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi):
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1211873
 CATALOG NUMBER: GKO-PB1D-850-U-T3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 --- 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 2.9 fc
 Type III - Medium - N/A

REPORT NUMBER: P1211873
CATALOG NUMBER: GKO-PB1D-850-U-T3

Luminous Intensity Polar Plot



REPORT NUMBER: P1211873

CATALOG NUMBER: GKO-PB1D-850-U-T3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	861.5	0.0	861.5
	% Fixture	25.6	0.0	25.6
Street Side	Lumens	2503.5	0.0	2503.5
	% Fixture	74.4	0.0	74.4
Total	Lumens	3365.0	0.0	3365.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	1.6
10°-20°	162.7	4.8
20°-30°	280.5	8.3
30°-40°	435.0	12.9
40°-50°	596.0	17.7
50°-60°	710.9	21.1
60°-70°	712.4	21.2
70°-80°	377.0	11.2
80°-90°	36.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3365.0	100.0
0°-180°	3365.0	100.0



REPORT NUMBER: P1211873


CATALOG NUMBER: GKO-PB1D-850-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	297.2	8.8			
FM	(30°-60°)	1317.6	39.2			
FH	(60°-80°)	874.4	26.0			G1/1800
FVH	(80°-90°)	14.3	0.4			G1/100
BL	(0°-30°)	200.1	5.9	B1/500		
BM	(30°-60°)	424.4	12.6	B1/1000		
BH	(60°-80°)	214.9	6.4	B1/500		G1/500
BVH	(80°-90°)	22.1	0.7			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type III Medium





REPORT NUMBER: P1211873

CATALOG NUMBER: GKO-PB1D-850-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	564.4	564.4	564.4	564.4	564.4	564.4	564.4	564.4	564.4	564.4	564.4
2.5°	587.9	587.9	586.6	585.9	585.3	581.4	578.8	575.5	575.5	570.3	565.7
5°	608.1	608.8	606.2	606.2	603.6	598.3	593.1	586.6	586.6	578.8	569.6
7.5°	625.8	627.7	625.1	625.1	622.5	616.6	608.1	599.0	599.0	587.9	574.8
10°	642.8	644.1	642.8	644.1	640.2	634.9	625.1	612.7	612.1	598.3	580.1
12.5°	656.5	657.8	658.4	660.4	657.1	653.2	644.1	628.4	626.4	610.1	586.6
15°	669.6	670.9	672.8	675.4	674.8	671.5	663.0	645.4	644.1	623.2	595.1
17.5°	680.0	680.7	684.6	689.8	691.1	691.8	682.6	664.3	663.0	638.2	604.2
20°	695.0	696.3	700.3	705.5	709.4	712.0	704.8	684.6	683.3	655.8	616.0
22.5°	729.0	727.0	729.0	729.0	731.0	734.9	729.6	709.4	706.8	676.7	630.4
25°	793.0	791.0	785.8	774.1	761.0	760.3	754.5	734.9	731.6	698.3	644.1
27.5°	882.5	877.9	868.1	843.3	812.0	791.7	782.6	762.3	758.4	719.8	657.1
30°	977.2	982.4	966.1	932.1	874.7	831.5	813.9	791.0	787.8	744.0	672.8
32.5°	1087.6	1088.3	1071.9	1024.9	950.4	881.8	851.8	823.7	821.1	772.1	693.7
35°	1151.6	1154.2	1147.1	1103.3	1018.4	937.4	897.5	863.6	861.6	807.4	719.8
37.5°	1218.3	1224.1	1213.0	1164.7	1070.0	989.0	948.5	911.2	909.3	847.9	752.5
40°	1316.9	1314.3	1302.5	1231.3	1118.3	1032.1	998.8	969.4	964.8	897.5	785.8
42.5°	1388.1	1394.6	1369.2	1288.8	1171.2	1075.2	1049.1	1015.8	1009.9	927.6	805.4
45°	1412.3	1406.4	1378.3	1319.5	1240.5	1114.4	1096.8	1071.3	1065.4	980.5	844.0
47.5°	1417.5	1407.0	1382.2	1337.8	1299.3	1165.3	1154.9	1149.0	1140.5	1047.1	890.3
50°	1385.5	1378.3	1366.5	1344.3	1337.1	1213.0	1218.3	1239.8	1232.6	1119.0	941.9
52.5°	1313.0	1309.7	1320.2	1334.5	1315.6	1254.2	1293.4	1337.1	1334.5	1198.0	997.5
55°	1176.5	1176.5	1235.2	1285.5	1296.6	1281.0	1374.4	1449.5	1446.2	1286.8	1050.4
57.5°	1051.7	1053.6	1102.6	1215.6	1262.7	1309.7	1464.5	1567.1	1561.9	1386.8	1105.9
60°	894.3	894.3	968.7	1110.5	1213.7	1331.9	1544.2	1680.7	1684.0	1483.5	1160.8
62.5°	708.1	710.1	813.3	979.8	1143.1	1335.8	1607.6	1787.9	1787.2	1571.0	1203.2
65°	521.9	522.6	663.0	834.8	1037.3	1308.4	1642.2	1870.2	1874.1	1640.2	1228.1
67.5°	339.0	345.6	488.0	677.4	887.7	1230.7	1623.9	1913.9	1918.5	1672.2	1220.2
68°	317.5	318.8	461.8	634.3	847.2	1211.1	1615.4	1915.9	1919.8	1671.6	1212.4
70°	205.8	205.8	330.5	495.1	676.1	1088.9	1541.6	1885.2	1889.8	1642.8	1155.5
72.5°	111.0	113.0	188.8	299.8	461.8	842.7	1391.4	1725.2	1733.0	1485.4	1010.5
75°	77.7	79.0	109.7	167.9	251.5	548.7	1087.6	1318.2	1316.9	1026.2	633.0
77.5°	56.2	56.2	62.7	104.5	132.0	250.8	538.3	634.9	627.7	501.0	319.4
80°	36.6	36.6	39.2	54.9	63.4	76.4	164.6	275.0	280.2	244.3	159.4
82.5°	15.0	15.7	17.0	22.2	22.9	32.0	47.0	79.0	76.4	62.1	45.1
85°	2.0	2.0	2.6	3.3	3.9	7.2	6.5	6.5	6.5	7.8	7.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.7	1.3	2.0	2.0	2.6	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1211873

CATALOG NUMBER: GKO-PB1D-850-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	564.4	564.4	564.4	564.4	564.4	564.4	564.4	564.4	564.4	564.4	564.4
2.5°	564.4	564.4	560.5	556.5	552.6	549.4	544.8	541.5	542.2	544.1	543.5
5°	567.6	564.4	556.5	548.1	541.5	535.6	527.1	522.6	521.9	523.2	522.6
7.5°	569.6	564.4	552.6	539.6	529.1	521.3	509.5	504.9	503.0	503.6	503.6
10°	573.5	565.0	548.7	530.4	517.4	506.2	493.8	487.3	485.3	485.3	484.7
12.5°	578.1	566.3	544.8	522.6	505.6	492.5	478.2	471.0	469.0	469.0	468.4
15°	582.7	568.3	540.9	514.1	494.5	478.8	465.1	456.6	454.0	454.0	455.3
17.5°	588.6	570.3	536.9	506.2	482.7	465.1	450.7	442.2	439.0	440.9	442.2
20°	594.4	574.2	533.0	497.8	471.0	452.7	438.3	429.8	426.6	429.8	430.5
22.5°	602.9	577.4	528.5	488.0	459.2	439.0	425.9	418.1	416.1	419.4	422.0
25°	611.4	581.4	522.6	477.5	444.2	424.6	414.1	408.3	408.9	413.5	416.1
27.5°	620.6	584.6	516.7	464.4	427.9	409.6	401.7	400.4	403.0	408.3	411.5
30°	631.7	589.2	508.9	449.4	409.6	393.2	390.0	393.9	398.5	403.7	407.0
32.5°	646.0	595.1	501.0	432.4	390.6	375.6	380.8	389.3	394.5	399.8	403.0
35°	666.3	606.8	496.4	415.4	370.4	360.6	372.3	386.1	390.0	393.2	397.2
37.5°	689.8	622.5	494.5	399.8	352.1	347.5	363.8	380.2	381.5	382.8	386.7
40°	712.7	634.3	489.3	382.8	333.1	333.1	353.4	369.1	368.4	366.5	369.1
42.5°	721.8	633.0	474.2	366.5	318.1	318.8	337.1	352.1	348.2	348.2	352.1
45°	747.9	643.4	463.1	353.4	304.4	301.8	316.2	327.9	334.4	342.9	346.9
47.5°	781.3	657.8	454.6	338.4	291.3	282.8	290.7	310.3	321.4	330.5	333.8
50°	815.9	674.1	446.8	322.7	278.3	261.3	265.2	286.8	296.6	301.1	303.1
52.5°	851.1	689.1	440.9	309.6	263.2	235.8	244.3	264.6	271.7	274.4	275.7
55°	882.5	701.6	435.7	298.5	246.3	215.6	222.1	243.0	248.2	250.8	252.8
57.5°	915.8	715.3	432.4	288.1	227.3	197.9	202.5	221.4	228.6	231.2	233.2
60°	945.2	728.3	429.8	277.0	209.7	182.2	184.9	203.2	211.0	212.3	214.3
62.5°	964.8	736.8	425.9	263.2	193.4	167.2	167.9	185.5	194.0	195.3	196.6
65°	970.0	734.9	414.1	245.0	177.0	152.2	152.2	169.2	178.3	182.9	184.9
67.5°	954.4	718.5	389.3	221.4	161.3	138.5	138.5	153.5	163.3	168.5	170.5
68°	949.1	711.4	381.5	215.6	157.4	135.2	135.2	150.9	160.0	164.6	165.9
70°	904.7	676.1	345.6	193.4	145.0	125.4	125.4	139.1	148.9	148.9	148.3
72.5°	785.8	585.9	284.2	162.0	126.7	111.0	113.0	126.1	129.3	132.6	132.0
75°	486.6	350.8	190.7	128.0	106.5	97.3	101.2	113.0	115.0	122.2	120.2
77.5°	243.7	171.8	101.2	74.5	82.3	83.6	90.8	99.3	105.2	113.0	107.8
80°	120.2	83.6	59.4	46.4	48.3	61.4	79.0	85.6	96.0	101.2	96.7
82.5°	33.3	25.5	24.2	25.5	35.9	47.7	62.1	75.8	89.5	94.1	87.5
85°	5.9	4.6	3.9	12.4	24.8	35.3	50.3	67.3	80.3	77.1	72.5
87.5°	2.0	1.3	1.3	7.8	18.3	28.7	43.1	60.1	68.6	62.1	55.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-4

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-850-U-T4W

Data in this report applies to families of products including GKO-PB1C

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-850-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 5005
 CIE u' : 0.2100
 CIE v' : 0.4867
 Duv: 0.0019
 CIE x: 0.3453
 CIE y: 0.3557
 CIE z: 0.2990
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 570
 Purity: 10.34221
 R_f: 83.7
 R_g: 95.5

CRI (Ra): 83.1
 R1: 81.4
 R2: 89.2
 R3: 93.9
 R4: 82.4
 R5: 82.2
 R6: 84.5
 R7: 86.1
 R8: 65.5
 R9: 4.4
 R10: 74.2
 R11: 81.9
 R12: 62.2
 R13: 83.6
 R14: 97.0
 R15: 75.4



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2511-595-4

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.97

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.21

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4




TM-30-18

Summary

$R_f = 83.7$
 $R_g = 95.5$
 $CIE R_a = 83.1$
 $R_9 = 4.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 81	CES51 = 94	CES76 = 74
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 91	CES53 = 90	CES78 = 73
CES04 = 69	CES29 = 87	CES54 = 89	CES79 = 91
CES05 = 47	CES30 = 95	CES55 = 87	CES80 = 88
CES06 = 50	CES31 = 89	CES56 = 85	CES81 = 82
CES07 = 39	CES32 = 81	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 95	CES58 = 85	CES83 = 96
CES09 = 29	CES34 = 86	CES59 = 91	CES84 = 90
CES10 = 73	CES35 = 92	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 82	CES61 = 87	CES86 = 77
CES12 = 62	CES37 = 91	CES62 = 83	CES87 = 84
CES13 = 42	CES38 = 90	CES63 = 85	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 95	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 98	CES66 = 74	CES91 = 71
CES17 = 49	CES42 = 92	CES67 = 73	CES92 = 64
CES18 = 55	CES43 = 90	CES68 = 77	CES93 = 79
CES19 = 71	CES44 = 99	CES69 = 81	CES94 = 63
CES20 = 64	CES45 = 94	CES70 = 73	CES95 = 72
CES21 = 85	CES46 = 92	CES71 = 67	CES96 = 83
CES22 = 77	CES47 = 97	CES72 = 89	CES97 = 91
CES23 = 91	CES48 = 86	CES73 = 67	CES98 = 86
CES24 = 90	CES49 = 91	CES74 = 91	CES99 = 75
CES25 = 71	CES50 = 94	CES75 = 69	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)