

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P972392

Luminaire Tested: **GKO-PB1E-722-U-T1**

Issue Date: 02/27/2025

Test Information

Test Method: LM-79-08
Report Number: P972392
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/27/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1E-722-U-T1
Description: GEKKO WALL PACK 5000LM PACKAGE 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (10) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4503.6 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B2 - U0 - G2

Input Watts (W): 38.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 9%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT


REPORT NUMBER: P972392

CATALOG NUMBER: GKO-PB1E-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 11.2 fc
 Type I - Short - N/A

REPORT NUMBER: P972392

CATALOG NUMBER: GKO-PB1E-722-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P972392

CATALOG NUMBER: GKO-PB1E-722-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2251.8	0.0	2251.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2251.8	0.0	2251.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	4503.6	0.0	4503.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	2.4
10°-20°	323.0	7.2
20°-30°	537.0	11.9
30°-40°	713.4	15.8
40°-50°	804.3	17.9
50°-60°	827.1	18.4
60°-70°	781.6	17.4
70°-80°	382.6	8.5
80°-90°	27.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4503.6	100.0
0°-180°	4503.6	100.0

Coefficient of Utilization



REPORT NUMBER: P972392


CATALOG NUMBER: GKO-PB1E-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	483.6	10.7			
FM	(30°-60°)	1172.4	26.0			
FH	(60°-80°)	582.1	12.9			G0/660
FVH	(80°-90°)	13.7	0.3			G1/100
BL	(0°-30°)	483.6	10.7	B1/500		
BM	(30°-60°)	1172.4	26.0	B2/2500		
BH	(60°-80°)	582.1	12.9	B2/1000		G2/1000
BVH	(80°-90°)	13.7	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type I Short



REPORT NUMBER: P972392

CATALOG NUMBER: GKO-PB1E-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1117.5	1117.5	1117.5	1117.5	1117.5	1117.5	1117.5	1117.5	1117.5	1117.5	1117.5
2.5°	1118.4	1120.0	1116.7	1116.7	1118.4	1119.2	1119.2	1120.0	1118.4	1118.4	1117.5
5°	1118.4	1119.2	1117.5	1117.5	1119.2	1121.7	1120.8	1122.5	1122.5	1121.7	1121.7
7.5°	1117.5	1119.2	1117.5	1118.4	1120.8	1125.8	1125.8	1125.8	1127.5	1129.1	1129.1
10°	1116.7	1118.4	1119.2	1120.0	1123.3	1130.8	1132.5	1133.3	1135.8	1138.3	1138.3
12.5°	1112.5	1114.2	1116.7	1120.0	1125.8	1135.8	1139.1	1141.6	1145.7	1148.2	1149.9
15°	1106.7	1107.6	1113.4	1120.0	1129.1	1141.6	1148.2	1152.4	1158.2	1161.5	1164.0
17.5°	1098.4	1099.3	1108.4	1118.4	1131.6	1149.1	1159.9	1166.5	1172.3	1177.3	1180.6
20°	1087.6	1090.1	1100.9	1116.7	1135.8	1156.5	1172.3	1183.9	1189.8	1194.7	1199.7
22.5°	1074.3	1076.8	1090.1	1112.5	1139.9	1166.5	1187.3	1202.2	1209.7	1216.3	1222.1
25°	1054.4	1057.7	1073.5	1102.6	1141.6	1177.3	1203.9	1223.0	1229.6	1237.9	1242.9
27.5°	1023.7	1026.2	1045.3	1082.7	1136.6	1188.9	1223.0	1245.4	1252.9	1262.0	1267.0
30°	975.5	980.5	1003.8	1050.3	1124.2	1198.1	1245.4	1267.8	1276.9	1286.1	1292.7
32.5°	913.3	920.8	946.5	1006.3	1100.1	1201.4	1269.5	1295.2	1306.8	1316.8	1325.1
35°	836.1	843.5	874.3	949.8	1061.9	1194.7	1293.5	1326.7	1340.9	1354.1	1364.1
37.5°	748.1	754.7	792.1	878.4	1007.1	1174.0	1312.6	1361.6	1380.7	1398.1	1411.4
40°	659.2	666.7	707.4	799.5	940.7	1134.1	1320.9	1399.8	1423.9	1446.3	1462.9
42.5°	562.9	572.0	617.7	715.7	863.5	1079.3	1314.3	1437.2	1467.1	1497.8	1522.7
45°	477.4	479.1	528.9	623.5	778.8	1008.8	1291.0	1472.9	1513.6	1556.7	1592.4
47.5°	395.2	398.5	441.7	535.5	690.8	929.1	1248.7	1501.1	1565.9	1621.5	1673.8
50°	322.1	326.3	365.3	449.2	602.8	841.9	1191.4	1517.7	1610.7	1686.2	1759.3
52.5°	262.4	267.3	299.7	373.6	513.9	750.5	1120.8	1520.2	1651.4	1751.0	1848.1
55°	218.4	221.7	246.6	305.5	428.4	655.9	1040.3	1507.7	1677.9	1809.1	1938.6
57.5°	184.3	187.6	205.1	251.6	351.2	558.8	942.3	1478.7	1692.1	1859.8	2030.0
60°	160.2	162.7	175.2	208.4	288.9	467.4	836.9	1427.2	1687.9	1891.3	2105.5
62.5°	142.8	143.6	154.4	177.7	238.3	381.1	718.2	1350.0	1653.9	1895.5	2157.0
65°	127.0	127.9	134.5	151.1	195.9	306.4	594.5	1243.7	1589.1	1866.4	2164.5
67.5°	103.0	104.6	114.6	127.0	161.1	242.4	468.3	1104.2	1487.8	1790.9	2122.1
70°	82.2	83.0	93.0	107.1	131.2	191.0	359.5	916.6	1329.2	1668.0	2012.5
72.5°	61.4	63.1	72.2	86.3	107.1	147.8	259.9	693.3	1062.7	1406.4	1752.7
75°	49.0	49.8	53.1	66.4	83.0	112.1	175.2	420.1	640.1	870.1	1074.3
77.5°	41.5	42.3	42.3	51.5	61.4	75.6	93.0	166.9	270.7	385.2	510.6
80°	34.0	35.7	32.4	38.2	44.0	44.0	43.2	79.7	127.9	181.0	237.5
82.5°	24.9	26.6	24.9	26.6	26.6	24.1	22.4	29.9	40.7	55.6	60.6
85°	17.4	18.3	19.9	18.3	17.4	14.1	10.8	8.3	5.0	5.8	8.3
87.5°	11.6	14.1	16.6	15.8	13.3	10.8	7.5	5.0	2.5	3.3	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P972392

CATALOG NUMBER: GKO-PB1E-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1117.5	1117.5	1117.5
2.5°	1118.4	1117.5	1116.7
5°	1122.5	1121.7	1120.8
7.5°	1128.3	1128.3	1128.3
10°	1137.4	1139.1	1139.1
12.5°	1149.1	1150.7	1150.7
15°	1163.2	1164.0	1165.7
17.5°	1180.6	1181.5	1181.5
20°	1201.4	1200.5	1202.2
22.5°	1222.1	1222.1	1222.1
25°	1243.7	1243.7	1243.7
27.5°	1268.6	1268.6	1267.0
30°	1296.0	1296.0	1296.0
32.5°	1329.2	1330.1	1330.9
35°	1371.6	1373.2	1375.7
37.5°	1419.7	1423.9	1426.4
40°	1477.0	1478.7	1482.8
42.5°	1541.0	1545.9	1546.8
45°	1620.7	1629.0	1632.3
47.5°	1714.5	1726.1	1731.9
50°	1819.1	1832.4	1840.7
52.5°	1932.8	1954.4	1964.4
55°	2054.0	2091.4	2102.2
57.5°	2191.0	2241.7	2256.6
60°	2325.5	2396.9	2421.0
62.5°	2440.1	2540.6	2570.5
65°	2520.6	2641.9	2685.9
67.5°	2537.3	2680.9	2733.2
70°	2437.6	2584.6	2645.2
72.5°	2119.6	2252.5	2328.0
75°	1252.0	1347.5	1324.3
77.5°	628.5	655.9	660.1
80°	275.6	292.2	298.9
82.5°	68.1	69.7	78.9
85°	9.1	10.8	10.0
87.5°	3.3	3.3	4.2
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-2

Test Date: 04/09/2025

Luminaire Tested: GKO-PB1E-722-U-T4W


Data in this report applies to families of products including GKO-PB1E-722-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-722-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	2281	CRI (Ra):	70.6		
CIE u':	0.2851	R1:	68.4	R9:	-35.1
CIE v':	0.5324	R2:	88.7	R10:	78.0
Duv:	-0.0016	R3:	85.7	R11:	60.2
CIE x:	0.4942	R4:	63.2	R12:	73.8
CIE y:	0.4102	R5:	69.0	R13:	72.8
CIE z:	0.0956	R6:	88.6	R14:	92.4
Peak Wavelength (nm):	602	R7:	68.8	R15:	58.4
Dominant Wavelength (nm):	587	R8:	32.6		
Purity:	71.48321				
Rf:	76.9				
Rg:	92.6				



Test Conditions


Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP2-2501-321-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.98

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.75


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2





TM-30-18

Summary

$R_f = 76.9$
 $R_g = 92.6$
 $CIE R_a = 70.6$
 $R_g = -35.1$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 76	CES51 = 88	CES76 = 78
CES02 = 65	CES27 = 94	CES52 = 84	CES77 = 76
CES03 = 32	CES28 = 93	CES53 = 79	CES78 = 79
CES04 = 72	CES29 = 81	CES54 = 86	CES79 = 82
CES05 = 51	CES30 = 92	CES55 = 83	CES80 = 81
CES06 = 52	CES31 = 83	CES56 = 76	CES81 = 52
CES07 = 44	CES32 = 75	CES57 = 74	CES82 = 92
CES08 = 42	CES33 = 89	CES58 = 76	CES83 = 88
CES09 = 29	CES34 = 88	CES59 = 84	CES84 = 90
CES10 = 79	CES35 = 94	CES60 = 91	CES85 = 65
CES11 = 62	CES36 = 90	CES61 = 81	CES86 = 49
CES12 = 68	CES37 = 96	CES62 = 91	CES87 = 76
CES13 = 44	CES38 = 98	CES63 = 86	CES88 = 78
CES14 = 75	CES39 = 98	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 95	CES65 = 71	CES90 = 80
CES16 = 48	CES41 = 95	CES66 = 70	CES91 = 80
CES17 = 51	CES42 = 89	CES67 = 69	CES92 = 52
CES18 = 57	CES43 = 80	CES68 = 73	CES93 = 69
CES19 = 74	CES44 = 99	CES69 = 84	CES94 = 45
CES20 = 68	CES45 = 83	CES70 = 71	CES95 = 66
CES21 = 88	CES46 = 81	CES71 = 74	CES96 = 75
CES22 = 81	CES47 = 89	CES72 = 89	CES97 = 75
CES23 = 92	CES48 = 73	CES73 = 67	CES98 = 72
CES24 = 92	CES49 = 82	CES74 = 85	CES99 = 64
CES25 = 73	CES50 = 87	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)