

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P977121

Luminaire Tested: **GKO-PB1F-722-U-T4W**

Issue Date: 03/19/2025



Test Information

Test Method: LM-79-08
Report Number: P977121
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/19/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1F-722-U-T4W
Description: GEKKO WALL PACK 6500LM PACKAGE 70CRI 2200K FIXTURE w/ TYPE IV WIDE DISTRIBUTION OPTIC
Light Source: (10) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5353.4 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 54.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 5.7%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P977121

CATALOG NUMBER: GKO-PB1F-722-U-T4W

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 10.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P977121

CATALOG NUMBER: GKO-PB1F-722-U-T4W

Luminous Intensity Polar Plot



REPORT NUMBER: P977121

CATALOG NUMBER: GKO-PB1F-722-U-T4W


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1439.9	0.0	1439.9
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	3913.5	0.0	3913.5
	% Fixture	73.1	0.0	73.1
Total	Lumens	5353.4	0.0	5353.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	1.6
10°-20°	258.1	4.8
20°-30°	446.9	8.3
30°-40°	663.3	12.4
40°-50°	901.0	16.8
50°-60°	1106.1	20.7
60°-70°	1165.7	21.8
70°-80°	643.5	12.0
80°-90°	84.8	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5353.4	100.0
0°-180°	5353.4	100.0



REPORT NUMBER: P977121


CATALOG NUMBER: GKO-PB1F-722-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	471.0	8.8			
FM	(30°-60°)	1955.2	36.5			
FH	(60°-80°)	1456.4	27.2			G1/1800
FVH	(80°-90°)	31.0	0.6			G1/100
BL	(0°-30°)	318.1	5.9	B1/500		
BM	(30°-60°)	715.1	13.4	B1/1000		
BH	(60°-80°)	352.9	6.6	B1/500		G1/500
BVH	(80°-90°)	53.8	1.0			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short



REPORT NUMBER: P977121

CATALOG NUMBER: GKO-PB1F-722-U-T4W

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	878.7	878.7	878.7	878.7	878.7	878.7	878.7	878.7	878.7	878.7	878.7
2.5°	919.4	921.5	919.4	917.3	913.0	910.8	908.7	903.3	896.9	887.2	879.7
5°	960.1	960.1	956.9	954.8	948.3	941.9	938.7	925.8	911.9	895.8	880.8
7.5°	997.6	1001.9	996.5	991.2	981.5	970.8	968.7	949.4	930.1	908.7	886.2
10°	1044.8	1048.0	1040.5	1036.2	1018.0	1004.0	999.8	976.2	950.5	923.7	894.8
12.5°	1093.0	1095.1	1089.8	1080.1	1060.8	1043.7	1037.3	1006.2	973.0	940.8	904.4
15°	1134.8	1136.9	1134.8	1124.1	1105.8	1084.4	1075.8	1041.6	1000.8	959.0	916.2
17.5°	1165.9	1170.1	1170.1	1164.8	1148.7	1128.3	1123.0	1080.1	1033.0	980.5	930.1
20°	1192.6	1194.8	1199.1	1195.9	1187.3	1170.1	1162.6	1121.9	1065.1	1005.1	944.0
22.5°	1214.1	1216.2	1223.7	1222.6	1217.3	1208.7	1201.2	1163.7	1102.6	1029.8	956.9
25°	1251.6	1250.5	1254.8	1251.6	1245.1	1241.9	1237.6	1204.4	1140.1	1058.7	974.0
27.5°	1316.9	1314.8	1310.5	1294.4	1278.4	1274.1	1270.9	1247.3	1184.1	1091.9	993.3
30°	1413.4	1415.5	1395.2	1358.7	1326.6	1313.7	1309.4	1293.4	1233.4	1130.5	1014.8
32.5°	1528.0	1527.0	1493.8	1442.3	1392.0	1366.2	1357.7	1340.5	1282.7	1169.1	1039.4
35°	1610.6	1608.4	1591.3	1545.2	1492.7	1431.6	1415.5	1388.7	1335.2	1213.0	1064.1
37.5°	1722.0	1718.8	1685.6	1637.3	1590.2	1502.3	1484.1	1447.7	1385.5	1255.9	1091.9
40°	1849.5	1829.1	1774.5	1725.2	1660.9	1567.7	1552.7	1505.5	1443.4	1308.4	1124.1
42.5°	1965.2	1935.2	1864.5	1802.4	1722.0	1644.8	1625.6	1569.8	1499.1	1356.6	1157.3
45°	2138.8	2066.0	1964.2	1927.7	1788.4	1717.7	1701.6	1633.1	1560.2	1409.1	1190.5
47.5°	2117.4	2066.0	2032.7	2028.5	1858.1	1797.0	1773.4	1702.7	1625.6	1464.8	1224.8
50°	2159.2	2118.5	2120.6	2068.1	1921.3	1864.5	1847.4	1775.6	1692.0	1519.5	1261.2
52.5°	2150.6	2162.4	2156.0	2074.5	1982.4	1935.2	1922.4	1850.6	1755.2	1572.0	1293.4
55°	2219.2	2212.8	2198.8	2118.5	2049.9	2001.7	1991.0	1928.8	1819.5	1617.0	1321.2
57.5°	2269.6	2236.3	2235.3	2167.8	2124.9	2085.3	2068.1	2009.2	1879.5	1656.6	1342.7
60°	2238.5	2198.8	2227.8	2175.3	2171.0	2156.0	2146.3	2079.9	1933.1	1686.6	1351.2
62.5°	2072.4	2082.0	2167.8	2164.5	2221.3	2235.3	2224.6	2129.2	1968.5	1697.3	1344.8
65°	1852.7	1881.7	2013.5	2126.0	2280.3	2328.5	2317.8	2164.5	1965.2	1672.7	1301.9
67°	1591.3	1622.3	1828.1	2032.7	2274.9	2377.8	2370.3	2190.3	1926.7	1609.5	1224.8
67.5°	1533.4	1568.8	1774.5	1989.9	2255.6	2373.5	2368.1	2192.4	1913.8	1579.5	1194.8
70°	1128.3	1170.1	1460.5	1748.8	2101.3	2249.2	2248.1	2112.0	1780.9	1416.6	1036.2
72.5°	702.9	740.4	1041.6	1364.1	1820.6	2002.7	1995.2	1839.9	1533.4	1156.2	817.6
75°	430.8	454.3	655.8	889.4	1320.2	1621.3	1632.0	1438.0	1045.8	686.9	461.8
77.5°	263.6	289.3	413.6	548.6	806.9	1008.3	1010.5	797.2	536.9	374.0	252.9
80°	146.8	153.2	215.4	287.2	413.6	415.8	398.6	351.5	278.6	180.0	129.7
82.5°	57.9	62.2	93.2	115.7	117.9	123.2	114.7	103.9	87.9	57.9	40.7
85°	0.0	0.0	0.0	2.1	7.5	15.0	15.0	10.7	4.3	3.2	3.2
87.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P977121

CATALOG NUMBER: GKO-PB1F-722-U-T4W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	878.7	878.7	878.7	878.7	878.7	878.7	878.7	878.7	878.7	878.7	878.7
2.5°	877.6	876.5	869.0	860.5	854.0	848.7	843.3	836.9	836.9	839.0	838.0
5°	875.5	870.1	856.2	841.2	829.4	818.7	809.0	800.5	799.4	800.5	801.5
7.5°	876.5	866.9	845.5	823.0	803.7	789.7	775.8	769.4	768.3	768.3	768.3
10°	880.8	866.9	838.0	806.9	783.3	762.9	747.9	741.5	742.6	743.7	744.7
12.5°	888.3	869.0	832.6	793.0	762.9	742.6	727.6	722.2	726.5	731.9	732.9
15°	895.8	873.3	827.2	781.2	746.9	724.4	713.7	712.6	720.1	729.7	731.9
17.5°	904.4	876.5	820.8	766.2	729.7	711.5	706.2	709.4	721.2	736.2	739.4
20°	913.0	880.8	813.3	752.2	713.7	700.8	704.0	713.7	728.7	746.9	750.1
22.5°	921.5	884.0	803.7	735.1	696.5	692.2	704.0	720.1	735.1	755.4	759.7
25°	931.2	888.3	791.9	713.7	679.4	682.6	702.9	722.2	738.3	759.7	765.1
27.5°	946.2	894.8	780.1	694.4	660.1	670.8	697.6	721.2	738.3	758.7	765.1
30°	961.2	901.2	770.4	674.0	640.8	654.7	686.9	715.8	732.9	751.2	759.7
32.5°	978.3	909.8	761.9	653.6	619.4	636.5	671.9	704.0	724.4	740.4	749.0
35°	996.5	922.6	755.4	635.4	597.9	612.9	649.4	689.0	709.4	724.4	731.9
37.5°	1020.1	936.5	751.2	617.2	575.4	588.3	625.8	667.6	691.2	702.9	712.6
40°	1045.8	956.9	751.2	602.2	554.0	562.6	601.1	646.1	669.7	679.4	689.0
42.5°	1071.6	977.3	750.1	587.2	531.5	537.9	576.5	622.6	645.1	652.6	660.1
45°	1101.6	1000.8	749.0	570.1	506.8	513.3	552.9	599.0	620.4	626.9	633.3
47.5°	1133.7	1024.4	744.7	548.6	484.3	489.7	529.3	572.2	593.6	601.1	607.6
50°	1162.6	1046.9	734.0	524.0	464.0	469.3	504.7	540.1	559.4	567.9	574.4
52.5°	1188.4	1063.0	716.9	496.1	441.5	447.9	474.7	505.8	520.8	527.2	531.5
55°	1208.7	1071.6	689.0	469.3	420.1	423.3	444.7	472.6	484.3	485.4	488.6
57.5°	1222.6	1070.5	651.5	438.3	398.6	399.7	414.7	439.3	447.9	446.8	449.0
60°	1225.9	1056.6	606.5	409.3	377.2	374.0	389.0	406.1	411.5	415.8	421.1
62.5°	1213.0	1023.3	555.1	380.4	355.8	350.4	361.1	376.1	384.7	386.8	389.0
65°	1165.9	962.3	492.9	350.4	334.3	324.7	336.5	357.9	371.8	376.1	375.0
67°	1083.3	876.5	439.3	327.9	312.9	304.3	321.5	344.0	353.6	360.0	360.0
67.5°	1056.6	845.5	421.1	320.4	307.5	300.0	316.1	337.5	350.4	357.9	357.9
70°	896.9	693.3	355.8	282.9	276.5	277.5	296.8	320.4	336.5	344.0	344.0
72.5°	683.7	536.9	289.3	246.5	244.3	251.8	276.5	297.9	318.3	331.1	330.0
75°	387.9	309.7	211.1	201.5	210.0	225.0	256.1	279.7	297.9	310.8	309.7
77.5°	226.1	186.5	145.7	138.2	162.9	197.2	229.3	259.3	272.2	276.5	273.2
80°	114.7	97.5	91.1	94.3	109.3	146.8	200.4	235.7	245.4	248.6	245.4
82.5°	36.4	33.2	36.4	48.2	72.9	115.7	161.8	213.2	225.0	225.0	224.0
85°	2.1	2.1	2.1	21.4	50.4	85.7	126.4	186.5	211.1	209.0	205.7
87.5°	1.1	1.1	1.1	13.9	39.6	71.8	111.4	169.3	201.5	186.5	175.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-2

Test Date: 04/09/2025

Luminaire Tested: GKO-PB1E-722-U-T4W

Data in this report applies to families of products including GKO-PB1E-722-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-722-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	2281	CRI (Ra):	70.6		
CIE u':	0.2851	R1:	68.4	R9:	-35.1
CIE v':	0.5324	R2:	88.7	R10:	78.0
Duv:	-0.0016	R3:	85.7	R11:	60.2
CIE x:	0.4942	R4:	63.2	R12:	73.8
CIE y:	0.4102	R5:	69.0	R13:	72.8
CIE z:	0.0956	R6:	88.6	R14:	92.4
Peak Wavelength (nm):	602	R7:	68.8	R15:	58.4
Dominant Wavelength (nm):	587	R8:	32.6		
Purity:	71.48321				
Rf:	76.9				
Rg:	92.6				



Test Conditions


Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP2-2501-321-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.98

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.75


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2



TM-30-18

Summary

$R_f = 76.9$
 $R_g = 92.6$
 $CIE R_a = 70.6$
 $R_g = -35.1$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 87	CES26 = 76	CES51 = 88	CES76 = 78
CES02 = 65	CES27 = 94	CES52 = 84	CES77 = 76
CES03 = 32	CES28 = 93	CES53 = 79	CES78 = 79
CES04 = 72	CES29 = 81	CES54 = 86	CES79 = 82
CES05 = 51	CES30 = 92	CES55 = 83	CES80 = 81
CES06 = 52	CES31 = 83	CES56 = 76	CES81 = 52
CES07 = 44	CES32 = 75	CES57 = 74	CES82 = 92
CES08 = 42	CES33 = 89	CES58 = 76	CES83 = 88
CES09 = 29	CES34 = 88	CES59 = 84	CES84 = 90
CES10 = 79	CES35 = 94	CES60 = 91	CES85 = 65
CES11 = 62	CES36 = 90	CES61 = 81	CES86 = 49
CES12 = 68	CES37 = 96	CES62 = 91	CES87 = 76
CES13 = 44	CES38 = 98	CES63 = 86	CES88 = 78
CES14 = 75	CES39 = 98	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 95	CES65 = 71	CES90 = 80
CES16 = 48	CES41 = 95	CES66 = 70	CES91 = 80
CES17 = 51	CES42 = 89	CES67 = 69	CES92 = 52
CES18 = 57	CES43 = 80	CES68 = 73	CES93 = 69
CES19 = 74	CES44 = 99	CES69 = 84	CES94 = 45
CES20 = 68	CES45 = 83	CES70 = 71	CES95 = 66
CES21 = 88	CES46 = 81	CES71 = 74	CES96 = 75
CES22 = 81	CES47 = 89	CES72 = 89	CES97 = 75
CES23 = 92	CES48 = 73	CES73 = 67	CES98 = 72
CES24 = 92	CES49 = 82	CES74 = 85	CES99 = 64
CES25 = 73	CES50 = 87	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)