

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1212061

Luminaire Tested: **GKO-PB2A-850-U-T1**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1212061
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2A-850-U-T1
Description: GEKKO WALL PACK 4000LM PACKAGE 80CRI 5000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4072.3 lumens
Efficiency: N/A
Efficacy: 153.7 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B2 - U0 - G2

Input Watts (W): 26.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 12%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1212061
 CATALOG NUMBER: GKO-PB2A-850-U-T1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 4.5 fc
 Type I - Short - N/A

REPORT NUMBER: P1212061
CATALOG NUMBER: GKO-PB2A-850-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1212061

CATALOG NUMBER: GKO-PB2A-850-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2036.2	0.0	2036.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2036.2	0.0	2036.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	4072.3	0.0	4072.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.9	2.4
10°-20°	292.0	7.2
20°-30°	485.6	11.9
30°-40°	645.1	15.8
40°-50°	727.3	17.9
50°-60°	747.9	18.4
60°-70°	706.7	17.4
70°-80°	346.0	8.5
80°-90°	24.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4072.3	100.0
0°-180°	4072.3	100.0



REPORT NUMBER: P1212061


CATALOG NUMBER: GKO-PB2A-850-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	437.3	10.7			
FM	(30°-60°)	1060.1	26.0			
FH	(60°-80°)	526.4	12.9			G0/660
FVH	(80°-90°)	12.4	0.3			G1/100
BL	(0°-30°)	437.3	10.7	B1/500		
BM	(30°-60°)	1060.1	26.0	B2/2500		
BH	(60°-80°)	526.4	12.9	B2/1000		G2/1000
BVH	(80°-90°)	12.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type I Short





REPORT NUMBER: P1212061

CATALOG NUMBER: GKO-PB2A-850-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1010.5	1010.5	1010.5	1010.5	1010.5	1010.5	1010.5	1010.5	1010.5	1010.5	1010.5
2.5°	1011.3	1012.8	1009.8	1009.8	1011.3	1012.0	1012.0	1012.8	1011.3	1011.3	1010.5
5°	1011.3	1012.0	1010.5	1010.5	1012.0	1014.3	1013.5	1015.0	1015.0	1014.3	1014.3
7.5°	1010.5	1012.0	1010.5	1011.3	1013.5	1018.0	1018.0	1018.0	1019.5	1021.0	1021.0
10°	1009.8	1011.3	1012.0	1012.8	1015.8	1022.5	1024.0	1024.8	1027.0	1029.3	1029.3
12.5°	1006.0	1007.5	1009.8	1012.8	1018.0	1027.0	1030.0	1032.3	1036.0	1038.3	1039.8
15°	1000.7	1001.5	1006.8	1012.8	1021.0	1032.3	1038.3	1042.0	1047.3	1050.3	1052.5
17.5°	993.2	994.0	1002.2	1011.3	1023.3	1039.0	1048.8	1054.8	1060.1	1064.6	1067.6
20°	983.5	985.7	995.5	1009.8	1027.0	1045.8	1060.1	1070.6	1075.8	1080.3	1084.8
22.5°	971.5	973.7	985.7	1006.0	1030.8	1054.8	1073.6	1087.1	1093.8	1099.8	1105.1
25°	953.4	956.5	970.7	997.0	1032.3	1064.6	1088.6	1105.9	1111.9	1119.4	1123.9
27.5°	925.7	927.9	945.2	979.0	1027.8	1075.1	1105.9	1126.1	1132.9	1141.1	1145.6
30°	882.1	886.6	907.7	949.7	1016.5	1083.3	1126.1	1146.4	1154.7	1162.9	1168.9
32.5°	825.8	832.6	855.9	909.9	994.7	1086.3	1147.9	1171.2	1181.7	1190.7	1198.2
35°	756.0	762.8	790.5	858.9	960.2	1080.3	1169.7	1199.7	1212.5	1224.5	1233.5
37.5°	676.4	682.4	716.2	794.3	910.7	1061.6	1186.9	1231.2	1248.5	1264.3	1276.3
40°	596.1	602.9	639.6	723.0	850.6	1025.5	1194.4	1265.8	1287.5	1307.8	1322.8
42.5°	509.0	517.3	558.6	647.1	780.8	976.0	1188.4	1299.5	1326.6	1354.3	1376.9
45°	431.7	433.2	478.2	563.8	704.2	912.2	1167.4	1331.8	1368.6	1407.7	1439.9
47.5°	357.4	360.4	399.4	484.2	624.6	840.1	1129.1	1357.4	1415.9	1466.2	1513.5
50°	291.3	295.0	330.3	406.2	545.0	761.3	1077.3	1372.4	1456.5	1524.8	1590.8
52.5°	237.2	241.7	271.0	337.8	464.7	678.7	1013.5	1374.6	1493.2	1583.3	1671.2
55°	197.4	200.4	223.0	276.3	387.4	593.1	940.7	1363.4	1517.3	1635.9	1753.0
57.5°	166.7	169.7	185.4	227.5	317.6	505.3	852.1	1337.1	1530.0	1681.7	1835.6
60°	144.9	147.1	158.4	188.4	261.3	422.7	756.8	1290.5	1526.3	1710.2	1903.9
62.5°	129.1	129.9	139.6	160.7	215.5	344.6	649.4	1220.7	1495.5	1714.0	1950.4
65°	114.9	115.6	121.6	136.6	177.2	277.0	537.5	1124.6	1436.9	1687.7	1957.2
67.5°	93.1	94.6	103.6	114.9	145.6	219.2	423.4	998.5	1345.3	1619.4	1918.9
70°	74.3	75.1	84.1	96.8	118.6	172.7	325.1	828.8	1201.9	1508.3	1819.8
72.5°	55.6	57.1	65.3	78.1	96.8	133.6	235.0	626.9	961.0	1271.8	1584.8
75°	44.3	45.0	48.0	60.1	75.1	101.4	158.4	379.9	578.8	786.8	971.5
77.5°	37.5	38.3	38.3	46.5	55.6	68.3	84.1	150.9	244.7	348.3	461.7
80°	30.8	32.3	29.3	34.5	39.8	39.8	39.0	72.1	115.6	163.7	214.7
82.5°	22.5	24.0	22.5	24.0	24.0	21.8	20.3	27.0	36.8	50.3	54.8
85°	15.8	16.5	18.0	16.5	15.8	12.8	9.8	7.5	4.5	5.3	7.5
87.5°	10.5	12.8	15.0	14.3	12.0	9.8	6.8	4.5	2.3	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1212061
 CATALOG NUMBER: GKO-PB2A-850-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1010.5	1010.5	1010.5
2.5°	1011.3	1010.5	1009.8
5°	1015.0	1014.3	1013.5
7.5°	1020.3	1020.3	1020.3
10°	1028.5	1030.0	1030.0
12.5°	1039.0	1040.5	1040.5
15°	1051.8	1052.5	1054.1
17.5°	1067.6	1068.3	1068.3
20°	1086.3	1085.6	1087.1
22.5°	1105.1	1105.1	1105.1
25°	1124.6	1124.6	1124.6
27.5°	1147.1	1147.1	1145.6
30°	1171.9	1171.9	1171.9
32.5°	1201.9	1202.7	1203.4
35°	1240.2	1241.7	1244.0
37.5°	1283.8	1287.5	1289.8
40°	1335.6	1337.1	1340.8
42.5°	1393.4	1397.9	1398.6
45°	1465.5	1473.0	1476.0
47.5°	1550.3	1560.8	1566.1
50°	1644.9	1656.9	1664.4
52.5°	1747.7	1767.3	1776.3
55°	1857.4	1891.1	1900.9
57.5°	1981.2	2027.0	2040.5
60°	2102.8	2167.4	2189.2
62.5°	2206.4	2297.3	2324.3
65°	2279.3	2388.9	2428.7
67.5°	2294.3	2424.2	2471.5
70°	2204.2	2337.1	2391.9
72.5°	1916.7	2036.8	2105.1
75°	1132.1	1218.5	1197.4
77.5°	568.3	593.1	596.8
80°	249.2	264.3	270.3
82.5°	61.6	63.1	71.3
85°	8.3	9.8	9.0
87.5°	3.0	3.0	3.8
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-4

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-850-U-T4W

Data in this report applies to families of products including GKO-PB1C

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-850-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 5005
 CIE u' : 0.2100
 CIE v' : 0.4867
 Duv: 0.0019
 CIE x: 0.3453
 CIE y: 0.3557
 CIE z: 0.2990
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 570
 Purity: 10.34221
 R_f: 83.7
 R_g: 95.5

CRI (Ra): 83.1
 R1: 81.4
 R2: 89.2
 R3: 93.9
 R4: 82.4
 R5: 82.2
 R6: 84.5
 R7: 86.1
 R8: 65.5
 R9: 4.4
 R10: 74.2
 R11: 81.9
 R12: 62.2
 R13: 83.6
 R14: 97.0
 R15: 75.4



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2511-595-4

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.97

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 4.21


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4




TM-30-18

Summary

$R_f = 83.7$
 $R_g = 95.5$
 $\text{CIE } R_a = 83.1$
 $R_9 = 4.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 81	CES51 = 94	CES76 = 74
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 91	CES53 = 90	CES78 = 73
CES04 = 69	CES29 = 87	CES54 = 89	CES79 = 91
CES05 = 47	CES30 = 95	CES55 = 87	CES80 = 88
CES06 = 50	CES31 = 89	CES56 = 85	CES81 = 82
CES07 = 39	CES32 = 81	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 95	CES58 = 85	CES83 = 96
CES09 = 29	CES34 = 86	CES59 = 91	CES84 = 90
CES10 = 73	CES35 = 92	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 82	CES61 = 87	CES86 = 77
CES12 = 62	CES37 = 91	CES62 = 83	CES87 = 84
CES13 = 42	CES38 = 90	CES63 = 85	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 95	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 98	CES66 = 74	CES91 = 71
CES17 = 49	CES42 = 92	CES67 = 73	CES92 = 64
CES18 = 55	CES43 = 90	CES68 = 77	CES93 = 79
CES19 = 71	CES44 = 99	CES69 = 81	CES94 = 63
CES20 = 64	CES45 = 94	CES70 = 73	CES95 = 72
CES21 = 85	CES46 = 92	CES71 = 67	CES96 = 83
CES22 = 77	CES47 = 97	CES72 = 89	CES97 = 91
CES23 = 91	CES48 = 86	CES73 = 67	CES98 = 86
CES24 = 90	CES49 = 91	CES74 = 91	CES99 = 75
CES25 = 71	CES50 = 94	CES75 = 69	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)