

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P972397

Luminaire Tested: **GKO-PB2E-722-U-T1**

Issue Date: 02/27/2025

Test Information

Test Method: LM-79-08
Report Number: P972397
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/27/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2E-722-U-T1
Description: GEKKO WALL PACK 12000LM PACKAGE 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11178.7 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 104.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 6%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P972397

CATALOG NUMBER: GKO-PB2E-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 27.7 fc
 Type I - Short - N/A

REPORT NUMBER: P972397

CATALOG NUMBER: GKO-PB2E-722-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P972397

CATALOG NUMBER: GKO-PB2E-722-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5589.3	0.0	5589.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5589.3	0.0	5589.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	11178.7	0.0	11178.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.0	2.4
10°-20°	801.7	7.2
20°-30°	1333.0	11.9
30°-40°	1770.9	15.8
40°-50°	1996.4	17.9
50°-60°	2052.9	18.4
60°-70°	1940.1	17.4
70°-80°	949.7	8.5
80°-90°	67.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11178.7	100.0
0°-180°	11178.7	100.0

Coefficient of Utilization



REPORT NUMBER: P972397


CATALOG NUMBER: GKO-PB2E-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1200.4	10.7			
FM	(30°-60°)	2910.1	26.0			
FH	(60°-80°)	1444.9	12.9			G1/1800
FVH	(80°-90°)	34.0	0.3			G1/100
BL	(0°-30°)	1200.4	10.7	B3/2500		
BM	(30°-60°)	2910.1	26.0	B3/5000		
BH	(60°-80°)	1444.9	12.9	B3/2500		G3/2500
BVH	(80°-90°)	34.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type I Short



REPORT NUMBER: P972397

CATALOG NUMBER: GKO-PB2E-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2773.9	2773.9	2773.9	2773.9	2773.9	2773.9	2773.9	2773.9	2773.9	2773.9	2773.9
2.5°	2776.0	2780.1	2771.8	2771.8	2776.0	2778.0	2778.0	2780.1	2776.0	2776.0	2773.9
5°	2776.0	2778.0	2773.9	2773.9	2778.0	2784.2	2782.1	2786.3	2786.3	2784.2	2784.2
7.5°	2773.9	2778.0	2773.9	2776.0	2782.1	2794.5	2794.5	2794.5	2798.6	2802.7	2802.7
10°	2771.8	2776.0	2778.0	2780.1	2788.3	2806.9	2811.0	2813.1	2819.2	2825.4	2825.4
12.5°	2761.5	2765.7	2771.8	2780.1	2794.5	2819.2	2827.5	2833.7	2844.0	2850.1	2854.3
15°	2747.1	2749.2	2763.6	2780.1	2802.7	2833.7	2850.1	2860.5	2874.9	2883.1	2889.3
17.5°	2726.5	2728.6	2751.2	2776.0	2808.9	2852.2	2879.0	2895.5	2909.9	2922.3	2930.5
20°	2699.7	2705.9	2732.7	2771.8	2819.2	2870.8	2909.9	2938.8	2953.2	2965.6	2977.9
22.5°	2666.7	2672.9	2705.9	2761.5	2829.5	2895.5	2947.0	2984.1	3002.6	3019.1	3033.6
25°	2617.3	2625.5	2664.7	2736.8	2833.7	2922.3	2988.2	3035.6	3052.1	3072.7	3085.1
27.5°	2541.0	2547.2	2594.6	2687.3	2821.3	2951.1	3035.6	3091.3	3109.8	3132.5	3144.8
30°	2421.5	2433.9	2491.6	2607.0	2790.4	2973.8	3091.3	3146.9	3169.6	3192.2	3208.7
32.5°	2266.9	2285.5	2349.4	2497.7	2730.6	2982.0	3151.0	3214.9	3243.8	3268.5	3289.1
35°	2075.3	2093.8	2170.1	2357.6	2635.8	2965.6	3210.8	3293.2	3328.3	3361.2	3386.0
37.5°	1856.8	1873.3	1966.0	2180.4	2499.8	2914.0	3258.2	3379.8	3427.2	3470.5	3503.4
40°	1636.3	1654.9	1755.8	1984.6	2334.9	2815.1	3278.8	3474.6	3534.3	3590.0	3631.2
42.5°	1397.3	1419.9	1533.3	1776.4	2143.3	2679.1	3262.3	3567.3	3641.5	3717.8	3779.6
45°	1185.0	1189.1	1312.8	1547.7	1933.1	2503.9	3204.6	3655.9	3756.9	3864.1	3952.7
47.5°	981.0	989.2	1096.4	1329.2	1714.6	2306.1	3099.5	3726.0	3886.8	4024.8	4154.7
50°	799.6	809.9	906.8	1114.9	1496.2	2089.7	2957.3	3767.2	3998.0	4185.6	4366.9
52.5°	651.2	663.6	744.0	927.4	1275.7	1863.0	2782.1	3773.4	4099.0	4346.3	4587.4
55°	542.0	550.2	612.1	758.4	1063.4	1628.1	2582.2	3742.5	4165.0	4490.6	4812.1
57.5°	457.5	465.8	509.0	624.4	871.7	1386.9	2339.1	3670.4	4200.0	4616.3	5038.8
60°	397.7	403.9	434.8	517.3	717.2	1160.3	2077.3	3542.6	4189.7	4694.6	5226.3
62.5°	354.5	356.5	383.3	441.0	591.5	945.9	1782.6	3350.9	4105.2	4704.9	5354.1
65°	315.3	317.4	333.9	375.1	486.4	760.5	1475.6	3087.1	3944.5	4632.8	5372.6
67.5°	255.5	259.7	284.4	315.3	399.8	601.8	1162.3	2740.9	3693.0	4445.2	5267.5
70°	204.0	206.1	230.8	265.8	325.6	474.0	892.3	2275.2	3299.4	4140.2	4995.5
72.5°	152.5	156.6	179.3	214.3	265.8	366.8	645.0	1720.8	2637.9	3491.1	4350.4
75°	121.6	123.7	131.9	164.9	206.1	278.2	434.8	1042.8	1588.9	2159.8	2666.7
77.5°	103.0	105.1	105.1	127.8	152.5	187.5	230.8	414.2	671.8	956.2	1267.4
80°	84.5	88.6	80.4	94.8	109.2	109.2	107.2	197.8	317.4	449.3	589.4
82.5°	61.8	65.9	61.8	65.9	65.9	59.8	55.6	74.2	101.0	138.1	150.4
85°	43.3	45.3	49.5	45.3	43.3	35.0	26.8	20.6	12.4	14.4	20.6
87.5°	28.9	35.0	41.2	39.2	33.0	26.8	18.5	12.4	6.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P972397

CATALOG NUMBER: GKO-PB2E-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2773.9	2773.9	2773.9
2.5°	2776.0	2773.9	2771.8
5°	2786.3	2784.2	2782.1
7.5°	2800.7	2800.7	2800.7
10°	2823.4	2827.5	2827.5
12.5°	2852.2	2856.3	2856.3
15°	2887.2	2889.3	2893.4
17.5°	2930.5	2932.6	2932.6
20°	2982.0	2980.0	2984.1
22.5°	3033.6	3033.6	3033.6
25°	3087.1	3087.1	3087.1
27.5°	3149.0	3149.0	3144.8
30°	3217.0	3217.0	3217.0
32.5°	3299.4	3301.5	3303.5
35°	3404.5	3408.6	3414.8
37.5°	3524.0	3534.3	3540.5
40°	3666.2	3670.4	3680.7
42.5°	3824.9	3837.3	3839.4
45°	4022.8	4043.4	4051.6
47.5°	4255.6	4284.5	4298.9
50°	4515.3	4548.3	4568.9
52.5°	4797.6	4851.2	4876.0
55°	5098.5	5191.3	5218.1
57.5°	5438.6	5564.3	5601.4
60°	5772.4	5949.7	6009.4
62.5°	6056.8	6306.2	6380.4
65°	6256.7	6557.6	6666.8
67.5°	6297.9	6654.5	6784.3
70°	6050.6	6415.4	6565.8
72.5°	5261.3	5591.1	5778.6
75°	3107.8	3344.7	3287.0
77.5°	1560.1	1628.1	1638.4
80°	684.2	725.4	741.9
82.5°	169.0	173.1	195.8
85°	22.7	26.8	24.7
87.5°	8.2	8.2	10.3
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-2

Test Date: 04/09/2025

Luminaire Tested: GKO-PB1E-722-U-T4W


Data in this report applies to families of products including GKO-PB1E-722-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-722-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	2281	CRI (Ra):	70.6		
CIE u':	0.2851	R1:	68.4	R9:	-35.1
CIE v':	0.5324	R2:	88.7	R10:	78.0
Duv:	-0.0016	R3:	85.7	R11:	60.2
CIE x:	0.4942	R4:	63.2	R12:	73.8
CIE y:	0.4102	R5:	69.0	R13:	72.8
CIE z:	0.0956	R6:	88.6	R14:	92.4
Peak Wavelength (nm):	602	R7:	68.8	R15:	58.4
Dominant Wavelength (nm):	587	R8:	32.6		
Purity:	71.48321				
Rf:	76.9				
Rg:	92.6				



Test Conditions


Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP2-2501-321-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.98

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.75


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	124	NR	620	894	NR	750	22	NR	880	0	NR
365	0	NR	495	141	NR	625	837	NR	755	19	NR	885	0	NR
370	0	NR	500	163	NR	630	774	NR	760	16	NR	890	0	NR
375	0	NR	505	184	NR	635	706	NR	765	13	NR	895	0	NR
380	0	NR	510	204	NR	640	638	NR	770	11	NR	900	0	NR
385	0	NR	515	221	NR	645	570	NR	775	10	NR	905	0	NR
390	0	NR	520	237	NR	650	505	NR	780	8	NR	910	0	NR
395	0	NR	525	252	NR	655	446	NR	785	7	NR	915	0	NR
400	0	NR	530	268	NR	660	389	NR	790	6	NR	920	0	NR
405	1	NR	535	287	NR	665	339	NR	795	5	NR	925	0	NR
410	2	NR	540	310	NR	670	292	NR	800	4	NR	930	0	NR
415	5	NR	545	339	NR	675	253	NR	805	4	NR	935	0	NR
420	9	NR	550	377	NR	680	217	NR	810	3	NR	940	0	NR
425	15	NR	555	424	NR	685	186	NR	815	3	NR	945	0	NR
430	26	NR	560	482	NR	690	158	NR	820	2	NR	950	0	NR
435	43	NR	565	551	NR	695	135	NR	825	2	NR	955	0	NR
440	71	NR	570	632	NR	700	114	NR	830	2	NR	960	0	NR
445	123	NR	575	714	NR	705	97	NR	835	2	NR	965	0	NR
450	210	NR	580	797	NR	710	82	NR	840	1	NR	970	0	NR
455	245	NR	585	873	NR	715	70	NR	845	1	NR	975	0	NR
460	190	NR	590	934	NR	720	59	NR	850	1	NR	980	0	NR
465	161	NR	595	975	NR	725	50	NR	855	1	NR	985	0	NR
470	145	NR	600	996	NR	730	43	NR	860	1	NR	990	0	NR
475	117	NR	605	997	NR	735	36	NR	865	1	NR	995	0	NR
480	107	NR	610	978	NR	740	30	NR	870	1	NR	1000	0	NR
485	113	NR	615	945	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-2





TM-30-18

Summary

$R_f = 76.9$
 $R_g = 92.6$
 $CIE R_a = 70.6$
 $R_g = -35.1$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 76	CES51 = 88	CES76 = 78
CES02 = 65	CES27 = 94	CES52 = 84	CES77 = 76
CES03 = 32	CES28 = 93	CES53 = 79	CES78 = 79
CES04 = 72	CES29 = 81	CES54 = 86	CES79 = 82
CES05 = 51	CES30 = 92	CES55 = 83	CES80 = 81
CES06 = 52	CES31 = 83	CES56 = 76	CES81 = 52
CES07 = 44	CES32 = 75	CES57 = 74	CES82 = 92
CES08 = 42	CES33 = 89	CES58 = 76	CES83 = 88
CES09 = 29	CES34 = 88	CES59 = 84	CES84 = 90
CES10 = 79	CES35 = 94	CES60 = 91	CES85 = 65
CES11 = 62	CES36 = 90	CES61 = 81	CES86 = 49
CES12 = 68	CES37 = 96	CES62 = 91	CES87 = 76
CES13 = 44	CES38 = 98	CES63 = 86	CES88 = 78
CES14 = 75	CES39 = 98	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 95	CES65 = 71	CES90 = 80
CES16 = 48	CES41 = 95	CES66 = 70	CES91 = 80
CES17 = 51	CES42 = 89	CES67 = 69	CES92 = 52
CES18 = 57	CES43 = 80	CES68 = 73	CES93 = 69
CES19 = 74	CES44 = 99	CES69 = 84	CES94 = 45
CES20 = 68	CES45 = 83	CES70 = 71	CES95 = 66
CES21 = 88	CES46 = 81	CES71 = 74	CES96 = 75
CES22 = 81	CES47 = 89	CES72 = 89	CES97 = 75
CES23 = 92	CES48 = 73	CES73 = 67	CES98 = 72
CES24 = 92	CES49 = 82	CES74 = 85	CES99 = 64
CES25 = 73	CES50 = 87	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)