

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P972366

Luminaire Tested: **GKO-PB1A-730-U-T2U**

Issue Date: 02/27/2025

Test Information

Test Method: LM-79-08
Report Number: P972366
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/27/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1A-730-U-T2U
Description: GEKKO WALL PACK 750LM PACKAGE 70CRI 3000K FIXTURE w/ TYPE II URBAN DISTRIBUTION OPTIC
Light Source: (10) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 724.7 lumens
Efficiency: N/A
Efficacy: 151.0 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B0 - U0 - G0


Input Watts (W): 4.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 16%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P972366

CATALOG NUMBER: GKO-PB1A-730-U-T2U

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 1.6 fc
 Type II - Medium - N/A

REPORT NUMBER: P972366

CATALOG NUMBER: GKO-PB1A-730-U-T2U

Luminous Intensity Polar Plot



REPORT NUMBER: P972366

CATALOG NUMBER: GKO-PB1A-730-U-T2U


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	239.1	0.0	239.1
	% Fixture	33.0	0.0	33.0
Street Side	Lumens	485.6	0.0	485.6
	% Fixture	67.0	0.0	67.0
Total	Lumens	724.7	0.0	724.7
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.5	1.9
10°-20°	41.4	5.7
20°-30°	71.3	9.8
30°-40°	102.4	14.1
40°-50°	129.9	17.9
50°-60°	142.6	19.7
60°-70°	138.3	19.1
70°-80°	76.4	10.5
80°-90°	8.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	724.7	100.0
0°-180°	724.7	100.0



REPORT NUMBER: P972366


CATALOG NUMBER: GKO-PB1A-730-U-T2U

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	73.4	10.1			
FM	(30°-60°)	257.8	35.6			
FH	(60°-80°)	151.3	20.9			G0/660
FVH	(80°-90°)	3.1	0.4			G0/10
BL	(0°-30°)	52.8	7.3	B0/110		
BM	(30°-60°)	117.2	16.2	B0/220		
BH	(60°-80°)	63.4	8.7	B0/110		G0/110
BVH	(80°-90°)	5.7	0.8			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G0

Type II Medium



REPORT NUMBER: P972366

CATALOG NUMBER: GKO-PB1A-730-U-T2U

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	76°	85°
0°	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9
2.5°	145.1	144.9	144.8	144.8	144.2	143.7	143.1	142.7	141.6	141.4	140.9
5°	149.4	149.4	149.0	148.9	148.0	146.6	145.4	144.1	142.6	142.3	141.0
7.5°	155.0	155.0	154.3	153.8	152.5	150.3	148.0	145.8	143.5	143.3	141.3
10°	162.2	162.2	161.6	160.4	157.7	154.8	151.1	147.6	144.7	144.4	141.6
12.5°	169.6	169.8	168.9	167.1	163.9	159.4	154.9	149.8	146.1	145.6	142.1
15°	177.2	177.3	176.8	174.8	170.5	165.0	159.0	152.9	147.9	147.5	143.0
17.5°	184.6	184.9	184.3	182.1	177.0	171.2	163.7	156.2	150.1	149.6	144.4
20°	191.6	191.6	191.6	189.1	184.2	177.5	168.9	160.1	152.7	152.1	146.1
22.5°	197.9	198.2	198.6	197.2	191.6	184.2	174.9	164.4	155.9	155.2	148.2
25°	204.2	204.4	205.5	204.5	199.1	191.3	181.4	169.9	159.8	159.1	150.7
27.5°	211.5	211.9	212.6	212.2	206.1	198.5	188.5	175.9	164.1	163.4	153.8
30°	220.1	220.1	220.5	219.8	213.6	206.1	195.7	182.2	169.6	168.5	157.6
32.5°	227.1	227.8	227.5	227.2	220.8	213.2	203.0	189.2	175.9	174.5	162.7
35°	233.7	233.8	233.7	234.0	227.5	220.4	210.7	197.4	182.9	182.4	169.3
37.5°	237.5	237.7	238.4	239.3	233.5	226.8	218.4	206.3	191.6	190.6	177.2
40°	239.3	239.7	243.5	244.7	238.6	233.0	226.5	214.5	200.0	198.9	185.0
42.5°	242.1	245.4	247.4	247.7	242.4	237.5	233.5	223.7	210.4	209.4	195.5
45°	232.8	231.6	236.8	242.8	242.5	240.4	240.3	234.1	223.2	222.2	207.5
47.5°	221.2	220.2	223.0	231.9	238.2	241.7	246.9	246.3	238.6	237.2	221.3
50°	193.4	195.1	208.9	220.9	231.9	242.1	252.5	259.0	253.6	252.5	236.1
52.5°	167.5	168.6	178.0	206.8	223.7	240.8	257.4	272.5	271.1	269.8	252.2
55°	149.3	150.4	165.4	183.8	211.7	234.4	260.6	285.3	288.9	287.6	269.3
57.5°	130.2	132.0	142.3	158.4	195.5	223.7	261.7	298.2	308.2	307.1	285.7
60°	111.9	114.4	120.4	137.9	175.6	211.1	258.8	308.5	326.9	326.9	302.6
62.5°	94.9	96.3	102.6	118.4	150.4	195.0	251.3	315.1	344.0	343.3	317.5
65°	80.9	81.6	86.6	100.2	129.2	177.2	238.4	314.7	356.2	356.3	327.3
67°	68.3	69.4	75.0	87.3	113.1	160.4	223.6	308.4	360.5	360.8	329.7
67.5°	63.9	65.2	71.3	84.1	109.8	155.7	220.1	305.7	360.3	360.8	329.0
70°	44.0	44.3	54.7	69.2	90.3	131.2	195.8	287.2	349.6	349.2	313.7
72.5°	28.0	27.6	37.6	50.6	72.6	106.3	165.3	254.8	317.2	316.8	276.6
75°	18.6	19.1	25.4	36.2	51.0	82.1	128.8	192.3	220.4	218.7	182.5
77.5°	13.3	13.0	15.7	26.1	34.2	49.9	69.9	102.3	117.0	117.0	100.2
80°	7.3	7.4	8.6	14.4	19.3	19.5	26.2	51.3	57.2	58.5	48.6
82.5°	2.1	2.2	3.1	4.9	5.3	5.9	9.1	14.7	15.4	16.3	13.2
85°	0.0	0.0	0.0	0.1	0.6	0.7	0.7	0.8	1.4	1.4	1.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.3	0.6	0.6	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P972366

CATALOG NUMBER: GKO-PB1A-730-U-T2U

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9	140.9
2.5°	140.7	140.9	140.3	139.6	139.1	138.8	137.9	137.2	137.7	138.1	138.1
5°	140.6	140.5	139.3	138.1	137.2	136.7	135.3	134.3	134.4	134.8	134.7
7.5°	140.6	140.0	138.5	136.7	135.3	134.1	132.3	131.2	131.1	131.3	131.1
10°	140.7	139.8	137.7	135.1	133.2	131.5	129.2	128.0	127.6	127.7	127.4
12.5°	141.0	139.5	136.8	133.6	131.1	128.8	126.3	124.8	124.5	124.8	124.8
15°	141.4	139.5	136.1	132.2	128.8	126.3	123.8	122.4	122.4	122.5	122.5
17.5°	142.3	139.9	135.6	130.6	126.6	123.8	121.5	120.6	120.7	121.1	121.1
20°	143.1	140.5	135.0	129.1	124.6	121.4	119.6	118.9	119.4	120.0	120.0
22.5°	144.4	141.2	134.4	127.7	122.4	119.2	117.6	117.0	117.6	118.3	118.0
25°	146.3	142.4	134.0	126.4	120.3	116.8	115.2	114.7	114.9	115.5	115.5
27.5°	148.6	144.0	133.9	124.9	117.7	114.0	112.1	111.3	111.3	111.4	111.6
30°	152.4	146.6	134.4	123.8	115.5	111.0	108.6	107.4	107.2	107.8	107.8
32.5°	156.9	150.3	135.8	122.8	113.3	107.5	104.3	103.3	103.0	103.5	103.0
35°	161.9	154.3	137.7	122.7	111.0	103.7	100.1	99.0	98.1	97.8	97.6
37.5°	169.1	159.9	139.5	122.0	108.8	99.7	95.7	93.4	92.4	92.1	92.1
40°	176.1	165.4	141.7	120.8	106.1	95.6	90.0	87.3	86.9	86.9	86.9
42.5°	184.9	172.6	144.8	120.1	102.9	91.5	83.8	80.7	80.7	80.7	80.6
45°	195.8	181.9	148.7	119.9	99.8	86.6	77.2	73.2	73.0	72.9	72.8
47.5°	208.6	191.8	152.5	119.2	96.2	80.7	69.7	65.2	64.2	63.9	63.5
50°	221.8	202.4	156.6	118.2	91.8	73.9	62.5	57.3	55.2	54.5	54.8
52.5°	235.8	212.8	160.5	116.8	86.6	67.0	55.2	49.8	47.7	46.8	46.7
55°	249.5	223.3	164.1	114.9	81.0	60.0	49.1	43.7	41.9	41.6	41.6
57.5°	263.4	233.4	167.0	112.3	74.9	53.8	43.7	39.4	38.1	38.7	38.7
60°	276.0	242.2	168.4	108.6	68.7	48.2	39.5	36.3	35.7	37.1	37.0
62.5°	287.4	248.1	167.7	103.3	62.7	43.5	36.3	33.9	34.1	35.7	35.9
65°	292.8	249.1	163.6	96.0	55.9	39.4	32.9	30.7	31.0	32.8	33.2
67°	291.6	245.3	156.9	87.8	50.5	36.3	30.8	28.6	28.7	30.3	30.4
67.5°	290.2	243.5	155.0	85.2	49.1	35.7	30.3	28.2	28.5	29.9	29.9
70°	271.5	225.0	138.2	72.3	42.5	31.8	27.6	26.2	26.5	27.3	27.3
72.5°	237.3	194.8	111.9	58.0	36.0	28.2	25.0	24.1	24.1	24.1	23.4
75°	151.4	122.1	73.2	44.4	29.7	24.1	22.4	21.4	20.9	21.7	21.4
77.5°	83.7	63.8	38.1	25.5	21.4	20.0	19.5	19.1	18.9	20.9	20.3
80°	39.7	31.5	21.4	14.6	12.3	14.9	16.8	16.5	19.8	27.1	27.2
82.5°	12.6	10.4	8.7	8.0	8.3	10.7	13.0	15.0	25.7	29.0	28.6
85°	1.5	1.4	1.0	3.2	5.5	7.8	10.1	19.5	23.5	19.6	18.5
87.5°	0.6	0.6	0.6	2.2	4.2	6.0	9.1	19.6	14.4	13.2	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-4

Test Date: 04/10/2025

Luminaire Tested: GKO-PB1E-730-U-T4W

Data in this report applies to families of products including GKO-PB1E-730-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-730-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3072
 CIE u' : 0.2482
 CIE v' : 0.5193
 Duv: -0.0004
 CIE x: 0.4313
 CIE y: 0.4010
 CIE z: 0.1677
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 49.8225
 R_f: 74.7
 R_g: 94.2

CRI (Ra): 71.7
 R1: 68.1
 R2: 82.1
 R3: 93.4
 R4: 67.3
 R5: 67.2
 R6: 74.9
 R7: 77.5
 R8: 43.4
 R9: -33.9
 R10: 58.6
 R11: 62.0
 R12: 48.5
 R13: 70.7
 R14: 96.4
 R15: 60.2



Test Conditions

Stabilization Time: 30M
 Operation Time: 1H 30M
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP2-2501-321-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-4

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.24

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.3


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

TM-30-18

Summary

$R_f = 74.7$
 $R_g = 94.2$
 $CIE R_a = 71.7$
 $R_g = -33.9$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 65	CES51 = 86	CES76 = 58
CES02 = 62	CES27 = 89	CES52 = 85	CES77 = 76
CES03 = 31	CES28 = 84	CES53 = 77	CES78 = 62
CES04 = 71	CES29 = 68	CES54 = 85	CES79 = 85
CES05 = 49	CES30 = 83	CES55 = 84	CES80 = 84
CES06 = 51	CES31 = 71	CES56 = 74	CES81 = 73
CES07 = 41	CES32 = 64	CES57 = 74	CES82 = 93
CES08 = 40	CES33 = 78	CES58 = 75	CES83 = 91
CES09 = 29	CES34 = 75	CES59 = 85	CES84 = 88
CES10 = 76	CES35 = 87	CES60 = 90	CES85 = 76
CES11 = 59	CES36 = 94	CES61 = 81	CES86 = 64
CES12 = 65	CES37 = 84	CES62 = 89	CES87 = 77
CES13 = 43	CES38 = 92	CES63 = 75	CES88 = 80
CES14 = 74	CES39 = 96	CES64 = 65	CES89 = 67
CES15 = 71	CES40 = 92	CES65 = 65	CES90 = 79
CES16 = 47	CES41 = 93	CES66 = 60	CES91 = 80
CES17 = 50	CES42 = 86	CES67 = 58	CES92 = 57
CES18 = 56	CES43 = 78	CES68 = 66	CES93 = 74
CES19 = 73	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 66	CES45 = 85	CES70 = 60	CES95 = 67
CES21 = 87	CES46 = 81	CES71 = 57	CES96 = 77
CES22 = 79	CES47 = 86	CES72 = 85	CES97 = 83
CES23 = 92	CES48 = 75	CES73 = 52	CES98 = 76
CES24 = 91	CES49 = 79	CES74 = 95	CES99 = 64
CES25 = 73	CES50 = 86	CES75 = 60	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)