

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P972320

Luminaire Tested: **GKO-PB2B-730-U-T2R**

Issue Date: 02/27/2025



Test Information

Test Method: LM-79-08
Report Number: P972320
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/27/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2B-730-U-T2R
Description: GEKKO WALL PACK 6000LM PACKAGE 70CRI 3000K FIXTURE w/ TYPE II
ROADWAY DISTRIBUTION OPTIC
Light Source: (20) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6050.1 lumens
Efficiency: N/A
Efficacy: 144.7 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B1 - U0 - G1


Input Watts (W): 41.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 8%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P972320

CATALOG NUMBER: GKO-PB2B-730-U-T2R

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 16.2 fc
 Type II - Medium - N/A

REPORT NUMBER: P972320

CATALOG NUMBER: GKO-PB2B-730-U-T2R

Luminous Intensity Polar Plot



REPORT NUMBER: P972320

CATALOG NUMBER: GKO-PB2B-730-U-T2R

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1868.2	0.0	1868.2
	% Fixture	30.9	0.0	30.9
Street Side	Lumens	4181.9	0.0	4181.9
	% Fixture	69.1	0.0	69.1
Total	Lumens	6050.1	0.0	6050.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.3	1.4
10°-20°	316.0	5.2
20°-30°	640.1	10.6
30°-40°	1009.4	16.7
40°-50°	1239.6	20.5
50°-60°	1184.2	19.6
60°-70°	993.1	16.4
70°-80°	526.1	8.7
80°-90°	54.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6050.1	100.0
0°-180°	6050.1	100.0



REPORT NUMBER: P972320


CATALOG NUMBER: GKO-PB2B-730-U-T2R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	634.6	10.5			
FM	(30°-60°)	2491.8	41.2			
FH	(60°-80°)	1038.6	17.2			G1/1800
FVH	(80°-90°)	16.9	0.3			G1/100
BL	(0°-30°)	408.8	6.8	B1/500		
BM	(30°-60°)	941.4	15.6	B1/1000		
BH	(60°-80°)	480.6	7.9	B1/500		G1/500
BVH	(80°-90°)	37.5	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type II Medium



REPORT NUMBER: P972320

CATALOG NUMBER: GKO-PB2B-730-U-T2R

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	81°	85°
0°	842.8	842.8	842.8	842.8	842.8	842.8	842.8	842.8	842.8	842.8	842.8
2.5°	891.4	893.7	889.1	887.9	883.3	876.3	868.2	862.4	853.2	848.6	846.2
5°	975.9	971.3	967.8	962.0	945.8	931.9	908.8	892.5	875.2	863.6	860.1
7.5°	1078.9	1081.2	1069.7	1054.6	1031.5	1003.7	966.6	936.5	904.1	889.1	882.1
10°	1191.2	1200.5	1188.9	1170.4	1126.4	1084.7	1039.6	987.5	943.5	920.3	911.1
12.5°	1327.8	1333.6	1318.6	1294.3	1241.0	1178.5	1114.8	1050.0	992.1	963.2	947.0
15°	1480.6	1476.0	1461.0	1425.1	1356.8	1287.3	1200.5	1116.0	1047.7	1011.8	988.6
17.5°	1638.1	1632.3	1612.6	1566.3	1488.7	1401.9	1298.9	1192.4	1106.7	1067.4	1036.1
20°	1788.6	1782.8	1768.9	1716.8	1623.0	1516.5	1396.1	1280.4	1173.9	1125.2	1090.5
22.5°	1955.3	1950.6	1928.6	1865.0	1764.3	1647.3	1507.3	1369.5	1246.8	1188.9	1147.2
25°	2135.9	2137.0	2112.7	2023.6	1910.1	1773.5	1626.5	1470.2	1329.0	1256.0	1208.6
27.5°	2346.6	2345.4	2303.7	2207.6	2065.2	1907.8	1744.6	1575.6	1410.0	1324.4	1269.9
30°	2537.6	2532.9	2486.6	2390.5	2226.2	2049.0	1869.6	1677.4	1501.5	1399.6	1333.6
32.5°	2678.8	2680.0	2641.8	2536.4	2375.5	2186.8	1986.5	1792.0	1589.5	1480.6	1407.7
35°	2780.7	2781.8	2744.8	2654.5	2504.0	2315.3	2110.4	1899.7	1687.9	1564.0	1485.3
37.5°	2813.1	2813.1	2788.8	2718.2	2595.4	2431.1	2231.9	2022.4	1786.3	1654.3	1564.0
40°	2769.1	2772.6	2771.4	2725.1	2640.6	2510.9	2344.2	2140.5	1896.2	1743.4	1643.9
42.5°	2669.5	2671.9	2675.3	2658.0	2631.3	2553.8	2434.5	2260.9	2006.2	1840.7	1722.6
45°	2505.2	2514.4	2531.8	2538.7	2549.1	2543.4	2490.1	2373.2	2128.9	1937.9	1800.1
47.5°	2296.8	2311.8	2335.0	2376.7	2434.5	2480.8	2504.0	2460.0	2248.2	2038.6	1887.0
50°	2007.4	2023.6	2086.1	2172.9	2287.5	2377.8	2465.8	2524.8	2381.3	2161.3	1984.2
52.5°	1606.8	1641.5	1746.9	1913.6	2110.4	2244.7	2384.8	2556.1	2516.7	2306.0	2100.0
55°	1222.5	1235.2	1370.7	1570.9	1874.2	2101.1	2273.6	2539.9	2644.1	2457.7	2231.9
57.5°	854.3	868.2	986.3	1205.1	1540.8	1913.6	2162.5	2485.5	2759.8	2636.0	2383.6
60°	606.6	621.7	709.6	871.7	1197.0	1640.4	2059.5	2416.0	2860.6	2805.0	2558.4
62.5°	441.1	449.2	495.5	632.1	864.8	1282.7	1912.4	2370.9	2931.2	2980.9	2737.8
65°	338.0	346.1	372.8	458.4	639.0	937.7	1648.5	2369.7	2949.7	3110.6	2893.0
67°	281.3	280.2	303.3	368.1	498.9	705.0	1376.4	2360.4	2928.9	3152.3	2971.7
67.5°	266.3	270.9	289.4	343.8	471.2	649.4	1317.4	2345.4	2921.9	3151.1	2977.5
70°	211.8	213.0	229.2	272.0	354.2	471.2	948.1	2197.2	2816.6	3037.7	2912.6
72.5°	155.1	154.0	178.3	206.1	270.9	342.7	635.5	1845.3	2588.5	2691.5	2589.7
75°	114.6	113.4	126.2	157.4	193.3	255.8	412.1	1204.0	1752.7	1712.2	1581.3
77.5°	76.4	78.7	90.3	115.8	137.8	158.6	206.1	554.5	965.5	872.9	840.5
80°	46.3	42.8	50.9	66.0	79.9	81.0	88.0	239.6	414.4	394.8	370.4
82.5°	16.2	16.2	19.7	26.6	26.6	26.6	32.4	57.9	82.2	75.2	71.8
85°	0.0	0.0	0.0	0.0	2.3	3.5	2.3	4.6	8.1	9.3	9.3
87.5°	0.0	0.0	0.0	0.0	0.0	1.2	1.2	2.3	3.5	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P972320

CATALOG NUMBER: GKO-PB2B-730-U-T2R

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	842.8	842.8	842.8	842.8	842.8	842.8	842.8	842.8	842.8	842.8	842.8
2.5°	846.2	846.2	842.8	838.1	835.8	834.7	831.2	826.6	830.0	833.5	833.5
5°	857.8	855.5	848.6	843.9	840.5	840.5	835.8	834.7	838.1	841.6	840.5
7.5°	876.3	871.7	863.6	856.7	857.8	859.0	852.0	852.0	855.5	859.0	859.0
10°	901.8	893.7	885.6	879.8	881.0	882.1	875.2	872.9	876.3	879.8	882.1
12.5°	934.2	923.8	914.5	908.8	907.6	908.8	901.8	899.5	899.5	901.8	901.8
15°	972.4	960.8	949.3	941.2	938.9	937.7	928.4	920.3	920.3	921.5	921.5
17.5°	1016.4	1000.2	985.2	975.9	970.1	962.0	951.6	940.0	936.5	937.7	937.7
20°	1060.4	1043.0	1023.4	1010.6	999.1	985.2	969.0	953.9	947.0	947.0	945.8
22.5°	1111.3	1088.2	1061.6	1044.2	1023.4	1000.2	977.1	957.4	950.4	948.1	948.1
25°	1163.4	1136.8	1098.6	1072.0	1041.9	1008.3	978.2	951.6	940.0	935.4	935.4
27.5°	1216.7	1185.4	1135.7	1097.5	1053.5	1007.2	966.6	933.1	916.9	911.1	908.8
30°	1276.9	1231.7	1168.1	1116.0	1055.8	996.7	944.6	905.3	881.0	867.1	868.2
32.5°	1339.4	1282.7	1198.2	1127.6	1052.3	977.1	911.1	861.3	830.0	817.3	812.7
35°	1403.1	1331.3	1224.8	1133.3	1040.7	947.0	868.2	812.7	777.9	759.4	759.4
37.5°	1467.9	1382.2	1243.3	1132.2	1019.9	907.6	818.5	759.4	718.9	695.7	690.0
40°	1531.6	1429.7	1257.2	1122.9	988.6	860.1	765.2	701.5	647.1	617.0	612.4
42.5°	1594.1	1469.1	1264.2	1107.9	951.6	808.0	705.0	619.3	567.2	539.5	538.3
45°	1650.8	1500.3	1265.3	1088.2	903.0	749.0	624.0	541.8	489.7	460.7	460.7
47.5°	1706.4	1535.0	1264.2	1062.7	849.7	672.6	538.3	458.4	411.0	392.4	386.7
50°	1773.5	1569.8	1263.0	1031.5	781.4	581.1	455.0	386.7	346.1	327.6	327.6
52.5°	1841.8	1610.3	1265.3	987.5	700.4	492.0	380.9	320.7	294.0	282.5	281.3
55°	1929.8	1653.1	1271.1	935.4	615.9	405.2	317.2	276.7	258.2	252.4	253.5
57.5°	2036.3	1712.2	1282.7	874.0	517.5	332.2	272.0	250.1	245.4	247.7	248.9
60°	2157.9	1785.1	1298.9	804.6	430.6	276.7	245.4	240.8	245.4	254.7	255.8
62.5°	2299.1	1873.1	1319.7	727.0	345.0	243.1	233.8	237.3	240.8	255.8	257.0
65°	2424.1	1968.0	1324.4	635.5	280.2	221.1	226.9	229.2	238.5	255.8	257.0
67°	2494.7	2032.8	1293.1	548.7	239.6	209.5	217.6	220.0	236.2	253.5	255.8
67.5°	2502.8	2046.7	1272.3	526.7	231.5	207.2	215.3	220.0	236.2	253.5	254.7
70°	2478.5	2037.5	1133.3	397.1	191.0	191.0	200.3	210.7	226.9	245.4	253.5
72.5°	2262.0	1858.0	877.5	269.7	162.1	172.5	186.4	201.4	216.5	238.5	252.4
75°	1429.7	1195.9	537.1	180.6	135.4	154.0	176.0	193.3	206.1	222.3	231.5
77.5°	764.0	591.6	231.5	106.5	106.5	136.6	163.2	179.4	186.4	192.2	198.0
80°	361.2	275.5	112.3	63.7	74.1	106.5	144.7	162.1	164.4	171.3	173.6
82.5°	71.8	62.5	37.0	33.6	48.6	76.4	120.4	140.1	141.2	152.8	155.1
85°	9.3	8.1	5.8	12.7	31.3	56.7	92.6	120.4	122.7	122.7	120.4
87.5°	4.6	3.5	3.5	9.3	23.2	42.8	76.4	100.7	101.9	79.9	77.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-4

Test Date: 04/10/2025

Luminaire Tested: GKO-PB1E-730-U-T4W

Data in this report applies to families of products including GKO-PB1E-730-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-730-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3072
 CIE u' : 0.2482
 CIE v' : 0.5193
 Duv: -0.0004
 CIE x: 0.4313
 CIE y: 0.4010
 CIE z: 0.1677
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 49.8225
 R_f: 74.7
 R_g: 94.2

CRI (Ra): 71.7
 R1: 68.1
 R2: 82.1
 R3: 93.4
 R4: 67.3
 R5: 67.2
 R6: 74.9
 R7: 77.5
 R8: 43.4
 R9: -33.9
 R10: 58.6
 R11: 62.0
 R12: 48.5
 R13: 70.7
 R14: 96.4
 R15: 60.2



Test Conditions

Stabilization Time: 30M
 Operation Time: 1H 30M
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP2-2501-321-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-4

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.24

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.3

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

TM-30-18

Summary

$R_f = 74.7$
 $R_g = 94.2$
 $\text{CIE } R_a = 71.7$
 $R_g = -33.9$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 65	CES51 = 86	CES76 = 58
CES02 = 62	CES27 = 89	CES52 = 85	CES77 = 76
CES03 = 31	CES28 = 84	CES53 = 77	CES78 = 62
CES04 = 71	CES29 = 68	CES54 = 85	CES79 = 85
CES05 = 49	CES30 = 83	CES55 = 84	CES80 = 84
CES06 = 51	CES31 = 71	CES56 = 74	CES81 = 73
CES07 = 41	CES32 = 64	CES57 = 74	CES82 = 93
CES08 = 40	CES33 = 78	CES58 = 75	CES83 = 91
CES09 = 29	CES34 = 75	CES59 = 85	CES84 = 88
CES10 = 76	CES35 = 87	CES60 = 90	CES85 = 76
CES11 = 59	CES36 = 94	CES61 = 81	CES86 = 64
CES12 = 65	CES37 = 84	CES62 = 89	CES87 = 77
CES13 = 43	CES38 = 92	CES63 = 75	CES88 = 80
CES14 = 74	CES39 = 96	CES64 = 65	CES89 = 67
CES15 = 71	CES40 = 92	CES65 = 65	CES90 = 79
CES16 = 47	CES41 = 93	CES66 = 60	CES91 = 80
CES17 = 50	CES42 = 86	CES67 = 58	CES92 = 57
CES18 = 56	CES43 = 78	CES68 = 66	CES93 = 74
CES19 = 73	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 66	CES45 = 85	CES70 = 60	CES95 = 67
CES21 = 87	CES46 = 81	CES71 = 57	CES96 = 77
CES22 = 79	CES47 = 86	CES72 = 85	CES97 = 83
CES23 = 92	CES48 = 75	CES73 = 52	CES98 = 76
CES24 = 91	CES49 = 79	CES74 = 95	CES99 = 64
CES25 = 73	CES50 = 86	CES75 = 60	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)