Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P1203755

Luminaire Tested: GWC-SB2D-735-U-SLR

Issue Date: 10/30/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2024
Report Number:	P1203755
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab:	INNOVATION CENTER
Issue Date:	3/16/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGRAW-EDISON
Catalog Number:	GWC-SB2D-735-U-SLR
Description:	GALLEON WALL LUMINAIRE
	(2) 70 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT ELIMINATOF
	RIGHT OPTICS
Light Source:	-
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	20273 lumens
Efficiency:	N/A
Efficacy:	137.4 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B3 - U0 - G4

Input Watts (W):	147.6
Input Voltage (V):	120.0
Input Current (Ain):	1.234
Voltage Rise (V):	NR
Power Factor:	0.999
Total Harmonic Distortion (THDi):	3.108
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

Iso-Footcandle Lines of Horizontal Illumination




Based on 10 foot mounting height. Maximum calculated value = 34.4 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5152.4	0.0	5152.4
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	15120.6	0.0	15120.6
	% Fixture	74.6	0.0	74.6
Total	Lumens	20273.0	0.0	20273.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.5	1.4
10°-20°	868.1	4.3
20°-30°	1340.9	6.6
30°-40°	1699.3	8.4
40°-50°	2563.0	12.6
50°-60°	4140.9	20.4
60°-70°	5162.2	25.5
70°-80°	3385.1	16.7
80°-90°	836.9	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20273.0	100.0
0°-180°	20273.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1363.6	6.7			
FM	(30°-60°)	5913.2	29.2			
FH	(60°-80°)	7154.4	35.3			G3/7500
FVH	(80°-90°)	689.4	3.4			G4/750
BL	(0°-30°)	1122.0	5.5	B3/2500		
BM	(30°-60°)	2489.9	12.3	B2/2500		
BH	(60°-80°)	1393.0	6.9	B3/2500		G3/2500
BVH	(80°-90°)	147.5	0.7			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7
2.5°	2997.9	2974.9	2951.9	2927.4	2903.0	2878.4	2853.8	2830.3	2806.8	2784.0	2758.6
5°	3223.6	3172.8	3122.0	3071.3	3020.7	2969.7	2918.8	2871.2	2823.5	2778.6	2734.2
7.5°	3450.4	3366.5	3282.8	3205.3	3127.9	3052.5	2977.1	2910.6	2844.2	2782.9	2725.5
10°	3624.2	3518.2	3412.2	3309.8	3207.6	3116.0	3024.3	2945.8	2867.1	2791.5	2729.7
12.5°	3730.7	3614.2	3497.8	3381.8	3265.9	3157.8	3049.8	2960.9	2872.0	2792.5	2735.1
15°	3795.4	3674.0	3552.6	3426.8	3301.0	3176.6	3052.1	2949.2	2846.3	2758.3	2712.3
17.5°	3831.8	3708.6	3585.5	3448.3	3311.0	3166.6	3022.2	2898.4	2774.7	2671.1	2642.8
20°	3871.9	3743.9	3615.9	3465.1	3314.2	3139.2	2964.2	2810.8	2657.4	2536.9	2529.4
22.5°	3918.4	3787.7	3656.9	3487.7	3318.5	3105.6	2892.8	2708.0	2523.3	2386.0	2400.7
25°	3978.3	3850.2	3722.1	3528.8	3335.4	3072.5	2809.6	2593.2	2376.9	2236.3	2275.8
27.5°	4059.6	3937.5	3815.2	3593.0	3370.7	3050.3	2729.9	2488.3	2246.6	2118.6	2166.7
30°	4169.3	4051.2	3933.2	3676.1	3419.1	3040.0	2660.6	2400.6	2140.5	2033.0	2070.8
32.5°	4298.7	4181.8	4065.0	3762.9	3460.8	3027.1	2593.2	2324.9	2056.6	1969.9	1986.7
35°	4456.0	4344.1	4232.1	3861.7	3491.4	3002.9	2514.7	2250.6	1986.5	1914.3	1907.3
37.5°	4720.7	4578.0	4435.3	3972.4	3509.6	2961.5	2413.5	2163.1	1912.7	1849.6	1824.1
40°	5120.8	4912.8	4704.9	4113.0	3521.0	2904.5	2288.1	2058.7	1829.2	1772.0	1733.0
42.5°	5651.4	5351.2	5051.0	4296.9	3542.7	2845.7	2148.9	1943.5	1738.1	1685.4	1636.1
45°	6306.6	5901.7	5496.8	4538.9	3580.9	2791.0	2001.2	1821.1	1641.0	1587.5	1539.9
47.5°	7126.0	6556.2	5986.2	4796.7	3607.1	2745.9	1884.6	1724.3	1563.9	1494.9	1454.0
50°	8200.0	7340.9	6481.7	5035.9	3590.0	2696.7	1803.3	1660.0	1516.7	1425.9	1378.3
52.5°	9432.9	8165.2	6897.6	5191.2	3484.6	2613.6	1742.6	1617.6	1492.8	1388.5	1322.0
55°	10745.4	8896.1	7046.8	5156.9	3267.0	2475.8	1684.6	1586.9	1489.3	1392.3	1292.0
57.5°	11939.2	9414.0	6888.8	4916.0	2943.4	2281.5	1619.6	1550.6	1481.6	1396.0	1274.0
60°	12660.8	9543.5	6426.1	4467.7	2509.4	2029.3	1549.2	1494.9	1440.7	1384.2	1257.1
62.5°	12294.4	8998.4	5702.5	3861.5	2020.5	1727.4	1434.3	1398.2	1362.3	1355.3	1237.5
65°	*11561.1*	*8227.3*	*4893.5*	*3243.0*	*1592.6*	*1455.8*	*1319.0*	*1302.0*	*1285.0*	*1285.8*	*1196.0*
67.5°	10578.5	7309.6	4040.6	2637.1	1233.6	1194.8	1155.8	1165.4	1174.8	1172.4	1121.9
70°	9398.1	6308.2	3218.3	2076.3	934.4	945.5	956.6	1000.6	1044.6	1044.6	1028.0
72.5°	7991.4	5222.6	2454.0	1587.4	720.8	754.3	787.9	850.3	912.7	923.2	923.4
75°	6211.9	3978.2	1744.5	1152.1	559.7	590.1	620.4	690.4	760.4	808.7	804.6
77.5°	4438.3	2784.4	1130.5	780.7	430.9	451.5	472.3	540.2	608.1	687.8	685.7
80°	2904.8	1793.9	683.0	503.0	323.1	331.6	340.2	397.7	455.2	550.4	550.1
82.5°	1688.6	1038.3	388.1	309.4	230.8	232.3	234.1	276.4	318.8	400.1	404.6
85°	742.9	467.0	191.3	165.4	139.6	138.9	138.0	169.0	200.0	260.5	266.4
87.5°	230.0	153.0	76.0	68.6	61.2	60.4	59.7	72.3	85.0	110.2	117.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7
2.5°	2738.1	2717.6	2699.1	2680.7	2664.6	2648.4	2632.2	2616.0	2603.5	2590.9	2580.7
5°	2695.5	2656.7	2624.2	2591.7	2563.1	2534.4	2508.4	2482.3	2462.3	2442.2	2428.2
7.5°	2673.9	2622.4	2579.6	2536.9	2500.8	2464.7	2432.8	2401.0	2377.2	2353.4	2336.7
10°	2675.4	2621.0	2578.3	2535.5	2496.6	2457.7	2421.9	2386.0	2357.6	2329.0	2310.4
12.5°	2690.6	2646.3	2617.8	2589.6	2559.0	2528.6	2491.5	2454.5	2418.1	2381.8	2357.7
15°	2691.0	2669.8	2673.7	2677.5	2669.6	2661.7	2629.5	2597.3	2545.5	2493.8	2457.2
17.5°	2650.6	2658.3	2704.9	2751.6	2776.4	2801.1	2775.1	2749.2	2680.6	2612.1	2558.1
20°	2565.7	2602.1	2683.1	2764.2	2816.1	2867.9	2856.0	2843.9	2765.5	2687.2	2621.0
22.5°	2454.5	2508.3	2600.7	2693.4	2760.9	2828.4	2835.6	2842.8	2767.9	2693.0	2625.0
25°	2337.9	2399.9	2483.1	2566.3	2632.7	2699.1	2724.0	2748.7	2687.3	2626.0	2565.4
27.5°	2226.6	2286.5	2354.9	2423.1	2476.4	2529.7	2557.3	2585.0	2541.2	2497.6	2450.6
30°	2118.3	2166.0	2222.7	2279.4	2323.6	2367.8	2390.3	2412.8	2379.5	2346.1	2312.5
32.5°	2014.8	2043.0	2088.2	2133.6	2175.9	2218.4	2243.3	2268.4	2237.8	2207.1	2180.2
35°	1915.0	1922.8	1957.4	1991.8	2033.8	2075.8	2105.8	2135.7	2113.9	2092.2	2067.4
37.5°	1815.5	1807.0	1831.8	1856.5	1898.3	1940.3	1977.3	2014.3	2004.2	1994.2	1971.4
40°	1713.6	1694.2	1712.1	1730.0	1770.4	1810.8	1853.4	1896.1	1898.6	1900.9	1881.5
42.5°	1610.5	1584.8	1599.4	1614.0	1652.3	1690.7	1736.7	1782.7	1795.0	1807.3	1790.9
45°	1514.8	1489.9	1502.1	1514.5	1550.9	1587.3	1635.0	1682.7	1700.3	1718.0	1703.2
47.5°	1433.0	1412.0	1423.6	1435.0	1470.7	1506.2	1553.2	1600.3	1620.6	1641.0	1630.7
50°	1359.7	1341.2	1359.2	1377.3	1410.9	1444.3	1486.5	1528.6	1554.7	1580.8	1580.2
52.5°	1303.6	1285.3	1312.3	1339.3	1370.1	1400.8	1440.1	1479.4	1510.3	1541.3	1546.8
55°	1262.9	1233.9	1272.3	1310.6	1343.8	1377.0	1411.4	1445.7	1478.5	1511.3	1519.0
57.5°	1231.7	1189.3	1230.6	1271.9	1310.8	1349.8	1383.8	1417.9	1451.0	1483.9	1491.7
60°	1202.3	1147.3	1183.5	1219.7	1264.4	1309.1	1343.7	1378.3	1411.5	1444.7	1453.2
62.5°	1168.8	1100.2	1123.2	1146.2	1198.3	1250.5	1287.4	1324.3	1354.7	1385.1	1393.3
65°	*1123.0*	*1049.9*	*1058.8*	*1067.6*	*1123.4*	*1179.4*	*1214.7*	*1250.0*	*1276.7*	*1303.5*	*1311.9*
67.5°	1061.2	1000.4	997.6	994.8	1046.4	1098.1	1131.6	1164.9	1188.0	1211.1	1219.4
70°	984.8	941.6	931.9	922.3	967.7	1013.0	1041.9	1070.8	1091.7	1112.5	1120.4
72.5°	893.8	864.1	850.0	836.0	871.7	907.3	933.4	959.5	980.0	1000.4	1009.8
75°	781.9	759.0	745.5	731.9	758.4	785.0	808.6	832.2	850.9	869.5	879.3
77.5°	667.4	649.1	635.4	621.7	643.3	664.8	685.2	705.5	725.1	744.5	753.7
80°	534.8	519.4	507.9	496.4	514.3	532.2	549.3	566.4	581.3	596.1	608.2
82.5°	397.1	389.6	381.5	373.3	371.8	370.3	364.3	358.4	390.0	421.7	442.4
85°	258.3	250.3	241.2	232.1	224.4	216.6	200.0	183.5	213.1	242.8	268.5
87.5°	114.5	111.3	109.5	107.8	107.5	107.2	94.6	81.8	94.2	106.8	117.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7
2.5°	2570.6	2562.6	2554.7	2547.5	2540.1	2531.0	2540.1	2547.5	2554.7	2562.6	2570.6
5°	2414.2	2404.2	2394.3	2386.7	2379.1	2371.6	2379.1	2386.7	2394.3	2404.2	2414.2
7.5°	2320.0	2308.6	2297.2	2290.4	2283.7	2278.5	2283.7	2290.4	2297.2	2308.6	2320.0
10°	2291.6	2280.8	2270.0	2264.2	2258.4	2256.1	2258.4	2264.2	2270.0	2280.8	2291.6
12.5°	2333.6	2321.5	2309.5	2304.6	2299.7	2298.8	2299.7	2304.6	2309.5	2321.5	2333.6
15°	2420.6	2403.8	2387.1	2380.7	2374.3	2373.7	2374.3	2380.7	2387.1	2403.8	2420.6
17.5°	2504.2	2479.4	2454.5	2446.4	2438.1	2436.8	2438.1	2446.4	2454.5	2479.4	2504.2
20°	2555.0	2523.3	2491.4	2481.2	2471.1	2467.9	2471.1	2481.2	2491.4	2523.3	2555.0
22.5°	2556.9	2523.4	2489.8	2478.6	2467.3	2462.5	2467.3	2478.6	2489.8	2523.4	2556.9
25°	2505.1	2476.0	2447.0	2436.4	2425.9	2419.7	2425.9	2436.4	2447.0	2476.0	2505.1
27.5°	2403.7	2384.2	2364.6	2359.8	2355.0	2353.4	2355.0	2359.8	2364.6	2384.2	2403.7
30°	2278.7	2268.8	2258.7	2258.7	2258.7	2260.3	2258.7	2258.7	2258.7	2268.8	2278.7
32.5°	2153.4	2146.8	2140.3	2141.2	2142.1	2143.7	2142.1	2141.2	2140.3	2146.8	2153.4
35°	2042.6	2032.7	2022.9	2020.7	2018.6	2017.5	2018.6	2020.7	2022.9	2032.7	2042.6
37.5°	1948.5	1930.4	1912.5	1902.9	1893.4	1888.1	1893.4	1902.9	1912.5	1930.4	1948.5
40°	1862.2	1835.9	1809.8	1792.0	1774.5	1764.0	1774.5	1792.0	1809.8	1835.9	1862.2
42.5°	1774.7	1742.1	1709.4	1683.6	1657.9	1641.0	1657.9	1683.6	1709.4	1742.1	1774.7
45°	1688.6	1651.2	1614.0	1583.7	1553.5	1534.0	1553.5	1583.7	1614.0	1651.2	1688.6
47.5°	1620.4	1587.3	1554.1	1526.1	1498.2	1479.4	1498.2	1526.1	1554.1	1587.3	1620.4
50°	1579.8	1553.2	1526.7	1500.8	1474.9	1457.0	1474.9	1500.8	1526.7	1553.2	1579.8
52.5°	1552.4	1530.8	1509.2	1486.0	1462.9	1446.3	1462.9	1486.0	1509.2	1530.8	1552.4
55°	1526.7	1507.9	1489.1	1468.7	1448.4	1433.4	1448.4	1468.7	1489.1	1507.9	1526.7
57.5°	1499.5	1480.5	1461.5	1441.4	1421.1	1405.6	1421.1	1441.4	1461.5	1480.5	1499.5
60°	1461.8	1443.2	1424.7	1403.9	1383.2	1367.1	1383.2	1403.9	1424.7	1443.2	1461.8
62.5°	1401.6	1384.8	1368.0	1346.1	1324.3	1305.1	1324.3	1346.1	1368.0	1384.8	1401.6
65°	*1320.3*	*1304.1*	*1288.0*	*1266.8*	*1245.7*	*1229.1*	*1245.7*	*1266.8*	*1288.0*	*1304.1*	*1320.3*
67.5°	1227.5	1212.6	1197.9	1178.2	1158.5	1143.5	1158.5	1178.2	1197.9	1212.6	1227.5
70°	1128.3	1116.3	1104.2	1085.3	1066.5	1049.4	1066.5	1085.3	1104.2	1116.3	1128.3
72.5°	1019.2	1009.2	999.1	981.2	963.3	946.7	963.3	981.2	999.1	1009.2	1019.2
75°	889.2	884.2	879.3	864.2	849.2	833.3	849.2	864.2	879.3	884.2	889.2
77.5°	762.9	756.1	749.0	733.8	718.6	706.0	718.6	733.8	749.0	756.1	762.9
80°	620.4	617.4	614.6	594.1	573.6	549.8	573.6	594.1	614.6	617.4	620.4
82.5°	463.2	461.9	460.5	443.3	426.0	410.8	426.0	443.3	460.5	461.9	463.2
85°	294.2	292.0	289.9	276.4	262.9	249.2	262.9	276.4	289.9	292.0	294.2
87.5°	127.5	124.9	122.2	115.3	108.3	101.6	108.3	115.3	122.2	124.9	127.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7
2.5°	2580.7	2590.9	2603.5	2616.0	2632.2	2648.4	2664.6	2680.7	2699.1	2717.6	2738.1
5°	2428.2	2442.2	2462.3	2482.3	2508.4	2534.4	2563.1	2591.7	2624.2	2656.7	2695.5
7.5°	2336.7	2353.4	2377.2	2401.0	2432.8	2464.7	2500.8	2536.9	2579.6	2622.4	2673.9
10°	2310.4	2329.0	2357.6	2386.0	2421.9	2457.7	2496.6	2535.5	2578.3	2621.0	2675.4
12.5°	2357.7	2381.8	2418.1	2454.5	2491.5	2528.6	2559.0	2589.6	2617.8	2646.3	2690.6
15°	2457.2	2493.8	2545.5	2597.3	2629.5	2661.7	2669.6	2677.5	2673.7	2669.8	2691.0
17.5°	2558.1	2612.1	2680.6	2749.2	2775.1	2801.1	2776.4	2751.6	2704.9	2658.3	2650.6
20°	2621.0	2687.2	2765.5	2843.9	2856.0	2867.9	2816.1	2764.2	2683.1	2602.1	2565.7
22.5°	2625.0	2693.0	2767.9	2842.8	2835.6	2828.4	2760.9	2693.4	2600.7	2508.3	2454.5
25°	2565.4	2626.0	2687.3	2748.7	2724.0	2699.1	2632.7	2566.3	2483.1	2399.9	2337.9
27.5°	2450.6	2497.6	2541.2	2585.0	2557.3	2529.7	2476.4	2423.1	2354.9	2286.5	2226.6
30°	2312.5	2346.1	2379.5	2412.8	2390.3	2367.8	2323.6	2279.4	2222.7	2166.0	2118.3
32.5°	2180.2	2207.1	2237.8	2268.4	2243.3	2218.4	2175.9	2133.6	2088.2	2043.0	2014.8
35°	2067.4	2092.2	2113.9	2135.7	2105.8	2075.8	2033.8	1991.8	1957.4	1922.8	1915.0
37.5°	1971.4	1994.2	2004.2	2014.3	1977.3	1940.3	1898.3	1856.5	1831.8	1807.0	1815.5
40°	1881.5	1900.9	1898.6	1896.1	1853.4	1810.8	1770.4	1730.0	1712.1	1694.2	1713.6
42.5°	1790.9	1807.3	1795.0	1782.7	1736.7	1690.7	1652.3	1614.0	1599.4	1584.8	1610.5
45°	1703.2	1718.0	1700.3	1682.7	1635.0	1587.3	1550.9	1514.5	1502.1	1489.9	1514.8
47.5°	1630.7	1641.0	1620.6	1600.3	1553.2	1506.2	1470.7	1435.0	1423.6	1412.0	1433.0
50°	1580.2	1580.8	1554.7	1528.6	1486.5	1444.3	1410.9	1377.3	1359.2	1341.2	1359.7
52.5°	1546.8	1541.3	1510.3	1479.4	1440.1	1400.8	1370.1	1339.3	1312.3	1285.3	1303.6
55°	1519.0	1511.3	1478.5	1445.7	1411.4	1377.0	1343.8	1310.6	1272.3	1233.9	1262.9
57.5°	1491.7	1483.9	1451.0	1417.9	1383.8	1349.8	1310.8	1271.9	1230.6	1189.3	1231.7
60°	1453.2	1444.7	1411.5	1378.3	1343.7	1309.1	1264.4	1219.7	1183.5	1147.3	1202.3
62.5°	1393.3	1385.1	1354.7	1324.3	1287.4	1250.5	1198.3	1146.2	1123.2	1100.2	1168.8
65°	*1311.9*	*1303.5*	*1276.7*	*1250.0*	*1214.7*	*1179.4*	*1123.4*	*1067.6*	*1058.8*	*1049.9*	*1123.0*
67.5°	1219.4	1211.1	1188.0	1164.9	1131.6	1098.1	1046.4	994.8	997.6	1000.4	1061.2
70°	1120.4	1112.5	1091.7	1070.8	1041.9	1013.0	967.7	922.3	931.9	941.6	984.8
72.5°	1009.8	1000.4	980.0	959.5	933.4	907.3	871.7	836.0	850.0	864.1	893.8
75°	879.3	869.5	850.9	832.2	808.6	785.0	758.4	731.9	745.5	759.0	781.9
77.5°	753.7	744.5	725.1	705.5	685.2	664.8	643.3	621.7	635.4	649.1	667.4
80°	608.2	596.1	581.3	566.4	549.3	532.2	514.3	496.4	507.9	519.4	534.8
82.5°	442.4	421.7	390.0	358.4	364.3	370.3	371.8	373.3	381.5	389.6	397.1
85°	268.5	242.8	213.1	183.5	200.0	216.6	224.4	232.1	241.2	250.3	258.3
87.5°	117.1	106.8	94.2	81.8	94.6	107.2	107.5	107.8	109.5	111.3	114.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7
2.5°	2758.6	2784.0	2806.8	2830.3	2853.8	2878.4	2903.0	2927.4	2951.9	2974.9	2997.9
5°	2734.2	2778.6	2823.5	2871.2	2918.8	2969.7	3020.7	3071.3	3122.0	3172.8	3223.6
7.5°	2725.5	2782.9	2844.2	2910.6	2977.1	3052.5	3127.9	3205.3	3282.8	3366.5	3450.4
10°	2729.7	2791.5	2867.1	2945.8	3024.3	3116.0	3207.6	3309.8	3412.2	3518.2	3624.2
12.5°	2735.1	2792.5	2872.0	2960.9	3049.8	3157.8	3265.9	3381.8	3497.8	3614.2	3730.7
15°	2712.3	2758.3	2846.3	2949.2	3052.1	3176.6	3301.0	3426.8	3552.6	3674.0	3795.4
17.5°	2642.8	2671.1	2774.7	2898.4	3022.2	3166.6	3311.0	3448.3	3585.5	3708.6	3831.8
20°	2529.4	2536.9	2657.4	2810.8	2964.2	3139.2	3314.2	3465.1	3615.9	3743.9	3871.9
22.5°	2400.7	2386.0	2523.3	2708.0	2892.8	3105.6	3318.5	3487.7	3656.9	3787.7	3918.4
25°	2275.8	2236.3	2376.9	2593.2	2809.6	3072.5	3335.4	3528.8	3722.1	3850.2	3978.3
27.5°	2166.7	2118.6	2246.6	2488.3	2729.9	3050.3	3370.7	3593.0	3815.2	3937.5	4059.6
30°	2070.8	2033.0	2140.5	2400.6	2660.6	3040.0	3419.1	3676.1	3933.2	4051.2	4169.3
32.5°	1986.7	1969.9	2056.6	2324.9	2593.2	3027.1	3460.8	3762.9	4065.0	4181.8	4298.7
35°	1907.3	1914.3	1986.5	2250.6	2514.7	3002.9	3491.4	3861.7	4232.1	4344.1	4456.0
37.5°	1824.1	1849.6	1912.7	2163.1	2413.5	2961.5	3509.6	3972.4	4435.3	4578.0	4720.7
40°	1733.0	1772.0	1829.2	2058.7	2288.1	2904.5	3521.0	4113.0	4704.9	4912.8	5120.8
42.5°	1636.1	1685.4	1738.1	1943.5	2148.9	2845.7	3542.7	4296.9	5051.0	5351.2	5651.4
45°	1539.9	1587.5	1641.0	1821.1	2001.2	2791.0	3580.9	4538.9	5496.8	5901.7	6306.6
47.5°	1454.0	1494.9	1563.9	1724.3	1884.6	2745.9	3607.1	4796.7	5986.2	6556.2	7126.0
50°	1378.3	1425.9	1516.7	1660.0	1803.3	2696.7	3590.0	5035.9	6481.7	7340.9	8200.0
52.5°	1322.0	1388.5	1492.8	1617.6	1742.6	2613.6	3484.6	5191.2	6897.6	8165.2	9432.9
55°	1292.0	1392.3	1489.3	1586.9	1684.6	2475.8	3267.0	5156.9	7046.8	8896.1	10745.4
57.5°	1274.0	1396.0	1481.6	1550.6	1619.6	2281.5	2943.4	4916.0	6888.8	9414.0	11939.2
60°	1257.1	1384.2	1440.7	1494.9	1549.2	2029.3	2509.4	4467.7	6426.1	9543.5	12660.8
62.5°	1237.5	1355.3	1362.3	1398.2	1434.3	1727.4	2020.5	3861.5	5702.5	8998.4	12294.4
65°	*1196.0*	*1285.8*	*1285.0*	*1302.0*	*1319.0*	*1455.8*	*1592.6*	*3243.0*	*4893.5*	*8227.3*	*11561.1*
67.5°	1121.9	1172.4	1174.8	1165.4	1155.8	1194.8	1233.6	2637.1	4040.6	7309.6	10578.5
70°	1028.0	1044.6	1044.6	1000.6	956.6	945.5	934.4	2076.3	3218.3	6308.2	9398.1
72.5°	923.4	923.2	912.7	850.3	787.9	754.3	720.8	1587.4	2454.0	5222.6	7991.4
75°	804.6	808.7	760.4	690.4	620.4	590.1	559.7	1152.1	1744.5	3978.2	6211.9
77.5°	685.7	687.8	608.1	540.2	472.3	451.5	430.9	780.7	1130.5	2784.4	4438.3
80°	550.1	550.4	455.2	397.7	340.2	331.6	323.1	503.0	683.0	1793.9	2904.8
82.5°	404.6	400.1	318.8	276.4	234.1	232.3	230.8	309.4	388.1	1038.3	1688.6
85°	266.4	260.5	200.0	169.0	138.0	138.9	139.6	165.4	191.3	467.0	742.9
87.5°	117.7	110.2	85.0	72.3	59.7	60.4	61.2	68.6	76.0	153.0	230.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	*2787.7*	2787.7	2787.7
2.5°	3009.3	3020.7	3036.9	3053.0	3062.6	3072.3	3077.1	3081.9	*3079.7*	3081.9	3077.1
5°	3263.3	3303.1	3342.5	3381.9	3403.3	3424.7	3437.7	3450.7	*3460.6*	3450.7	3437.7
7.5°	3515.0	3579.5	3637.6	3695.7	3730.7	3765.7	3784.6	3803.4	*3812.5*	3803.4	3784.6
10°	3700.6	3777.0	3845.1	3913.3	3954.6	3995.6	4014.0	4032.3	*4039.3*	4032.3	4014.0
12.5°	3813.5	3896.2	3957.8	4019.2	4049.1	4079.1	4089.1	4099.2	*4100.3*	4099.2	4089.1
15°	3866.9	3938.2	3976.8	4015.5	4016.6	4017.7	4007.0	3996.3	*3983.7*	3996.3	4007.0
17.5°	3880.0	3928.3	3929.0	3929.6	3886.3	3843.0	3803.3	3763.5	*3735.5*	3763.5	3803.3
20°	3888.7	3905.6	3854.8	3804.0	3708.3	3612.7	3543.0	3473.4	*3430.6*	3473.4	3543.0
22.5°	3896.4	3874.3	3769.1	3663.8	3523.2	3382.5	3295.4	3208.3	*3161.0*	3208.3	3295.4
25°	3908.8	3839.3	3679.4	3519.6	3348.8	3177.9	3086.4	2995.0	*2950.3*	2995.0	3086.4
27.5°	3935.3	3810.9	3599.2	3387.6	3198.3	3008.9	2918.9	2828.9	*2786.6*	2828.9	2918.9
30°	3983.9	3798.6	3538.0	3277.4	3080.2	2882.9	2799.4	2715.8	*2676.5*	2715.8	2799.4
32.5°	4044.9	3791.1	3496.3	3201.5	3016.1	2830.7	2765.1	2699.5	*2671.1*	2699.5	2765.1
35°	4145.3	3834.8	3527.5	3220.4	3091.6	2962.9	2947.6	2932.3	*2930.0*	2932.3	2947.6
37.5°	4355.3	3989.9	3710.7	3431.5	3423.1	3414.8	3484.7	3554.7	*3591.1*	3554.7	3484.7
40°	4723.4	4326.0	4118.3	3910.7	4057.3	4203.8	4373.9	4544.0	*4628.7*	4544.0	4373.9
42.5°	5257.1	4862.8	4743.2	4623.6	4943.2	5262.8	5572.2	5881.6	*6063.2*	5881.6	5572.2
45°	5952.4	5598.1	5545.4	5492.5	6004.6	6516.8	7025.1	7533.6	*7842.2*	7533.6	7025.1
47.5°	6781.4	6436.8	6426.1	6415.4	7154.1	7892.7	8636.9	9381.0	*9818.0*	9381.0	8636.9
50°	7774.4	7348.8	7350.6	7352.5	8304.5	9256.6	10238.9	11221.2	*11815.1*	11221.2	10238.9
52.5°	8917.5	8402.2	8350.1	8297.9	9435.1	10572.3	11787.8	13003.1	*13715.0*	13003.1	11787.8
55°	10236.2	9727.0	9523.9	9320.8	10586.5	11852.1	13301.0	14749.9	*15596.6*	14749.9	13301.0
57.5°	11662.0	11384.6	10977.1	10569.8	11847.8	13125.8	14767.0	16408.0	*17458.0*	16408.0	14767.0
60°	13091.4	13522.2	13016.2	12510.3	13719.7	14929.1	16686.3	18443.4	*19578.2*	18443.4	16686.3
62.5°	13471.2	14648.0	14591.0	14533.9	15641.8	16749.8	18421.6	20093.2	*21142.1*	20093.2	18421.6
65°	*12665.6*	*13770.1*	*13988.6*	*14207.1*	*15615.0*	*17023.1*	*18644.2*	*20265.1*	*21158.2*	*20265.1*	*18644.2*
67.5°	11629.0	12679.5	12782.0	12884.3	14351.4	15818.3	17446.3	19074.3	*19773.9*	19074.3	17446.3
70°	10540.7	11683.4	11729.1	11775.0	13086.9	14398.8	15799.8	17200.7	*17589.5*	17200.7	15799.8
72.5°	9302.6	10613.8	10646.8	10679.6	11706.0	12732.4	13781.7	14830.9	*14870.3*	14830.9	13781.7
75°	7569.0	8926.0	9047.9	9169.7	9968.3	10766.8	11505.5	12244.1	*12046.2*	12244.1	11505.5
77.5°	5705.1	6972.0	7146.3	7320.7	7927.8	8534.8	9058.7	9582.6	*9242.5*	9582.6	9058.7
80°	3970.6	5036.3	5253.0	5469.7	5928.2	6386.5	6661.6	6936.7	*6389.5*	6936.7	6661.6
82.5°	2417.2	3145.9	3387.9	3630.1	3945.7	4261.3	4376.0	4490.7	*4060.7*	4490.7	4376.0
85°	1129.6	1516.3	1722.3	1928.2	2187.5	2446.7	2511.8	2577.0	*2232.5*	2577.0	2511.8
87.5°	360.0	489.9	604.8	719.7	849.4	979.0	984.6	990.0	*831.2*	990.0	984.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1203755
CATALOG NUMBER: GWC-SB2D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7	2787.7
2.5°	3072.3	3062.6	3053.0	3036.9	3020.7	3009.3	2997.9
5°	3424.7	3403.3	3381.9	3342.5	3303.1	3263.3	3223.6
7.5°	3765.7	3730.7	3695.7	3637.6	3579.5	3515.0	3450.4
10°	3995.6	3954.6	3913.3	3845.1	3777.0	3700.6	3624.2
12.5°	4079.1	4049.1	4019.2	3957.8	3896.2	3813.5	3730.7
15°	4017.7	4016.6	4015.5	3976.8	3938.2	3866.9	3795.4
17.5°	3843.0	3886.3	3929.6	3929.0	3928.3	3880.0	3831.8
20°	3612.7	3708.3	3804.0	3854.8	3905.6	3888.7	3871.9
22.5°	3382.5	3523.2	3663.8	3769.1	3874.3	3896.4	3918.4
25°	3177.9	3348.8	3519.6	3679.4	3839.3	3908.8	3978.3
27.5°	3008.9	3198.3	3387.6	3599.2	3810.9	3935.3	4059.6
30°	2882.9	3080.2	3277.4	3538.0	3798.6	3983.9	4169.3
32.5°	2830.7	3016.1	3201.5	3496.3	3791.1	4044.9	4298.7
35°	2962.9	3091.6	3220.4	3527.5	3834.8	4145.3	4456.0
37.5°	3414.8	3423.1	3431.5	3710.7	3989.9	4355.3	4720.7
40°	4203.8	4057.3	3910.7	4118.3	4326.0	4723.4	5120.8
42.5°	5262.8	4943.2	4623.6	4743.2	4862.8	5257.1	5651.4
45°	6516.8	6004.6	5492.5	5545.4	5598.1	5952.4	6306.6
47.5°	7892.7	7154.1	6415.4	6426.1	6436.8	6781.4	7126.0
50°	9256.6	8304.5	7352.5	7350.6	7348.8	7774.4	8200.0
52.5°	10572.3	9435.1	8297.9	8350.1	8402.2	8917.5	9432.9
55°	11852.1	10586.5	9320.8	9523.9	9727.0	10236.2	10745.4
57.5°	13125.8	11847.8	10569.8	10977.1	11384.6	11662.0	11939.2
60°	14929.1	13719.7	12510.3	13016.2	13522.2	13091.4	12660.8
62.5°	16749.8	15641.8	14533.9	14591.0	14648.0	13471.2	12294.4
65°	*17023.1*	*15615.0*	*14207.1*	*13988.6*	*13770.1*	*12665.6*	*11561.1*
67.5°	15818.3	14351.4	12884.3	12782.0	12679.5	11629.0	10578.5
70°	14398.8	13086.9	11775.0	11729.1	11683.4	10540.7	9398.1
72.5°	12732.4	11706.0	10679.6	10646.8	10613.8	9302.6	7991.4
75°	10766.8	9968.3	9169.7	9047.9	8926.0	7569.0	6211.9
77.5°	8534.8	7927.8	7320.7	7146.3	6972.0	5705.1	4438.3
80°	6386.5	5928.2	5469.7	5253.0	5036.3	3970.6	2904.8
82.5°	4261.3	3945.7	3630.1	3387.9	3145.9	2417.2	1688.6
85°	2446.7	2187.5	1928.2	1722.3	1516.3	1129.6	742.9
87.5°	979.0	849.4	719.7	604.8	489.9	360.0	230.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0


HS
SS

0

(END OF REPORT)