

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P972418

Luminaire Tested: **GKO-PB2D-730-U-T1**

Issue Date: 02/27/2025

Test Information

Test Method: LM-79-08
Report Number: P972418
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/27/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2D-730-U-T1
Description: GEKKO WALL PACK 10000LM PACKAGE 70CRI 3000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10260.1 lumens
Efficiency: N/A
Efficacy: 134.6 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B3 - U0 - G3

Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 8%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT


REPORT NUMBER: P972418

CATALOG NUMBER: GKO-PB2D-730-U-T1

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 25.5 fc
 Type I - Short - N/A

REPORT NUMBER: P972418

CATALOG NUMBER: GKO-PB2D-730-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P972418

CATALOG NUMBER: GKO-PB2D-730-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5130.0	0.0	5130.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5130.0	0.0	5130.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	10260.1	0.0	10260.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.2	2.4
10°-20°	735.8	7.2
20°-30°	1223.5	11.9
30°-40°	1625.3	15.8
40°-50°	1832.4	17.9
50°-60°	1884.2	18.4
60°-70°	1780.6	17.4
70°-80°	871.7	8.5
80°-90°	62.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10260.1	100.0
0°-180°	10260.1	100.0



REPORT NUMBER: P972418


CATALOG NUMBER: GKO-PB2D-730-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1101.7	10.7			
FM	(30°-60°)	2671.0	26.0			
FH	(60°-80°)	1326.2	12.9			G1/1800
FVH	(80°-90°)	31.2	0.3			G1/100
BL	(0°-30°)	1101.7	10.7	B3/2500		
BM	(30°-60°)	2671.0	26.0	B3/5000		
BH	(60°-80°)	1326.2	12.9	B3/2500		G3/2500
BVH	(80°-90°)	31.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type I Short



REPORT NUMBER: P972418

CATALOG NUMBER: GKO-PB2D-730-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2545.9	2545.9	2545.9	2545.9	2545.9	2545.9	2545.9	2545.9	2545.9	2545.9	2545.9
2.5°	2547.8	2551.6	2544.1	2544.1	2547.8	2549.7	2549.7	2551.6	2547.8	2547.8	2545.9
5°	2547.8	2549.7	2545.9	2545.9	2549.7	2555.4	2553.5	2557.3	2557.3	2555.4	2555.4
7.5°	2545.9	2549.7	2545.9	2547.8	2553.5	2564.9	2564.9	2564.9	2568.6	2572.4	2572.4
10°	2544.1	2547.8	2549.7	2551.6	2559.2	2576.2	2580.0	2581.9	2587.6	2593.2	2593.2
12.5°	2534.6	2538.4	2544.1	2551.6	2564.9	2587.6	2595.1	2600.8	2610.3	2615.9	2619.7
15°	2521.4	2523.2	2536.5	2551.6	2572.4	2600.8	2615.9	2625.4	2638.6	2646.2	2651.9
17.5°	2502.4	2504.3	2525.1	2547.8	2578.1	2617.8	2642.4	2657.5	2670.8	2682.1	2689.7
20°	2477.9	2483.5	2508.1	2544.1	2587.6	2634.8	2670.8	2697.3	2710.5	2721.9	2733.2
22.5°	2447.6	2453.3	2483.5	2534.6	2597.0	2657.5	2704.8	2738.9	2755.9	2771.0	2784.3
25°	2402.2	2409.8	2445.7	2511.9	2600.8	2682.1	2742.7	2786.2	2801.3	2820.2	2831.6
27.5°	2332.2	2337.9	2381.4	2466.5	2589.4	2708.6	2786.2	2837.2	2854.3	2875.1	2886.4
30°	2222.5	2233.8	2286.8	2392.7	2561.1	2729.4	2837.2	2888.3	2909.1	2929.9	2945.0
32.5°	2080.6	2097.7	2156.3	2292.5	2506.2	2737.0	2892.1	2950.7	2977.2	2999.9	3018.8
35°	1904.7	1921.8	1991.7	2163.9	2419.2	2721.9	2946.9	3022.6	3054.8	3085.0	3107.7
37.5°	1704.2	1719.4	1804.5	2001.2	2294.4	2674.6	2990.4	3102.0	3145.5	3185.3	3215.5
40°	1501.8	1518.9	1611.5	1821.5	2143.1	2583.8	3009.4	3189.1	3243.9	3295.0	3332.8
42.5°	1282.4	1303.2	1407.3	1630.5	1967.1	2458.9	2994.2	3274.2	3342.3	3412.2	3469.0
45°	1087.6	1091.4	1204.9	1420.5	1774.2	2298.2	2941.3	3355.5	3448.2	3546.5	3627.9
47.5°	900.3	907.9	1006.3	1220.0	1573.7	2116.6	2844.8	3419.8	3567.4	3694.1	3813.2
50°	733.9	743.4	832.3	1023.3	1373.2	1918.0	2714.3	3457.6	3669.5	3841.6	4008.1
52.5°	597.7	609.1	682.8	851.2	1170.8	1709.9	2553.5	3463.3	3762.2	3989.2	4210.5
55°	497.5	505.0	561.8	696.1	976.0	1494.3	2370.0	3434.9	3822.7	4121.6	4416.6
57.5°	419.9	427.5	467.2	573.1	800.1	1273.0	2146.8	3368.7	3854.9	4236.9	4624.7
60°	365.1	370.7	399.1	474.8	658.2	1064.9	1906.6	3251.5	3845.4	4308.8	4796.8
62.5°	325.3	327.2	351.8	404.8	542.9	868.2	1636.1	3075.6	3767.8	4318.3	4914.1
65°	289.4	291.3	306.4	344.3	446.4	698.0	1354.3	2833.5	3620.3	4252.1	4931.1
67.5°	234.5	238.3	261.0	289.4	366.9	552.3	1066.8	2515.7	3389.6	4079.9	4834.6
70°	187.3	189.1	211.8	244.0	298.9	435.0	819.0	2088.2	3028.3	3800.0	4585.0
72.5°	140.0	143.8	164.6	196.7	244.0	336.7	592.0	1579.4	2421.1	3204.2	3992.9
75°	111.6	113.5	121.1	151.3	189.1	255.4	399.1	957.1	1458.3	1982.3	2447.6
77.5°	94.6	96.5	96.5	117.3	140.0	172.1	211.8	380.2	616.6	877.7	1163.3
80°	77.6	81.3	73.8	87.0	100.2	100.2	98.4	181.6	291.3	412.3	541.0
82.5°	56.7	60.5	56.7	60.5	60.5	54.9	51.1	68.1	92.7	126.7	138.1
85°	39.7	41.6	45.4	41.6	39.7	32.2	24.6	18.9	11.3	13.2	18.9
87.5°	26.5	32.2	37.8	35.9	30.3	24.6	17.0	11.3	5.7	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P972418

CATALOG NUMBER: GKO-PB2D-730-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2545.9	2545.9	2545.9
2.5°	2547.8	2545.9	2544.1
5°	2557.3	2555.4	2553.5
7.5°	2570.5	2570.5	2570.5
10°	2591.3	2595.1	2595.1
12.5°	2617.8	2621.6	2621.6
15°	2650.0	2651.9	2655.7
17.5°	2689.7	2691.6	2691.6
20°	2737.0	2735.1	2738.9
22.5°	2784.3	2784.3	2784.3
25°	2833.5	2833.5	2833.5
27.5°	2890.2	2890.2	2886.4
30°	2952.6	2952.6	2952.6
32.5°	3028.3	3030.2	3032.1
35°	3124.7	3128.5	3134.2
37.5°	3234.4	3243.9	3249.6
40°	3365.0	3368.7	3378.2
42.5°	3510.6	3522.0	3523.8
45°	3692.2	3711.1	3718.7
47.5°	3905.9	3932.4	3945.6
50°	4144.3	4174.5	4193.4
52.5°	4403.4	4452.6	4475.3
55°	4679.5	4764.7	4789.3
57.5°	4991.6	5107.0	5141.1
60°	5298.1	5460.7	5515.6
62.5°	5559.1	5788.0	5856.1
65°	5742.6	6018.7	6119.0
67.5°	5780.4	6107.6	6226.8
70°	5553.4	5888.2	6026.3
72.5°	4829.0	5131.6	5303.7
75°	2852.4	3069.9	3016.9
77.5°	1431.9	1494.3	1503.7
80°	628.0	665.8	680.9
82.5°	155.1	158.9	179.7
85°	20.8	24.6	22.7
87.5°	7.6	7.6	9.5
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-4

Test Date: 04/10/2025

Luminaire Tested: GKO-PB1E-730-U-T4W

Data in this report applies to families of products including GKO-PB1E-730-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-730-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3072
 CIE u' : 0.2482
 CIE v' : 0.5193
 Duv: -0.0004
 CIE x : 0.4313
 CIE y : 0.4010
 CIE z : 0.1677
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 49.8225
 R_f: 74.7
 R_g: 94.2

CRI (Ra): 71.7
 R1: 68.1
 R2: 82.1
 R3: 93.4
 R4: 67.3
 R5: 67.2
 R6: 74.9
 R7: 77.5
 R8: 43.4
 R9: -33.9
 R10: 58.6
 R11: 62.0
 R12: 48.5
 R13: 70.7
 R14: 96.4
 R15: 60.2



Test Conditions

Stabilization Time: 30M
 Operation Time: 1H 30M
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP2-2501-321-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-4

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.24

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.3

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	114	NR	620	817	NR	750	22	NR	880	1	NR
365	0	NR	495	141	NR	625	756	NR	755	19	NR	885	1	NR
370	0	NR	500	189	NR	630	693	NR	760	16	NR	890	0	NR
375	0	NR	505	247	NR	635	628	NR	765	14	NR	895	0	NR
380	0	NR	510	307	NR	640	564	NR	770	12	NR	900	0	NR
385	0	NR	515	366	NR	645	504	NR	775	10	NR	905	0	NR
390	0	NR	520	415	NR	650	446	NR	780	9	NR	910	0	NR
395	2	NR	525	455	NR	655	393	NR	785	8	NR	915	0	NR
400	3	NR	530	491	NR	660	344	NR	790	7	NR	920	0	NR
405	6	NR	535	523	NR	665	300	NR	795	6	NR	925	0	NR
410	11	NR	540	556	NR	670	260	NR	800	5	NR	930	0	NR
415	21	NR	545	591	NR	675	226	NR	805	4	NR	935	0	NR
420	41	NR	550	632	NR	680	195	NR	810	4	NR	940	0	NR
425	76	NR	555	679	NR	685	167	NR	815	3	NR	945	0	NR
430	129	NR	560	732	NR	690	144	NR	820	3	NR	950	0	NR
435	205	NR	565	787	NR	695	123	NR	825	2	NR	955	0	NR
440	307	NR	570	847	NR	700	105	NR	830	2	NR	960	0	NR
445	451	NR	575	900	NR	705	90	NR	835	2	NR	965	0	NR
450	603	NR	580	944	NR	710	77	NR	840	2	NR	970	0	NR
455	544	NR	585	977	NR	715	66	NR	845	1	NR	975	0	NR
460	348	NR	590	997	NR	720	56	NR	850	1	NR	980	0	NR
465	249	NR	595	998	NR	725	48	NR	855	1	NR	985	0	NR
470	191	NR	600	986	NR	730	41	NR	860	1	NR	990	0	NR
475	133	NR	605	960	NR	735	35	NR	865	1	NR	995	0	NR
480	107	NR	610	921	NR	740	30	NR	870	1	NR	1000	0	NR
485	104	NR	615	874	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP2-2501-321-4

TM-30-18

Summary

$R_f = 74.7$
 $R_g = 94.2$
 $\text{CIE } R_a = 71.7$
 $R_g = -33.9$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 65	CES51 = 86	CES76 = 58
CES02 = 62	CES27 = 89	CES52 = 85	CES77 = 76
CES03 = 31	CES28 = 84	CES53 = 77	CES78 = 62
CES04 = 71	CES29 = 68	CES54 = 85	CES79 = 85
CES05 = 49	CES30 = 83	CES55 = 84	CES80 = 84
CES06 = 51	CES31 = 71	CES56 = 74	CES81 = 73
CES07 = 41	CES32 = 64	CES57 = 74	CES82 = 93
CES08 = 40	CES33 = 78	CES58 = 75	CES83 = 91
CES09 = 29	CES34 = 75	CES59 = 85	CES84 = 88
CES10 = 76	CES35 = 87	CES60 = 90	CES85 = 76
CES11 = 59	CES36 = 94	CES61 = 81	CES86 = 64
CES12 = 65	CES37 = 84	CES62 = 89	CES87 = 77
CES13 = 43	CES38 = 92	CES63 = 75	CES88 = 80
CES14 = 74	CES39 = 96	CES64 = 65	CES89 = 67
CES15 = 71	CES40 = 92	CES65 = 65	CES90 = 79
CES16 = 47	CES41 = 93	CES66 = 60	CES91 = 80
CES17 = 50	CES42 = 86	CES67 = 58	CES92 = 57
CES18 = 56	CES43 = 78	CES68 = 66	CES93 = 74
CES19 = 73	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 66	CES45 = 85	CES70 = 60	CES95 = 67
CES21 = 87	CES46 = 81	CES71 = 57	CES96 = 77
CES22 = 79	CES47 = 86	CES72 = 85	CES97 = 83
CES23 = 92	CES48 = 75	CES73 = 52	CES98 = 76
CES24 = 91	CES49 = 79	CES74 = 95	CES99 = 64
CES25 = 73	CES50 = 86	CES75 = 60	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)