

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P386042

Luminaire Tested: **GWC-SA1C-830-U-5MQ**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P386042  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GWC-SA1C-830-U-5MQ  
Description: GALLEON WALL LUMINAIRE  
(1) 80 CRI, 3000K, 1050mA LIGHTSQUARE WITH 16 LEDS AND TYPE V MEDIUM OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6305 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G1

Input Watts (W): 58  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P386042

CATALOG NUMBER: GWC-SA1C-830-U-5MQ

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 3.1 fc  
 Type V - Short - N/A

REPORT NUMBER: P386042

CATALOG NUMBER: GWC-SA1C-830-U-5MQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P386042

CATALOG NUMBER: GWC-SA1C-830-U-5MQ


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 3152.5   | 0.0    | 3152.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 3152.5   | 0.0    | 3152.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 6305.0   | 0.0    | 6305.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 65.2   | 1.0       |
| 10°-20°   | 191.5  | 3.0       |
| 20°-30°   | 325.9  | 5.2       |
| 30°-40°   | 516.9  | 8.2       |
| 40°-50°   | 841.2  | 13.3      |
| 50°-60°   | 1387.0 | 22.0      |
| 60°-70°   | 2036.1 | 32.3      |
| 70°-80°   | 900.4  | 14.3      |
| 80°-90°   | 40.8   | 0.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6305.0 | 100.0     |
| 0°-180°   | 6305.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P386042


CATALOG NUMBER: GWC-SA1C-830-U-5MQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 291.3  | 4.6       |                         |      |         |
| FM   | (30°-60°)   | 1372.6 | 21.8      |                         |      |         |
| FH   | (60°-80°)   | 1468.2 | 23.3      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 20.4   | 0.3       |                         |      | G1/100  |
| BL   | (0°-30°)    | 291.3  | 4.6       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1372.6 | 21.8      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1468.2 | 23.3      | B3/2500                 |      | G1/1800 |
| BVH  | (80°-90°)   | 20.4   | 0.3       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G1**

Type V Short



REPORT NUMBER: P386042

CATALOG NUMBER: GWC-SA1C-830-U-5MQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 688.6  | 688.6  | 688.6  | 688.6  | 688.6  | 688.6  | 688.6  | 688.6  | 688.6  | 688.6  | 688.6  |
| 2.5°  | 687.6  | 686.9  | 688.4  | 688.2  | 686.9  | 687.1  | 687.1  | 687.8  | 687.8  | 687.4  | 687.4  |
| 5°    | 685.1  | 684.6  | 686.3  | 686.3  | 685.1  | 685.5  | 685.9  | 686.5  | 686.3  | 685.9  | 685.7  |
| 7.5°  | 681.9  | 681.7  | 683.4  | 683.4  | 682.6  | 683.0  | 682.6  | 682.8  | 682.3  | 681.9  | 681.3  |
| 10°   | 676.7  | 677.1  | 678.6  | 679.0  | 679.0  | 679.2  | 678.8  | 677.8  | 677.1  | 676.5  | 675.9  |
| 12.5° | 671.9  | 671.7  | 673.8  | 674.8  | 676.5  | 678.4  | 677.1  | 674.2  | 673.0  | 671.7  | 671.3  |
| 15°   | 668.8  | 669.0  | 671.1  | 673.0  | 675.9  | 679.8  | 678.4  | 673.8  | 671.3  | 669.8  | 669.4  |
| 17.5° | 668.2  | 668.6  | 671.3  | 674.6  | 677.8  | 682.1  | 681.3  | 676.7  | 672.5  | 669.8  | 669.2  |
| 20°   | 669.6  | 669.8  | 674.0  | 678.8  | 684.2  | 688.4  | 686.5  | 681.5  | 675.9  | 671.7  | 670.7  |
| 22.5° | 672.3  | 673.2  | 678.4  | 685.9  | 694.2  | 699.9  | 697.6  | 689.0  | 680.3  | 675.0  | 673.6  |
| 25°   | 680.9  | 681.1  | 688.2  | 698.4  | 708.4  | 714.9  | 712.2  | 700.1  | 688.8  | 683.0  | 681.1  |
| 27.5° | 698.6  | 699.2  | 706.3  | 718.2  | 726.8  | 731.0  | 729.3  | 719.5  | 709.9  | 703.6  | 704.3  |
| 30°   | 724.3  | 725.1  | 733.1  | 746.2  | 751.4  | 752.5  | 752.0  | 747.4  | 738.7  | 730.3  | 731.0  |
| 32.5° | 755.6  | 756.0  | 766.6  | 778.5  | 782.7  | 783.5  | 782.7  | 778.5  | 768.1  | 756.8  | 757.5  |
| 35°   | 795.9  | 797.1  | 807.3  | 818.8  | 822.2  | 823.8  | 822.4  | 816.9  | 806.1  | 795.0  | 794.6  |
| 37.5° | 845.5  | 845.7  | 856.4  | 868.3  | 872.4  | 872.9  | 871.2  | 867.6  | 854.1  | 844.1  | 843.4  |
| 40°   | 903.1  | 903.9  | 916.5  | 929.2  | 930.9  | 929.0  | 931.3  | 929.2  | 915.2  | 903.7  | 905.6  |
| 42.5° | 973.2  | 975.1  | 990.1  | 1002.6 | 997.8  | 996.8  | 998.3  | 998.9  | 987.6  | 973.6  | 972.4  |
| 45°   | 1054.8 | 1056.5 | 1075.3 | 1085.3 | 1082.2 | 1075.3 | 1078.2 | 1083.2 | 1067.5 | 1050.2 | 1051.9 |
| 47.5° | 1147.9 | 1152.1 | 1172.1 | 1181.5 | 1173.8 | 1164.4 | 1170.0 | 1177.5 | 1159.2 | 1137.7 | 1136.6 |
| 50°   | 1251.4 | 1256.6 | 1283.3 | 1296.5 | 1288.7 | 1271.4 | 1280.8 | 1285.8 | 1259.3 | 1231.6 | 1229.3 |
| 52.5° | 1361.8 | 1367.0 | 1400.6 | 1427.7 | 1422.7 | 1395.8 | 1408.9 | 1403.7 | 1373.2 | 1335.9 | 1333.0 |
| 55°   | 1486.8 | 1488.8 | 1525.2 | 1569.0 | 1574.0 | 1554.2 | 1553.3 | 1544.8 | 1499.7 | 1456.5 | 1454.4 |
| 57.5° | 1615.3 | 1616.8 | 1663.7 | 1715.5 | 1739.0 | 1739.0 | 1715.7 | 1697.5 | 1637.6 | 1587.5 | 1582.3 |
| 60°   | 1754.1 | 1759.3 | 1811.2 | 1881.6 | 1936.6 | 1952.9 | 1911.6 | 1862.2 | 1797.0 | 1735.9 | 1729.9 |
| 62.5° | 1877.6 | 1883.6 | 1963.1 | 2067.9 | 2156.4 | 2215.6 | 2114.6 | 2034.1 | 1915.6 | 1817.5 | 1806.0 |
| 65°   | 1893.2 | 1909.5 | 2025.3 | 2215.0 | 2413.0 | 2531.4 | 2337.7 | 2139.3 | 1923.3 | 1787.0 | 1775.3 |
| 67.5° | 1729.0 | 1756.6 | 1913.1 | 2208.3 | 2617.5 | 2871.5 | 2480.2 | 2079.2 | 1784.7 | 1634.1 | 1621.1 |
| 70°   | 1328.6 | 1368.7 | 1549.2 | 1931.6 | 2582.3 | 2981.0 | 2390.9 | 1820.2 | 1488.0 | 1325.9 | 1307.7 |
| 72.5° | 728.9  | 745.4  | 907.7  | 1322.7 | 2070.2 | 2533.2 | 1994.2 | 1345.9 | 986.8  | 803.0  | 772.5  |
| 75°   | 231.2  | 237.0  | 319.7  | 541.3  | 1171.0 | 1677.9 | 1266.8 | 660.6  | 363.7  | 268.1  | 265.0  |
| 77.5° | 102.7  | 103.3  | 115.6  | 158.0  | 403.4  | 850.1  | 484.5  | 179.9  | 123.9  | 108.3  | 111.8  |
| 80°   | 64.9   | 64.9   | 71.6   | 78.3   | 109.8  | 246.9  | 131.0  | 85.6   | 73.0   | 67.8   | 69.3   |
| 82.5° | 31.1   | 34.4   | 46.5   | 50.1   | 60.3   | 83.0   | 67.2   | 55.9   | 48.8   | 36.3   | 33.8   |
| 85°   | 20.4   | 17.1   | 29.4   | 33.2   | 35.1   | 39.9   | 39.0   | 36.9   | 31.9   | 18.2   | 20.2   |
| 87.5° | 9.2    | 8.8    | 15.2   | 14.0   | 13.1   | 10.0   | 15.0   | 18.6   | 17.9   | 9.0    | 9.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

INVUE

Report Number: SP1-2012-088-3

Luminaire Tested: WIS-SA-830-2D-U-SL4

Test Date: 01/11/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2012-088-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 01/11/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: INVUE  
 Catalog Number: **WIS-SA-830-2D-U-SL4**  
 Description: INVUE. WALL PACK LIGHT SQUARE SL4 OPTICS 2-SQUARE.

### Spectral Parameters

|                           |        |           |      |      |      |
|---------------------------|--------|-----------|------|------|------|
| CCT (K):                  | 3049   | CRI (Ra): | 81.7 |      |      |
| CIE u':                   | 0.2482 | R1:       | 79.6 | R9:  | 1.9  |
| CIE v':                   | 0.5224 | R2:       | 90.6 | R10: | 79.3 |
| Duv:                      | 0.0015 | R3:       | 95.7 | R11: | 78.7 |
| CIE x:                    | 0.4354 | R4:       | 79.4 | R12: | 72.2 |
| CIE y:                    | 0.4072 | R5:       | 80.2 | R13: | 82.2 |
| CIE z:                    | 0.1574 | R6:       | 89.0 | R14: | 98.1 |
| Peak Wavelength (nm):     | 601    | R7:       | 82.2 |      |      |
| Dominant Wavelength (nm): | 582    | R8:       | 57.0 |      |      |
| Purity:                   | 53     |           |      |      |      |
| Rf:                       | 85.1   |           |      |      |      |
| Rg:                       | 94.3   |           |      |      |      |



### Test Conditions

Stabilization Time: 83M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.6/29%  
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-2012-088-3

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 7/29/2020        | 1/29/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2012-088-3

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2012-088-3

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 6.7              | 620       | 161309           | 42.0             | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 9.8              | 625       | 153301           | 33.8             | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 13.6             | 630       | 143292           | 25.9             | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 19.3             | 635       | 132368           | 19.9             | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 25.5             | 640       | 122334           | 14.6             | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 32.9             | 645       | 112200           | 10.8             | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 40.6             | 650       | 102448           | 7.5              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 47.1             | 655       | 91886            | 5.3              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 53.7             | 660       | 81865            | 3.4              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.0              | 535       | 94694            | 58.7             | 665       | 72448            | 2.3              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.0              | 540       | 98431            | 64.1             | 670       | 63654            | 1.4              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.0              | 545       | 103765           | 69.1             | 675       | 55284            | 0.9              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 0.0              | 550       | 109130           | 74.2             | 680       | 47949            | 0.6              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 0.1              | 555       | 115271           | 78.7             | 685       | 42173            | 0.4              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 0.1              | 560       | 123390           | 83.9             | 690       | 36755            | 0.2              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 0.3              | 565       | 131926           | 87.7             | 695       | 31630            | 0.1              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 0.7              | 570       | 141815           | 92.2             | 700       | 27642            | 0.1              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 1.3              | 575       | 151359           | 94.2             | 705       | 24213            | 0.1              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 2.1              | 580       | 160364           | 95.3             | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 2.6              | 585       | 166836           | 92.7             | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 2.6              | 590       | 172885           | 89.4             | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 2.7              | 595       | 176548           | 83.7             | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 2.8              | 600       | 178427           | 76.9             | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 3.0              | 605       | 177729           | 68.8             | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 3.6              | 610       | 174846           | 60.1             | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 4.9              | 615       | 169274           | 51.1             | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 4584.8

S/P: 0.52

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 72.6             | 620       | 161309           | 2.0              | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 87.7             | 625       | 153301           | 1.3              | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 103.4            | 630       | 143292           | 0.8              | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 117.0            | 635       | 132368           | 0.5              | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 126.0            | 640       | 122334           | 0.3              | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 131.6            | 645       | 112200           | 0.2              | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 133.2            | 650       | 102448           | 0.1              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 131.3            | 655       | 91886            | 0.1              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 125.8            | 660       | 81865            | 0.0              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.1              | 535       | 94694            | 118.0            | 665       | 72448            | 0.0              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.2              | 540       | 98431            | 108.8            | 670       | 63654            | 0.0              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.4              | 545       | 103765           | 99.5             | 675       | 55284            | 0.0              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 1.0              | 550       | 109130           | 89.2             | 680       | 47949            | 0.0              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 2.3              | 555       | 115271           | 78.8             | 685       | 42173            | 0.0              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 5.4              | 560       | 123390           | 69.0             | 690       | 36755            | 0.0              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 11.6             | 565       | 131926           | 59.2             | 695       | 31630            | 0.0              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 23.2             | 570       | 141815           | 50.0             | 700       | 27642            | 0.0              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 42.1             | 575       | 151359           | 41.2             | 705       | 24213            | 0.0              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 63.1             | 580       | 160364           | 33.0             | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 67.4             | 585       | 166836           | 25.5             | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 60.3             | 590       | 172885           | 19.3             | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 55.1             | 595       | 176548           | 14.1             | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 51.0             | 600       | 178427           | 10.1             | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 48.4             | 605       | 177729           | 7.0              | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 51.4             | 610       | 174846           | 4.7              | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 60.4             | 615       | 169274           | 3.1              | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 12033.4 S/P: 1.36**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 39.3             | 620       | 161309           | 0.1              | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 44.8             | 625       | 153301           | 0.1              | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 49.7             | 630       | 143292           | 0.0              | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 52.8             | 635       | 132368           | 0.0              | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 53.4             | 640       | 122334           | 0.0              | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 51.9             | 645       | 112200           | 0.0              | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 48.8             | 650       | 102448           | 0.0              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 44.5             | 655       | 91886            | 0.0              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 39.4             | 660       | 81865            | 0.0              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.0              | 535       | 94694            | 34.1             | 665       | 72448            | 0.0              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.1              | 540       | 98431            | 28.8             | 670       | 63654            | 0.0              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.2              | 545       | 103765           | 24.1             | 675       | 55284            | 0.0              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 0.7              | 550       | 109130           | 19.6             | 680       | 47949            | 0.0              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 1.5              | 555       | 115271           | 15.5             | 685       | 42173            | 0.0              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 3.3              | 560       | 123390           | 12.2             | 690       | 36755            | 0.0              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 6.9              | 565       | 131926           | 9.3              | 695       | 31630            | 0.0              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 13.9             | 570       | 141815           | 6.9              | 700       | 27642            | 0.0              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 24.8             | 575       | 151359           | 5.0              | 705       | 24213            | 0.0              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 37.5             | 580       | 160364           | 3.6              | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 40.4             | 585       | 166836           | 2.5              | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 36.8             | 590       | 172885           | 1.7              | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 34.1             | 595       | 176548           | 1.1              | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 31.7             | 600       | 178427           | 0.8              | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 29.5             | 605       | 177729           | 0.5              | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 30.6             | 610       | 174846           | 0.3              | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 34.3             | 615       | 169274           | 0.2              | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3


TM-30-18

### Summary

$R_f = 85.1$   
 $R_g = 94.3$   
 CIE  $R_a = 81.7$   
 $R_9 = 1.9$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 85 | CES51 = 93 | CES76 = 82 |
| CES02 = 63 | CES27 = 94 | CES52 = 93 | CES77 = 85 |
| CES03 = 31 | CES28 = 95 | CES53 = 89 | CES78 = 82 |
| CES04 = 70 | CES29 = 90 | CES54 = 90 | CES79 = 91 |
| CES05 = 49 | CES30 = 96 | CES55 = 89 | CES80 = 90 |
| CES06 = 51 | CES31 = 91 | CES56 = 86 | CES81 = 72 |
| CES07 = 42 | CES32 = 85 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 95 | CES58 = 86 | CES83 = 95 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 76 | CES35 = 96 | CES60 = 92 | CES85 = 77 |
| CES11 = 59 | CES36 = 87 | CES61 = 88 | CES86 = 68 |
| CES12 = 65 | CES37 = 96 | CES62 = 90 | CES87 = 84 |
| CES13 = 43 | CES38 = 94 | CES63 = 88 | CES88 = 87 |
| CES14 = 74 | CES39 = 98 | CES64 = 81 | CES89 = 75 |
| CES15 = 71 | CES40 = 96 | CES65 = 79 | CES90 = 88 |
| CES16 = 47 | CES41 = 97 | CES66 = 80 | CES91 = 79 |
| CES17 = 50 | CES42 = 98 | CES67 = 78 | CES92 = 65 |
| CES18 = 56 | CES43 = 92 | CES68 = 82 | CES93 = 78 |
| CES19 = 72 | CES44 = 99 | CES69 = 87 | CES94 = 61 |
| CES20 = 66 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 90 | CES71 = 77 | CES96 = 83 |
| CES22 = 79 | CES47 = 95 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 84 | CES73 = 75 | CES98 = 84 |
| CES24 = 91 | CES49 = 91 | CES74 = 92 | CES99 = 75 |
| CES25 = 72 | CES50 = 94 | CES75 = 80 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**


(END OF REPORT)