

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1212009

Luminaire Tested: **GKO-PB2C-735-U-T1**

Issue Date: 11/5/2025

Test Information

Test Method: LM-79-08
Report Number: P1212009
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2C-735-U-T1
Description: GEKKO WALL PACK 8000LM PACKAGE 70CRI 3500K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8350.4 lumens
Efficiency: N/A
Efficacy: 143.5 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B3 - U0 - G3

Input Watts (W): 58.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 5%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1212009
 CATALOG NUMBER: GKO-PB2C-735-U-T1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 9.2 fc
 Type I - Short - N/A

REPORT NUMBER: P1212009
CATALOG NUMBER: GKO-PB2C-735-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1212009

CATALOG NUMBER: GKO-PB2C-735-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4175.2	0.0	4175.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	4175.2	0.0	4175.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	8350.4	0.0	8350.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.7	2.4
10°-20°	598.8	7.2
20°-30°	995.8	11.9
30°-40°	1322.8	15.8
40°-50°	1491.3	17.9
50°-60°	1533.5	18.4
60°-70°	1449.2	17.4
70°-80°	709.4	8.5
80°-90°	50.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8350.4	100.0
0°-180°	8350.4	100.0

Coefficient of Utilization



REPORT NUMBER: P1212009


CATALOG NUMBER: GKO-PB2C-735-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	896.7	10.7			
FM	(30°-60°)	2173.9	26.0			
FH	(60°-80°)	1079.3	12.9			G1/1800
FVH	(80°-90°)	25.4	0.3			G1/100
BL	(0°-30°)	896.7	10.7	B2/1000		
BM	(30°-60°)	2173.9	26.0	B2/2500		
BH	(60°-80°)	1079.3	12.9	B3/2500		G3/2500
BVH	(80°-90°)	25.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type I Short





REPORT NUMBER: P1212009

CATALOG NUMBER: GKO-PB2C-735-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1	2072.1
2.5°	2073.6	2076.7	2070.5	2070.5	2073.6	2075.2	2075.2	2076.7	2073.6	2073.6	2072.1
5°	2073.6	2075.2	2072.1	2072.1	2075.2	2079.8	2078.2	2081.3	2081.3	2079.8	2079.8
7.5°	2072.1	2075.2	2072.1	2073.6	2078.2	2087.5	2087.5	2087.5	2090.6	2093.6	2093.6
10°	2070.5	2073.6	2075.2	2076.7	2082.9	2096.7	2099.8	2101.3	2106.0	2110.6	2110.6
12.5°	2062.9	2065.9	2070.5	2076.7	2087.5	2106.0	2112.1	2116.7	2124.4	2129.0	2132.1
15°	2052.1	2053.6	2064.4	2076.7	2093.6	2116.7	2129.0	2136.7	2147.5	2153.7	2158.3
17.5°	2036.7	2038.2	2055.2	2073.6	2098.3	2130.6	2150.6	2162.9	2173.7	2182.9	2189.1
20°	2016.7	2021.3	2041.3	2070.5	2106.0	2144.4	2173.7	2195.2	2206.0	2215.3	2224.5
22.5°	1992.0	1996.7	2021.3	2062.9	2113.7	2162.9	2201.4	2229.1	2243.0	2255.3	2266.1
25°	1955.1	1961.2	1990.5	2044.4	2116.7	2182.9	2232.2	2267.6	2279.9	2295.3	2304.5
27.5°	1898.1	1902.8	1938.2	2007.4	2107.5	2204.5	2267.6	2309.2	2323.0	2340.0	2349.2
30°	1808.8	1818.1	1861.2	1947.4	2084.4	2221.4	2309.2	2350.7	2367.7	2384.6	2396.9
32.5°	1693.4	1707.2	1755.0	1865.8	2039.8	2227.6	2353.8	2401.5	2423.1	2441.6	2456.9
35°	1550.2	1564.1	1621.0	1761.1	1968.9	2215.3	2398.5	2460.0	2486.2	2510.8	2529.3
37.5°	1387.0	1399.4	1468.6	1628.7	1867.3	2176.8	2433.9	2524.7	2560.1	2592.4	2617.1
40°	1222.3	1236.2	1311.6	1482.5	1744.2	2102.9	2449.3	2595.5	2640.1	2681.7	2712.5
42.5°	1043.7	1060.7	1145.3	1327.0	1601.0	2001.3	2436.9	2664.8	2720.2	2777.2	2823.3
45°	885.2	888.3	980.6	1156.1	1444.0	1870.4	2393.8	2731.0	2806.4	2886.5	2952.7
47.5°	732.8	738.9	819.0	992.9	1280.8	1722.6	2315.3	2783.3	2903.4	3006.5	3103.5
50°	597.3	605.0	677.4	832.8	1117.6	1561.0	2209.1	2814.1	2986.5	3126.6	3262.1
52.5°	486.5	495.7	555.7	692.7	952.9	1391.7	2078.2	2818.7	3062.0	3246.7	3426.8
55°	404.9	411.0	457.2	566.5	794.4	1216.2	1928.9	2795.6	3111.2	3354.4	3594.6
57.5°	341.8	347.9	380.2	466.5	651.2	1036.0	1747.3	2741.7	3137.4	3448.4	3763.9
60°	297.1	301.7	324.8	386.4	535.7	866.7	1551.8	2646.3	3129.7	3506.8	3904.0
62.5°	264.8	266.3	286.3	329.4	441.8	706.6	1331.6	2503.1	3066.6	3514.5	3999.5
65°	235.5	237.1	249.4	280.2	363.3	568.1	1102.2	2306.1	2946.5	3460.7	4013.3
67.5°	190.9	194.0	212.4	235.5	298.7	449.5	868.2	2047.5	2758.7	3320.6	3934.8
70°	152.4	153.9	172.4	198.6	243.2	354.1	666.6	1699.5	2464.6	3092.7	3731.6
72.5°	113.9	117.0	133.9	160.1	198.6	274.0	481.8	1285.4	1970.5	2607.8	3249.8
75°	90.8	92.4	98.5	123.2	153.9	207.8	324.8	779.0	1186.9	1613.3	1992.0
77.5°	77.0	78.5	78.5	95.4	113.9	140.1	172.4	309.4	501.9	714.3	946.8
80°	63.1	66.2	60.0	70.8	81.6	81.6	80.1	147.8	237.1	335.6	440.3
82.5°	46.2	49.3	46.2	49.3	49.3	44.6	41.6	55.4	75.4	103.1	112.4
85°	32.3	33.9	36.9	33.9	32.3	26.2	20.0	15.4	9.2	10.8	15.4
87.5°	21.6	26.2	30.8	29.2	24.6	20.0	13.9	9.2	4.6	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1212009
 CATALOG NUMBER: GKO-PB2C-735-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2072.1	2072.1	2072.1
2.5°	2073.6	2072.1	2070.5
5°	2081.3	2079.8	2078.2
7.5°	2092.1	2092.1	2092.1
10°	2109.0	2112.1	2112.1
12.5°	2130.6	2133.7	2133.7
15°	2156.8	2158.3	2161.4
17.5°	2189.1	2190.6	2190.6
20°	2227.6	2226.0	2229.1
22.5°	2266.1	2266.1	2266.1
25°	2306.1	2306.1	2306.1
27.5°	2352.3	2352.3	2349.2
30°	2403.1	2403.1	2403.1
32.5°	2464.6	2466.2	2467.7
35°	2543.2	2546.2	2550.9
37.5°	2632.4	2640.1	2644.8
40°	2738.7	2741.7	2749.4
42.5°	2857.2	2866.4	2868.0
45°	3005.0	3020.4	3026.5
47.5°	3178.9	3200.5	3211.3
50°	3372.9	3397.5	3412.9
52.5°	3583.8	3623.8	3642.3
55°	3808.6	3877.9	3897.9
57.5°	4062.6	4156.5	4184.2
60°	4312.0	4444.4	4489.0
62.5°	4524.4	4710.7	4766.1
65°	4673.7	4898.5	4980.1
67.5°	4704.5	4970.9	5067.8
70°	4519.8	4792.3	4904.7
72.5°	3930.2	4176.5	4316.6
75°	2321.5	2498.5	2455.4
77.5°	1165.4	1216.2	1223.9
80°	511.1	541.9	554.2
82.5°	126.2	129.3	146.2
85°	16.9	20.0	18.5
87.5°	6.2	6.2	7.7
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-2

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-735-U-T4W


Data in this report applies to families of products including GKO-PB1C

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-735-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	3481	CRI (Ra):	71.1		
CIE u':	0.2357	R1:	67.5	R9:	-37.9
CIE v':	0.5131	R2:	79.5	R10:	52.4
Duv:	0.0011	R3:	90.0	R11:	64.5
CIE x:	0.4076	R4:	69.0	R12:	43.0
CIE y:	0.3944	R5:	67.0	R13:	69.5
CIE z:	0.1981	R6:	71.2	R14:	94.3
Peak Wavelength (nm):	589	R7:	78.9	R15:	59.3
Dominant Wavelength (nm):	580	R8:	45.9		
Purity:	40.6853				
Rf:	73.8				
Rg:	93.8				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-595-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.36

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.56


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	771	NR	750	19	NR	880	1	NR
365	0	NR	495	165	NR	625	705	NR	755	16	NR	885	1	NR
370	0	NR	500	230	NR	630	641	NR	760	14	NR	890	0	NR
375	0	NR	505	305	NR	635	575	NR	765	12	NR	895	0	NR
380	1	NR	510	380	NR	640	513	NR	770	10	NR	900	0	NR
385	2	NR	515	453	NR	645	455	NR	775	9	NR	905	0	NR
390	3	NR	520	507	NR	650	401	NR	780	7	NR	910	0	NR
395	5	NR	525	551	NR	655	351	NR	785	6	NR	915	0	NR
400	7	NR	530	587	NR	660	305	NR	790	5	NR	920	0	NR
405	10	NR	535	620	NR	665	265	NR	795	5	NR	925	0	NR
410	15	NR	540	648	NR	670	229	NR	800	4	NR	930	0	NR
415	25	NR	545	680	NR	675	197	NR	805	4	NR	935	0	NR
420	48	NR	550	716	NR	680	169	NR	810	3	NR	940	0	NR
425	90	NR	555	757	NR	685	145	NR	815	3	NR	945	0	NR
430	161	NR	560	807	NR	690	124	NR	820	2	NR	950	0	NR
435	279	NR	565	856	NR	695	106	NR	825	2	NR	955	0	NR
440	460	NR	570	901	NR	700	90	NR	830	2	NR	960	0	NR
445	771	NR	575	942	NR	705	77	NR	835	2	NR	965	0	NR
450	915	NR	580	974	NR	710	65	NR	840	1	NR	970	0	NR
455	572	NR	585	991	NR	715	56	NR	845	1	NR	975	0	NR
460	342	NR	590	999	NR	720	48	NR	850	1	NR	980	0	NR
465	264	NR	595	992	NR	725	40	NR	855	1	NR	985	0	NR
470	169	NR	600	966	NR	730	35	NR	860	1	NR	990	0	NR
475	115	NR	605	931	NR	735	29	NR	865	1	NR	995	0	NR
480	103	NR	610	885	NR	740	25	NR	870	1	NR	1000	0	NR
485	103	NR	615	829	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-2





TM-30-18

Summary

$R_f = 73.8$
 $R_g = 93.8$
 $CIE R_a = 71.1$
 $R_g = -37.9$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 63	CES51 = 88	CES76 = 53
CES02 = 61	CES27 = 88	CES52 = 87	CES77 = 73
CES03 = 31	CES28 = 83	CES53 = 77	CES78 = 56
CES04 = 70	CES29 = 65	CES54 = 84	CES79 = 83
CES05 = 48	CES30 = 79	CES55 = 83	CES80 = 81
CES06 = 51	CES31 = 69	CES56 = 73	CES81 = 76
CES07 = 40	CES32 = 61	CES57 = 72	CES82 = 92
CES08 = 39	CES33 = 75	CES58 = 74	CES83 = 90
CES09 = 29	CES34 = 72	CES59 = 85	CES84 = 87
CES10 = 75	CES35 = 85	CES60 = 90	CES85 = 77
CES11 = 58	CES36 = 93	CES61 = 82	CES86 = 68
CES12 = 64	CES37 = 81	CES62 = 88	CES87 = 77
CES13 = 42	CES38 = 89	CES63 = 73	CES88 = 79
CES14 = 74	CES39 = 96	CES64 = 66	CES89 = 68
CES15 = 71	CES40 = 91	CES65 = 63	CES90 = 79
CES16 = 47	CES41 = 92	CES66 = 60	CES91 = 78
CES17 = 50	CES42 = 83	CES67 = 57	CES92 = 57
CES18 = 56	CES43 = 77	CES68 = 65	CES93 = 74
CES19 = 72	CES44 = 99	CES69 = 75	CES94 = 50
CES20 = 65	CES45 = 85	CES70 = 58	CES95 = 66
CES21 = 87	CES46 = 81	CES71 = 53	CES96 = 76
CES22 = 79	CES47 = 84	CES72 = 84	CES97 = 83
CES23 = 92	CES48 = 74	CES73 = 49	CES98 = 75
CES24 = 91	CES49 = 79	CES74 = 96	CES99 = 63
CES25 = 72	CES50 = 87	CES75 = 55	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)