

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P972382

Luminaire Tested: **GKO-PB1E-750-U-T2U**

Issue Date: 02/27/2025

Test Information

Test Method: LM-79-08
Report Number: P972382
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/27/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1E-750-U-T2U
Description: GEKKO WALL PACK 5000LM PACKAGE 70CRI 5000K FIXTURE w/ TYPE II URBAN DISTRIBUTION OPTIC
Light Source: (10) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5170.9 lumens
Efficiency: N/A
Efficacy: 133.6 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B1 - U0 - G1


Input Watts (W): 38.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 9%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P972382

CATALOG NUMBER: GKO-PB1E-750-U-T2U

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 11.4 fc
 Type II - Medium - N/A

REPORT NUMBER: P972382

CATALOG NUMBER: GKO-PB1E-750-U-T2U

Luminous Intensity Polar Plot



REPORT NUMBER: P972382

CATALOG NUMBER: GKO-PB1E-750-U-T2U


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1705.9	0.0	1705.9
	% Fixture	33.0	0.0	33.0
Street Side	Lumens	3464.9	0.0	3464.9
	% Fixture	67.0	0.0	67.0
Total	Lumens	5170.9	0.0	5170.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.9
10°-20°	295.6	5.7
20°-30°	508.5	9.8
30°-40°	730.7	14.1
40°-50°	926.7	17.9
50°-60°	1017.6	19.7
60°-70°	986.9	19.1
70°-80°	544.9	10.5
80°-90°	63.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5170.9	100.0
0°-180°	5170.9	100.0



REPORT NUMBER: P972382


CATALOG NUMBER: GKO-PB1E-750-U-T2U

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	523.8	10.1			
FM	(30°-60°)	1839.2	35.6			
FH	(60°-80°)	1079.6	20.9			G1/1800
FVH	(80°-90°)	22.3	0.4			G1/100
BL	(0°-30°)	376.9	7.3	B1/500		
BM	(30°-60°)	836.0	16.2	B1/1000		
BH	(60°-80°)	452.2	8.7	B1/500		G1/500
BVH	(80°-90°)	40.9	0.8			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type II Medium





REPORT NUMBER: P972382

CATALOG NUMBER: GKO-PB1E-750-U-T2U

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	76°	85°
0°	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2
2.5°	1035.2	1034.2	1033.2	1033.2	1029.2	1025.2	1021.2	1018.2	1010.2	1009.2	1005.2
5°	1066.2	1066.2	1063.2	1062.2	1056.2	1046.2	1037.2	1028.2	1017.2	1015.2	1006.2
7.5°	1106.2	1106.2	1101.2	1097.2	1088.2	1072.2	1056.2	1040.2	1024.2	1022.2	1008.2
10°	1157.2	1157.2	1153.2	1144.2	1125.2	1104.2	1078.2	1053.2	1032.2	1030.2	1010.2
12.5°	1210.2	1211.2	1205.2	1192.2	1169.2	1137.2	1105.2	1069.2	1042.2	1039.2	1014.2
15°	1264.2	1265.2	1261.2	1247.2	1216.2	1177.2	1134.2	1091.2	1055.2	1052.2	1020.2
17.5°	1317.2	1319.2	1315.2	1299.2	1263.2	1221.2	1168.2	1114.2	1071.2	1067.2	1030.2
20°	1367.2	1367.2	1367.2	1349.2	1314.2	1266.2	1205.2	1142.2	1089.2	1085.2	1042.2
22.5°	1412.2	1414.2	1417.2	1407.2	1367.2	1314.2	1248.2	1173.2	1112.2	1107.2	1057.2
25°	1457.2	1458.2	1466.2	1459.2	1420.2	1365.2	1294.2	1212.2	1140.2	1135.2	1075.2
27.5°	1509.3	1512.3	1517.3	1514.3	1470.2	1416.2	1345.2	1255.2	1171.2	1166.2	1097.2
30°	1570.3	1570.3	1573.3	1568.3	1524.3	1470.2	1396.2	1300.2	1210.2	1202.2	1124.2
32.5°	1620.3	1625.3	1623.3	1621.3	1575.3	1521.3	1448.2	1350.2	1255.2	1245.2	1161.2
35°	1667.3	1668.3	1667.3	1669.3	1623.3	1572.3	1503.3	1408.2	1305.2	1301.2	1208.2
37.5°	1694.3	1696.3	1701.3	1707.3	1666.3	1618.3	1558.3	1472.2	1367.2	1360.2	1264.2
40°	1707.3	1710.3	1737.3	1746.3	1702.3	1662.3	1616.3	1530.3	1427.2	1419.2	1320.2
42.5°	1727.3	1751.3	1765.3	1767.3	1729.3	1694.3	1666.3	1596.3	1501.2	1494.2	1395.2
45°	1661.3	1652.3	1689.3	1732.3	1730.3	1715.3	1714.3	1670.3	1592.3	1585.3	1480.2
47.5°	1578.3	1571.3	1591.3	1654.3	1699.3	1724.3	1761.3	1757.3	1702.3	1692.3	1579.3
50°	1380.2	1392.2	1490.2	1576.3	1654.3	1727.3	1801.3	1848.3	1809.3	1801.3	1684.3
52.5°	1195.2	1203.2	1270.2	1475.2	1596.3	1718.3	1836.3	1944.3	1934.3	1925.3	1799.3
55°	1065.2	1073.2	1180.2	1311.2	1510.3	1672.3	1859.3	2035.3	2061.3	2052.3	1921.3
57.5°	929.2	942.2	1015.2	1130.2	1395.2	1596.3	1867.3	2127.4	2199.4	2191.4	2038.3
60°	798.1	816.1	859.1	984.2	1253.2	1506.3	1846.3	2201.4	2332.4	2332.4	2159.4
62.5°	677.1	687.1	732.1	845.1	1073.2	1391.2	1793.3	2248.4	2454.4	2449.4	2265.4
65°	577.1	582.1	618.1	715.1	922.2	1264.2	1701.3	2245.4	2541.4	2542.4	2335.4
67°	487.1	495.1	535.1	623.1	807.1	1144.2	1595.3	2200.4	2572.4	2574.4	2352.4
67.5°	456.1	465.1	509.1	600.1	783.1	1111.2	1570.3	2181.4	2570.4	2574.4	2347.4
70°	314.1	316.1	390.1	494.1	644.1	936.2	1397.2	2049.3	2494.4	2491.4	2238.4
72.5°	200.0	197.0	268.0	361.1	518.1	758.1	1179.2	1818.3	2263.4	2260.4	1973.3
75°	133.0	136.0	181.0	258.0	364.1	586.1	919.2	1372.2	1572.3	1560.3	1302.2
77.5°	95.0	93.0	112.0	186.0	244.0	356.1	499.1	730.1	835.1	835.1	715.1
80°	52.0	53.0	61.0	103.0	138.0	139.0	187.0	366.1	408.1	417.1	347.1
82.5°	15.0	16.0	22.0	35.0	38.0	42.0	65.0	105.0	110.0	116.0	94.0
85°	0.0	0.0	0.0	1.0	4.0	5.0	5.0	6.0	10.0	10.0	11.0
87.5°	0.0	0.0	0.0	0.0	0.0	1.0	1.0	2.0	4.0	4.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P972382

CATALOG NUMBER: GKO-PB1E-750-U-T2U

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2
2.5°	1004.2	1005.2	1001.2	996.2	992.2	990.2	984.2	979.2	982.2	985.2	985.2
5°	1003.2	1002.2	994.2	985.2	979.2	975.2	965.2	958.2	959.2	962.2	961.2
7.5°	1003.2	999.2	988.2	975.2	965.2	957.2	944.2	936.2	935.2	937.2	935.2
10°	1004.2	997.2	982.2	964.2	950.2	938.2	922.2	913.2	910.2	911.2	909.2
12.5°	1006.2	995.2	976.2	953.2	935.2	919.2	901.1	890.1	888.1	890.1	890.1
15°	1009.2	995.2	971.2	943.2	919.2	901.1	883.1	873.1	873.1	874.1	874.1
17.5°	1015.2	998.2	967.2	932.2	903.2	883.1	867.1	860.1	861.1	864.1	864.1
20°	1021.2	1002.2	963.2	921.2	889.1	866.1	853.1	848.1	852.1	856.1	856.1
22.5°	1030.2	1007.2	959.2	911.2	873.1	850.1	839.1	835.1	839.1	844.1	842.1
25°	1044.2	1016.2	956.2	902.2	858.1	833.1	822.1	818.1	820.1	824.1	824.1
27.5°	1060.2	1027.2	955.2	891.1	840.1	813.1	800.1	794.1	794.1	795.1	796.1
30°	1087.2	1046.2	959.2	883.1	824.1	792.1	775.1	766.1	765.1	769.1	769.1
32.5°	1119.2	1072.2	969.2	876.1	808.1	767.1	744.1	737.1	735.1	738.1	735.1
35°	1155.2	1101.2	982.2	875.1	792.1	740.1	714.1	706.1	700.1	698.1	696.1
37.5°	1206.2	1141.2	995.2	870.1	776.1	711.1	683.1	666.1	659.1	657.1	657.1
40°	1256.2	1180.2	1011.2	862.1	757.1	682.1	642.1	623.1	620.1	620.1	620.1
42.5°	1319.2	1231.2	1033.2	857.1	734.1	653.1	598.1	576.1	576.1	576.1	575.1
45°	1397.2	1298.2	1061.2	855.1	712.1	618.1	551.1	522.1	521.1	520.1	519.1
47.5°	1488.2	1368.2	1088.2	850.1	686.1	576.1	497.1	465.1	458.1	456.1	453.1
50°	1582.3	1444.2	1117.2	843.1	655.1	527.1	446.1	409.1	394.1	389.1	391.1
52.5°	1682.3	1518.3	1145.2	833.1	618.1	478.1	394.1	355.1	340.1	334.1	333.1
55°	1780.3	1593.3	1171.2	820.1	578.1	428.1	350.1	312.1	299.0	297.0	297.0
57.5°	1879.3	1665.3	1191.2	801.1	534.1	384.1	312.1	281.0	272.0	276.0	276.0
60°	1969.3	1728.3	1201.2	775.1	490.1	344.1	282.0	259.0	255.0	265.0	264.0
62.5°	2050.3	1770.3	1196.2	737.1	447.1	310.1	259.0	242.0	243.0	255.0	256.0
65°	2089.3	1777.3	1167.2	685.1	399.1	281.0	235.0	219.0	221.0	234.0	237.0
67°	2080.3	1750.3	1119.2	626.1	360.1	259.0	220.0	204.0	205.0	216.0	217.0
67.5°	2070.3	1737.3	1106.2	608.1	350.1	255.0	216.0	201.0	203.0	213.0	213.0
70°	1937.3	1605.3	986.2	516.1	303.1	227.0	197.0	187.0	189.0	195.0	195.0
72.5°	1693.3	1390.2	798.1	414.1	257.0	201.0	178.0	172.0	172.0	172.0	167.0
75°	1080.2	871.1	522.1	317.1	212.0	172.0	160.0	153.0	149.0	155.0	153.0
77.5°	597.1	455.1	272.0	182.0	153.0	143.0	139.0	136.0	135.0	149.0	145.0
80°	283.0	225.0	153.0	104.0	88.0	106.0	120.0	118.0	141.0	193.0	194.0
82.5°	90.0	74.0	62.0	57.0	59.0	76.0	93.0	107.0	183.0	207.0	204.0
85°	11.0	10.0	7.0	23.0	39.0	56.0	72.0	139.0	168.0	140.0	132.0
87.5°	4.0	4.0	4.0	16.0	30.0	43.0	65.0	140.0	103.0	94.0	86.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP2-2501-321-5

Test Date: 04/10/2025

Luminaire Tested: GKO-PB1E-750-U-T4W


Data in this report applies to families of products including GKO-PB1E-750-U-T4W

Test Information

Test Method: LM-79-2019
 Report Number: SP2-2501-321-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP2 - 165CM SPHERE
 Measurement Geometry: 4π
 Issue Date: 04/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1E-750-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K):	5105	CRI (Ra):	72.2		
CIE u':	0.2079	R1:	68.8	R9:	-38.2
CIE v':	0.4868	R2:	78.3	R10:	48.2
Duv:	0.0035	R3:	84.9	R11:	68.1
CIE x:	0.3428	R4:	71.7	R12:	42.9
CIE y:	0.3567	R5:	69.8	R13:	70.6
CIE z:	0.3005	R6:	69.8	R14:	91.6
Peak Wavelength (nm):	451	R7:	81.2	R15:	61.7
Dominant Wavelength (nm):	567	R8:	53.5		
Purity:	9.884628				
Rf:	74.2				
Rg:	92.7				



Test Conditions


Stabilization Time: 30M
 Operation Time: 1H 30M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP2-2501-321-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN2187	1/6/2025	7/6/2025
Power Meter	INXT2011002	1/21/2025	1/21/2026
AC Power Source	IN0458	10/22/2024	10/22/2025
DC Power Source	IN0212	10/22/2024	10/22/2025
Sphere Thermometer	IN4036B	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP2-2501-321-5

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP2-2501-321-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	134	NR	620	390	NR	750	10	NR	880	0	NR
365	0	NR	495	165	NR	625	354	NR	755	9	NR	885	0	NR
370	0	NR	500	218	NR	630	319	NR	760	8	NR	890	0	NR
375	0	NR	505	281	NR	635	285	NR	765	7	NR	895	0	NR
380	0	NR	510	343	NR	640	254	NR	770	6	NR	900	0	NR
385	1	NR	515	400	NR	645	224	NR	775	5	NR	905	0	NR
390	2	NR	520	444	NR	650	197	NR	780	4	NR	910	0	NR
395	4	NR	525	477	NR	655	173	NR	785	4	NR	915	0	NR
400	6	NR	530	501	NR	660	150	NR	790	3	NR	920	0	NR
405	9	NR	535	520	NR	665	131	NR	795	3	NR	925	0	NR
410	14	NR	540	534	NR	670	113	NR	800	2	NR	930	0	NR
415	26	NR	545	547	NR	675	98	NR	805	2	NR	935	0	NR
420	50	NR	550	561	NR	680	85	NR	810	2	NR	940	0	NR
425	95	NR	555	574	NR	685	73	NR	815	2	NR	945	0	NR
430	168	NR	560	586	NR	690	63	NR	820	1	NR	950	0	NR
435	284	NR	565	596	NR	695	54	NR	825	1	NR	955	0	NR
440	452	NR	570	604	NR	700	46	NR	830	1	NR	960	0	NR
445	705	NR	575	606	NR	705	40	NR	835	1	NR	965	0	NR
450	980	NR	580	603	NR	710	34	NR	840	1	NR	970	0	NR
455	869	NR	585	592	NR	715	29	NR	845	1	NR	975	0	NR
460	531	NR	590	577	NR	720	25	NR	850	1	NR	980	0	NR
465	372	NR	595	554	NR	725	22	NR	855	1	NR	985	0	NR
470	268	NR	600	527	NR	730	19	NR	860	1	NR	990	0	NR
475	174	NR	605	497	NR	735	16	NR	865	0	NR	995	0	NR
480	135	NR	610	462	NR	740	14	NR	870	0	NR	1000	0	NR
485	126	NR	615	428	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP2-2501-321-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.82

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	134	NR	620	390	NR	750	10	NR	880	0	NR
365	0	NR	495	165	NR	625	354	NR	755	9	NR	885	0	NR
370	0	NR	500	218	NR	630	319	NR	760	8	NR	890	0	NR
375	0	NR	505	281	NR	635	285	NR	765	7	NR	895	0	NR
380	0	NR	510	343	NR	640	254	NR	770	6	NR	900	0	NR
385	1	NR	515	400	NR	645	224	NR	775	5	NR	905	0	NR
390	2	NR	520	444	NR	650	197	NR	780	4	NR	910	0	NR
395	4	NR	525	477	NR	655	173	NR	785	4	NR	915	0	NR
400	6	NR	530	501	NR	660	150	NR	790	3	NR	920	0	NR
405	9	NR	535	520	NR	665	131	NR	795	3	NR	925	0	NR
410	14	NR	540	534	NR	670	113	NR	800	2	NR	930	0	NR
415	26	NR	545	547	NR	675	98	NR	805	2	NR	935	0	NR
420	50	NR	550	561	NR	680	85	NR	810	2	NR	940	0	NR
425	95	NR	555	574	NR	685	73	NR	815	2	NR	945	0	NR
430	168	NR	560	586	NR	690	63	NR	820	1	NR	950	0	NR
435	284	NR	565	596	NR	695	54	NR	825	1	NR	955	0	NR
440	452	NR	570	604	NR	700	46	NR	830	1	NR	960	0	NR
445	705	NR	575	606	NR	705	40	NR	835	1	NR	965	0	NR
450	980	NR	580	603	NR	710	34	NR	840	1	NR	970	0	NR
455	869	NR	585	592	NR	715	29	NR	845	1	NR	975	0	NR
460	531	NR	590	577	NR	720	25	NR	850	1	NR	980	0	NR
465	372	NR	595	554	NR	725	22	NR	855	1	NR	985	0	NR
470	268	NR	600	527	NR	730	19	NR	860	1	NR	990	0	NR
475	174	NR	605	497	NR	735	16	NR	865	0	NR	995	0	NR
480	135	NR	610	462	NR	740	14	NR	870	0	NR	1000	0	NR
485	126	NR	615	428	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP2-2501-321-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.75


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	134	NR	620	390	NR	750	10	NR	880	0	NR
365	0	NR	495	165	NR	625	354	NR	755	9	NR	885	0	NR
370	0	NR	500	218	NR	630	319	NR	760	8	NR	890	0	NR
375	0	NR	505	281	NR	635	285	NR	765	7	NR	895	0	NR
380	0	NR	510	343	NR	640	254	NR	770	6	NR	900	0	NR
385	1	NR	515	400	NR	645	224	NR	775	5	NR	905	0	NR
390	2	NR	520	444	NR	650	197	NR	780	4	NR	910	0	NR
395	4	NR	525	477	NR	655	173	NR	785	4	NR	915	0	NR
400	6	NR	530	501	NR	660	150	NR	790	3	NR	920	0	NR
405	9	NR	535	520	NR	665	131	NR	795	3	NR	925	0	NR
410	14	NR	540	534	NR	670	113	NR	800	2	NR	930	0	NR
415	26	NR	545	547	NR	675	98	NR	805	2	NR	935	0	NR
420	50	NR	550	561	NR	680	85	NR	810	2	NR	940	0	NR
425	95	NR	555	574	NR	685	73	NR	815	2	NR	945	0	NR
430	168	NR	560	586	NR	690	63	NR	820	1	NR	950	0	NR
435	284	NR	565	596	NR	695	54	NR	825	1	NR	955	0	NR
440	452	NR	570	604	NR	700	46	NR	830	1	NR	960	0	NR
445	705	NR	575	606	NR	705	40	NR	835	1	NR	965	0	NR
450	980	NR	580	603	NR	710	34	NR	840	1	NR	970	0	NR
455	869	NR	585	592	NR	715	29	NR	845	1	NR	975	0	NR
460	531	NR	590	577	NR	720	25	NR	850	1	NR	980	0	NR
465	372	NR	595	554	NR	725	22	NR	855	1	NR	985	0	NR
470	268	NR	600	527	NR	730	19	NR	860	1	NR	990	0	NR
475	174	NR	605	497	NR	735	16	NR	865	0	NR	995	0	NR
480	135	NR	610	462	NR	740	14	NR	870	0	NR	1000	0	NR
485	126	NR	615	428	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP2-2501-321-5





TM-30-18

Summary

$R_f = 74.2$
 $R_g = 92.7$
 $CIE R_a = 72.2$
 $R_g = -38.2$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 63	CES51 = 89	CES76 = 51
CES02 = 59	CES27 = 89	CES52 = 89	CES77 = 68
CES03 = 30	CES28 = 81	CES53 = 79	CES78 = 54
CES04 = 69	CES29 = 69	CES54 = 84	CES79 = 80
CES05 = 46	CES30 = 88	CES55 = 83	CES80 = 77
CES06 = 50	CES31 = 72	CES56 = 74	CES81 = 79
CES07 = 38	CES32 = 63	CES57 = 73	CES82 = 91
CES08 = 38	CES33 = 82	CES58 = 74	CES83 = 90
CES09 = 29	CES34 = 70	CES59 = 86	CES84 = 85
CES10 = 72	CES35 = 83	CES60 = 88	CES85 = 78
CES11 = 56	CES36 = 88	CES61 = 82	CES86 = 75
CES12 = 61	CES37 = 78	CES62 = 81	CES87 = 77
CES13 = 41	CES38 = 98	CES63 = 73	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 64	CES89 = 73
CES15 = 70	CES40 = 91	CES65 = 61	CES90 = 80
CES16 = 46	CES41 = 96	CES66 = 56	CES91 = 72
CES17 = 49	CES42 = 80	CES67 = 54	CES92 = 58
CES18 = 55	CES43 = 79	CES68 = 64	CES93 = 75
CES19 = 71	CES44 = 99	CES69 = 73	CES94 = 53
CES20 = 63	CES45 = 87	CES70 = 56	CES95 = 64
CES21 = 85	CES46 = 85	CES71 = 47	CES96 = 76
CES22 = 77	CES47 = 90	CES72 = 82	CES97 = 86
CES23 = 91	CES48 = 80	CES73 = 47	CES98 = 76
CES24 = 90	CES49 = 83	CES74 = 90	CES99 = 62
CES25 = 71	CES50 = 89	CES75 = 50	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)