

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055189

Luminaire Tested: S122R3DRP-S290D935-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1055189  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/25/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122R3DRP-S290D935-X4F0-XX-UDD-F-S  
Description: DEFINE 2, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS  
CORE LIGHT ENGINE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 350.4 lumens  
Efficiency: N/A  
Efficacy: 27.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.64 / 0.81  
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1055189

CATALOG NUMBER: S122R3DRP-S290D935-X4F0-XX-UDD-F-S

### Luminous Intensity Polar Plot



TEST NUMBER: P1055189

CATALOG NUMBER: S122R3DRP-S290D935-X4F0-XX-UDD-F-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5794	5794	5794
5°	5723	5702	5666
10°	5681	5350	5012
15°	5594	4786	4088
20°	5478	4103	3083
25°	5343	3361	2201
30°	5180	2623	1402
35°	5028	1924	937
40°	4857	1298	705
45°	4670	914	501
50°	4474	696	354
55°	4284	482	261
60°	4077	326	212
65°	3779	233	166
70°	3446	188	144
75°	2987	161	110
80°	2368	120	120
85°	1304	152	87

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4670 cd/sqm



TEST NUMBER: P1055189

CATALOG NUMBER: S122R3DRP-S290D935-X4F0-XX-UDD-F-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	28.0	8.0
10°-20°	68.6	19.6
20°-30°	78.4	22.4
30°-40°	66.5	19.0
40°-50°	49.6	14.2
50°-60°	32.0	9.1
60°-70°	17.9	5.1
70°-80°	7.8	2.2
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	175.0	49.9
0°-40°	241.5	68.9
0°-60°	323.1	92.2
0°-90°	350.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	350.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	306	306	306	306	306	
5°	301	305	300	297	298	29
15°	285	278	244	218	208	80
25°	256	226	161	118	105	118
35°	217	164	83	45	40	136
45°	174	103	34	22	19	134
55°	130	49	15	9	8	116
65°	84	18	5	4	4	84
75°	41	4	2	2	2	44
85°	6	0	1	0	0	9
90°	0	0	0	0	0	



TEST NUMBER: P1055189

CATALOG NUMBER: S122R3DRP-S290D935-X4F0-XX-UDD-F-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	305.8	305.8	305.8	305.8	305.8
2.5°	302.4	306.9	303.2	303.2	303.9
5°	300.9	304.7	299.8	296.8	297.9
7.5°	298.7	301.3	291.2	282.2	281.4
10°	295.3	296.4	278.1	264.2	260.5
12.5°	290.4	287.8	262.0	242.5	236.1
15°	285.2	278.1	244.0	218.1	208.4
17.5°	278.8	266.1	224.1	192.6	180.6
20°	271.7	253.7	203.5	166.0	152.9
22.5°	263.8	239.8	182.1	140.9	127.8
25°	255.6	225.6	160.8	117.7	105.3
27.5°	247.0	210.6	139.8	96.7	83.2
30°	236.8	195.2	119.9	76.5	64.1
32.5°	227.5	179.1	101.6	59.2	48.7
35°	217.4	163.8	83.2	45.3	40.5
37.5°	206.9	148.4	67.1	38.2	34.1
40°	196.4	133.0	52.5	32.2	28.5
42.5°	185.5	118.0	40.5	27.0	23.2
45°	174.3	103.4	34.1	22.1	18.7
47.5°	163.0	88.8	28.5	17.6	15.0
50°	151.8	75.0	23.6	13.9	12.0
52.5°	140.9	61.8	18.7	11.2	9.7
55°	129.7	49.1	14.6	9.0	7.9
57.5°	118.4	38.2	11.2	7.5	6.7
60°	107.6	28.9	8.6	6.0	5.6
62.5°	96.3	23.2	6.7	4.9	4.5
65°	84.3	18.0	5.2	4.1	3.7
67.5°	73.5	13.1	4.1	3.4	3.0
70°	62.2	9.0	3.4	3.0	2.6
72.5°	51.3	5.6	2.6	2.2	2.2
75°	40.8	3.7	2.2	1.9	1.5
77.5°	31.1	2.2	1.5	1.5	1.1
80°	21.7	1.5	1.1	1.1	1.1
82.5°	13.5	1.1	0.7	0.7	0.7
85°	6.0	0.4	0.7	0.4	0.4
87.5°	1.1	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055189

CATALOG NUMBER: S122R3DRP-S290D935-X4F0-XX-UDD-F-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.35	15.67	14.72	15.99	16.30	0.66	1.98	1.03	2.29	2.61
	3H	16.82	18.00	17.20	18.33	18.69	1.51	2.69	1.89	3.02	3.38
	4H	17.78	18.87	18.18	19.22	19.60	1.79	2.88	2.19	3.23	3.61
	6H	18.47	19.47	18.88	19.84	20.23	1.97	2.97	2.38	3.34	3.74
	8H	18.66	19.61	19.09	20.00	20.41	2.03	2.98	2.46	3.37	3.78
	12H	18.74	19.65	19.18	20.03	20.46	2.06	2.97	2.49	3.35	3.78
4H	2H	14.14	15.23	14.54	15.58	15.96	1.22	2.31	1.63	2.67	3.05
	3H	16.62	17.52	17.04	17.92	18.33	2.26	3.15	2.67	3.56	3.96
	4H	17.56	18.37	18.00	18.78	19.23	2.63	3.43	3.06	3.85	4.29
	6H	18.32	19.01	18.78	19.46	19.92	2.91	3.60	3.37	4.05	4.51
	8H	18.56	19.21	19.03	19.65	20.12	3.00	3.64	3.47	4.09	4.56
	12H	18.69	19.26	19.18	19.74	20.22	3.04	3.61	3.53	4.09	4.57
8H	4H	17.43	18.08	17.90	18.52	18.99	3.00	3.64	3.47	4.09	4.56
	6H	18.17	18.69	18.67	19.19	19.67	3.34	3.87	3.84	4.36	4.85
	8H	18.41	18.88	18.94	19.40	19.89	3.46	3.93	3.99	4.45	4.94
	12H	18.57	18.98	19.08	19.47	20.05	3.55	3.96	4.06	4.46	5.03
12H	4H	17.39	17.96	17.87	18.44	18.91	3.12	3.68	3.60	4.17	4.64
	6H	18.11	18.58	18.63	19.10	19.59	3.46	3.93	3.98	4.44	4.94
	8H	18.37	18.79	18.89	19.28	19.85	3.62	4.03	4.13	4.53	5.10