

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058477

Luminaire Tested: S122RDRP-H675D927-X4F0-XX-UDD-SVL-S

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1058477  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-59)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDRP-H675D927-X4F0-XX-UDD-SVL-S  
Description: DEFINE 2 SILVER REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 492.0 lumens  
Efficiency: N/A  
Efficacy: 20.9 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.97 / 0.94  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 23.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1058477

CATALOG NUMBER: S122RDRP-H675D927-X4F0-XX-UDD-SVL-S

### Luminous Intensity Polar Plot





TEST NUMBER: P1058477

CATALOG NUMBER: S122RDRP-H675D927-X4F0-XX-UDD-SVL-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46
9	67	56	49	45	66	56	49	44	55	49	44	54	48	44	53	48	44	42
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7525	7525	7525
5°	7261	7387	7485
10°	6768	7008	7317
15°	6167	6497	7015
20°	5483	5895	6472
25°	4750	5178	5868
30°	3976	4440	5276
35°	3136	3679	4645
40°	2247	3009	3806
45°	1315	2375	2946
50°	950	1728	1987
55°	798	1235	1042
60°	638	1000	889
65°	524	886	821
70°	448	852	772
75°	428	913	749
80°	478	1116	797
85°	805	1757	1122

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 2946 cd/sqm



TEST NUMBER: P1058477

CATALOG NUMBER: S122RDRP-H675D927-X4F0-XX-UDD-SVL-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.4	7.6
10°-20°	95.7	19.5
20°-30°	117.7	23.9
30°-40°	104.0	21.1
40°-50°	66.4	13.5
50°-60°	32.4	6.6
60°-70°	19.3	3.9
70°-80°	12.3	2.5
80°-90°	6.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.8	51.0
0°-40°	354.8	72.1
0°-60°	453.6	92.2
0°-90°	492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	408	408	408	408	408	
5°	392	400	399	400	404	36
15°	323	332	340	355	367	90
25°	233	242	254	270	288	107
35°	139	147	163	186	206	86
45°	50	65	91	102	113	42
55°	25	33	38	36	32	22
65°	12	23	20	19	19	12
75°	6	14	13	11	10	7
85°	4	8	8	8	5	3
90°	0	0	0	0	0	



TEST NUMBER: P1058477

CATALOG NUMBER: S122RDRP-H675D927-X4F0-XX-UDD-SVL-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	407.8	407.8	407.8	407.8	407.8
2.5°	401.8	409.3	404.8	404.8	405.6
5°	392.0	400.3	398.8	400.3	404.1
7.5°	378.5	386.8	388.3	394.3	398.8
10°	361.2	369.4	374.0	383.7	390.5
12.5°	343.1	351.4	358.2	371.0	380.7
15°	322.8	331.8	340.1	355.2	367.2
17.5°	301.7	310.8	321.3	336.3	350.6
20°	279.2	287.4	300.2	314.5	329.6
22.5°	257.3	264.9	278.4	291.9	310.0
25°	233.3	241.5	254.3	270.1	288.2
27.5°	209.9	218.2	231.0	249.1	267.9
30°	186.6	194.1	208.4	227.2	247.6
32.5°	162.5	170.1	185.9	206.2	227.2
35°	139.2	146.7	163.3	185.9	206.2
37.5°	115.9	124.2	143.0	164.0	181.3
40°	93.3	103.1	124.9	143.0	158.0
42.5°	70.7	84.3	107.6	122.6	134.7
45°	50.4	64.7	91.0	102.3	112.9
47.5°	38.4	49.7	75.2	83.5	90.3
50°	33.1	40.6	60.2	66.2	69.2
52.5°	28.6	36.1	48.2	50.4	48.9
55°	24.8	33.1	38.4	36.1	32.4
57.5°	21.1	30.8	31.6	27.1	27.8
60°	17.3	27.8	27.1	23.3	24.1
62.5°	14.3	25.6	23.3	21.1	21.1
65°	12.0	22.6	20.3	18.8	18.8
67.5°	9.8	20.3	18.1	16.6	16.6
70°	8.3	18.1	15.8	14.3	14.3
72.5°	7.5	15.8	14.3	12.8	12.8
75°	6.0	13.5	12.8	11.3	10.5
77.5°	5.3	11.3	11.3	10.5	9.0
80°	4.5	9.8	10.5	9.0	7.5
82.5°	4.5	9.0	9.0	8.3	6.0
85°	3.8	7.5	8.3	7.5	5.3
87.5°	2.3	6.8	6.8	6.0	3.8
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058477

CATALOG NUMBER: S122RDRP-H675D927-X4F0-XX-UDD-SVL-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.03	10.31	9.40	10.62	10.94	8.57	9.85	8.93	10.16	10.47
	3H	10.21	11.35	10.59	11.68	12.05	10.13	11.27	10.51	11.60	11.97
	4H	10.64	11.70	11.04	12.05	12.44	10.81	11.88	11.22	12.23	12.61
	6H	10.99	11.96	11.40	12.34	12.73	11.46	12.43	11.87	12.80	13.20
	8H	11.18	12.11	11.61	12.50	12.91	11.74	12.67	12.18	13.06	13.47
	12H	11.40	12.29	11.84	12.67	13.10	12.06	12.95	12.50	13.33	13.76
4H	2H	9.53	10.60	9.94	10.95	11.33	9.16	10.23	9.57	10.58	10.96
	3H	11.19	12.06	11.60	12.47	12.87	10.97	11.84	11.38	12.25	12.65
	4H	11.95	12.73	12.38	13.15	13.59	11.81	12.59	12.24	13.01	13.46
	6H	12.55	13.23	13.01	13.68	14.14	12.66	13.34	13.12	13.79	14.25
	8H	12.85	13.49	13.32	13.93	14.40	13.05	13.68	13.52	14.13	14.60
	12H	13.16	13.73	13.65	14.21	14.68	13.49	14.05	13.97	14.53	15.01
8H	4H	12.37	13.00	12.83	13.45	13.92	12.27	12.90	12.74	13.35	13.82
	6H	13.32	13.84	13.82	14.33	14.82	13.37	13.89	13.87	14.39	14.87
	8H	13.86	14.33	14.38	14.85	15.34	13.95	14.42	14.47	14.93	15.42
	12H	14.43	14.84	14.94	15.34	15.91	14.62	15.03	15.13	15.53	16.10
12H	4H	12.43	13.00	12.92	13.48	13.96	12.35	12.91	12.84	13.40	13.87
	6H	13.50	13.97	14.02	14.48	14.98	13.55	14.02	14.07	14.54	15.03
	8H	14.19	14.60	14.70	15.10	15.67	14.26	14.68	14.78	15.17	15.75