

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058113

Luminaire Tested: S122RDRP-S865D830-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-S865D830-X4F0-XX-UDD-BVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
CORE LIGHT ENGINE
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 527.8 lumens
Efficiency: N/A
Efficacy: 15.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058113

CATALOG NUMBER: S122RDRP-S865D830-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058113

CATALOG NUMBER: S122RDRP-S865D830-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93					93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86					86			
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54					54			
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51					51			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47					47			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10356	10356	10356
5°	10286	10132	10177
10°	10071	9648	9404
15°	9475	8818	8455
20°	8458	7829	7385
25°	7393	6619	6281
30°	6345	5410	5056
35°	5291	4224	3796
40°	4117	3115	2430
45°	2878	2075	1052
50°	1567	1091	376
55°	228	383	267
60°	44	89	173
65°	0	52	105
70°	0	0	65
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2878 cd/sqm



TEST NUMBER: P1058113

CATALOG NUMBER: S122RDRP-S865D830-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	9.8
10°-20°	130.0	24.6
20°-30°	151.5	28.7
30°-40°	121.4	23.0
40°-50°	60.3	11.4
50°-60°	11.9	2.3
60°-70°	1.1	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	333.0	63.1
0°-40°	454.4	86.1
0°-60°	526.6	99.8
0°-90°	527.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	527.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	561	561	561	561	561	
5°	555	555	547	548	549	52
15°	496	486	462	450	443	138
25°	363	345	325	318	308	167
35°	235	211	188	179	168	146
45°	110	97	80	53	40	85
55°	7	14	12	7	8	14
65°	0	0	1	1	2	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058113

CATALOG NUMBER: S122RDRP-S865D830-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	561.2	561.2	561.2	561.2	561.2
2.5°	558.8	561.2	555.3	561.2	562.4
5°	555.3	555.3	547.0	548.2	549.4
7.5°	549.4	547.0	532.7	530.4	528.0
10°	537.5	532.7	514.9	505.5	501.9
12.5°	520.9	513.8	490.0	479.3	473.4
15°	496.0	486.5	461.6	449.7	442.6
17.5°	463.9	455.6	431.9	418.8	411.7
20°	430.7	418.8	398.7	385.6	376.1
22.5°	398.7	383.2	361.9	352.4	342.9
25°	363.1	345.3	325.1	318.0	308.5
27.5°	333.4	310.9	287.1	282.4	274.1
30°	297.8	276.5	253.9	246.8	237.3
32.5°	267.0	243.2	220.7	212.4	204.1
35°	234.9	211.2	187.5	179.2	168.5
37.5°	204.1	181.5	157.8	144.8	135.3
40°	170.9	151.9	129.3	112.7	100.9
42.5°	141.2	124.6	103.2	81.9	70.0
45°	110.3	97.3	79.5	53.4	40.3
47.5°	81.9	72.4	58.1	30.8	21.4
50°	54.6	51.0	38.0	15.4	13.1
52.5°	29.7	32.0	22.5	9.5	10.7
55°	7.1	14.2	11.9	7.1	8.3
57.5°	1.2	2.4	5.9	5.9	5.9
60°	1.2	1.2	2.4	3.6	4.7
62.5°	1.2	0.0	1.2	2.4	3.6
65°	0.0	0.0	1.2	1.2	2.4
67.5°	0.0	0.0	0.0	1.2	1.2
70°	0.0	0.0	0.0	1.2	1.2
72.5°	0.0	0.0	0.0	0.0	1.2
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058113
 CATALOG NUMBER: S122RDRP-S865D830-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00