

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058407

Luminaire Tested: S122RDRP-H485D930-X4F0-XX-UDD-WVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058407
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-19)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H485D930-X4F0-XX-UDD-WVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 526.7 lumens
Efficiency: N/A
Efficacy: 30.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 0.92 / 1.02
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058407

CATALOG NUMBER: S122RDRP-H485D930-X4F0-XX-UDD-WVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058407

CATALOG NUMBER: S122RDRP-H485D930-X4F0-XX-UDD-WVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41
9	64	52	45	40	63	51	44	39	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6399	6399	6399
5°	6363	6270	6311
10°	6251	6033	5981
15°	6023	5708	5592
20°	5575	5292	5172
25°	5116	4779	4689
30°	4671	4259	4212
35°	4230	3769	3683
40°	3765	3286	3112
45°	3244	2824	2492
50°	2678	2377	2093
55°	1937	1972	1882
60°	1609	1690	1712
65°	1375	1471	1567
70°	1133	1311	1430
75°	948	1105	1298
80°	701	882	1169
85°	233	466	1059

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3244 cd/sqm

TEST NUMBER: P1058407

CATALOG NUMBER: S122RDRP-H485D930-X4F0-XX-UDD-WVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.1	6.1
10°-20°	84.4	16.0
20°-30°	109.3	20.7
30°-40°	107.2	20.3
40°-50°	84.4	16.0
50°-60°	55.3	10.5
60°-70°	33.7	6.4
70°-80°	16.8	3.2
80°-90°	3.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	225.7	42.9
0°-40°	332.9	63.2
0°-60°	472.6	89.7
0°-90°	526.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	526.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	347	347	347	347	347	
5°	344	344	338	341	341	32
15°	315	311	299	295	293	88
25°	251	243	235	234	230	116
35°	188	177	167	167	164	117
45°	124	116	108	100	96	96
55°	60	64	61	59	58	57
65°	32	32	34	35	36	31
75°	13	14	16	18	18	14
85°	1	2	2	4	5	2
90°	0	0	0	0	0	



TEST NUMBER: P1058407

CATALOG NUMBER: S122RDRP-H485D930-X4F0-XX-UDD-WVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	346.8	346.8	346.8	346.8	346.8
2.5°	345.7	346.3	342.9	346.3	347.4
5°	343.5	343.5	338.5	340.7	340.7
7.5°	339.6	339.1	331.4	331.4	330.8
10°	333.6	331.4	322.0	320.3	319.2
12.5°	325.8	322.0	310.9	308.2	306.5
15°	315.3	310.9	298.8	294.9	292.7
17.5°	299.9	295.5	285.0	280.5	278.3
20°	283.9	277.2	269.5	265.6	263.4
22.5°	267.3	259.6	252.4	249.6	247.4
25°	251.3	243.0	234.7	233.6	230.3
27.5°	235.8	225.9	217.6	217.0	214.3
30°	219.2	208.8	199.9	200.5	197.7
32.5°	203.8	193.8	183.3	183.9	180.6
35°	187.8	177.3	167.3	166.8	163.5
37.5°	171.2	161.3	151.9	149.7	146.3
40°	156.3	146.3	136.4	132.5	129.2
42.5°	140.3	131.4	122.6	116.5	112.1
45°	124.3	116.5	108.2	100.5	95.5
47.5°	108.8	102.7	95.5	86.2	82.8
50°	93.3	88.9	82.8	74.6	72.9
52.5°	77.3	75.7	71.8	66.3	65.7
55°	60.2	63.5	61.3	59.1	58.5
57.5°	50.8	51.4	53.0	52.5	52.5
60°	43.6	43.6	45.8	46.4	46.4
62.5°	37.0	37.6	39.8	40.9	40.9
65°	31.5	32.0	33.7	35.3	35.9
67.5°	26.0	27.1	28.7	30.4	30.9
70°	21.0	22.1	24.3	26.0	26.5
72.5°	17.1	17.7	19.9	21.5	22.1
75°	13.3	13.8	15.5	17.7	18.2
77.5°	9.4	10.5	12.1	13.8	14.9
80°	6.6	7.2	8.3	10.5	11.0
82.5°	3.9	4.4	5.5	7.2	7.7
85°	1.1	1.7	2.2	3.9	5.0
87.5°	0.0	0.0	0.0	1.1	2.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058407

CATALOG NUMBER: S122RDRP-H485D930-X4F0-XX-UDD-WVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.58	13.97	12.94	14.28	14.60	12.76	14.15	13.12	14.46	14.78
	3H	13.71	14.95	14.09	15.28	15.65	14.21	15.46	14.59	15.79	16.15
	4H	14.06	15.22	14.46	15.57	15.96	14.76	15.92	15.16	16.27	16.65
	6H	14.24	15.32	14.66	15.68	16.08	15.17	16.24	15.58	16.61	17.00
	8H	14.27	15.29	14.70	15.68	16.08	15.29	16.31	15.72	16.70	17.10
	12H	14.26	15.23	14.69	15.61	16.04	15.38	16.35	15.81	16.73	17.16
4H	2H	13.03	14.20	13.43	14.55	14.93	13.18	14.34	13.58	14.69	15.08
	3H	14.37	15.33	14.79	15.73	16.14	14.85	15.81	15.26	16.21	16.62
	4H	14.82	15.68	15.25	16.09	16.54	15.52	16.38	15.95	16.79	17.24
	6H	15.09	15.83	15.55	16.28	16.74	16.05	16.79	16.51	17.24	17.70
	8H	15.13	15.83	15.60	16.27	16.74	16.22	16.91	16.69	17.36	17.83
	12H	15.13	15.74	15.61	16.23	16.70	16.34	16.96	16.82	17.44	17.91
8H	4H	15.03	15.73	15.50	16.17	16.64	15.67	16.36	16.13	16.81	17.28
	6H	15.38	15.95	15.88	16.44	16.92	16.30	16.87	16.80	17.36	17.84
	8H	15.46	15.97	15.98	16.48	16.97	16.53	17.04	17.05	17.55	18.04
	12H	15.47	15.92	15.99	16.42	16.99	16.72	17.17	17.23	17.66	18.23
12H	4H	15.04	15.66	15.53	16.14	16.61	15.65	16.27	16.14	16.75	17.22
	6H	15.40	15.91	15.92	16.43	16.92	16.29	16.80	16.81	17.31	17.81
	8H	15.52	15.97	16.03	16.46	17.03	16.57	17.02	17.08	17.51	18.08