

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058329

Luminaire Tested: S122RDRP-H290D935-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1058329  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDRP-H290D935-X4F0-XX-UDD-BVL-B  
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 162.9 lumens  
Efficiency: N/A  
Efficacy: 13.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1058329

CATALOG NUMBER: S122RDRP-H290D935-X4F0-XX-UDD-BVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1058329

CATALOG NUMBER: S122RDRP-H290D935-X4F0-XX-UDD-BVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93					93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86					86			
3	101	95	89	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54					54			
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51					51			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47					47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3196	3196	3196
5°	3175	3127	3141
10°	3108	2977	2902
15°	2925	2722	2610
20°	2610	2415	2280
25°	2282	2042	1938
30°	1958	1670	1560
35°	1633	1304	1171
40°	1269	961	749
45°	890	639	326
50°	482	336	115
55°	71	119	84
60°	15	26	55
65°	0	17	31
70°	0	0	22
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 890 cd/sqm



TEST NUMBER: P1058329

CATALOG NUMBER: S122RDRP-H290D935-X4F0-XX-UDD-BVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	15.9	9.8
10°-20°	40.1	24.6
20°-30°	46.8	28.7
30°-40°	37.5	23.0
40°-50°	18.6	11.4
50°-60°	3.7	2.3
60°-70°	0.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	102.8	63.1
0°-40°	140.2	86.1
0°-60°	162.5	99.8
0°-90°	162.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	162.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	173	173	173	173	173	
5°	171	171	169	169	170	16
15°	153	150	142	139	137	42
25°	112	107	100	98	95	52
35°	72	65	58	55	52	45
45°	34	30	24	16	12	26
55°	2	4	4	2	3	4
65°	0	0	0	0	1	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058329

CATALOG NUMBER: S122RDRP-H290D935-X4F0-XX-UDD-BVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	173.2	173.2	173.2	173.2	173.2
2.5°	172.5	173.2	171.4	173.2	173.6
5°	171.4	171.4	168.8	169.2	169.6
7.5°	169.6	168.8	164.4	163.7	163.0
10°	165.9	164.4	158.9	156.0	154.9
12.5°	160.8	158.6	151.2	147.9	146.1
15°	153.1	150.1	142.5	138.8	136.6
17.5°	143.2	140.6	133.3	129.3	127.1
20°	132.9	129.3	123.0	119.0	116.1
22.5°	123.0	118.3	111.7	108.8	105.8
25°	112.1	106.6	100.3	98.1	95.2
27.5°	102.9	95.9	88.6	87.2	84.6
30°	91.9	85.3	78.4	76.2	73.2
32.5°	82.4	75.1	68.1	65.6	63.0
35°	72.5	65.2	57.9	55.3	52.0
37.5°	63.0	56.0	48.7	44.7	41.7
40°	52.7	46.9	39.9	34.8	31.1
42.5°	43.6	38.5	31.9	25.3	21.6
45°	34.1	30.0	24.5	16.5	12.5
47.5°	25.3	22.3	17.9	9.5	6.6
50°	16.8	15.7	11.7	4.8	4.0
52.5°	9.2	9.9	7.0	2.9	3.3
55°	2.2	4.4	3.7	2.2	2.6
57.5°	0.4	0.7	1.8	1.8	1.8
60°	0.4	0.4	0.7	1.1	1.5
62.5°	0.4	0.0	0.4	0.7	1.1
65°	0.0	0.0	0.4	0.4	0.7
67.5°	0.0	0.0	0.0	0.4	0.4
70°	0.0	0.0	0.0	0.4	0.4
72.5°	0.0	0.0	0.0	0.0	0.4
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058329  
 CATALOG NUMBER: S122RDRP-H290D935-X4F0-XX-UDD-BVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00