

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1211759

Luminaire Tested: **GKO-PB1F-835-U-T1**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1211759
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1F-835-U-T1
Description: GEKKO WALL PACK 6500LM PACKAGE 80CRI 3500K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (10) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6269.6 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B2 - U0 - G2

Input Watts (W): 54.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 5.7%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1211759
 CATALOG NUMBER: GKO-PB1F-835-U-T1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6.9 fc
 Type I - Short - N/A

REPORT NUMBER: P1211759
CATALOG NUMBER: GKO-PB1F-835-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1211759

CATALOG NUMBER: GKO-PB1F-835-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3134.8	0.0	3134.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3134.8	0.0	3134.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	6269.6	0.0	6269.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.2	2.4
10°-20°	449.6	7.2
20°-30°	747.6	11.9
30°-40°	993.2	15.8
40°-50°	1119.7	17.9
50°-60°	1151.4	18.4
60°-70°	1088.1	17.4
70°-80°	532.6	8.5
80°-90°	38.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6269.6	100.0
0°-180°	6269.6	100.0

Coefficient of Utilization



REPORT NUMBER: P1211759


CATALOG NUMBER: GKO-PB1F-835-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	673.2	10.7			
FM	(30°-60°)	1632.2	26.0			
FH	(60°-80°)	810.4	12.9			G1/1800
FVH	(80°-90°)	19.0	0.3			G1/100
BL	(0°-30°)	673.2	10.7	B2/1000		
BM	(30°-60°)	1632.2	26.0	B2/2500		
BH	(60°-80°)	810.4	12.9	B2/1000		G2/1000
BVH	(80°-90°)	19.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type I Short





REPORT NUMBER: P1211759

CATALOG NUMBER: GKO-PB1F-835-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1555.7	1555.7	1555.7	1555.7	1555.7	1555.7	1555.7	1555.7	1555.7	1555.7	1555.7
2.5°	1556.9	1559.2	1554.6	1554.6	1556.9	1558.1	1558.1	1559.2	1556.9	1556.9	1555.7
5°	1556.9	1558.1	1555.7	1555.7	1558.1	1561.5	1560.4	1562.7	1562.7	1561.5	1561.5
7.5°	1555.7	1558.1	1555.7	1556.9	1560.4	1567.3	1567.3	1567.3	1569.6	1571.9	1571.9
10°	1554.6	1556.9	1558.1	1559.2	1563.8	1574.2	1576.5	1577.7	1581.2	1584.6	1584.6
12.5°	1548.8	1551.1	1554.6	1559.2	1567.3	1581.2	1585.8	1589.3	1595.0	1598.5	1600.8
15°	1540.7	1541.9	1550.0	1559.2	1571.9	1589.3	1598.5	1604.3	1612.4	1617.0	1620.5
17.5°	1529.2	1530.3	1543.0	1556.9	1575.4	1599.7	1614.7	1623.9	1632.0	1639.0	1643.6
20°	1514.1	1517.6	1532.6	1554.6	1581.2	1610.1	1632.0	1648.2	1656.3	1663.2	1670.2
22.5°	1495.6	1499.1	1517.6	1548.8	1587.0	1623.9	1652.8	1673.6	1684.0	1693.3	1701.4
25°	1467.9	1472.5	1494.5	1534.9	1589.3	1639.0	1675.9	1702.5	1711.8	1723.3	1730.3
27.5°	1425.1	1428.6	1455.2	1507.2	1582.3	1655.1	1702.5	1733.7	1744.1	1756.9	1763.8
30°	1358.1	1365.0	1397.4	1462.1	1565.0	1667.9	1733.7	1764.9	1777.7	1790.4	1799.6
32.5°	1271.4	1281.8	1317.6	1400.9	1531.5	1672.5	1767.3	1803.1	1819.3	1833.1	1844.7
35°	1163.9	1174.3	1217.1	1322.3	1478.3	1663.2	1800.8	1847.0	1866.7	1885.2	1899.0
37.5°	1041.4	1050.6	1102.7	1222.9	1402.0	1634.3	1827.4	1895.6	1922.1	1946.4	1964.9
40°	917.7	928.1	984.8	1113.1	1309.6	1578.9	1838.9	1948.7	1982.2	2013.5	2036.6
42.5°	783.7	796.4	859.9	996.3	1202.1	1502.6	1829.7	2000.7	2042.3	2085.1	2119.8
45°	664.6	666.9	736.3	868.0	1084.2	1404.3	1797.3	2050.4	2107.1	2167.2	2216.9
47.5°	550.2	554.8	614.9	745.5	961.6	1293.4	1738.4	2089.7	2179.9	2257.3	2330.1
50°	448.5	454.2	508.6	625.3	839.1	1172.0	1658.6	2112.9	2242.3	2347.5	2449.2
52.5°	365.2	372.2	417.3	520.1	715.5	1044.9	1560.4	2116.3	2298.9	2437.6	2572.9
55°	304.0	308.6	343.3	425.3	596.4	913.1	1448.3	2099.0	2335.9	2518.5	2698.9
57.5°	256.6	261.2	285.5	350.2	488.9	777.9	1311.9	2058.5	2355.6	2589.1	2826.0
60°	223.1	226.5	243.9	290.1	402.2	650.7	1165.1	1986.9	2349.8	2633.0	2931.2
62.5°	198.8	200.0	215.0	247.3	331.7	530.5	999.8	1879.4	2302.4	2638.8	3002.8
65°	176.8	178.0	187.2	210.4	272.8	426.5	827.6	1731.4	2212.3	2598.3	3013.2
67.5°	143.3	145.6	159.5	176.8	224.2	337.5	651.9	1537.3	2071.2	2493.1	2954.3
70°	114.4	115.6	129.5	149.1	182.6	265.8	500.5	1276.0	1850.5	2322.1	2801.7
72.5°	85.5	87.8	100.6	120.2	149.1	205.7	361.8	965.1	1479.5	1958.0	2440.0
75°	68.2	69.3	74.0	92.5	115.6	156.0	243.9	584.8	891.1	1211.3	1495.6
77.5°	57.8	58.9	58.9	71.7	85.5	105.2	129.5	232.3	376.8	536.3	710.8
80°	47.4	49.7	45.1	53.2	61.3	61.3	60.1	111.0	178.0	252.0	330.6
82.5°	34.7	37.0	34.7	37.0	37.0	33.5	31.2	41.6	56.6	77.4	84.4
85°	24.3	25.4	27.7	25.4	24.3	19.6	15.0	11.6	6.9	8.1	11.6
87.5°	16.2	19.6	23.1	22.0	18.5	15.0	10.4	6.9	3.5	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1211759
 CATALOG NUMBER: GKO-PB1F-835-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1555.7	1555.7	1555.7
2.5°	1556.9	1555.7	1554.6
5°	1562.7	1561.5	1560.4
7.5°	1570.8	1570.8	1570.8
10°	1583.5	1585.8	1585.8
12.5°	1599.7	1602.0	1602.0
15°	1619.3	1620.5	1622.8
17.5°	1643.6	1644.7	1644.7
20°	1672.5	1671.3	1673.6
22.5°	1701.4	1701.4	1701.4
25°	1731.4	1731.4	1731.4
27.5°	1766.1	1766.1	1763.8
30°	1804.2	1804.2	1804.2
32.5°	1850.5	1851.6	1852.8
35°	1909.4	1911.7	1915.2
37.5°	1976.5	1982.2	1985.7
40°	2056.2	2058.5	2064.3
42.5°	2145.2	2152.2	2153.3
45°	2256.2	2267.7	2272.4
47.5°	2386.8	2403.0	2411.1
50°	2532.4	2550.9	2562.5
52.5°	2690.8	2720.8	2734.7
55°	2859.5	2911.5	2926.6
57.5°	3050.2	3120.7	3141.5
60°	3237.5	3336.9	3370.4
62.5°	3397.0	3536.8	3578.4
65°	3509.1	3677.8	3739.1
67.5°	3532.2	3732.2	3805.0
70°	3393.5	3598.1	3682.5
72.5°	2950.8	3135.8	3240.9
75°	1743.0	1875.9	1843.5
77.5°	875.0	913.1	918.9
80°	383.7	406.9	416.1
82.5°	94.8	97.1	109.8
85°	12.7	15.0	13.9
87.5°	4.6	4.6	5.8
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-3

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-835-U-T4W

Data in this report applies to families of products including GKO-PB1C


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-835-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3422
 CIE u' : 0.2372
 CIE v' : 0.5144
 Duv: 0.0012
 CIE x: 0.4111
 CIE y: 0.3962
 CIE z: 0.1928
 Peak Wavelength (nm): 598
 Dominant Wavelength (nm): 580
 Purity: 42.28884
 R_f: 83.9
 R_g: 95.8

CRI (Ra): 81.5
 R1: 79.2
 R2: 88.7
 R3: 96.3
 R4: 80.3
 R5: 79.7
 R6: 85.6
 R7: 83.5
 R8: 58.4
 R9: -1.4
 R10: 74.4
 R11: 79.7
 R12: 66.0
 R13: 81.3
 R14: 98.3
 R15: 71.2



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2511-595-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	278	NR	620	878	NR	750	23	NR	880	1	NR
365	0	NR	495	338	NR	625	823	NR	755	20	NR	885	0	NR
370	0	NR	500	398	NR	630	763	NR	760	17	NR	890	0	NR
375	0	NR	505	448	NR	635	697	NR	765	14	NR	895	0	NR
380	0	NR	510	490	NR	640	633	NR	770	12	NR	900	0	NR
385	1	NR	515	527	NR	645	568	NR	775	10	NR	905	0	NR
390	2	NR	520	550	NR	650	508	NR	780	9	NR	910	0	NR
395	3	NR	525	571	NR	655	450	NR	785	7	NR	915	0	NR
400	5	NR	530	589	NR	660	395	NR	790	6	NR	920	0	NR
405	8	NR	535	610	NR	665	345	NR	795	5	NR	925	0	NR
410	13	NR	540	631	NR	670	299	NR	800	5	NR	930	0	NR
415	21	NR	545	656	NR	675	259	NR	805	4	NR	935	0	NR
420	37	NR	550	685	NR	680	223	NR	810	4	NR	940	0	NR
425	65	NR	555	717	NR	685	191	NR	815	3	NR	945	0	NR
430	114	NR	560	758	NR	690	164	NR	820	3	NR	950	0	NR
435	198	NR	565	799	NR	695	139	NR	825	2	NR	955	0	NR
440	359	NR	570	841	NR	700	118	NR	830	2	NR	960	0	NR
445	663	NR	575	883	NR	705	101	NR	835	2	NR	965	0	NR
450	782	NR	580	924	NR	710	86	NR	840	1	NR	970	0	NR
455	533	NR	585	954	NR	715	73	NR	845	1	NR	975	0	NR
460	398	NR	590	982	NR	720	62	NR	850	1	NR	980	0	NR
465	341	NR	595	999	NR	725	52	NR	855	1	NR	985	0	NR
470	244	NR	600	996	NR	730	44	NR	860	1	NR	990	0	NR
475	204	NR	605	984	NR	735	37	NR	865	1	NR	995	0	NR
480	214	NR	610	960	NR	740	32	NR	870	1	NR	1000	0	NR
485	236	NR	615	923	NR	745	27	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.48

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	278	NR	620	878	NR	750	23	NR	880	1	NR
365	0	NR	495	338	NR	625	823	NR	755	20	NR	885	0	NR
370	0	NR	500	398	NR	630	763	NR	760	17	NR	890	0	NR
375	0	NR	505	448	NR	635	697	NR	765	14	NR	895	0	NR
380	0	NR	510	490	NR	640	633	NR	770	12	NR	900	0	NR
385	1	NR	515	527	NR	645	568	NR	775	10	NR	905	0	NR
390	2	NR	520	550	NR	650	508	NR	780	9	NR	910	0	NR
395	3	NR	525	571	NR	655	450	NR	785	7	NR	915	0	NR
400	5	NR	530	589	NR	660	395	NR	790	6	NR	920	0	NR
405	8	NR	535	610	NR	665	345	NR	795	5	NR	925	0	NR
410	13	NR	540	631	NR	670	299	NR	800	5	NR	930	0	NR
415	21	NR	545	656	NR	675	259	NR	805	4	NR	935	0	NR
420	37	NR	550	685	NR	680	223	NR	810	4	NR	940	0	NR
425	65	NR	555	717	NR	685	191	NR	815	3	NR	945	0	NR
430	114	NR	560	758	NR	690	164	NR	820	3	NR	950	0	NR
435	198	NR	565	799	NR	695	139	NR	825	2	NR	955	0	NR
440	359	NR	570	841	NR	700	118	NR	830	2	NR	960	0	NR
445	663	NR	575	883	NR	705	101	NR	835	2	NR	965	0	NR
450	782	NR	580	924	NR	710	86	NR	840	1	NR	970	0	NR
455	533	NR	585	954	NR	715	73	NR	845	1	NR	975	0	NR
460	398	NR	590	982	NR	720	62	NR	850	1	NR	980	0	NR
465	341	NR	595	999	NR	725	52	NR	855	1	NR	985	0	NR
470	244	NR	600	996	NR	730	44	NR	860	1	NR	990	0	NR
475	204	NR	605	984	NR	735	37	NR	865	1	NR	995	0	NR
480	214	NR	610	960	NR	740	32	NR	870	1	NR	1000	0	NR
485	236	NR	615	923	NR	745	27	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-3

Melanopic Flux vs. Wavelength








Melanopic Lumens: NR

M/P: 2.92


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	278	NR	620	878	NR	750	23	NR	880	1	NR
365	0	NR	495	338	NR	625	823	NR	755	20	NR	885	0	NR
370	0	NR	500	398	NR	630	763	NR	760	17	NR	890	0	NR
375	0	NR	505	448	NR	635	697	NR	765	14	NR	895	0	NR
380	0	NR	510	490	NR	640	633	NR	770	12	NR	900	0	NR
385	1	NR	515	527	NR	645	568	NR	775	10	NR	905	0	NR
390	2	NR	520	550	NR	650	508	NR	780	9	NR	910	0	NR
395	3	NR	525	571	NR	655	450	NR	785	7	NR	915	0	NR
400	5	NR	530	589	NR	660	395	NR	790	6	NR	920	0	NR
405	8	NR	535	610	NR	665	345	NR	795	5	NR	925	0	NR
410	13	NR	540	631	NR	670	299	NR	800	5	NR	930	0	NR
415	21	NR	545	656	NR	675	259	NR	805	4	NR	935	0	NR
420	37	NR	550	685	NR	680	223	NR	810	4	NR	940	0	NR
425	65	NR	555	717	NR	685	191	NR	815	3	NR	945	0	NR
430	114	NR	560	758	NR	690	164	NR	820	3	NR	950	0	NR
435	198	NR	565	799	NR	695	139	NR	825	2	NR	955	0	NR
440	359	NR	570	841	NR	700	118	NR	830	2	NR	960	0	NR
445	663	NR	575	883	NR	705	101	NR	835	2	NR	965	0	NR
450	782	NR	580	924	NR	710	86	NR	840	1	NR	970	0	NR
455	533	NR	585	954	NR	715	73	NR	845	1	NR	975	0	NR
460	398	NR	590	982	NR	720	62	NR	850	1	NR	980	0	NR
465	341	NR	595	999	NR	725	52	NR	855	1	NR	985	0	NR
470	244	NR	600	996	NR	730	44	NR	860	1	NR	990	0	NR
475	204	NR	605	984	NR	735	37	NR	865	1	NR	995	0	NR
480	214	NR	610	960	NR	740	32	NR	870	1	NR	1000	0	NR
485	236	NR	615	923	NR	745	27	NR	875	1	NR			

REPORT NUMBER: SP1-2511-595-3




TM-30-18
Summary
 $R_f = 83.9$
 $R_g = 95.8$
 CIE $R_a = 81.5$
 $R_g = -1.4$

Color Vector Graphics


Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 81	CES51 = 95	CES76 = 76
CES02 = 62	CES27 = 94	CES52 = 94	CES77 = 84
CES03 = 31	CES28 = 92	CES53 = 89	CES78 = 75
CES04 = 70	CES29 = 84	CES54 = 91	CES79 = 91
CES05 = 49	CES30 = 94	CES55 = 90	CES80 = 89
CES06 = 51	CES31 = 86	CES56 = 85	CES81 = 76
CES07 = 41	CES32 = 80	CES57 = 85	CES82 = 95
CES08 = 40	CES33 = 90	CES58 = 86	CES83 = 95
CES09 = 29	CES34 = 87	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 93	CES60 = 92	CES85 = 78
CES11 = 58	CES36 = 87	CES61 = 88	CES86 = 70
CES12 = 64	CES37 = 93	CES62 = 91	CES87 = 83
CES13 = 43	CES38 = 98	CES63 = 86	CES88 = 87
CES14 = 74	CES39 = 98	CES64 = 81	CES89 = 75
CES15 = 71	CES40 = 94	CES65 = 77	CES90 = 88
CES16 = 47	CES41 = 97	CES66 = 78	CES91 = 77
CES17 = 50	CES42 = 94	CES67 = 77	CES92 = 63
CES18 = 56	CES43 = 89	CES68 = 80	CES93 = 78
CES19 = 72	CES44 = 99	CES69 = 85	CES94 = 60
CES20 = 66	CES45 = 93	CES70 = 76	CES95 = 73
CES21 = 86	CES46 = 89	CES71 = 73	CES96 = 83
CES22 = 78	CES47 = 93	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 84	CES73 = 70	CES98 = 84
CES24 = 91	CES49 = 89	CES74 = 94	CES99 = 74
CES25 = 72	CES50 = 94	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)