

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058580

Luminaire Tested: S122RDRP-H865D935-X4F0-XX-UDD-WVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-55)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H865D935-X4F0-XX-UDD-WVL-W
Description: DEFINE 2 WHITE REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1598.2 lumens
Efficiency: N/A
Efficacy: 51.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 1.05 / 1.05
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058580

CATALOG NUMBER: S122RDRP-H865D935-X4F0-XX-UDD-WVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1058580

CATALOG NUMBER: S122RDRP-H865D935-X4F0-XX-UDD-WVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	68	67
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59
5	81	70	62	56	80	69	62	56	67	60	55	65	59	55	63	58	54	52
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47
7	71	59	51	46	69	58	51	45	57	50	45	55	49	45	54	49	44	43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36
10	59	47	40	35	58	46	40	35	46	39	35	45	39	35	44	38	34	33

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18091	18091	18091
5°	17534	17769	18101
10°	16652	17085	17757
15°	15586	16171	17279
20°	14407	15152	16291
25°	13092	13865	15282
30°	11702	12533	14263
35°	10258	11232	13250
40°	8583	10030	11960
45°	6876	8886	10454
50°	5902	7656	8776
55°	5392	6511	6476
60°	4901	5757	5643
65°	4467	5157	4925
70°	4095	4721	4381
75°	3836	4356	3836
80°	3581	4027	3358
85°	3578	4234	2901

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10454 cd/sqm



TEST NUMBER: P1058580

CATALOG NUMBER: S122RDRP-H865D935-X4F0-XX-UDD-WVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	5.7
10°-20°	239.6	15.0
20°-30°	316.0	19.8
30°-40°	318.2	19.9
40°-50°	259.0	16.2
50°-60°	176.6	11.0
60°-70°	114.6	7.2
70°-80°	63.1	3.9
80°-90°	20.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.1	40.4
0°-40°	964.3	60.3
0°-60°	1399.9	87.6
0°-90°	1598.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1598.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	980	980	980	980	980	
5°	947	965	959	968	977	89
15°	816	837	846	881	904	229
25°	643	664	681	712	751	295
35°	455	479	499	542	588	283
45°	264	296	340	370	401	208
55°	168	184	202	204	201	150
65°	102	121	118	112	113	102
75°	54	66	61	55	54	57
85°	17	22	20	16	14	18
90°	0	0	0	0	0	



TEST NUMBER: P1058580

CATALOG NUMBER: S122RDRP-H865D935-X4F0-XX-UDD-WVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	980.4	980.4	980.4	980.4	980.4
2.5°	967.7	983.5	973.0	974.0	976.2
5°	946.6	964.6	959.3	967.7	977.2
7.5°	920.3	938.2	940.3	953.0	964.6
10°	888.7	908.7	911.8	930.8	947.7
12.5°	853.9	876.0	880.2	907.6	929.8
15°	815.9	837.0	846.5	881.3	904.5
17.5°	775.9	795.9	810.6	842.3	868.6
20°	733.7	752.7	771.6	800.1	829.6
22.5°	688.4	709.4	727.4	755.8	789.6
25°	643.0	664.1	681.0	711.6	750.6
27.5°	596.7	617.7	634.6	667.3	709.4
30°	549.2	571.4	588.2	625.1	669.4
32.5°	502.8	525.0	543.9	582.9	629.3
35°	455.4	478.6	498.6	541.8	588.2
37.5°	404.8	431.2	456.5	499.7	545.0
40°	356.3	385.8	416.4	456.5	496.5
42.5°	307.8	340.5	378.4	412.2	449.1
45°	263.5	296.2	340.5	370.0	400.6
47.5°	228.8	256.2	303.6	327.8	355.3
50°	205.6	224.5	266.7	285.7	305.7
52.5°	186.6	202.4	231.9	244.6	255.1
55°	167.6	184.5	202.4	203.5	201.3
57.5°	148.6	167.6	177.1	169.7	173.9
60°	132.8	151.8	156.0	148.6	152.9
62.5°	116.0	137.0	137.0	129.7	131.8
65°	102.3	121.2	118.1	111.7	112.8
67.5°	88.5	107.5	102.3	95.9	95.9
70°	75.9	93.8	87.5	81.2	81.2
72.5°	64.3	79.1	74.8	67.5	66.4
75°	53.8	66.4	61.1	54.8	53.8
77.5°	43.2	53.8	49.5	44.3	42.2
80°	33.7	43.2	37.9	33.7	31.6
82.5°	25.3	32.7	28.5	24.2	22.1
85°	16.9	22.1	20.0	15.8	13.7
87.5°	8.4	14.8	12.6	10.5	8.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058580
 CATALOG NUMBER: S122RDRP-H865D935-X4F0-XX-UDD-WVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.78	18.22	17.14	18.53	18.84	17.02	18.46	17.39	18.78	19.09
	3H	18.31	19.59	18.68	19.92	20.28	18.38	19.67	18.76	20.00	20.36
	4H	18.87	20.07	19.27	20.42	20.80	18.86	20.07	19.27	20.42	20.80
	6H	19.29	20.40	19.71	20.77	21.16	19.21	20.32	19.63	20.69	21.09
	8H	19.44	20.50	19.87	20.89	21.29	19.32	20.38	19.75	20.77	21.17
	12H	19.56	20.57	19.99	20.95	21.38	19.39	20.40	19.82	20.78	21.21
4H	2H	17.35	18.56	17.75	18.90	19.29	17.55	18.75	17.95	19.10	19.48
	3H	19.15	20.15	19.57	20.55	20.96	19.12	20.12	19.54	20.52	20.93
	4H	19.90	20.79	20.33	21.21	21.65	19.72	20.62	20.15	21.03	21.47
	6H	20.48	21.26	20.94	21.71	22.17	20.19	20.97	20.65	21.41	21.87
	8H	20.69	21.42	21.16	21.87	22.34	20.34	21.07	20.80	21.51	21.98
	12H	20.86	21.51	21.34	21.99	22.46	20.44	21.09	20.93	21.57	22.05
8H	4H	20.16	20.89	20.63	21.34	21.80	20.01	20.74	20.47	21.18	21.65
	6H	20.92	21.52	21.41	22.01	22.49	20.60	21.20	21.10	21.69	22.17
	8H	21.24	21.78	21.76	22.29	22.78	20.82	21.36	21.34	21.87	22.36
	12H	21.52	22.00	22.03	22.49	23.06	21.00	21.48	21.51	21.97	22.54
12H	4H	20.17	20.82	20.66	21.30	21.78	20.04	20.69	20.53	21.17	21.64
	6H	20.96	21.50	21.48	22.01	22.50	20.67	21.21	21.18	21.72	22.21
	8H	21.36	21.84	21.87	22.33	22.90	20.95	21.43	21.46	21.92	22.49