

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1212039

Luminaire Tested: **GKO-PB2C-835-U-T1**

Issue Date: 11/5/2025

Test Information

Test Method: LM-79-08
Report Number: P1212039
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2C-835-U-T1
Description: GEKKO WALL PACK 8000LM PACKAGE 80CRI 3500K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (20) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7808.3 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B3 - U0 - G3

Input Watts (W): 58.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 5%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1212039
 CATALOG NUMBER: GKO-PB2C-835-U-T1

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 8.6 fc
 Type I - Short - N/A

REPORT NUMBER: P1212039
CATALOG NUMBER: GKO-PB2C-835-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1212039

CATALOG NUMBER: GKO-PB2C-835-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3904.2	0.0	3904.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3904.2	0.0	3904.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	7808.3	0.0	7808.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	2.4
10°-20°	560.0	7.2
20°-30°	931.1	11.9
30°-40°	1236.9	15.8
40°-50°	1394.5	17.9
50°-60°	1434.0	18.4
60°-70°	1355.1	17.4
70°-80°	663.4	8.5
80°-90°	47.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7808.3	100.0
0°-180°	7808.3	100.0

Coefficient of Utilization



REPORT NUMBER: P1212039


CATALOG NUMBER: GKO-PB2C-835-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	838.5	10.7			
FM	(30°-60°)	2032.7	26.0			
FH	(60°-80°)	1009.2	12.9			G1/1800
FVH	(80°-90°)	23.7	0.3			G1/100
BL	(0°-30°)	838.5	10.7	B2/1000		
BM	(30°-60°)	2032.7	26.0	B2/2500		
BH	(60°-80°)	1009.2	12.9	B3/2500		G3/2500
BVH	(80°-90°)	23.7	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type I Short



REPORT NUMBER: P1212039

CATALOG NUMBER: GKO-PB2C-835-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1937.6	1937.6	1937.6	1937.6	1937.6	1937.6	1937.6	1937.6	1937.6	1937.6	1937.6
2.5°	1939.0	1941.9	1936.1	1936.1	1939.0	1940.4	1940.4	1941.9	1939.0	1939.0	1937.6
5°	1939.0	1940.4	1937.6	1937.6	1940.4	1944.8	1943.3	1946.2	1946.2	1944.8	1944.8
7.5°	1937.6	1940.4	1937.6	1939.0	1943.3	1952.0	1952.0	1952.0	1954.8	1957.7	1957.7
10°	1936.1	1939.0	1940.4	1941.9	1947.6	1960.6	1963.5	1964.9	1969.2	1973.6	1973.6
12.5°	1928.9	1931.8	1936.1	1941.9	1952.0	1969.2	1975.0	1979.3	1986.5	1990.8	1993.7
15°	1918.9	1920.3	1930.4	1941.9	1957.7	1979.3	1990.8	1998.0	2008.1	2013.9	2018.2
17.5°	1904.5	1905.9	1921.7	1939.0	1962.0	1992.3	2011.0	2022.5	2032.6	2041.2	2047.0
20°	1885.7	1890.1	1908.8	1936.1	1969.2	2005.2	2032.6	2052.7	2062.8	2071.4	2080.1
22.5°	1862.7	1867.0	1890.1	1928.9	1976.4	2022.5	2058.5	2084.4	2097.3	2108.9	2118.9
25°	1828.2	1833.9	1861.3	1911.7	1979.3	2041.2	2087.3	2120.4	2131.9	2146.3	2154.9
27.5°	1774.9	1779.2	1812.3	1877.1	1970.7	2061.4	2120.4	2159.2	2172.2	2188.0	2196.7
30°	1691.4	1700.0	1740.4	1821.0	1949.1	2077.2	2159.2	2198.1	2213.9	2229.8	2241.3
32.5°	1583.4	1596.4	1641.0	1744.7	1907.3	2083.0	2201.0	2245.6	2265.8	2283.0	2297.4
35°	1449.6	1462.5	1515.8	1646.8	1841.1	2071.4	2242.7	2300.3	2324.8	2347.8	2365.1
37.5°	1297.0	1308.5	1373.3	1523.0	1746.1	2035.4	2275.8	2360.8	2393.9	2424.1	2447.1
40°	1143.0	1155.9	1226.5	1386.2	1631.0	1966.4	2290.2	2427.0	2468.7	2507.6	2536.4
42.5°	976.0	991.8	1071.0	1240.8	1497.1	1871.3	2278.7	2491.8	2543.6	2596.9	2640.0
45°	827.7	830.6	917.0	1081.1	1350.2	1749.0	2238.4	2553.7	2624.2	2699.1	2761.0
47.5°	685.2	691.0	765.8	928.5	1197.7	1610.8	2165.0	2602.6	2714.9	2811.3	2902.0
50°	558.5	565.7	633.4	778.8	1045.1	1459.7	2065.7	2631.4	2792.6	2923.6	3050.3
52.5°	454.9	463.5	519.7	647.8	891.0	1301.3	1943.3	2635.7	2863.2	3035.9	3204.3
55°	378.6	384.3	427.5	529.7	742.8	1137.2	1803.7	2614.1	2909.2	3136.7	3361.2
57.5°	319.6	325.3	355.6	436.2	608.9	968.8	1633.8	2563.7	2933.7	3224.5	3519.6
60°	277.8	282.1	303.7	361.3	500.9	810.4	1451.0	2474.5	2926.5	3279.2	3650.6
62.5°	247.6	249.0	267.7	308.1	413.1	660.7	1245.2	2340.6	2867.5	3286.4	3739.8
65°	220.2	221.7	233.2	262.0	339.7	531.2	1030.7	2156.4	2755.2	3236.0	3752.8
67.5°	178.5	181.4	198.7	220.2	279.3	420.3	811.9	1914.5	2579.6	3105.0	3679.4
70°	142.5	143.9	161.2	185.7	227.4	331.1	623.3	1589.2	2304.6	2892.0	3489.3
72.5°	106.5	109.4	125.2	149.7	185.7	256.2	450.6	1202.0	1842.6	2438.5	3038.8
75°	84.9	86.4	92.1	115.2	143.9	194.3	303.7	728.4	1109.9	1508.6	1862.7
77.5°	72.0	73.4	73.4	89.2	106.5	131.0	161.2	289.3	469.3	667.9	885.3
80°	59.0	61.9	56.1	66.2	76.3	76.3	74.9	138.2	221.7	313.8	411.7
82.5°	43.2	46.1	43.2	46.1	46.1	41.7	38.9	51.8	70.5	96.4	105.1
85°	30.2	31.7	34.5	31.7	30.2	24.5	18.7	14.4	8.6	10.1	14.4
87.5°	20.2	24.5	28.8	27.4	23.0	18.7	13.0	8.6	4.3	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1212039
 CATALOG NUMBER: GKO-PB2C-835-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1937.6	1937.6	1937.6
2.5°	1939.0	1937.6	1936.1
5°	1946.2	1944.8	1943.3
7.5°	1956.3	1956.3	1956.3
10°	1972.1	1975.0	1975.0
12.5°	1992.3	1995.1	1995.1
15°	2016.7	2018.2	2021.1
17.5°	2047.0	2048.4	2048.4
20°	2083.0	2081.5	2084.4
22.5°	2118.9	2118.9	2118.9
25°	2156.4	2156.4	2156.4
27.5°	2199.6	2199.6	2196.7
30°	2247.1	2247.1	2247.1
32.5°	2304.6	2306.1	2307.5
35°	2378.1	2380.9	2385.2
37.5°	2461.5	2468.7	2473.1
40°	2560.9	2563.7	2570.9
42.5°	2671.7	2680.3	2681.8
45°	2809.9	2824.3	2830.1
47.5°	2972.6	2992.7	3002.8
50°	3153.9	3177.0	3191.4
52.5°	3351.2	3388.6	3405.9
55°	3561.3	3626.1	3644.8
57.5°	3798.8	3886.6	3912.6
60°	4032.0	4155.8	4197.6
62.5°	4230.7	4404.9	4456.7
65°	4370.3	4580.5	4656.8
67.5°	4399.1	4648.1	4738.8
70°	4226.4	4481.2	4586.2
72.5°	3675.0	3905.4	4036.4
75°	2170.8	2336.3	2296.0
77.5°	1089.7	1137.2	1144.4
80°	477.9	506.7	518.2
82.5°	118.0	120.9	136.8
85°	15.8	18.7	17.3
87.5°	5.8	5.8	7.2
90°	0.0	0.0	0.0

(END OF REPORT)