

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058455

Luminaire Tested: S122RDRP-H675D840-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H675D840-X4F0-XX-UDD-BVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 426.1 lumens
Efficiency: N/A
Efficacy: 18.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058455

CATALOG NUMBER: S122RDRP-H675D840-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058455

CATALOG NUMBER: S122RDRP-H675D840-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	101	95	89	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8361	8361	8361
5°	8304	8180	8215
10°	8132	7791	7592
15°	7649	7118	6826
20°	6828	6321	5964
25°	5968	5345	5072
30°	5122	4368	4082
35°	4273	3410	3064
40°	3322	2515	1961
45°	2325	1675	851
50°	1266	881	301
55°	183	309	216
60°	37	70	140
65°	0	44	83
70°	0	0	54
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2325 cd/sqm



TEST NUMBER: P1058455

CATALOG NUMBER: S122RDRP-H675D840-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	9.8
10°-20°	104.9	24.6
20°-30°	122.3	28.7
30°-40°	98.0	23.0
40°-50°	48.7	11.4
50°-60°	9.6	2.3
60°-70°	0.9	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.8	63.1
0°-40°	366.9	86.1
0°-60°	425.2	99.8
0°-90°	426.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	426.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	453	453	453	453	453	
5°	448	448	442	443	444	42
15°	400	393	373	363	357	111
25°	293	279	262	257	249	135
35°	190	170	151	145	136	118
45°	89	79	64	43	33	69
55°	6	12	10	6	7	12
65°	0	0	1	1	2	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1058455

CATALOG NUMBER: S122RDRP-H675D840-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	453.1	453.1	453.1	453.1	453.1
2.5°	451.2	453.1	448.3	453.1	454.1
5°	448.3	448.3	441.6	442.6	443.5
7.5°	443.5	441.6	430.1	428.2	426.3
10°	434.0	430.1	415.8	408.1	405.2
12.5°	420.5	414.8	395.6	387.0	382.2
15°	400.4	392.8	372.6	363.1	357.3
17.5°	374.6	367.9	348.7	338.2	332.4
20°	347.7	338.2	321.9	311.3	303.7
22.5°	321.9	309.4	292.2	284.5	276.9
25°	293.1	278.8	262.5	256.7	249.1
27.5°	269.2	251.0	231.8	228.0	221.3
30°	240.4	223.2	205.0	199.3	191.6
32.5°	215.5	196.4	178.2	171.5	164.8
35°	189.7	170.5	151.4	144.7	136.0
37.5°	164.8	146.6	127.4	116.9	109.2
40°	137.9	122.6	104.4	91.0	81.4
42.5°	114.0	100.6	83.3	66.1	56.5
45°	89.1	78.6	64.2	43.1	32.6
47.5°	66.1	58.4	46.9	24.9	17.2
50°	44.1	41.2	30.7	12.5	10.5
52.5°	23.9	25.9	18.2	7.7	8.6
55°	5.7	11.5	9.6	5.7	6.7
57.5°	1.0	1.9	4.8	4.8	4.8
60°	1.0	1.0	1.9	2.9	3.8
62.5°	1.0	0.0	1.0	1.9	2.9
65°	0.0	0.0	1.0	1.0	1.9
67.5°	0.0	0.0	0.0	1.0	1.0
70°	0.0	0.0	0.0	1.0	1.0
72.5°	0.0	0.0	0.0	0.0	1.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058455
 CATALOG NUMBER: S122RDRP-H675D840-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00