

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058257

Luminaire Tested: S122RDRP-H1005D940-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H1005D940-X4F0-XX-UDD-BVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 566.8 lumens
Efficiency: N/A
Efficacy: 15.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058257

CATALOG NUMBER: S122RDRP-H1005D940-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058257

CATALOG NUMBER: S122RDRP-H1005D940-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93					93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86					86			
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54					54			
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51					51			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47					47			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11123	11123	11123
5°	11047	10882	10929
10°	10817	10364	10099
15°	10176	9470	9080
20°	9084	8408	7933
25°	7940	7110	6745
30°	6816	5810	5431
35°	5683	4535	4077
40°	4420	3346	2609
45°	3092	2229	1130
50°	1682	1171	402
55°	244	409	286
60°	48	92	188
65°	0	57	109
70°	0	0	70
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3092 cd/sqm



TEST NUMBER: P1058257

CATALOG NUMBER: S122RDRP-H1005D940-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.4	9.8
10°-20°	139.6	24.6
20°-30°	162.7	28.7
30°-40°	130.4	23.0
40°-50°	64.8	11.4
50°-60°	12.8	2.3
60°-70°	1.1	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.6	63.1
0°-40°	488.0	86.1
0°-60°	565.6	99.8
0°-90°	566.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	566.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	603	603	603	603	603	
5°	596	596	588	589	590	56
15°	533	522	496	483	475	148
25°	390	371	349	342	331	179
35°	252	227	201	192	181	157
45°	118	104	85	57	43	91
55°	8	15	13	8	9	15
65°	0	0	1	1	2	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058257

CATALOG NUMBER: S122RDRP-H1005D940-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	602.8	602.8	602.8	602.8	602.8
2.5°	600.2	602.8	596.4	602.8	604.0
5°	596.4	596.4	587.5	588.7	590.0
7.5°	590.0	587.5	572.2	569.6	567.1
10°	577.3	572.2	553.1	542.9	539.0
12.5°	559.4	551.8	526.3	514.8	508.5
15°	532.7	522.5	495.7	483.0	475.3
17.5°	498.3	489.4	463.9	449.8	442.2
20°	462.6	449.8	428.2	414.2	404.0
22.5°	428.2	411.6	388.7	378.5	368.3
25°	390.0	370.8	349.2	341.5	331.3
27.5°	358.1	333.9	308.4	303.3	294.4
30°	319.9	296.9	272.7	265.1	254.9
32.5°	286.7	261.2	237.0	228.1	219.2
35°	252.3	226.8	201.3	192.4	181.0
37.5°	219.2	195.0	169.5	155.5	145.3
40°	183.5	163.1	138.9	121.1	108.3
42.5°	151.6	133.8	110.9	87.9	75.2
45°	118.5	104.5	85.4	57.3	43.3
47.5°	87.9	77.7	62.4	33.1	22.9
50°	58.6	54.8	40.8	16.6	14.0
52.5°	31.9	34.4	24.2	10.2	11.5
55°	7.6	15.3	12.7	7.6	8.9
57.5°	1.3	2.5	6.4	6.4	6.4
60°	1.3	1.3	2.5	3.8	5.1
62.5°	1.3	0.0	1.3	2.5	3.8
65°	0.0	0.0	1.3	1.3	2.5
67.5°	0.0	0.0	0.0	1.3	1.3
70°	0.0	0.0	0.0	1.3	1.3
72.5°	0.0	0.0	0.0	0.0	1.3
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058257
 CATALOG NUMBER: S122RDRP-H1005D940-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00