

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1211871

Luminaire Tested: **GKO-PB2A-840-U-T3**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1211871
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB2A-840-U-T3
Description: GEKKO WALL PACK 4000LM PACKAGE 80CRI 4000K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source: (20) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3866.1 lumens
Efficiency: N/A
Efficacy: 145.9 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G1

Input Watts (W): 26.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 12%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1211871
 CATALOG NUMBER: GKO-PB2A-840-U-T3

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 3.3 fc
 Type III - Medium - N/A

REPORT NUMBER: P1211871
CATALOG NUMBER: GKO-PB2A-840-U-T3

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 68-Deg Vertical

REPORT NUMBER: P1211871

CATALOG NUMBER: GKO-PB2A-840-U-T3


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	989.8	0.0	989.8
	% Fixture	25.6	0.0	25.6
Street Side	Lumens	2876.3	0.0	2876.3
	% Fixture	74.4	0.0	74.4
Total	Lumens	3866.1	0.0	3866.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.2	1.6
10°-20°	187.0	4.8
20°-30°	322.2	8.3
30°-40°	499.8	12.9
40°-50°	684.7	17.7
50°-60°	816.8	21.1
60°-70°	818.5	21.2
70°-80°	433.1	11.2
80°-90°	41.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3866.1	100.0
0°-180°	3866.1	100.0



REPORT NUMBER: P1211871


CATALOG NUMBER: GKO-PB2A-840-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	341.5	8.8			
FM	(30°-60°)	1513.8	39.2			
FH	(60°-80°)	1004.6	26.0			G1/1800
FVH	(80°-90°)	16.4	0.4			G1/100
BL	(0°-30°)	229.9	5.9	B1/500		
BM	(30°-60°)	487.6	12.6	B1/1000		
BH	(60°-80°)	246.9	6.4	B1/500		G1/500
BVH	(80°-90°)	25.4	0.7			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type III Medium





REPORT NUMBER: P1211871

CATALOG NUMBER: GKO-PB2A-840-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	648.4	648.4	648.4	648.4	648.4	648.4	648.4	648.4	648.4	648.4	648.4
2.5°	675.5	675.5	673.9	673.2	672.4	667.9	664.9	661.2	661.2	655.2	649.9
5°	698.7	699.5	696.5	696.5	693.5	687.5	681.5	673.9	673.9	664.9	654.4
7.5°	719.0	721.2	718.2	718.2	715.2	708.5	698.7	688.2	688.2	675.5	660.4
10°	738.5	740.0	738.5	740.0	735.5	729.5	718.2	704.0	703.2	687.5	666.4
12.5°	754.3	755.8	756.5	758.8	755.0	750.5	740.0	722.0	719.7	701.0	673.9
15°	769.3	770.8	773.0	776.0	775.3	771.5	761.8	741.5	740.0	716.0	683.7
17.5°	781.3	782.0	786.5	792.5	794.0	794.8	784.3	763.3	761.8	733.2	694.2
20°	798.5	800.0	804.5	810.5	815.0	818.0	809.8	786.5	785.0	753.5	707.7
22.5°	837.6	835.3	837.6	837.6	839.8	844.3	838.3	815.0	812.0	777.5	724.2
25°	911.1	908.9	902.9	889.3	874.3	873.6	866.8	844.3	840.6	802.3	740.0
27.5°	1013.9	1008.7	997.4	968.9	932.9	909.6	899.1	875.8	871.3	827.1	755.0
30°	1122.7	1128.8	1110.0	1071.0	1004.9	955.4	935.1	908.9	905.1	854.8	773.0
32.5°	1249.6	1250.3	1231.6	1177.5	1092.0	1013.2	978.7	946.4	943.4	887.1	797.0
35°	1323.1	1326.1	1317.9	1267.6	1170.0	1077.0	1031.2	992.2	989.9	927.6	827.1
37.5°	1399.7	1406.4	1393.7	1338.1	1229.3	1136.3	1089.7	1046.9	1044.7	974.1	864.6
40°	1513.0	1510.0	1496.5	1414.7	1284.9	1185.8	1147.5	1113.7	1108.5	1031.2	902.9
42.5°	1594.8	1602.3	1573.0	1480.7	1345.6	1235.3	1205.3	1167.0	1160.3	1065.7	925.4
45°	1622.6	1615.8	1583.6	1516.0	1425.2	1280.4	1260.1	1230.8	1224.1	1126.5	969.6
47.5°	1628.6	1616.6	1588.1	1537.0	1492.7	1338.9	1326.9	1320.1	1310.4	1203.1	1022.9
50°	1591.8	1583.6	1570.0	1544.5	1536.3	1393.7	1399.7	1424.5	1416.2	1285.6	1082.2
52.5°	1508.5	1504.8	1516.8	1533.3	1511.5	1441.0	1486.0	1536.3	1533.3	1376.4	1146.0
55°	1351.7	1351.7	1419.2	1477.0	1489.7	1471.7	1579.1	1665.4	1661.6	1478.5	1206.8
57.5°	1208.3	1210.6	1266.8	1396.7	1450.7	1504.8	1682.6	1800.5	1794.4	1593.3	1270.6
60°	1027.4	1027.4	1113.0	1275.9	1394.4	1530.3	1774.2	1931.0	1934.8	1704.4	1333.6
62.5°	813.5	815.8	934.4	1125.8	1313.4	1534.8	1847.0	2054.1	2053.4	1805.0	1382.4
65°	599.7	600.4	761.8	959.1	1191.8	1503.3	1886.8	2148.7	2153.2	1884.5	1410.9
67.5°	389.5	397.0	560.6	778.3	1019.9	1413.9	1865.7	2199.0	2204.2	1921.3	1401.9
68°	364.7	366.2	530.6	728.7	973.4	1391.4	1856.0	2201.2	2205.7	1920.5	1392.9
70°	236.4	236.4	379.8	568.9	776.8	1251.1	1771.2	2165.9	2171.2	1887.5	1327.6
72.5°	127.6	129.8	216.9	344.5	530.6	968.1	1598.6	1982.1	1991.1	1706.6	1161.0
75°	89.3	90.8	126.1	192.9	288.9	630.4	1249.6	1514.5	1513.0	1179.0	727.2
77.5°	64.5	64.5	72.0	120.1	151.6	288.2	618.4	729.5	721.2	575.6	367.0
80°	42.0	42.0	45.0	63.0	72.8	87.8	189.1	316.0	322.0	280.7	183.1
82.5°	17.3	18.0	19.5	25.5	26.3	36.8	54.0	90.8	87.8	71.3	51.8
85°	2.3	2.3	3.0	3.8	4.5	8.3	7.5	7.5	7.5	9.0	8.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.8	1.5	2.3	2.3	3.0	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1211871

CATALOG NUMBER: GKO-PB2A-840-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	648.4	648.4	648.4	648.4	648.4	648.4	648.4	648.4	648.4	648.4	648.4
2.5°	648.4	648.4	643.9	639.4	634.9	631.2	625.9	622.2	622.9	625.2	624.4
5°	652.2	648.4	639.4	629.7	622.2	615.4	605.7	600.4	599.7	601.2	600.4
7.5°	654.4	648.4	634.9	619.9	607.9	598.9	585.4	580.1	577.9	578.6	578.6
10°	658.9	649.2	630.4	609.4	594.4	581.6	567.4	559.9	557.6	557.6	556.9
12.5°	664.2	650.7	625.9	600.4	580.9	565.9	549.4	541.1	538.9	538.9	538.1
15°	669.4	652.9	621.4	590.6	568.1	550.1	534.4	524.6	521.6	521.6	523.1
17.5°	676.2	655.2	616.9	581.6	554.6	534.4	517.8	508.1	504.3	506.6	508.1
20°	683.0	659.7	612.4	571.9	541.1	520.1	503.6	493.8	490.1	493.8	494.6
22.5°	692.7	663.4	607.2	560.6	527.6	504.3	489.3	480.3	478.1	481.8	484.8
25°	702.5	667.9	600.4	548.6	510.3	487.8	475.8	469.1	469.8	475.1	478.1
27.5°	713.0	671.7	593.6	533.6	491.6	470.6	461.6	460.1	463.1	469.1	472.8
30°	725.7	677.0	584.6	516.3	470.6	451.8	448.0	452.6	457.8	463.8	467.6
32.5°	742.2	683.7	575.6	496.8	448.8	431.5	437.5	447.3	453.3	459.3	463.1
35°	765.5	697.2	570.4	477.3	425.5	414.3	427.8	443.5	448.0	451.8	456.3
37.5°	792.5	715.2	568.1	459.3	404.5	399.3	418.0	436.8	438.3	439.8	444.3
40°	818.8	728.7	562.1	439.8	382.8	382.8	406.0	424.0	423.3	421.0	424.0
42.5°	829.3	727.2	544.9	421.0	365.5	366.2	387.3	404.5	400.0	400.0	404.5
45°	859.3	739.2	532.1	406.0	349.7	346.7	363.2	376.8	384.3	394.0	398.5
47.5°	897.6	755.8	522.3	388.8	334.7	325.0	334.0	356.5	369.2	379.8	383.5
50°	937.4	774.5	513.3	370.7	319.7	300.2	304.7	329.5	340.7	346.0	348.2
52.5°	977.9	791.8	506.6	355.7	302.5	270.9	280.7	304.0	312.2	315.2	316.7
55°	1013.9	806.0	500.6	343.0	282.9	247.7	255.2	279.2	285.2	288.2	290.4
57.5°	1052.2	821.8	496.8	331.0	261.2	227.4	232.7	254.4	262.7	265.7	267.9
60°	1086.0	836.8	493.8	318.2	240.9	209.4	212.4	233.4	242.4	243.9	246.2
62.5°	1108.5	846.6	489.3	302.5	222.1	192.1	192.9	213.1	222.9	224.4	225.9
65°	1114.5	844.3	475.8	281.4	203.4	174.9	174.9	194.4	204.9	210.1	212.4
67.5°	1096.5	825.6	447.3	254.4	185.4	159.1	159.1	176.4	187.6	193.6	195.9
68°	1090.5	817.3	438.3	247.7	180.9	155.4	155.4	173.4	183.9	189.1	190.6
70°	1039.4	776.8	397.0	222.1	166.6	144.1	144.1	159.9	171.1	171.1	170.4
72.5°	902.9	673.2	326.5	186.1	145.6	127.6	129.8	144.8	148.6	152.4	151.6
75°	559.1	403.0	219.1	147.1	122.3	111.8	116.3	129.8	132.1	140.3	138.1
77.5°	279.9	197.4	116.3	85.6	94.6	96.1	104.3	114.1	120.8	129.8	123.8
80°	138.1	96.1	68.3	53.3	55.5	70.5	90.8	98.3	110.3	116.3	111.1
82.5°	38.3	29.3	27.8	29.3	41.3	54.8	71.3	87.1	102.8	108.1	100.6
85°	6.8	5.3	4.5	14.3	28.5	40.5	57.8	77.3	92.3	88.6	83.3
87.5°	2.3	1.5	1.5	9.0	21.0	33.0	49.5	69.0	78.8	71.3	63.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP3-2511-595-3

Test Date: 11/12/2025

Luminaire Tested: GKO-PB1C-840-U-T4W

Data in this report applies to families of products including GKO-PB1C-840*


Test Information

Test Method: LM-79-2019
 Report Number: SP3-2511-595-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP3 - 3M SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/27/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-840-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 3958
 CIE u' : 0.2251
 CIE v' : 0.5041
 Duv: 0.0014
 CIE x: 0.3833
 CIE y: 0.3816
 CIE z: 0.2351
 Peak Wavelength (nm): 450
 Dominant Wavelength (nm): 578
 Purity: 29.56261
 R_f: 82.9
 R_g: 94.7

CRI (Ra): 80.8
 R1: 78.3
 R2: 87.6
 R3: 95.0
 R4: 79.6
 R5: 78.8
 R6: 83.3
 R7: 84.3
 R8: 59.4
 R9: -5.1
 R10: 71.4
 R11: 78.5
 R12: 60.5
 R13: 80.5
 R14: 97.5
 R15: 70.7



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2511-595-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	7/1/2025	1/1/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2511-595-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP3-2511-595-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.65

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.36


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	296	NR	620	736	NR	750	18	NR	880	0	NR
365	0	NR	495	355	NR	625	683	NR	755	15	NR	885	0	NR
370	0	NR	500	415	NR	630	628	NR	760	13	NR	890	0	NR
375	0	NR	505	468	NR	635	571	NR	765	11	NR	895	0	NR
380	0	NR	510	511	NR	640	515	NR	770	9	NR	900	0	NR
385	0	NR	515	545	NR	645	460	NR	775	8	NR	905	0	NR
390	1	NR	520	570	NR	650	408	NR	780	7	NR	910	0	NR
395	3	NR	525	590	NR	655	359	NR	785	6	NR	915	0	NR
400	5	NR	530	606	NR	660	313	NR	790	5	NR	920	0	NR
405	7	NR	535	623	NR	665	273	NR	795	4	NR	925	0	NR
410	12	NR	540	641	NR	670	236	NR	800	4	NR	930	0	NR
415	22	NR	545	664	NR	675	204	NR	805	3	NR	935	0	NR
420	40	NR	550	690	NR	680	175	NR	810	3	NR	940	0	NR
425	73	NR	555	715	NR	685	151	NR	815	2	NR	945	0	NR
430	133	NR	560	747	NR	690	128	NR	820	2	NR	950	0	NR
435	236	NR	565	781	NR	695	109	NR	825	2	NR	955	0	NR
440	416	NR	570	809	NR	700	93	NR	830	1	NR	960	0	NR
445	757	NR	575	840	NR	705	78	NR	835	1	NR	965	0	NR
450	1000	NR	580	863	NR	710	67	NR	840	1	NR	970	0	NR
455	730	NR	585	880	NR	715	57	NR	845	1	NR	975	0	NR
460	494	NR	590	890	NR	720	48	NR	850	1	NR	980	0	NR
465	419	NR	595	890	NR	725	41	NR	855	1	NR	985	0	NR
470	305	NR	600	879	NR	730	35	NR	860	1	NR	990	0	NR
475	235	NR	605	856	NR	735	29	NR	865	1	NR	995	0	NR
480	237	NR	610	824	NR	740	25	NR	870	1	NR	1000	0	NR
485	257	NR	615	783	NR	745	21	NR	875	1	NR			

REPORT NUMBER: SP3-2511-595-3





TM-30-18

Summary

$R_f = 82.9$
 $R_g = 94.7$
 $CIE R_a = 80.8$
 $R_g = -5.1$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 80	CES51 = 94	CES76 = 73
CES02 = 61	CES27 = 93	CES52 = 94	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 88	CES78 = 72
CES04 = 70	CES29 = 85	CES54 = 89	CES79 = 91
CES05 = 48	CES30 = 96	CES55 = 88	CES80 = 89
CES06 = 50	CES31 = 87	CES56 = 84	CES81 = 79
CES07 = 40	CES32 = 80	CES57 = 83	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 84	CES83 = 95
CES09 = 29	CES34 = 86	CES59 = 90	CES84 = 90
CES10 = 74	CES35 = 92	CES60 = 90	CES85 = 78
CES11 = 57	CES36 = 83	CES61 = 86	CES86 = 72
CES12 = 63	CES37 = 91	CES62 = 86	CES87 = 83
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 87
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 76
CES15 = 71	CES40 = 95	CES65 = 75	CES90 = 87
CES16 = 47	CES41 = 99	CES66 = 74	CES91 = 71
CES17 = 49	CES42 = 93	CES67 = 73	CES92 = 62
CES18 = 56	CES43 = 89	CES68 = 77	CES93 = 77
CES19 = 71	CES44 = 99	CES69 = 82	CES94 = 60
CES20 = 65	CES45 = 93	CES70 = 73	CES95 = 70
CES21 = 86	CES46 = 90	CES71 = 67	CES96 = 82
CES22 = 78	CES47 = 96	CES72 = 89	CES97 = 90
CES23 = 91	CES48 = 84	CES73 = 66	CES98 = 84
CES24 = 90	CES49 = 89	CES74 = 93	CES99 = 73
CES25 = 71	CES50 = 94	CES75 = 70	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)