

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1212056

Luminaire Tested: **GKO-PB1A-850-U-T1**

Issue Date: 11/5/2025



Test Information

Test Method: LM-79-08
Report Number: P1212056
Test Lab: INNOVATION CENTER(G1)
Issue Date: 11/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GKO-PB1A-850-U-T1
Description: GEKKO WALL PACK 750LM PACKAGE 80CRI 5000K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source: (10) 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 747.5 lumens
Efficiency: N/A
Efficacy: 155.7 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type I - Short
BUG Rating: B0 - U0 - G0

Input Watts (W): 4.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): 16%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1212056
 CATALOG NUMBER: GKO-PB1A-850-U-T1

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 --- 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 0.8 fc
 Type I - Short - N/A

REPORT NUMBER: P1212056
CATALOG NUMBER: GKO-PB1A-850-U-T1

Luminous Intensity Polar Plot



REPORT NUMBER: P1212056

CATALOG NUMBER: GKO-PB1A-850-U-T1


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	373.8	0.0	373.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	373.8	0.0	373.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	747.5	0.0	747.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.8	2.4
10°-20°	53.6	7.2
20°-30°	89.1	11.9
30°-40°	118.4	15.8
40°-50°	133.5	17.9
50°-60°	137.3	18.4
60°-70°	129.7	17.4
70°-80°	63.5	8.5
80°-90°	4.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	747.5	100.0
0°-180°	747.5	100.0

Coefficient of Utilization



REPORT NUMBER: P1212056


CATALOG NUMBER: GKO-PB1A-850-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	80.3	10.7			
FM	(30°-60°)	194.6	26.0			
FH	(60°-80°)	96.6	12.9			G0/660
FVH	(80°-90°)	2.3	0.3			G0/10
BL	(0°-30°)	80.3	10.7	B0/110		
BM	(30°-60°)	194.6	26.0	B0/220		
BH	(60°-80°)	96.6	12.9	B0/110		G0/110
BVH	(80°-90°)	2.3	0.3			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G0

Type I Short



REPORT NUMBER: P1212056

CATALOG NUMBER: GKO-PB1A-850-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5
2.5°	185.6	185.9	185.4	185.4	185.6	185.8	185.8	185.9	185.6	185.6	185.5
5°	185.6	185.8	185.5	185.5	185.8	186.2	186.0	186.3	186.3	186.2	186.2
7.5°	185.5	185.8	185.5	185.6	186.0	186.9	186.9	186.9	187.1	187.4	187.4
10°	185.4	185.6	185.8	185.9	186.5	187.7	188.0	188.1	188.5	188.9	188.9
12.5°	184.7	184.9	185.4	185.9	186.9	188.5	189.1	189.5	190.2	190.6	190.9
15°	183.7	183.8	184.8	185.9	187.4	189.5	190.6	191.3	192.2	192.8	193.2
17.5°	182.3	182.5	184.0	185.6	187.8	190.7	192.5	193.6	194.6	195.4	196.0
20°	180.5	180.9	182.7	185.4	188.5	192.0	194.6	196.5	197.5	198.3	199.1
22.5°	178.3	178.7	180.9	184.7	189.2	193.6	197.1	199.5	200.8	201.9	202.9
25°	175.0	175.6	178.2	183.0	189.5	195.4	199.8	203.0	204.1	205.5	206.3
27.5°	169.9	170.3	173.5	179.7	188.7	197.3	203.0	206.7	208.0	209.5	210.3
30°	161.9	162.8	166.6	174.3	186.6	198.9	206.7	210.4	212.0	213.5	214.6
32.5°	151.6	152.8	157.1	167.0	182.6	199.4	210.7	215.0	216.9	218.6	219.9
35°	138.8	140.0	145.1	157.7	176.3	198.3	214.7	220.2	222.6	224.8	226.4
37.5°	124.2	125.3	131.5	145.8	167.2	194.9	217.9	226.0	229.2	232.1	234.3
40°	109.4	110.7	117.4	132.7	156.1	188.2	219.3	232.3	236.3	240.1	242.8
42.5°	93.4	95.0	102.5	118.8	143.3	179.2	218.2	238.5	243.5	248.6	252.7
45°	79.2	79.5	87.8	103.5	129.3	167.4	214.3	244.5	251.2	258.4	264.3
47.5°	65.6	66.1	73.3	88.9	114.7	154.2	207.3	249.2	259.9	269.1	277.8
50°	53.5	54.2	60.6	74.6	100.0	139.7	197.8	251.9	267.4	279.9	292.0
52.5°	43.5	44.4	49.7	62.0	85.3	124.6	186.0	252.3	274.1	290.6	306.8
55°	36.2	36.8	40.9	50.7	71.1	108.9	172.7	250.3	278.5	300.3	321.8
57.5°	30.6	31.1	34.0	41.8	58.3	92.7	156.4	245.4	280.9	308.7	336.9
60°	26.6	27.0	29.1	34.6	48.0	77.6	138.9	236.9	280.2	313.9	349.5
62.5°	23.7	23.8	25.6	29.5	39.6	63.3	119.2	224.1	274.5	314.6	358.0
65°	21.1	21.2	22.3	25.1	32.5	50.9	98.7	206.4	263.8	309.8	359.3
67.5°	17.1	17.4	19.0	21.1	26.7	40.2	77.7	183.3	247.0	297.3	352.2
70°	13.6	13.8	15.4	17.8	21.8	31.7	59.7	152.1	220.6	276.9	334.1
72.5°	10.2	10.5	12.0	14.3	17.8	24.5	43.1	115.1	176.4	233.4	290.9
75°	8.1	8.3	8.8	11.0	13.8	18.6	29.1	69.7	106.3	144.4	178.3
77.5°	6.9	7.0	7.0	8.5	10.2	12.5	15.4	27.7	44.9	63.9	84.8
80°	5.7	5.9	5.4	6.3	7.3	7.3	7.2	13.2	21.2	30.0	39.4
82.5°	4.1	4.4	4.1	4.4	4.4	4.0	3.7	5.0	6.8	9.2	10.1
85°	2.9	3.0	3.3	3.0	2.9	2.3	1.8	1.4	0.8	1.0	1.4
87.5°	1.9	2.3	2.8	2.6	2.2	1.8	1.2	0.8	0.4	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1212056
 CATALOG NUMBER: GKO-PB1A-850-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	185.5	185.5	185.5
2.5°	185.6	185.5	185.4
5°	186.3	186.2	186.0
7.5°	187.3	187.3	187.3
10°	188.8	189.1	189.1
12.5°	190.7	191.0	191.0
15°	193.1	193.2	193.5
17.5°	196.0	196.1	196.1
20°	199.4	199.3	199.5
22.5°	202.9	202.9	202.9
25°	206.4	206.4	206.4
27.5°	210.6	210.6	210.3
30°	215.1	215.1	215.1
32.5°	220.6	220.8	220.9
35°	227.7	227.9	228.4
37.5°	235.7	236.3	236.8
40°	245.2	245.4	246.1
42.5°	255.8	256.6	256.7
45°	269.0	270.4	270.9
47.5°	284.6	286.5	287.5
50°	301.9	304.1	305.5
52.5°	320.8	324.4	326.1
55°	340.9	347.1	348.9
57.5°	363.7	372.1	374.6
60°	386.0	397.9	401.9
62.5°	405.0	421.7	426.7
65°	418.4	438.5	445.8
67.5°	421.1	445.0	453.7
70°	404.6	429.0	439.1
72.5°	351.8	373.9	386.4
75°	207.8	223.7	219.8
77.5°	104.3	108.9	109.6
80°	45.8	48.5	49.6
82.5°	11.3	11.6	13.1
85°	1.5	1.8	1.7
87.5°	0.6	0.6	0.7
90°	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2511-595-4

Test Date: 01/09/2026

Luminaire Tested: GKO-PB1C-850-U-T4W

Data in this report applies to families of products including GKO-PB1C

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-595-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/09/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GKO-PB1C-850-U-T4W**
 Description: Gekko Wedge Wall Pack Fixture 1 SQ w/ T4W distribution

Spectral Parameters

CCT (K): 5005
 CIE u' : 0.2100
 CIE v' : 0.4867
 Duv: 0.0019
 CIE x: 0.3453
 CIE y: 0.3557
 CIE z: 0.2990
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 570
 Purity: 10.34221
 R_f: 83.7
 R_g: 95.5

CRI (Ra): 83.1
 R1: 81.4
 R2: 89.2
 R3: 93.9
 R4: 82.4
 R5: 82.2
 R6: 84.5
 R7: 86.1
 R8: 65.5
 R9: 4.4
 R10: 74.2
 R11: 81.9
 R12: 62.2
 R13: 83.6
 R14: 97.0
 R15: 75.4



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-595-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-595-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2511-595-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.97

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.21

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	267	NR	620	453	NR	750	11	NR	880	0	NR
365	0	NR	495	305	NR	625	420	NR	755	10	NR	885	0	NR
370	0	NR	500	350	NR	630	387	NR	760	8	NR	890	0	NR
375	1	NR	505	386	NR	635	351	NR	765	7	NR	895	0	NR
380	1	NR	510	415	NR	640	317	NR	770	6	NR	900	0	NR
385	2	NR	515	441	NR	645	283	NR	775	5	NR	905	0	NR
390	3	NR	520	454	NR	650	252	NR	780	4	NR	910	0	NR
395	4	NR	525	466	NR	655	222	NR	785	4	NR	915	0	NR
400	6	NR	530	474	NR	660	194	NR	790	3	NR	920	0	NR
405	8	NR	535	484	NR	665	170	NR	795	3	NR	925	0	NR
410	12	NR	540	492	NR	670	147	NR	800	2	NR	930	0	NR
415	19	NR	545	502	NR	675	127	NR	805	2	NR	935	0	NR
420	33	NR	550	512	NR	680	109	NR	810	2	NR	940	0	NR
425	57	NR	555	522	NR	685	94	NR	815	2	NR	945	0	NR
430	101	NR	560	535	NR	690	80	NR	820	1	NR	950	0	NR
435	183	NR	565	546	NR	695	69	NR	825	1	NR	955	0	NR
440	325	NR	570	555	NR	700	58	NR	830	1	NR	960	0	NR
445	630	NR	575	562	NR	705	50	NR	835	1	NR	965	0	NR
450	982	NR	580	567	NR	710	42	NR	840	1	NR	970	0	NR
455	847	NR	585	567	NR	715	36	NR	845	1	NR	975	0	NR
460	545	NR	590	566	NR	720	31	NR	850	1	NR	980	0	NR
465	456	NR	595	561	NR	725	26	NR	855	0	NR	985	0	NR
470	349	NR	600	547	NR	730	22	NR	860	0	NR	990	0	NR
475	253	NR	605	530	NR	735	19	NR	865	0	NR	995	0	NR
480	235	NR	610	509	NR	740	16	NR	870	0	NR	1000	0	NR
485	247	NR	615	482	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2511-595-4




TM-30-18

Summary

$R_f = 83.7$
 $R_g = 95.5$
 $\text{CIE } R_a = 83.1$
 $R_9 = 4.4$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 81	CES51 = 94	CES76 = 74
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 91	CES53 = 90	CES78 = 73
CES04 = 69	CES29 = 87	CES54 = 89	CES79 = 91
CES05 = 47	CES30 = 95	CES55 = 87	CES80 = 88
CES06 = 50	CES31 = 89	CES56 = 85	CES81 = 82
CES07 = 39	CES32 = 81	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 95	CES58 = 85	CES83 = 96
CES09 = 29	CES34 = 86	CES59 = 91	CES84 = 90
CES10 = 73	CES35 = 92	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 82	CES61 = 87	CES86 = 77
CES12 = 62	CES37 = 91	CES62 = 83	CES87 = 84
CES13 = 42	CES38 = 90	CES63 = 85	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 95	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 98	CES66 = 74	CES91 = 71
CES17 = 49	CES42 = 92	CES67 = 73	CES92 = 64
CES18 = 55	CES43 = 90	CES68 = 77	CES93 = 79
CES19 = 71	CES44 = 99	CES69 = 81	CES94 = 63
CES20 = 64	CES45 = 94	CES70 = 73	CES95 = 72
CES21 = 85	CES46 = 92	CES71 = 67	CES96 = 83
CES22 = 77	CES47 = 97	CES72 = 89	CES97 = 91
CES23 = 91	CES48 = 86	CES73 = 67	CES98 = 86
CES24 = 90	CES49 = 91	CES74 = 91	CES99 = 75
CES25 = 71	CES50 = 94	CES75 = 69	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)