

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055786

Luminaire Tested: S123R3DRP-H560D940-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1055786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123R3DRP-H560D940-X4F0-XX-UDD-F-S
Description: DEFINE 3, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 904.6 lumens
Efficiency: N/A
Efficacy: 52.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 0.77 / 0.94
Luminous Opening: Rectangular (W 0.23' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 17.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055786

CATALOG NUMBER: S123R3DRP-H560D940-X4F0-XX-UDD-F-S

Luminous Intensity Polar Plot





TEST NUMBER: P1055786

CATALOG NUMBER: S123R3DRP-H560D940-X4F0-XX-UDD-F-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89				89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79				79
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70				70
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	62				62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56				56
6	78	67	60	54	77	66	59	54	65	58	53	63	57	53	62	57	53	51				51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				46
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	42				42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39				39
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36				36

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7843	7843	7843
5°	7760	7731	7708
10°	7699	7420	7186
15°	7596	6957	6396
20°	7459	6329	5387
25°	7283	5570	4347
30°	7090	4772	3348
35°	6869	3939	2477
40°	6648	3135	1689
45°	6402	2344	1272
50°	6141	1630	994
55°	5871	1192	725
60°	5589	892	521
65°	5261	599	405
70°	4759	434	324
75°	4109	317	256
80°	3298	257	215
85°	1701	249	166

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6402 cd/sqm



TEST NUMBER: P1055786

CATALOG NUMBER: S123R3DRP-H560D940-X4F0-XX-UDD-F-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.1	6.6
10°-20°	156.5	17.3
20°-30°	196.7	21.7
30°-40°	183.2	20.2
40°-50°	140.2	15.5
50°-60°	93.2	10.3
60°-70°	50.2	5.6
70°-80°	20.6	2.3
80°-90°	3.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.3	45.7
0°-40°	596.5	65.9
0°-60°	829.9	91.7
0°-90°	904.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	904.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	650	650	650	650	650	
5°	641	648	639	636	637	61
15°	609	599	557	525	512	171
25°	548	510	419	349	327	252
35°	467	398	268	189	168	292
45°	376	278	138	81	75	290
55°	279	162	57	40	34	250
65°	184	62	21	15	14	182
75°	88	15	7	6	6	94
85°	12	2	2	2	1	18
90°	0	0	0	0	0	



TEST NUMBER: P1055786

CATALOG NUMBER: S123R3DRP-H560D940-X4F0-XX-UDD-F-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	650.5	650.5	650.5	650.5	650.5
2.5°	644.9	653.0	646.2	646.8	646.8
5°	641.2	648.0	638.8	636.3	636.9
7.5°	636.3	640.6	625.2	617.2	616.0
10°	628.9	630.1	606.1	591.9	587.0
12.5°	619.7	615.3	583.9	560.5	551.2
15°	608.6	598.7	557.4	524.7	512.4
17.5°	596.2	579.6	527.2	484.6	469.8
20°	581.4	558.0	493.3	440.2	419.9
22.5°	565.4	535.2	457.5	394.6	371.8
25°	547.5	510.5	418.7	349.0	326.8
27.5°	529.0	484.0	380.4	305.8	283.0
30°	509.3	456.9	342.8	263.9	240.5
32.5°	487.7	427.3	304.0	225.0	201.6
35°	466.7	397.7	267.6	189.3	168.3
37.5°	444.5	368.1	232.4	157.8	134.4
40°	422.4	337.9	199.2	127.0	107.3
42.5°	398.9	307.7	167.7	101.1	85.7
45°	375.5	277.5	137.5	80.8	74.6
47.5°	352.1	247.2	111.0	69.7	63.5
50°	327.4	218.3	86.9	59.2	53.0
52.5°	304.0	189.3	67.8	48.7	43.2
55°	279.3	161.5	56.7	39.5	34.5
57.5°	256.5	133.2	46.9	30.8	27.1
60°	231.8	107.9	37.0	24.0	21.6
62.5°	208.4	84.5	28.4	19.1	17.3
65°	184.4	62.3	21.0	15.4	14.2
67.5°	160.3	45.0	16.0	12.3	11.7
70°	135.0	33.9	12.3	9.9	9.2
72.5°	111.0	24.0	9.2	8.0	7.4
75°	88.2	14.8	6.8	6.2	5.5
77.5°	67.8	8.6	4.9	4.9	4.3
80°	47.5	4.9	3.7	3.7	3.1
82.5°	29.0	3.1	2.5	2.5	2.5
85°	12.3	1.8	1.8	1.8	1.2
87.5°	1.8	0.6	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055786
 CATALOG NUMBER: S123R3DRP-H560D940-X4F0-XX-UDD-F-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.97	18.33	17.33	18.64	18.95	5.54	6.89	5.90	7.20	7.52
	3H	18.72	19.93	19.10	20.26	20.62	6.20	7.40	6.58	7.73	8.10
	4H	19.42	20.55	19.82	20.90	21.28	6.39	7.52	6.80	7.87	8.25
	6H	19.93	20.97	20.35	21.34	21.73	6.51	7.55	6.93	7.92	8.31
	8H	20.07	21.05	20.50	21.45	21.85	6.55	7.53	6.98	7.92	8.33
	12H	20.13	21.06	20.56	21.44	21.87	6.56	7.50	6.99	7.88	8.31
4H	2H	16.78	17.90	17.18	18.25	18.63	6.10	7.22	6.50	7.57	7.95
	3H	18.57	19.49	18.98	19.89	20.30	6.89	7.81	7.31	8.22	8.62
	4H	19.26	20.09	19.70	20.51	20.95	7.15	7.98	7.59	8.39	8.84
	6H	19.83	20.54	20.30	20.99	21.46	7.35	8.06	7.81	8.50	8.97
	8H	20.01	20.67	20.48	21.12	21.59	7.40	8.07	7.87	8.51	8.98
	12H	20.10	20.68	20.58	21.16	21.64	7.44	8.02	7.92	8.50	8.98
8H	4H	19.14	19.80	19.61	20.25	20.72	7.46	8.13	7.93	8.57	9.04
	6H	19.69	20.24	20.20	20.73	21.21	7.71	8.25	8.21	8.75	9.23
	8H	19.87	20.36	20.39	20.87	21.36	7.80	8.29	8.32	8.80	9.29
	12H	19.98	20.40	20.49	20.90	21.47	7.88	8.31	8.40	8.80	9.37
12H	4H	19.10	19.68	19.58	20.17	20.64	7.51	8.10	7.99	8.58	9.05
	6H	19.64	20.12	20.16	20.64	21.13	7.76	8.24	8.28	8.76	9.25
	8H	19.83	20.26	20.35	20.75	21.32	7.89	8.32	8.40	8.81	9.38