

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059657

Luminaire Tested: S123RDRP-H560D830-X4F0-XX-UDD-SVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-65)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-H560D830-X4F0-XX-UDD-SVL-W
Description: DEFINE 3 WHITE REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 673.5 lumens
Efficiency: N/A
Efficacy: 38.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 1.08 / 0.98
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059657

CATALOG NUMBER: S123RDRP-H560D830-X4F0-XX-UDD-SVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1059657

CATALOG NUMBER: S123RDRP-H560D830-X4F0-XX-UDD-SVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	56	51	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	43	65	54	47	43	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5891	5891	5891
5°	5700	5789	5907
10°	5321	5522	5804
15°	4849	5159	5652
20°	4315	4720	5413
25°	3739	4224	5104
30°	3135	3684	4800
35°	2484	3136	4511
40°	1758	2580	4232
45°	1035	2039	3809
50°	775	1549	3336
55°	651	1046	2680
60°	526	892	1902
65°	417	761	1003
70°	364	663	621
75°	340	622	594
80°	338	676	588
85°	418	1010	754

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 3809 cd/sqm



TEST NUMBER: P1059657

CATALOG NUMBER: S123RDRP-H560D830-X4F0-XX-UDD-SVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	6.9
10°-20°	120.0	17.8
20°-30°	152.8	22.7
30°-40°	143.8	21.3
40°-50°	103.5	15.4
50°-60°	59.8	8.9
60°-70°	27.3	4.1
70°-80°	13.7	2.0
80°-90°	6.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	319.0	47.4
0°-40°	462.8	68.7
0°-60°	626.1	93.0
0°-90°	673.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	673.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	484	492	491	496	501	45
15°	399	413	424	448	465	111
25°	289	304	326	362	394	132
35°	173	188	219	269	315	107
45°	62	78	123	184	229	53
55°	32	33	51	97	131	28
65°	15	21	27	30	36	15
75°	8	14	14	13	13	8
85°	3	7	8	7	6	3
90°	0	0	0	0	0	



TEST NUMBER: P1059657

CATALOG NUMBER: S123RDRP-H560D830-X4F0-XX-UDD-SVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	501.7	501.7	501.7	501.7	501.7
2.5°	496.1	502.3	498.0	498.6	499.9
5°	483.6	491.7	491.1	496.1	501.1
7.5°	466.2	475.5	480.5	488.0	494.9
10°	446.3	456.8	463.1	476.8	486.8
12.5°	423.2	436.9	445.0	463.1	477.4
15°	398.9	413.2	424.4	448.1	464.9
17.5°	371.5	387.0	401.4	429.4	450.0
20°	345.3	360.2	377.7	408.2	433.2
22.5°	316.6	332.8	352.8	385.2	413.2
25°	288.6	303.5	326.0	362.1	393.9
27.5°	260.5	275.5	299.2	339.1	374.0
30°	231.2	246.8	271.7	316.0	354.0
32.5°	202.6	217.5	245.6	293.6	333.4
35°	173.3	188.2	218.8	269.2	314.7
37.5°	144.6	160.2	192.6	249.3	296.0
40°	114.7	131.5	168.3	228.7	276.1
42.5°	86.6	104.7	144.0	207.5	254.3
45°	62.3	77.9	122.8	184.5	229.4
47.5°	48.6	56.7	103.5	160.8	206.3
50°	42.4	43.6	84.8	139.0	182.6
52.5°	36.8	38.0	66.7	118.4	157.7
55°	31.8	33.0	51.1	97.2	130.9
57.5°	26.8	28.7	42.4	77.3	105.3
60°	22.4	24.9	38.0	59.2	81.0
62.5°	18.1	22.4	32.4	43.6	58.0
65°	15.0	21.2	27.4	30.5	36.1
67.5°	12.5	19.3	23.1	21.8	21.2
70°	10.6	17.5	19.3	17.5	18.1
72.5°	8.7	16.2	16.2	15.0	15.0
75°	7.5	14.3	13.7	13.1	13.1
77.5°	6.2	12.5	11.8	11.2	10.6
80°	5.0	10.0	10.0	9.3	8.7
82.5°	4.4	8.1	8.1	8.1	6.9
85°	3.1	6.9	7.5	6.9	5.6
87.5°	2.5	6.2	6.2	5.6	3.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059657

CATALOG NUMBER: S123RDRP-H560D830-X4F0-XX-UDD-SVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.14	7.46	6.50	7.77	8.08	13.50	14.81	13.86	15.13	15.44
	3H	7.53	8.70	7.91	9.03	9.39	13.73	14.90	14.11	15.23	15.59
	4H	8.08	9.17	8.48	9.52	9.90	13.84	14.93	14.24	15.28	15.67
	6H	8.51	9.51	8.93	9.88	10.28	13.96	14.96	14.37	15.33	15.72
	8H	8.69	9.64	9.12	10.03	10.44	14.01	14.96	14.44	15.35	15.75
	12H	8.85	9.75	9.28	10.14	10.57	14.07	14.98	14.50	15.36	15.79
4H	2H	7.23	8.32	7.64	8.68	9.06	13.45	14.54	13.86	14.89	15.28
	3H	8.90	9.79	9.31	10.20	10.60	13.81	14.71	14.23	15.11	15.52
	4H	9.71	10.51	10.14	10.92	11.37	14.01	14.81	14.45	15.23	15.67
	6H	10.34	11.03	10.81	11.48	11.95	14.24	14.93	14.70	15.38	15.84
	8H	10.58	11.23	11.05	11.67	12.14	14.34	14.99	14.81	15.44	15.91
	12H	10.79	11.37	11.28	11.85	12.32	14.47	15.04	14.96	15.53	16.00
8H	4H	10.15	10.79	10.62	11.24	11.71	14.05	14.70	14.52	15.14	15.61
	6H	11.06	11.59	11.56	12.09	12.57	14.38	14.91	14.88	15.40	15.88
	8H	11.48	11.96	12.00	12.47	12.96	14.57	15.04	15.09	15.56	16.05
	12H	11.90	12.32	12.42	12.82	13.39	14.82	15.24	15.33	15.73	16.31
12H	4H	10.20	10.78	10.69	11.26	11.73	14.04	14.61	14.53	15.09	15.57
	6H	11.19	11.67	11.72	12.19	12.68	14.39	14.87	14.91	15.38	15.88
	8H	11.74	12.16	12.25	12.65	13.22	14.65	15.07	15.16	15.57	16.14