

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P385599

Luminaire Tested: **GWC-SA1A-830-U-RW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P385599  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GWC-SA1A-830-U-RW  
Description: GALLEON WALL LUMINAIRE  
(1) 80 CRI, 3000K, 615mA LIGHTSQUARE WITH 16 LEDS AND RECTANGULAR WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4042 lumens  
Efficiency: N/A  
Efficacy: 118.9 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B2 - U0 - G2

Input Watts (W): 34  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P385599

CATALOG NUMBER: GWC-SA1A-830-U-RW

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 --- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 2.1 fc  
 Type III - Short - N/A

REPORT NUMBER: P385599

CATALOG NUMBER: GWC-SA1A-830-U-RW

## Luminous Intensity Polar Plot



REPORT NUMBER: P385599

CATALOG NUMBER: GWC-SA1A-830-U-RW


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2021.0   | 0.0    | 2021.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2021.0   | 0.0    | 2021.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 4042.0   | 0.0    | 4042.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 41.1   | 1.0       |
| 10°-20°   | 137.8  | 3.4       |
| 20°-30°   | 268.6  | 6.6       |
| 30°-40°   | 451.3  | 11.2      |
| 40°-50°   | 711.1  | 17.6      |
| 50°-60°   | 950.9  | 23.5      |
| 60°-70°   | 924.4  | 22.9      |
| 70°-80°   | 505.3  | 12.5      |
| 80°-90°   | 51.4   | 1.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4042.0 | 100.0     |
| 0°-180°   | 4042.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P385599


CATALOG NUMBER: GWC-SA1A-830-U-RW

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 223.8  | 5.5       |                         |      |         |
| FM   | (30°-60°)   | 1056.6 | 26.1      |                         |      |         |
| FH   | (60°-80°)   | 714.9  | 17.7      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 25.7   | 0.6       |                         |      | G1/100  |
| BL   | (0°-30°)    | 223.8  | 5.5       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1056.6 | 26.1      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 714.9  | 17.7      | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 25.7   | 0.6       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**

Type III Short



REPORT NUMBER: P385599

CATALOG NUMBER: GWC-SA1A-830-U-RW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°    | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|-------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 420.3 | 420.3 | 420.3  | 420.3  | 420.3  | 420.3  | 420.3  | 420.3  | 420.3  | 420.3  | 420.3  |
| 2.5°  | 417.3 | 417.4 | 418.1  | 418.9  | 419.6  | 421.4  | 421.8  | 422.4  | 422.7  | 423.4  | 423.4  |
| 5°    | 413.6 | 413.9 | 415.5  | 417.7  | 420.1  | 424.5  | 427.6  | 431.1  | 432.9  | 434.8  | 434.6  |
| 7.5°  | 413.2 | 413.9 | 416.2  | 419.7  | 423.8  | 431.0  | 437.5  | 444.5  | 449.3  | 453.6  | 453.3  |
| 10°   | 417.4 | 418.5 | 421.8  | 427.0  | 433.1  | 442.1  | 451.7  | 461.2  | 469.5  | 476.1  | 476.4  |
| 12.5° | 423.8 | 425.2 | 430.3  | 438.3  | 447.5  | 459.0  | 470.4  | 481.1  | 492.5  | 502.4  | 503.2  |
| 15°   | 432.2 | 434.0 | 441.7  | 453.6  | 467.7  | 481.4  | 493.6  | 504.6  | 517.7  | 531.4  | 532.8  |
| 17.5° | 444.7 | 447.1 | 457.3  | 473.4  | 492.0  | 507.0  | 519.8  | 528.0  | 539.0  | 553.1  | 555.7  |
| 20°   | 463.6 | 466.8 | 479.6  | 498.9  | 521.5  | 537.2  | 547.0  | 548.8  | 554.2  | 566.8  | 569.8  |
| 22.5° | 488.3 | 491.0 | 505.4  | 528.3  | 553.6  | 570.7  | 575.9  | 568.8  | 568.3  | 578.4  | 581.3  |
| 25°   | 515.8 | 518.3 | 534.9  | 560.7  | 587.9  | 606.8  | 606.6  | 592.9  | 583.4  | 591.3  | 594.3  |
| 27.5° | 546.7 | 550.5 | 566.5  | 593.6  | 622.8  | 641.3  | 640.2  | 619.1  | 601.1  | 603.1  | 605.7  |
| 30°   | 582.2 | 586.4 | 602.0  | 629.5  | 658.7  | 676.8  | 675.5  | 647.6  | 620.4  | 615.0  | 616.9  |
| 32.5° | 626.3 | 631.3 | 646.1  | 673.2  | 698.9  | 715.3  | 711.4  | 678.5  | 643.8  | 632.0  | 633.7  |
| 35°   | 679.3 | 682.2 | 697.8  | 724.5  | 745.4  | 756.7  | 748.4  | 714.2  | 673.3  | 659.1  | 659.1  |
| 37.5° | 732.9 | 735.2 | 752.7  | 778.6  | 798.8  | 804.8  | 788.6  | 753.4  | 711.9  | 691.7  | 692.1  |
| 40°   | 784.4 | 790.7 | 810.3  | 836.9  | 856.8  | 858.4  | 837.0  | 798.1  | 754.9  | 734.0  | 736.5  |
| 42.5° | 838.2 | 844.3 | 867.8  | 897.9  | 915.5  | 918.2  | 893.1  | 848.3  | 803.4  | 786.5  | 789.2  |
| 45°   | 886.2 | 891.1 | 918.2  | 953.2  | 975.1  | 982.2  | 952.5  | 905.7  | 855.9  | 839.3  | 840.0  |
| 47.5° | 919.7 | 926.1 | 955.9  | 997.1  | 1029.1 | 1039.9 | 1010.8 | 961.7  | 907.5  | 887.4  | 889.2  |
| 50°   | 950.1 | 953.4 | 983.7  | 1028.7 | 1069.3 | 1091.7 | 1066.7 | 1017.0 | 959.7  | 938.4  | 940.3  |
| 52.5° | 967.0 | 971.3 | 1000.6 | 1047.5 | 1095.6 | 1131.7 | 1116.5 | 1066.7 | 1010.1 | 989.4  | 991.7  |
| 55°   | 955.2 | 958.5 | 993.6  | 1051.7 | 1111.9 | 1156.3 | 1158.6 | 1115.4 | 1059.6 | 1041.4 | 1047.9 |
| 57.5° | 901.5 | 905.6 | 948.4  | 1024.6 | 1113.9 | 1173.0 | 1190.3 | 1160.5 | 1105.8 | 1091.0 | 1094.8 |
| 60°   | 817.6 | 820.2 | 865.9  | 951.5  | 1074.3 | 1179.9 | 1210.5 | 1197.4 | 1151.0 | 1136.3 | 1141.4 |
| 62.5° | 668.2 | 671.9 | 726.6  | 841.4  | 990.7  | 1159.4 | 1230.1 | 1227.9 | 1193.2 | 1179.6 | 1184.2 |
| 65°   | 456.7 | 463.4 | 523.8  | 669.0  | 861.8  | 1096.8 | 1247.8 | 1263.4 | 1230.5 | 1213.4 | 1219.5 |
| 67.5° | 275.8 | 280.7 | 324.5  | 441.7  | 659.5  | 970.5  | 1229.5 | 1303.8 | 1256.8 | 1229.2 | 1234.3 |
| 68°   | 246.5 | 251.0 | 287.6  | 398.6  | 610.0  | 934.9  | 1212.8 | 1308.4 | 1259.6 | 1229.0 | 1233.4 |
| 70°   | 148.9 | 151.9 | 176.5  | 246.4  | 406.7  | 741.6  | 1099.1 | 1304.6 | 1277.8 | 1232.8 | 1235.3 |
| 72.5° | 97.0  | 98.0  | 102.1  | 126.4  | 207.8  | 414.7  | 825.0  | 1215.7 | 1305.0 | 1254.9 | 1254.4 |
| 75°   | 80.6  | 80.1  | 80.5   | 83.3   | 102.5  | 181.9  | 482.1  | 960.4  | 1244.0 | 1220.0 | 1211.5 |
| 77.5° | 68.2  | 67.8  | 67.6   | 67.8   | 68.6   | 87.8   | 209.3  | 598.2  | 951.9  | 1079.2 | 1086.8 |
| 80°   | 55.2  | 54.6  | 56.4   | 55.6   | 53.1   | 54.6   | 87.7   | 248.8  | 448.7  | 482.8  | 452.4  |
| 82.5° | 40.1  | 38.1  | 45.7   | 43.5   | 41.5   | 38.5   | 48.4   | 80.4   | 107.1  | 73.5   | 51.6   |
| 85°   | 30.9  | 28.7  | 34.7   | 33.3   | 28.5   | 19.7   | 28.7   | 39.3   | 43.4   | 24.8   | 19.5   |
| 87.5° | 12.6  | 13.3  | 25.1   | 19.8   | 16.7   | 9.5    | 11.8   | 15.7   | 21.1   | 10.6   | 8.1    |
| 90°   | 0.0   | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

INVUE

Report Number: SP1-2012-088-3

Luminaire Tested: WIS-SA-830-2D-U-SL4

Test Date: 01/11/2021




### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2012-088-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 01/11/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: INVUE  
 Catalog Number: **WIS-SA-830-2D-U-SL4**  
 Description: INVUE. WALL PACK LIGHT SQUARE SL4 OPTICS 2-SQUARE.

### Spectral Parameters

|                           |        |           |      |      |      |
|---------------------------|--------|-----------|------|------|------|
| CCT (K):                  | 3049   | CRI (Ra): | 81.7 |      |      |
| CIE u':                   | 0.2482 | R1:       | 79.6 | R9:  | 1.9  |
| CIE v':                   | 0.5224 | R2:       | 90.6 | R10: | 79.3 |
| Duv:                      | 0.0015 | R3:       | 95.7 | R11: | 78.7 |
| CIE x:                    | 0.4354 | R4:       | 79.4 | R12: | 72.2 |
| CIE y:                    | 0.4072 | R5:       | 80.2 | R13: | 82.2 |
| CIE z:                    | 0.1574 | R6:       | 89.0 | R14: | 98.1 |
| Peak Wavelength (nm):     | 601    | R7:       | 82.2 |      |      |
| Dominant Wavelength (nm): | 582    | R8:       | 57.0 |      |      |
| Purity:                   | 53     |           |      |      |      |
| Rf:                       | 85.1   |           |      |      |      |
| Rg:                       | 94.3   |           |      |      |      |



### Test Conditions


Stabilization Time: 83M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.6/29%  
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-2012-088-3


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 7/29/2020        | 1/29/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2012-088-3

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2012-088-3

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 6.7              | 620       | 161309           | 42.0             | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 9.8              | 625       | 153301           | 33.8             | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 13.6             | 630       | 143292           | 25.9             | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 19.3             | 635       | 132368           | 19.9             | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 25.5             | 640       | 122334           | 14.6             | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 32.9             | 645       | 112200           | 10.8             | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 40.6             | 650       | 102448           | 7.5              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 47.1             | 655       | 91886            | 5.3              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 53.7             | 660       | 81865            | 3.4              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.0              | 535       | 94694            | 58.7             | 665       | 72448            | 2.3              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.0              | 540       | 98431            | 64.1             | 670       | 63654            | 1.4              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.0              | 545       | 103765           | 69.1             | 675       | 55284            | 0.9              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 0.0              | 550       | 109130           | 74.2             | 680       | 47949            | 0.6              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 0.1              | 555       | 115271           | 78.7             | 685       | 42173            | 0.4              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 0.1              | 560       | 123390           | 83.9             | 690       | 36755            | 0.2              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 0.3              | 565       | 131926           | 87.7             | 695       | 31630            | 0.1              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 0.7              | 570       | 141815           | 92.2             | 700       | 27642            | 0.1              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 1.3              | 575       | 151359           | 94.2             | 705       | 24213            | 0.1              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 2.1              | 580       | 160364           | 95.3             | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 2.6              | 585       | 166836           | 92.7             | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 2.6              | 590       | 172885           | 89.4             | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 2.7              | 595       | 176548           | 83.7             | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 2.8              | 600       | 178427           | 76.9             | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 3.0              | 605       | 177729           | 68.8             | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 3.6              | 610       | 174846           | 60.1             | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 4.9              | 615       | 169274           | 51.1             | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3


### Scotopic Flux vs. Wavelength


**Scotopic Lumens: 4584.8**
**S/P: 0.52**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 72.6             | 620       | 161309           | 2.0              | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 87.7             | 625       | 153301           | 1.3              | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 103.4            | 630       | 143292           | 0.8              | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 117.0            | 635       | 132368           | 0.5              | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 126.0            | 640       | 122334           | 0.3              | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 131.6            | 645       | 112200           | 0.2              | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 133.2            | 650       | 102448           | 0.1              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 131.3            | 655       | 91886            | 0.1              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 125.8            | 660       | 81865            | 0.0              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.1              | 535       | 94694            | 118.0            | 665       | 72448            | 0.0              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.2              | 540       | 98431            | 108.8            | 670       | 63654            | 0.0              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.4              | 545       | 103765           | 99.5             | 675       | 55284            | 0.0              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 1.0              | 550       | 109130           | 89.2             | 680       | 47949            | 0.0              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 2.3              | 555       | 115271           | 78.8             | 685       | 42173            | 0.0              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 5.4              | 560       | 123390           | 69.0             | 690       | 36755            | 0.0              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 11.6             | 565       | 131926           | 59.2             | 695       | 31630            | 0.0              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 23.2             | 570       | 141815           | 50.0             | 700       | 27642            | 0.0              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 42.1             | 575       | 151359           | 41.2             | 705       | 24213            | 0.0              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 63.1             | 580       | 160364           | 33.0             | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 67.4             | 585       | 166836           | 25.5             | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 60.3             | 590       | 172885           | 19.3             | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 55.1             | 595       | 176548           | 14.1             | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 51.0             | 600       | 178427           | 10.1             | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 48.4             | 605       | 177729           | 7.0              | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 51.4             | 610       | 174846           | 4.7              | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 60.4             | 615       | 169274           | 3.1              | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 12033.4 S/P: 1.36**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 39.3             | 620       | 161309           | 0.1              | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 44.8             | 625       | 153301           | 0.1              | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 49.7             | 630       | 143292           | 0.0              | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 52.8             | 635       | 132368           | 0.0              | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 53.4             | 640       | 122334           | 0.0              | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 51.9             | 645       | 112200           | 0.0              | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 48.8             | 650       | 102448           | 0.0              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 44.5             | 655       | 91886            | 0.0              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 39.4             | 660       | 81865            | 0.0              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.0              | 535       | 94694            | 34.1             | 665       | 72448            | 0.0              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.1              | 540       | 98431            | 28.8             | 670       | 63654            | 0.0              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.2              | 545       | 103765           | 24.1             | 675       | 55284            | 0.0              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 0.7              | 550       | 109130           | 19.6             | 680       | 47949            | 0.0              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 1.5              | 555       | 115271           | 15.5             | 685       | 42173            | 0.0              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 3.3              | 560       | 123390           | 12.2             | 690       | 36755            | 0.0              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 6.9              | 565       | 131926           | 9.3              | 695       | 31630            | 0.0              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 13.9             | 570       | 141815           | 6.9              | 700       | 27642            | 0.0              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 24.8             | 575       | 151359           | 5.0              | 705       | 24213            | 0.0              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 37.5             | 580       | 160364           | 3.6              | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 40.4             | 585       | 166836           | 2.5              | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 36.8             | 590       | 172885           | 1.7              | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 34.1             | 595       | 176548           | 1.1              | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 31.7             | 600       | 178427           | 0.8              | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 29.5             | 605       | 177729           | 0.5              | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 30.6             | 610       | 174846           | 0.3              | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 34.3             | 615       | 169274           | 0.2              | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3





TM-30-18

### Summary

$R_f = 85.1$   
 $R_g = 94.3$   
 CIE  $R_a = 81.7$   
 $R_g = 1.9$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 85 | CES51 = 93 | CES76 = 82 |
| CES02 = 63 | CES27 = 94 | CES52 = 93 | CES77 = 85 |
| CES03 = 31 | CES28 = 95 | CES53 = 89 | CES78 = 82 |
| CES04 = 70 | CES29 = 90 | CES54 = 90 | CES79 = 91 |
| CES05 = 49 | CES30 = 96 | CES55 = 89 | CES80 = 90 |
| CES06 = 51 | CES31 = 91 | CES56 = 86 | CES81 = 72 |
| CES07 = 42 | CES32 = 85 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 95 | CES58 = 86 | CES83 = 95 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 76 | CES35 = 96 | CES60 = 92 | CES85 = 77 |
| CES11 = 59 | CES36 = 87 | CES61 = 88 | CES86 = 68 |
| CES12 = 65 | CES37 = 96 | CES62 = 90 | CES87 = 84 |
| CES13 = 43 | CES38 = 94 | CES63 = 88 | CES88 = 87 |
| CES14 = 74 | CES39 = 98 | CES64 = 81 | CES89 = 75 |
| CES15 = 71 | CES40 = 96 | CES65 = 79 | CES90 = 88 |
| CES16 = 47 | CES41 = 97 | CES66 = 80 | CES91 = 79 |
| CES17 = 50 | CES42 = 98 | CES67 = 78 | CES92 = 65 |
| CES18 = 56 | CES43 = 92 | CES68 = 82 | CES93 = 78 |
| CES19 = 72 | CES44 = 99 | CES69 = 87 | CES94 = 61 |
| CES20 = 66 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 90 | CES71 = 77 | CES96 = 83 |
| CES22 = 79 | CES47 = 95 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 84 | CES73 = 75 | CES98 = 84 |
| CES24 = 91 | CES49 = 91 | CES74 = 92 | CES99 = 75 |
| CES25 = 72 | CES50 = 94 | CES75 = 80 |            |





**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)