

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059420

Luminaire Tested: S123RDRP-H1000D835-X4F0-XX-UDD-BVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-66)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-H1000D835-X4F0-XX-UDD-BVL-W
Description: DEFINE 3 WHITE REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1091.4 lumens
Efficiency: N/A
Efficacy: 35.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.06 / 0.94
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059420

CATALOG NUMBER: S123RDRP-H1000D835-X4F0-XX-UDD-BVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1059420

CATALOG NUMBER: S123RDRP-H1000D835-X4F0-XX-UDD-BVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	83	79	76	81	78	75	73
4	92	83	76	71	90	81	75	70	79	74	70	77	72	69	75	71	68	66
5	86	76	69	64	84	75	69	64	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10675	10675	10675
5°	10307	10477	10702
10°	9515	9956	10526
15°	8539	9207	10209
20°	7449	8300	9718
25°	6284	7275	9116
30°	5053	6220	8520
35°	3698	5120	7963
40°	2307	3992	7416
45°	873	2976	6606
50°	415	2051	5630
55°	317	1126	4352
60°	225	953	2860
65°	167	831	1195
70°	165	779	779
75°	218	812	812
80°	325	967	886
85°	647	1603	1293

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 6606 cd/sqm



TEST NUMBER: P1059420

CATALOG NUMBER: S123RDRP-H1000D835-X4F0-XX-UDD-BVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	7.6
10°-20°	214.0	19.6
20°-30°	264.9	24.3
30°-40°	237.5	21.8
40°-50°	155.7	14.3
50°-60°	77.9	7.1
60°-70°	30.4	2.8
70°-80°	17.1	1.6
80°-90°	10.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.3	51.5
0°-40°	799.8	73.3
0°-60°	1033.4	94.7
0°-90°	1091.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1091.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	909	909	909	909	909	
5°	874	889	889	898	908	81
15°	702	731	757	808	840	196
25°	485	515	562	642	704	221
35°	258	293	357	465	556	161
45°	53	85	179	307	398	50
55°	16	19	55	150	213	14
65°	6	18	30	39	43	6
75°	5	18	18	18	18	5
85°	5	12	12	12	10	4
90°	0	0	0	0	0	



TEST NUMBER: P1059420

CATALOG NUMBER: S123RDRP-H1000D835-X4F0-XX-UDD-BVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	909.1	909.1	909.1	909.1	909.1
2.5°	897.1	910.3	901.9	903.1	904.3
5°	874.4	888.8	888.8	898.3	907.9
7.5°	839.8	856.5	868.5	885.2	898.3
10°	798.0	818.3	835.0	864.9	882.8
12.5°	752.6	777.7	799.2	838.6	863.7
15°	702.4	731.1	757.4	807.5	839.8
17.5°	648.7	677.3	712.0	770.5	809.9
20°	596.1	624.8	664.2	729.9	777.7
22.5°	541.1	571.0	612.8	685.7	741.8
25°	485.0	514.9	561.5	641.5	703.6
27.5°	428.9	458.7	511.3	598.5	666.6
30°	372.7	402.6	458.7	551.9	628.4
32.5°	316.6	348.8	407.4	508.9	590.1
35°	258.0	292.7	357.2	464.7	555.5
37.5°	204.3	236.5	309.4	426.5	520.8
40°	150.5	185.2	260.4	389.4	483.8
42.5°	98.0	135.0	216.2	348.8	442.0
45°	52.6	84.8	179.2	307.0	397.8
47.5°	28.7	46.6	144.5	262.8	352.4
50°	22.7	26.3	112.3	224.6	308.2
52.5°	19.1	21.5	80.0	188.7	259.2
55°	15.5	19.1	55.0	150.5	212.6
57.5°	13.1	16.7	43.0	117.1	166.0
60°	9.6	14.3	40.6	86.0	121.8
62.5°	7.2	15.5	35.8	59.7	80.0
65°	6.0	17.9	29.9	39.4	43.0
67.5°	4.8	19.1	26.3	25.1	25.1
70°	4.8	17.9	22.7	21.5	22.7
72.5°	4.8	19.1	20.3	19.1	20.3
75°	4.8	17.9	17.9	17.9	17.9
77.5°	4.8	16.7	16.7	15.5	15.5
80°	4.8	14.3	14.3	14.3	13.1
82.5°	4.8	13.1	13.1	13.1	10.8
85°	4.8	11.9	11.9	11.9	9.6
87.5°	3.6	10.8	11.9	10.8	7.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059420

CATALOG NUMBER: S123RDRP-H1000D835-X4F0-XX-UDD-BVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.57	1.83	0.94	2.14	2.46	14.83	16.09	15.20	16.40	16.72
	3H	2.91	4.02	3.29	4.35	4.72	14.91	16.02	15.29	16.35	16.72
	4H	4.02	5.05	4.42	5.40	5.79	14.99	16.02	15.39	16.37	16.76
	6H	5.01	5.96	5.43	6.33	6.73	15.09	16.04	15.51	16.41	16.81
	8H	5.49	6.39	5.93	6.78	7.19	15.15	16.05	15.58	16.44	16.85
	12H	6.05	6.91	6.49	7.29	7.73	15.23	16.09	15.67	16.47	16.90
4H	2H	3.83	4.87	4.24	5.22	5.60	14.69	15.72	15.09	16.07	16.46
	3H	6.15	7.00	6.56	7.40	7.80	14.86	15.71	15.28	16.11	16.52
	4H	7.52	8.28	7.96	8.70	9.14	15.01	15.77	15.45	16.19	16.63
	6H	8.61	9.26	9.07	9.71	10.17	15.24	15.89	15.70	16.34	16.80
	8H	9.06	9.67	9.53	10.12	10.59	15.36	15.97	15.83	16.42	16.89
	12H	9.56	10.10	10.04	10.58	11.05	15.54	16.08	16.02	16.56	17.03
8H	4H	8.49	9.10	8.96	9.55	10.02	15.01	15.62	15.48	16.07	16.54
	6H	10.01	10.51	10.51	11.01	11.49	15.35	15.84	15.85	16.34	16.82
	8H	10.78	11.23	11.31	11.75	12.24	15.58	16.03	16.10	16.54	17.04
	12H	11.59	11.99	12.10	12.48	13.05	15.91	16.31	16.43	16.81	17.38
12H	4H	8.67	9.21	9.16	9.69	10.16	14.99	15.53	15.48	16.02	16.49
	6H	10.32	10.77	10.85	11.29	11.78	15.36	15.81	15.89	16.33	16.82
	8H	11.28	11.68	11.79	12.17	12.74	15.67	16.07	16.19	16.57	17.14