

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P228260

Luminaire Tested: **ISC-AF-350-LED-E1-SL3-ULG**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P228260
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29762)-DOWNLIGHT AND
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: ISC-AF-350-LED-E1-SL3-ULG
Description: IMPACT ELITE LED CYLINDER LUMINAIRE WITH UPLIGHT
LIGHT SQUARE WITH ACCULED OPTICS-TYPE III W/SPILL CONTROL, WITH UPLIGHT
GLOW
Light Source: (16) 4000K CCT, 70 CRI LEDs and (1) UPLIGHT LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3729.8 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 0.5' x L: 0.5' x H: 0.54')
IES Classification: Type III - Medium - Non-Cutoff
BUG Rating: B0 - U5 - G1


Input Watts (W): 36.79
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P228260
 CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 6 fc
 Type III - Medium - Non-Cutoff

REPORT NUMBER: P228260
CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

Luminous Intensity Polar Plot



— Vertical Plane Through 57.5-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P228260

CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	281.0	729.4	1010.5
	% Fixture	7.5	19.6	27.1
Street Side	Lumens	1989.9	729.4	2719.4
	% Fixture	53.4	19.6	72.9
Total	Lumens	2271.0	1458.9	3729.8
	% Fixture	60.9	39.1	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	1.4
10°-20°	112.7	3.0
20°-30°	141.6	3.8
30°-40°	185.1	5.0
40°-50°	277.7	7.4
50°-60°	438.9	11.8
60°-70°	632.7	17.0
70°-80°	391.6	10.5
80°-90°	38.8	1.0
90°-100°	4.8	0.1
100°-110°	70.6	1.9
110°-120°	156.6	4.2
120°-130°	229.0	6.1
130°-140°	271.7	7.3
140°-150°	275.5	7.4
150°-160°	236.4	6.3
160°-170°	158.7	4.3
170°-180°	55.6	1.5
0°-90°	2271.0	60.9
0°-180°	3729.8	100.0



REPORT NUMBER: P228260


CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	210.9	5.7			
FM	(30°-60°)	805.0	21.6			
FH	(60°-80°)	938.3	25.2			G1/1800
FVH	(80°-90°)	35.7	1.0			G1/100
BL	(0°-30°)	95.3	2.6	B0/110		
BM	(30°-60°)	96.6	2.6	B0/220		
BH	(60°-80°)	86.0	2.3	B0/110		G0/110
BVH	(80°-90°)	3.1	0.1			G0/10
UL	(90°-100°)	4.8	0.1		U1/10	
UH	(100°-180°)	729.4	19.6		U4/1000	

BUG Rating: B0-U5-G1

Type III Medium





REPORT NUMBER: P228260

CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	37.5°	40°	42.5°	45°	47.5°	50°
0°	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1
2.5°	630.9	630.1	628.5	625.2	623.7	625.2	623.7	621.2	618.0	620.4	618.8
5°	629.3	630.9	627.7	625.2	629.3	630.9	627.7	627.7	624.4	627.7	626.0
7.5°	597.8	598.6	599.4	598.6	609.2	609.2	607.5	609.2	610.0	611.5	612.3
10°	558.4	559.1	560.8	563.2	576.1	577.8	578.5	580.1	582.6	584.2	589.0
12.5°	518.9	520.5	523.8	531.8	545.4	547.1	549.5	551.9	556.0	558.4	567.2
15°	485.9	486.6	489.9	498.8	518.9	522.9	524.6	527.7	535.8	535.8	545.4
17.5°	455.2	456.8	459.3	469.7	489.9	496.3	501.1	502.8	513.2	515.7	526.9
20°	431.9	432.7	433.5	443.1	461.7	471.4	475.4	481.8	489.9	496.3	506.1
22.5°	419.0	419.8	418.2	422.2	438.3	450.4	455.2	461.7	464.9	476.2	481.8
25°	419.8	420.6	416.5	414.2	422.2	435.1	439.2	445.6	444.0	460.1	460.1
27.5°	427.8	429.4	425.4	418.2	419.0	429.4	431.9	434.3	429.4	445.6	442.3
30°	444.0	445.6	440.8	435.1	426.3	432.7	432.7	432.7	423.8	437.5	431.9
32.5°	460.8	462.5	460.8	456.8	445.6	447.2	444.0	442.3	430.3	441.5	432.7
35°	485.9	486.6	487.4	487.4	471.4	474.5	465.7	460.8	449.6	458.5	446.4
37.5°	515.7	515.7	521.3	523.8	506.1	506.1	496.3	489.9	479.5	482.6	470.6
40°	542.3	544.7	557.6	564.9	548.7	542.3	534.2	528.6	520.5	520.5	508.4
42.5°	572.9	577.8	593.0	606.7	597.8	588.2	580.1	574.5	570.5	569.7	556.8
45°	610.7	616.4	633.3	646.2	648.7	641.4	634.9	629.3	626.0	624.4	613.2
47.5°	653.5	659.1	674.4	689.7	701.0	699.4	692.1	686.5	689.0	687.3	680.1
50°	701.0	704.2	713.9	731.6	757.4	763.0	761.4	757.4	762.2	762.2	755.8
52.5°	738.9	741.2	748.5	769.5	812.2	825.1	835.5	843.6	851.7	856.5	852.4
55°	773.6	773.6	774.3	800.9	864.6	885.5	908.9	925.8	936.3	955.6	963.6
57.5°	829.9	825.9	825.1	853.2	927.4	949.2	983.0	1007.2	1021.7	1061.2	1060.4
60°	813.8	815.4	844.4	927.4	1056.3	1075.6	1106.3	1132.1	1159.4	1188.5	1190.9
62.5°	701.8	705.8	749.3	873.4	1138.5	1239.2	1333.5	1405.2	1445.5	1471.3	1435.8
65°	491.5	501.1	560.0	711.5	1048.2	1203.8	1352.9	1518.8	1646.1	1843.6	1900.7
67.5°	244.9	252.2	261.9	373.1	783.2	1001.6	1207.0	1433.5	1602.7	1892.7	2054.6
70°	175.6	178.9	186.2	209.5	350.5	524.6	766.3	1090.2	1289.2	1726.7	1955.6
72.5°	136.2	139.4	149.0	182.1	232.0	256.2	304.5	498.0	740.5	1192.5	1501.9
75°	105.6	110.4	124.1	164.4	223.2	236.9	239.3	257.1	293.3	529.4	842.0
77.5°	74.2	75.0	88.6	141.8	216.8	243.4	239.3	239.3	244.2	270.0	360.2
80°	49.1	49.9	58.8	98.3	190.2	221.6	244.9	233.6	234.5	238.4	244.9
82.5°	25.8	27.4	34.7	59.6	111.2	149.9	203.9	212.7	209.5	213.5	212.0
85°	7.3	7.3	12.1	22.6	54.8	58.0	90.2	123.3	125.7	142.6	152.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.5	3.3	7.3	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
97.5°	2.0	2.0	2.0	3.1	4.1	5.3	6.6	8.0	9.2	10.2	11.3
100°	8.2	8.2	10.2	14.3	22.5	24.6	26.6	28.6	30.7	31.2	31.7
102.5°	28.6	28.6	32.7	38.9	46.0	47.3	48.6	49.9	51.1	51.4	51.7
105°	55.2	55.2	57.3	62.4	67.5	68.5	69.6	70.6	71.6	71.8	72.1
107.5°	79.8	78.8	81.8	85.9	90.0	90.8	91.6	92.3	93.1	93.6	94.1
110°	103.3	104.3	105.4	108.4	112.5	113.0	113.5	114.1	114.6	115.1	115.6



REPORT NUMBER: P228260

CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	37.5°	40°	42.5°	45°	47.5°	50°
112.5°	126.8	126.8	128.9	132.0	135.0	135.5	136.1	136.6	137.1	137.6	138.1
115°	149.4	150.4	152.4	154.5	157.5	158.0	158.6	159.1	159.6	160.1	160.6
117.5°	172.9	173.9	175.9	178.0	181.1	181.6	182.1	182.6	183.1	183.3	183.6
120°	197.4	199.5	200.5	202.5	205.6	205.8	206.1	206.4	206.6	207.1	207.7
122.5°	224.0	225.0	226.1	228.1	231.2	231.4	231.7	232.0	232.2	232.4	232.7
125°	249.6	251.6	252.7	253.7	256.8	257.0	257.3	257.6	257.8	258.0	258.3
127.5°	273.1	275.2	276.2	278.2	280.3	280.8	281.3	281.8	282.3	282.8	283.4
130°	296.7	298.7	299.7	300.7	304.8	305.0	305.4	305.7	305.9	306.4	306.9
132.5°	320.2	321.2	324.3	325.3	328.4	328.6	328.9	329.2	329.4	330.2	330.9
135°	343.7	344.7	346.8	348.8	352.9	352.9	352.9	352.9	352.9	353.7	354.5
137.5°	367.2	368.3	371.3	372.4	375.4	375.4	375.4	375.4	375.4	375.9	376.4
140°	390.8	391.8	393.8	394.9	396.9	397.1	397.4	397.7	397.9	398.1	398.4
142.5°	413.3	415.3	417.4	416.3	419.4	419.4	419.4	419.4	419.4	419.9	420.4
145°	434.8	435.8	437.8	437.8	440.9	441.1	441.4	441.7	441.9	442.4	442.9
147.5°	454.2	454.2	457.3	458.3	462.4	462.6	462.9	463.2	463.4	463.6	463.9
150°	471.6	472.6	474.6	475.7	479.8	480.0	480.3	480.6	480.8	481.0	481.3
152.5°	490.0	491.0	494.1	493.1	496.1	496.3	496.6	496.9	497.2	497.4	497.7
155°	510.5	511.5	513.5	512.5	514.5	514.5	514.5	514.5	514.5	514.7	515.1
157.5°	524.8	526.8	528.9	527.8	530.9	530.9	530.9	530.9	530.9	530.9	530.9
160°	537.0	539.1	541.1	541.1	544.2	544.2	544.2	544.2	544.2	544.2	544.2
162.5°	547.3	548.3	551.4	550.3	553.4	553.4	553.4	553.4	553.4	553.6	553.9
165°	558.5	559.6	561.6	560.6	564.7	564.7	564.7	564.7	564.7	564.9	565.2
167.5°	567.7	568.8	571.8	570.8	573.9	573.7	573.4	573.1	572.9	572.9	572.9
170°	574.9	575.9	579.0	578.0	580.0	579.8	579.5	579.2	579.0	578.8	578.5
172.5°	578.0	579.0	582.1	580.0	582.1	581.9	581.5	581.2	581.0	581.2	581.5
175°	580.0	582.1	583.1	582.1	585.1	585.1	585.1	585.1	585.1	585.3	585.6
177.5°	585.1	586.2	588.2	587.2	591.3	591.1	590.8	590.4	590.2	590.2	590.2
180°	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2



REPORT NUMBER: P228260

CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

CANDELA DISTRIBUTION (continued):

	52.5°	55°	57.5°	59°	60°	62.5°	65°	67.5°	70°	72.5°	75°
0°	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1
2.5°	620.4	617.1	616.4	614.8	615.6	613.2	612.3	609.2	609.2	607.5	605.9
5°	624.4	621.2	624.4	618.8	619.6	617.1	613.2	613.2	610.0	607.5	602.7
7.5°	613.2	613.2	614.0	610.7	611.5	610.7	605.9	605.1	600.3	600.3	594.6
10°	592.2	592.2	595.5	593.0	593.8	593.0	590.7	589.8	588.2	588.2	579.3
12.5°	568.0	572.9	577.8	575.3	575.3	576.9	576.9	577.8	576.9	576.1	568.9
15°	547.9	555.2	560.0	559.1	560.0	564.1	565.6	566.4	568.9	568.0	561.6
17.5°	529.4	537.5	541.4	544.7	547.1	550.3	555.2	557.6	560.8	560.0	553.5
20°	512.5	519.7	526.9	531.0	531.8	538.3	543.9	551.2	552.7	554.3	546.3
22.5°	494.7	501.1	515.7	513.2	518.9	531.0	534.2	544.7	544.7	550.3	539.0
25°	479.5	480.2	502.8	498.8	503.6	525.4	527.7	546.3	541.4	549.5	536.6
27.5°	464.1	463.3	490.7	485.9	491.5	521.3	522.9	548.7	543.9	553.5	536.6
30°	452.9	450.4	481.8	472.2	480.2	517.3	518.1	551.2	547.1	560.0	542.3
32.5°	450.4	446.4	473.7	466.6	474.5	513.2	518.1	560.0	555.2	571.3	548.7
35°	460.8	454.4	477.8	471.4	477.8	514.9	522.1	573.7	568.0	586.6	564.1
37.5°	480.2	475.4	494.7	488.3	493.1	526.1	532.5	591.4	590.7	613.2	587.4
40°	514.0	509.2	524.6	515.7	519.7	550.3	553.5	616.4	618.8	646.2	620.4
42.5°	560.0	551.9	564.1	553.5	559.1	586.6	583.4	647.0	654.3	692.1	662.4
45°	618.8	608.3	615.6	604.3	608.3	631.7	622.9	688.1	695.4	742.0	715.5
47.5°	683.2	670.3	679.2	664.7	667.2	692.1	676.0	737.2	748.5	807.3	781.5
50°	760.7	743.7	747.0	733.3	734.8	759.8	742.0	797.7	811.4	876.7	854.1
52.5°	859.7	835.5	835.5	817.0	817.8	842.8	821.0	869.4	884.8	950.7	935.5
55°	990.2	970.9	966.9	947.6	941.1	945.9	915.3	949.2	966.1	1028.2	1016.0
57.5°	1094.1	1091.8	1103.9	1076.5	1070.0	1071.6	1033.0	1035.3	1054.8	1103.0	1107.0
60°	1220.7	1224.7	1226.3	1203.8	1201.4	1178.8	1139.4	1132.9	1157.1	1190.1	1203.0
62.5°	1422.1	1418.1	1398.0	1381.1	1365.7	1305.3	1283.5	1248.1	1282.0	1300.5	1327.1
65°	1854.8	1812.9	1684.0	1695.2	1655.0	1523.7	1505.2	1433.5	1486.6	1487.4	1537.4
67.5°	2283.4	2365.7	2286.7	2288.3	2197.3	1959.6	1902.4	1759.8	1789.6	1754.9	1780.7
70°	2356.8	2472.0	2687.9	2649.2	2644.4	2461.5	2269.0	2031.3	1941.9	1867.7	1808.1
72.5°	2028.0	2143.3	2459.9	2372.1	2405.2	2460.7	2260.1	2082.0	1882.2	1787.9	1659.0
75°	1427.0	1592.9	1914.5	1868.5	1892.7	1984.5	1812.2	1791.2	1559.9	1497.1	1298.8
77.5°	764.7	970.1	1330.2	1273.9	1284.3	1336.7	1157.1	1120.0	896.8	834.7	610.0
80°	344.0	477.0	747.0	684.0	665.5	635.8	468.1	369.0	225.6	149.9	103.9
82.5°	228.0	236.9	331.1	286.8	268.3	221.6	143.4	84.6	66.9	56.4	54.0
85°	153.1	140.2	139.4	123.3	114.4	90.2	66.9	41.9	34.7	29.1	26.6
87.5°	8.9	5.6	8.1	8.9	6.4	5.6	4.0	0.0	0.8	0.0	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
97.5°	12.3	13.3	11.8	10.8	10.2	8.7	7.2	6.6	6.1	5.6	5.1
100°	32.2	32.7	32.2	31.9	31.7	31.2	30.7	29.9	29.2	28.4	27.6
102.5°	52.0	52.2	52.0	51.8	51.7	51.4	51.1	50.6	50.1	49.6	49.1
105°	72.4	72.6	72.6	72.6	72.6	72.6	72.6	72.1	71.6	71.1	70.6
107.5°	94.6	95.1	94.9	94.7	94.6	94.3	94.1	93.9	93.6	93.3	93.1
110°	116.1	116.6	116.6	116.6	116.6	116.6	116.6	116.4	116.1	115.8	115.6



REPORT NUMBER: P228260

CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

CANDELA DISTRIBUTION (continued):

	52.5°	55°	57.5°	59°	60°	62.5°	65°	67.5°	70°	72.5°	75°
112.5°	138.6	139.1	139.1	139.1	139.1	139.1	139.1	138.9	138.6	138.3	138.1
115°	161.1	161.6	161.6	161.6	161.6	161.6	161.6	161.6	161.6	161.6	161.6
117.5°	183.9	184.1	184.3	184.5	184.6	184.9	185.2	184.9	184.6	184.3	184.1
120°	208.2	208.7	208.7	208.7	208.7	208.7	208.7	208.7	208.7	208.7	208.7
122.5°	233.0	233.2	233.2	233.2	233.2	233.2	233.2	233.4	233.7	234.1	234.3
125°	258.6	258.8	259.0	259.2	259.3	259.6	259.8	259.8	259.8	259.8	259.8
127.5°	283.9	284.4	284.2	284.0	283.9	283.6	283.4	283.6	283.9	284.2	284.4
130°	307.4	307.9	307.9	307.9	307.9	307.9	307.9	308.1	308.4	308.7	308.9
132.5°	331.6	332.5	332.5	332.5	332.5	332.5	332.5	332.7	333.0	333.3	333.5
135°	355.2	356.0	356.0	356.0	356.0	356.0	356.0	356.2	356.5	356.8	357.0
137.5°	377.0	377.5	377.5	377.5	377.5	377.5	377.5	377.7	378.0	378.3	378.5
140°	398.7	399.0	399.0	399.0	399.0	399.0	399.0	399.5	400.0	400.5	401.0
142.5°	420.9	421.5	421.5	421.5	421.5	421.5	421.5	421.7	422.0	422.3	422.5
145°	443.4	444.0	443.8	443.6	443.4	443.1	442.9	443.1	443.4	443.8	444.0
147.5°	464.2	464.4	463.9	463.6	463.4	462.9	462.4	462.6	462.9	463.2	463.4
150°	481.6	481.8	481.3	481.0	480.8	480.3	479.8	479.8	479.8	479.8	479.8
152.5°	498.0	498.2	498.0	497.8	497.7	497.4	497.2	497.2	497.2	497.2	497.2
155°	515.4	515.6	515.4	515.2	515.1	514.7	514.5	514.7	515.1	515.4	515.6
157.5°	530.9	530.9	530.4	530.1	529.9	529.4	528.9	529.1	529.4	529.7	529.9
160°	544.2	544.2	543.7	543.4	543.2	542.7	542.2	542.2	542.2	542.2	542.2
162.5°	554.2	554.4	553.9	553.6	553.4	552.9	552.4	551.9	551.4	550.9	550.3
165°	565.5	565.7	564.9	564.5	564.2	563.4	562.6	562.1	561.6	561.1	560.6
167.5°	572.9	572.9	572.3	572.0	571.8	571.3	570.8	571.0	571.3	571.6	571.8
170°	578.2	578.0	577.8	577.6	577.5	577.1	576.9	577.5	578.0	578.5	579.0
172.5°	581.9	582.1	581.5	581.2	581.0	580.5	580.0	580.2	580.5	580.8	581.0
175°	585.9	586.2	585.3	584.9	584.6	583.9	583.1	582.6	582.1	581.5	581.0
177.5°	590.2	590.2	589.4	589.0	588.7	588.0	587.2	587.2	587.2	587.2	587.2
180°	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2



REPORT NUMBER: P228260

CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

CANDELA DISTRIBUTION (continued):

	77.5°	80°	85°	90°	95°	100°	102.5°	105°	107.5°	110°	112.5°
0°	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1
2.5°	601.9	601.9	601.1	595.5	592.2	590.7	584.9	584.2	581.8	580.9	580.9
5°	601.1	597.8	593.8	585.7	577.8	570.5	568.0	562.4	558.4	553.5	553.5
7.5°	589.8	586.6	577.8	565.6	555.2	544.7	539.0	531.0	524.6	518.1	516.5
10°	576.9	572.0	560.0	543.9	530.2	511.7	504.4	493.9	486.6	477.0	467.3
12.5°	563.2	560.0	545.4	526.9	506.1	482.6	471.4	456.8	447.2	435.9	421.4
15°	557.6	551.2	532.5	509.2	483.4	455.2	439.2	423.8	409.3	396.4	377.1
17.5°	550.3	542.3	521.3	493.9	461.7	427.8	406.9	389.9	370.6	356.9	335.2
20°	542.3	530.2	507.6	474.5	438.3	398.0	371.4	354.6	328.8	315.1	289.3
22.5°	535.8	520.5	493.1	456.0	412.6	367.4	336.0	316.7	287.7	271.5	239.3
25°	534.2	515.7	482.6	440.8	390.8	337.6	299.7	280.4	244.2	225.6	187.7
27.5°	535.0	513.2	476.2	427.8	371.4	311.0	265.9	243.4	197.4	178.1	134.5
30°	535.8	514.0	469.7	416.5	353.7	283.7	230.5	203.9	149.0	132.2	93.5
32.5°	543.9	517.3	468.1	407.7	337.6	256.2	190.2	166.0	105.6	95.9	69.3
35°	553.5	527.7	471.4	406.1	325.5	228.8	149.0	124.1	75.7	73.3	56.4
37.5°	573.7	543.9	484.3	410.1	318.2	200.6	111.2	95.0	59.6	61.3	49.1
40°	604.3	571.3	505.2	422.2	317.4	172.5	82.1	74.2	51.6	53.2	45.1
42.5°	645.4	609.2	537.5	448.0	321.5	145.9	66.1	63.6	47.6	49.1	43.5
45°	699.4	662.4	582.6	481.0	332.8	124.1	58.0	58.0	45.9	47.6	42.7
47.5°	767.8	726.8	638.1	525.4	350.5	112.0	54.8	55.5	45.1	47.6	42.7
50°	845.3	800.0	709.0	582.6	377.9	108.7	55.5	55.5	45.9	47.6	42.7
52.5°	925.8	883.9	785.6	647.8	415.7	116.0	57.2	56.4	45.9	47.6	41.9
55°	1008.0	970.1	870.2	724.4	468.1	141.8	61.3	58.8	45.9	47.6	42.7
57.5°	1090.2	1063.6	958.8	806.6	533.4	188.5	77.3	68.5	50.7	51.6	43.5
60°	1182.8	1163.5	1058.8	914.5	626.0	261.1	113.6	86.2	60.5	57.2	46.7
62.5°	1302.9	1298.0	1215.1	1070.0	775.1	365.8	161.1	104.8	65.3	59.6	49.9
65°	1514.8	1527.7	1448.7	1252.1	874.2	368.3	157.1	91.9	61.3	56.4	49.1
67.5°	1727.5	1689.6	1486.6	1224.7	788.8	244.9	99.9	71.7	54.0	52.4	45.9
70°	1719.5	1616.4	1348.0	1070.8	622.9	133.0	72.5	59.6	48.4	48.4	43.5
72.5°	1542.2	1389.1	1102.2	847.6	415.7	84.6	61.3	52.4	44.3	43.5	40.3
75°	1161.0	980.6	708.3	488.3	185.4	54.8	46.7	42.7	38.7	38.7	35.5
77.5°	546.3	307.8	170.8	113.6	62.1	37.0	32.2	32.2	31.4	32.2	29.1
80°	74.2	66.9	57.2	49.9	37.8	25.8	23.3	24.1	23.3	24.1	21.8
82.5°	45.1	40.3	33.0	31.4	23.3	17.7	16.9	17.7	16.2	16.9	12.9
85°	21.8	19.3	15.3	14.5	12.1	10.4	8.9	10.4	8.1	8.9	5.6
87.5°	0.0	1.6	0.8	1.6	1.6	1.6	0.0	1.6	0.0	1.6	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
97.5°	4.9	4.6	4.1	4.1	4.1	4.6	4.9	5.1	5.6	6.1	6.6
100°	27.4	27.1	26.6	25.6	26.6	27.1	27.4	27.6	28.4	29.2	29.9
102.5°	49.3	49.6	50.1	49.1	50.1	49.6	49.3	49.1	49.6	50.1	50.6
105°	71.1	71.6	72.6	70.6	72.6	71.6	71.1	70.6	71.1	71.6	72.1
107.5°	93.3	93.6	94.1	93.1	94.1	93.6	93.3	93.1	93.3	93.6	93.9
110°	115.8	116.1	116.6	115.6	116.6	116.1	115.8	115.6	115.8	116.1	116.4



REPORT NUMBER: P228260
 CATALOG NUMBER: ISC-AF-350-LED-E1-SL3-ULG

REPORT N
 CATALOG

CANDELA DISTRIBUTION (continued):

CANDELA

	77.5°	80°	85°	90°	95°	100°	102.5°	105°	107.5°	110°	112.5°	
112.5°	138.6	139.1	140.1	138.1	140.1	139.1	138.6	138.1	138.3	138.6	138.9	0°
115°	162.1	162.6	163.7	162.6	163.7	162.6	162.1	161.6	161.6	161.6	161.6	2.5°
117.5°	184.6	185.2	186.2	184.1	186.2	185.2	184.6	184.1	184.3	184.6	184.9	5°
120°	209.2	209.7	210.7	208.7	210.7	209.7	209.2	208.7	208.7	208.7	208.7	7.5°
122.5°	235.3	236.3	238.3	237.3	238.3	236.3	235.3	234.3	234.1	233.7	233.4	10°
125°	260.6	261.4	262.9	261.9	262.9	261.4	260.6	259.8	259.8	259.8	259.8	12.5°
127.5°	285.2	285.9	287.4	284.4	287.4	285.9	285.2	284.4	284.2	283.9	283.6	15°
130°	309.7	310.5	312.0	310.0	312.0	310.5	309.7	308.9	308.7	308.4	308.1	17.5°
132.5°	334.3	335.0	336.6	334.5	336.6	335.0	334.3	333.5	333.3	333.0	332.7	20°
135°	357.5	358.0	359.1	358.0	359.1	358.0	357.5	357.0	356.8	356.5	356.2	22.5°
137.5°	379.5	380.5	382.6	380.5	382.6	380.5	379.5	378.5	378.3	378.0	377.7	25°
140°	402.0	403.0	405.1	403.0	405.1	403.0	402.0	401.0	400.5	400.0	399.5	27.5°
142.5°	423.3	424.0	425.5	424.5	425.5	424.0	423.3	422.5	422.3	422.0	421.7	30°
145°	444.8	445.5	447.0	445.0	447.0	445.5	444.8	444.0	443.8	443.4	443.1	32.5°
147.5°	464.2	464.9	466.5	463.4	466.5	464.9	464.2	463.4	463.2	462.9	462.6	35°
150°	480.8	481.8	483.9	480.8	483.9	481.8	480.8	479.8	479.8	479.8	479.8	37.5°
152.5°	498.0	498.7	500.2	497.2	500.2	498.7	498.0	497.2	497.2	497.2	497.2	40°
155°	516.4	517.1	518.6	516.6	518.6	517.1	516.4	515.6	515.4	515.1	514.7	42.5°
157.5°	531.1	532.4	535.0	531.9	535.0	532.4	531.1	529.9	529.7	529.4	529.1	45°
160°	543.0	543.7	545.2	543.2	545.2	543.7	543.0	542.2	542.2	542.2	542.2	47.5°
162.5°	550.9	551.4	552.4	549.3	552.4	551.4	550.9	550.3	550.9	551.4	551.9	50°
165°	561.1	561.6	562.6	560.6	562.6	561.6	561.1	560.6	561.1	561.6	562.1	52.5°
167.5°	572.9	573.9	575.9	573.9	575.9	573.9	572.9	571.8	571.6	571.3	571.0	55°
170°	580.2	581.5	584.1	582.1	584.1	581.5	580.2	579.0	578.5	578.0	577.5	57.5°
172.5°	581.9	582.6	584.1	581.0	584.1	582.6	581.9	581.0	580.8	580.5	580.2	60°
175°	581.9	582.6	584.1	581.0	584.1	582.6	581.9	581.0	581.5	582.1	582.6	62.5°
177.5°	588.0	588.7	590.2	587.2	590.2	588.7	588.0	587.2	587.2	587.2	587.2	65°
180°	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	67.5°
												70°
												72.5°
												75°
												77.5°
												80°
												82.5°
												85°
												87.5°
												90°
												92.5°
												95°
												97.5°
												100°
												102.5°
												105°
												107.5°
												110°

NUMBER: P228260
 NUMBER: ISC-AF-350-LED-E1-SL3-ULG

REPORT NUMBER: P
 CATALOG NUMBER:

DISTRIBUTION (continued):

CANDELA DISTRIBUTION

115°	117.5°	120°	122.5°	125°	127.5°	130°	135°	145°	155°	165°	115°	115°
601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	601.1	112.5°	139.1
576.9	574.5	573.7	570.5	569.7	566.4	565.6	562.4	556.8	554.3	550.3	115°	161.6
546.3	542.3	539.0	537.5	531.0	527.7	522.9	516.5	504.4	498.8	489.1	117.5°	185.2
503.6	502.8	493.1	489.9	481.8	476.2	468.9	458.5	440.8	430.3	414.9	120°	208.7
456.8	453.7	442.3	435.9	425.4	417.4	407.7	392.4	365.0	343.2	319.9	122.5°	233.2
413.4	403.7	390.8	381.2	368.3	356.9	345.7	322.3	278.8	243.4	211.1	125°	259.8
368.3	353.7	340.0	323.9	310.3	292.5	279.6	249.0	191.8	148.2	128.1	127.5°	283.4
322.3	302.2	286.8	265.0	249.8	225.6	212.0	174.8	125.7	106.4	99.9	130°	307.9
273.9	247.3	230.5	203.9	188.5	157.9	147.4	120.8	96.7	89.4	87.9	132.5°	332.5
222.4	190.2	171.7	142.6	132.2	113.6	105.6	92.7	81.4	78.2	79.8	135°	356.0
168.4	133.8	121.6	100.8	96.7	87.1	83.8	77.3	71.7	71.7	74.2	137.5°	377.5
120.1	93.5	90.2	77.3	76.5	71.7	69.3	66.1	64.4	66.1	69.3	140°	399.0
87.9	70.9	70.9	63.6	63.6	60.5	59.6	58.0	58.0	61.3	64.4	142.5°	421.5
69.3	58.0	59.6	54.0	54.8	52.4	53.2	52.4	53.2	55.5	58.0	145°	442.9
58.0	49.9	52.4	47.6	49.1	46.7	48.4	48.4	49.9	50.7	51.6	147.5°	462.4
51.6	45.9	47.6	44.3	45.9	43.5	45.9	45.9	46.7	46.7	46.7	150°	479.8
47.6	42.7	45.1	41.9	44.3	41.9	44.3	44.3	43.5	42.7	43.5	152.5°	497.2
45.1	41.9	44.3	41.1	43.5	41.1	42.7	41.9	40.3	40.3	40.3	155°	514.5
44.3	41.1	42.7	40.3	41.9	39.5	41.1	40.3	37.8	37.0	38.7	157.5°	528.9
44.3	40.3	42.7	39.5	41.1	38.7	40.3	37.8	35.5	35.5	37.8	160°	542.2
44.3	40.3	42.7	39.5	41.1	37.8	38.7	36.2	33.0	33.9	37.0	162.5°	552.4
45.1	41.9	43.5	40.3	41.1	36.2	37.8	34.7	32.2	33.0	35.5	165°	562.6
45.9	41.9	43.5	38.7	39.5	36.2	36.2	34.7	32.2	32.2	34.7	167.5°	570.8
45.9	41.1	41.9	37.8	38.7	34.7	35.5	33.9	31.4	30.6	32.2	170°	576.9
47.6	42.7	42.7	37.0	37.8	33.9	34.7	33.0	30.6	29.1	29.8	172.5°	580.0
49.1	43.5	44.3	38.7	38.7	34.7	35.5	32.2	29.1	27.4	28.2	175°	583.1
49.1	43.5	44.3	39.5	39.5	35.5	35.5	32.2	27.4	25.8	25.8	177.5°	587.2
46.7	42.7	43.5	39.5	39.5	35.5	35.5	31.4	26.6	24.1	23.3	180°	589.2
45.1	41.1	41.9	37.0	37.8	33.9	33.9	29.8	25.0	22.6	21.0		
41.1	37.8	37.8	34.7	33.9	29.8	29.8	27.4	23.3	20.2	18.5		
35.5	32.2	31.4	28.2	28.2	25.8	25.0	22.6	19.3	16.9	16.2		
29.1	25.0	25.0	21.0	21.0	18.5	19.3	16.9	14.5	13.7	12.9		
21.0	16.9	16.9	13.7	13.7	11.3	12.1	11.3	10.4	10.4	9.7		
12.9	8.9	9.7	7.3	8.9	6.4	7.3	6.4	6.4	5.6	5.6		
6.4	3.3	4.8	2.5	4.0	0.8	2.5	1.6	1.6	1.6	1.6		
0.8	0.0	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0		
7.2	8.7	10.2	11.8	13.3	12.3	11.3	9.2	4.1	3.1	2.0		
30.7	31.2	31.7	32.2	32.7	32.2	31.7	30.7	22.5	14.3	10.2		
51.1	51.4	51.7	52.0	52.2	52.0	51.7	51.1	46.0	38.9	32.7		
72.6	72.6	72.6	72.6	72.6	72.4	72.1	71.6	67.5	62.4	57.3		
94.1	94.3	94.6	94.9	95.1	94.6	94.1	93.1	90.0	85.9	81.8		
116.6	116.6	116.6	116.6	116.6	116.1	115.6	114.6	112.5	108.4	105.4		

'228260
 ISC-AF-350-LED-E1-SL3-ULG

REPORT NUMBER: P228260
 CATALOG NUMBER: ISC-AF-35

TION (continued):

CANDELA DISTRIBUTION (con

117.5°	120°	122.5°	125°	127.5°	130°	135°	145°	155°	165°		175°	180°
139.1	139.1	139.1	139.1	138.6	138.1	137.1	135.0	132.0	128.9	0°	601.1	601.1
161.6	161.6	161.6	161.6	161.1	160.6	159.6	157.5	154.5	152.4	2.5°	546.3	548.7
184.9	184.6	184.3	184.1	183.9	183.6	183.1	181.1	178.0	175.9	5°	485.9	486.6
208.7	208.7	208.7	208.7	208.2	207.7	206.6	205.6	202.5	200.5	7.5°	412.6	410.9
233.2	233.2	233.2	233.2	233.0	232.7	232.2	231.2	228.1	226.1	10°	315.1	311.0
259.6	259.3	259.0	258.8	258.6	258.3	257.8	256.8	253.7	252.7	12.5°	203.1	197.4
283.6	283.9	284.2	284.4	283.9	283.4	282.3	280.3	278.2	276.2	15°	122.4	120.8
307.9	307.9	307.9	307.9	307.4	306.9	305.9	304.8	300.7	299.7	17.5°	98.3	98.3
332.5	332.5	332.5	332.5	331.6	330.9	329.4	328.4	325.3	324.3	20°	87.9	87.9
356.0	356.0	356.0	356.0	355.2	354.5	352.9	352.9	348.8	346.8	22.5°	81.4	81.4
377.5	377.5	377.5	377.5	377.0	376.4	375.4	375.4	372.4	371.3	25°	76.5	77.3
399.0	399.0	399.0	399.0	398.7	398.4	397.9	396.9	394.9	393.8	27.5°	72.5	72.5
421.5	421.5	421.5	421.5	420.9	420.4	419.4	419.4	416.3	417.4	30°	67.7	67.7
443.1	443.4	443.8	444.0	443.4	442.9	441.9	440.9	437.8	437.8	32.5°	59.6	59.6
462.9	463.4	463.9	464.4	464.2	463.9	463.4	462.4	458.3	457.3	35°	53.2	52.4
480.3	480.8	481.3	481.8	481.6	481.3	480.8	479.8	475.7	474.6	37.5°	47.6	48.4
497.4	497.7	498.0	498.2	498.0	497.7	497.2	496.1	493.1	494.1	40°	43.5	44.3
514.7	515.1	515.4	515.6	515.4	515.1	514.5	514.5	512.5	513.5	42.5°	41.9	41.9
529.4	529.9	530.4	530.9	530.9	530.9	530.9	530.9	527.8	528.9	45°	40.3	40.3
542.7	543.2	543.7	544.2	544.2	544.2	544.2	544.2	541.1	541.1	47.5°	40.3	40.3
552.9	553.4	553.9	554.4	554.2	553.9	553.4	553.4	550.3	551.4	50°	39.5	40.3
563.4	564.2	564.9	565.7	565.5	565.2	564.7	564.7	560.6	561.6	52.5°	38.7	38.7
571.3	571.8	572.3	572.9	572.9	572.9	572.9	573.9	570.8	571.8	55°	36.2	37.0
577.1	577.5	577.8	578.0	578.2	578.5	579.0	580.0	578.0	579.0	57.5°	33.9	34.7
580.5	581.0	581.5	582.1	581.9	581.5	581.0	582.1	580.0	582.1	60°	31.4	31.4
583.9	584.6	585.3	586.2	585.9	585.6	585.1	585.1	582.1	583.1	62.5°	28.2	28.2
588.0	588.7	589.4	590.2	590.2	590.2	590.2	591.3	587.2	588.2	65°	25.8	25.8
589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	67.5°	22.6	22.6
										70°	20.2	20.2
										72.5°	17.7	17.7
										75°	15.3	15.3
										77.5°	12.9	12.1
										80°	9.7	9.7
										82.5°	5.6	5.6
										85°	1.6	1.6
										87.5°	0.0	0.0
										90°	0.0	0.0
										92.5°	0.0	0.0
										95°	1.0	1.0
										97.5°	2.0	2.0
										100°	8.2	8.2
										102.5°	28.6	28.6
										105°	55.2	55.2
										107.5°	78.8	79.8
										110°	104.3	103.3



REPORT NUMBER: P228260

CATALOG NUMBER: ISC-AF-350-LED-E1-S

CANDELA DISTRIBUTION (continued):

	175°	180°
112.5°	126.8	126.8
115°	150.4	149.4
117.5°	173.9	172.9
120°	199.5	197.4
122.5°	225.0	224.0
125°	251.6	249.6
127.5°	275.2	273.1
130°	298.7	296.7
132.5°	321.2	320.2
135°	344.7	343.7
137.5°	368.3	367.2
140°	391.8	390.8
142.5°	415.3	413.3
145°	435.8	434.8
147.5°	454.2	454.2
150°	472.6	471.6
152.5°	491.0	490.0
155°	511.5	510.5
157.5°	526.8	524.8
160°	539.1	537.0
162.5°	548.3	547.3
165°	559.6	558.5
167.5°	568.8	567.7
170°	575.9	574.9
172.5°	579.0	578.0
175°	582.1	580.0
177.5°	586.2	585.1
180°	589.2	589.2

(END OF REPORT)

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

